

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585025

Luminaire Tested: **HCC8W55D010SL-HM82555935-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
 Report Number: P585025
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 10/21/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO COMMERCIAL
 Catalog Number: HCC8W55D010SL-HM82555935-81RWWH
 Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
 Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
 CYLINDER
 Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 4851.0 lumens
 Efficiency: N/A
 Efficacy: 93.3 lumens/watt
 Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
 Luminous Opening: Circular (Dia: 0.67' x H: 0')
 CIE Type: Direct

Input Watts (W): 52
 Input Voltage (V): NR
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



TEST NUMBER: P585025
CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P585025

CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79795	79795	79795
5°	81292	79447	77602
10°	82564	78061	74767
15°	83392	76117	71526
20°	83072	73178	68230
25°	80886	68953	64421
30°	77032	63925	60677
35°	69559	58337	56361
40°	61114	52362	52221
45°	52750	46025	48014
50°	45920	40369	43060
55°	40714	35063	37515
60°	36325	29628	31139
65°	32747	24049	24560
70°	29076	18014	14543
75°	25068	10449	6267
80°	19285	3747	1865
85°	12383	1238	1238



TEST NUMBER: P585025
 CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.9	5.0
10°-20°	676.2	13.9
20°-30°	956.4	19.7
30°-40°	1007.8	20.8
40°-50°	856.5	17.7
50°-60°	616.8	12.7
60°-70°	355.8	7.3
70°-80°	121.7	2.5
80°-90°	16.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1875.6	38.7
0°-40°	2883.4	59.4
0°-60°	4356.7	89.8
0°-90°	4851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4851.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2588	2588	2588	2588	2588	
5°	2626	2609	2567	2521	2507	251
15°	2612	2532	2384	2279	2240	736
25°	2377	2255	2027	1922	1893	1090
35°	1848	1739	1550	1494	1497	1151
45°	1210	1154	1055	1062	1101	940
55°	757	698	652	677	698	682
65°	449	386	330	322	337	446
75°	210	158	88	56	53	222
85°	35	21	4	4	4	47
90°	0	0	0	0	0	



TEST NUMBER: P585025

CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7
2.5°	2612.2	2615.7	2612.2	2612.2	2608.6	2605.1	2601.7	2598.2	2591.2	2584.1	2584.1
5°	2626.2	2633.2	2626.2	2626.2	2615.7	2608.6	2601.7	2591.2	2577.1	2566.6	2566.6
7.5°	2636.8	2636.8	2636.8	2626.2	2619.2	2608.6	2591.2	2573.6	2556.1	2538.6	2531.5
10°	2636.8	2636.8	2633.2	2619.2	2612.2	2591.2	2573.6	2549.1	2524.5	2500.0	2493.0
12.5°	2626.2	2629.7	2622.7	2608.6	2591.2	2566.6	2542.1	2510.5	2482.4	2454.4	2440.3
15°	2612.2	2608.6	2601.7	2584.1	2563.0	2531.5	2507.0	2472.0	2433.3	2398.3	2384.3
17.5°	2577.1	2577.1	2566.6	2549.1	2521.0	2485.9	2447.4	2408.8	2366.7	2328.2	2310.6
20°	2531.5	2531.5	2517.5	2496.5	2468.5	2422.9	2380.8	2335.2	2286.1	2247.5	2230.0
22.5°	2465.0	2468.5	2450.9	2426.4	2394.7	2342.2	2300.2	2244.0	2194.9	2149.3	2135.4
25°	2377.3	2384.3	2366.7	2342.2	2300.2	2254.6	2202.0	2149.3	2093.3	2047.7	2026.6
27.5°	2275.6	2279.1	2261.6	2237.0	2194.9	2145.8	2093.3	2037.2	1984.5	1935.4	1914.5
30°	2163.4	2149.3	2142.3	2110.8	2065.2	2023.1	1963.6	1918.0	1861.8	1819.8	1795.3
32.5°	2005.6	2012.6	1991.6	1967.1	1931.9	1882.8	1833.8	1781.2	1728.6	1697.1	1679.5
35°	1847.8	1854.8	1844.3	1819.8	1781.2	1739.1	1690.0	1651.5	1605.9	1567.3	1549.7
37.5°	1683.0	1683.0	1676.0	1662.0	1633.9	1595.3	1546.2	1507.7	1469.1	1437.6	1427.0
40°	1518.2	1511.2	1507.7	1497.2	1472.6	1437.6	1406.0	1374.5	1335.8	1314.9	1300.8
42.5°	1356.9	1356.9	1349.9	1339.4	1314.9	1297.3	1265.8	1230.7	1202.7	1181.6	1181.6
45°	1209.6	1213.1	1202.7	1195.7	1181.6	1153.6	1125.5	1101.0	1076.5	1062.4	1055.4
47.5°	1079.9	1079.9	1069.4	1062.4	1048.4	1023.9	999.2	978.3	960.7	950.3	946.7
50°	957.2	957.2	957.2	939.7	922.1	904.7	887.1	862.6	852.0	845.0	841.5
52.5°	852.0	848.5	848.5	834.5	817.0	795.9	778.4	757.3	746.8	739.9	743.3
55°	757.3	757.3	753.8	736.4	718.8	697.8	680.2	662.6	655.7	648.7	652.2
56°	718.8	718.8	715.3	701.2	680.2	662.6	641.7	624.1	613.5	617.1	617.1
57°	690.8	683.7	683.7	666.2	648.7	624.1	606.6	589.0	582.0	578.5	578.5
58°	655.7	652.2	648.7	631.1	613.5	592.6	575.0	557.5	547.0	547.0	543.5
59°	620.6	620.6	613.5	599.6	582.0	561.0	543.5	526.0	515.4	511.9	511.9
60°	589.0	592.6	582.0	568.1	554.0	529.4	508.4	494.3	483.9	480.4	480.4
61°	561.0	561.0	554.0	536.4	519.0	501.4	480.4	462.8	455.8	448.8	448.8
62°	536.4	529.4	526.0	508.4	490.8	469.9	452.3	434.8	424.3	417.2	420.7
63°	504.9	501.4	494.3	480.4	462.8	441.8	420.7	406.7	396.3	385.7	389.2
64°	480.4	476.9	466.3	452.3	434.8	413.7	392.7	378.7	371.6	361.1	357.7
65°	448.8	445.2	441.8	424.3	406.7	385.7	368.1	354.2	343.6	336.6	329.6
66°	420.7	424.3	417.2	403.2	382.2	364.6	340.1	326.1	319.0	308.6	301.6
67°	396.3	396.3	389.2	375.2	354.2	336.6	319.0	301.6	291.0	280.5	276.9
67.5°	382.2	382.2	375.2	357.7	343.6	322.5	305.1	291.0	276.9	270.0	263.0
68°	368.1	368.1	364.6	350.7	333.1	312.1	294.5	276.9	263.0	252.4	248.9
69°	343.6	347.1	340.1	326.1	308.6	287.5	270.0	256.0	241.9	231.5	224.4
70°	322.5	319.0	312.1	298.0	280.5	266.5	248.9	231.5	217.4	203.3	199.8
71°	294.5	294.5	287.5	276.9	259.5	241.9	224.4	210.4	196.3	178.8	175.3
72°	273.5	273.5	266.5	252.4	238.4	220.9	203.3	185.9	175.3	157.8	150.7
72.5°	259.5	263.0	256.0	241.9	228.0	206.9	192.8	178.8	161.3	147.3	140.3
73°	252.4	248.9	245.4	231.5	213.9	199.8	182.4	168.3	150.7	136.8	129.7



TEST NUMBER: P585025
 CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	157.8	157.8	154.2	140.3	126.2	112.2	98.2	84.1	70.1	56.1	49.1
80°	108.6	112.2	105.2	98.2	87.7	73.6	59.7	49.1	35.0	28.0	21.1
82.5°	70.1	70.1	66.6	59.7	52.6	42.1	35.0	24.5	17.6	14.1	10.5
85°	35.0	38.6	35.0	31.5	24.5	21.1	17.6	10.5	7.0	3.5	3.5
87.5°	14.1	14.1	14.1	10.5	10.5	7.0	3.5	3.5	3.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585025

CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7	2587.7
2.5°	2577.1	2577.1	2570.1	2566.6	2563.0	2559.5	2556.1	2552.6	2552.6	2556.1
5°	2556.1	2549.1	2535.0	2531.5	2521.0	2517.5	2510.5	2507.0	2510.5	2507.0
7.5°	2524.5	2510.5	2493.0	2485.9	2472.0	2465.0	2454.4	2454.4	2447.4	2450.9
10°	2482.4	2461.4	2440.3	2426.4	2415.8	2405.3	2398.3	2391.2	2387.8	2387.8
12.5°	2429.9	2405.3	2384.3	2363.2	2345.8	2338.7	2324.7	2324.7	2317.6	2314.1
15°	2370.3	2338.7	2314.1	2293.1	2279.1	2265.0	2254.6	2247.5	2240.5	2240.5
17.5°	2293.1	2265.0	2240.5	2216.0	2194.9	2184.4	2173.9	2163.4	2163.4	2156.4
20°	2209.0	2177.5	2156.4	2131.9	2114.3	2096.7	2082.8	2082.8	2075.7	2079.2
22.5°	2114.3	2075.7	2054.6	2037.2	2019.6	2005.6	1991.6	1991.6	1988.1	1984.5
25°	2009.2	1977.5	1953.0	1931.9	1921.5	1907.4	1903.9	1896.9	1893.4	1893.4
27.5°	1896.9	1872.4	1840.7	1830.3	1816.2	1809.2	1809.2	1805.7	1798.7	1802.2
30°	1777.7	1749.7	1732.1	1725.1	1711.1	1711.1	1707.6	1700.6	1700.6	1704.1
32.5°	1662.0	1633.9	1619.9	1616.4	1602.4	1602.4	1598.8	1602.4	1602.4	1605.9
35°	1535.8	1511.2	1507.7	1497.2	1493.7	1493.7	1493.7	1500.7	1507.7	1497.2
37.5°	1416.6	1399.0	1388.5	1385.0	1388.5	1388.5	1392.0	1402.5	1399.0	1395.5
40°	1293.8	1279.8	1272.8	1272.8	1279.8	1286.9	1286.9	1297.3	1300.8	1297.3
42.5°	1171.1	1160.6	1160.6	1164.0	1171.1	1174.6	1185.1	1195.7	1199.2	1202.7
45°	1055.4	1055.4	1055.4	1058.9	1062.4	1069.4	1083.4	1093.9	1097.5	1101.0
47.5°	943.2	939.7	950.3	953.7	964.2	967.7	978.3	992.3	995.7	999.2
50°	838.0	845.0	848.5	859.1	866.1	866.1	880.1	887.1	897.6	897.6
52.5°	739.9	750.3	753.8	764.4	767.9	771.4	778.4	788.9	795.9	795.9
55°	652.2	655.7	662.6	666.2	676.7	680.2	687.3	690.8	701.2	697.8
56°	613.5	620.6	624.1	631.1	638.2	641.7	648.7	652.2	659.1	662.6
57°	578.5	582.0	592.6	596.1	603.1	603.1	606.6	617.1	617.1	620.6
58°	543.5	550.5	554.0	557.5	564.6	568.1	575.0	578.5	582.0	578.5
59°	511.9	515.4	519.0	519.0	526.0	526.0	536.4	543.5	547.0	547.0
60°	480.4	480.4	483.9	487.3	494.3	497.9	497.9	504.9	504.9	504.9
61°	448.8	448.8	452.3	455.8	459.3	459.3	466.3	466.3	469.9	473.4
62°	420.7	417.2	417.2	420.7	420.7	427.8	431.3	434.8	438.3	434.8
63°	389.2	385.7	385.7	385.7	385.7	392.7	392.7	396.3	403.2	399.8
64°	354.2	354.2	354.2	354.2	357.7	357.7	364.6	368.1	371.6	375.2
65°	329.6	322.5	319.0	319.0	322.5	326.1	329.6	333.1	336.6	336.6
66°	301.6	294.5	291.0	291.0	291.0	291.0	298.0	298.0	305.1	305.1
67°	270.0	263.0	259.5	256.0	256.0	256.0	266.5	263.0	263.0	263.0
67.5°	259.5	248.9	245.4	241.9	238.4	245.4	241.9	245.4	245.4	241.9
68°	245.4	238.4	231.5	224.4	224.4	224.4	228.0	231.5	228.0	224.4
69°	217.4	213.9	203.3	196.3	192.8	196.3	192.8	196.3	192.8	196.3
70°	192.8	182.4	171.8	168.3	164.8	164.8	164.8	161.3	164.8	161.3
71°	168.3	157.8	147.3	140.3	136.8	136.8	133.3	136.8	133.3	136.8
72°	143.8	133.3	119.2	112.2	112.2	112.2	112.2	108.6	112.2	108.6
72.5°	133.3	119.2	108.6	101.7	98.2	98.2	98.2	98.2	94.7	98.2
73°	122.7	108.6	94.7	91.2	91.2	91.2	87.7	84.1	87.7	87.7



TEST NUMBER: P585025
 CATALOG NUMBER: HCC8W55D010SL-HM82555935-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	42.1	31.5	28.0	28.0	28.0	28.0	28.0	28.0	24.5	24.5
80°	17.6	14.1	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
82.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
85°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



74°	228.0	228.0	220.9	210.4	192.8	175.3	161.3	147.3	129.7	112.2	105.2
75°	210.4	206.9	199.8	189.4	175.3	157.8	143.8	126.2	112.2	94.7	87.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	101.7	84.1	77.1	70.1	70.1	70.1	66.6	66.6	66.6	70.1
75°	80.6	66.6	59.7	52.6	56.1	52.6	56.1	52.6	52.6	52.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)