

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584891

Luminaire Tested: **HCC8S50D010MW-HM82555935-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584891  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S50D010MW-HM82555935-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5625.4 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584891  
CATALOG NUMBER: HCC8S50D010MW-HM82555935-81WDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P584891

CATALOG NUMBER: HCC8S50D010MW-HM82555935-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92											92																	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84											84																	
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77											77																	
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70											70																	
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64											64																	
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59											59																	
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54											54																	
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50											50																	
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46											46																	
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43											43																	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134967
5°	131335
10°	130336
15°	128392
20°	124505
25°	119864
30°	111965
35°	92654
40°	55941
45°	37678
50°	27148
55°	15483
60°	6815
65°	2437
70°	911
75°	405
80°	0
85°	0



TEST NUMBER: P584891  
 CATALOG NUMBER: HCC8S50D010MW-HM82555935-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	403.1	7.2
10°-20°	1130.3	20.1
20°-30°	1612.4	28.7
30°-40°	1468.2	26.1
40°-50°	692.6	12.3
50°-60°	272.4	4.8
60°-70°	43.4	0.8
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3145.7	55.9
0°-40°	4613.9	82.0
0°-60°	5578.9	99.2
0°-90°	5625.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5625.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4377	
5°	4243	403
15°	4022	1130
25°	3523	1612
35°	2461	1468
45°	864	693
55°	288	272
65°	33	43
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P584891  
CATALOG NUMBER: HCC8S50D010MW-HM82555935-81WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4376.9
2.5°	4319.9
5°	4242.9
7.5°	4199.4
10°	4162.5
12.5°	4102.3
15°	4021.8
17.5°	3921.4
20°	3794.1
22.5°	3660.1
25°	3522.9
27.5°	3355.5
30°	3144.5
32.5°	2859.8
35°	2461.3
37.5°	1902.1
40°	1389.7
42.5°	1068.2
45°	864.0
47.5°	709.9
50°	565.9
52.5°	425.3
55°	288.0
57.5°	180.8
60°	110.5
62.5°	67.0
65°	33.4
67.5°	16.7
70°	10.1
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)