

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584895

Luminaire Tested: **HCC8S50D010BZ-HM82555935-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S50D010BZ-HM82555935-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4172.2 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584895
CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584895

CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59				59
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47				47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43				43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39				39
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69070	69070	69070
5°	71925	68919	66016
10°	74328	68038	62796
15°	76209	66482	59535
20°	76358	63724	56583
25°	75071	59692	53656
30°	71053	55076	51145
35°	64782	49532	48019
40°	56335	43667	44340
45°	48328	37818	40591
50°	41281	32607	36459
55°	36181	28080	31682
60°	32212	23947	26636
65°	28580	19540	21255
70°	25362	14489	12081
75°	21148	7577	3598
80°	16657	2380	604
85°	11817	1203	0



TEST NUMBER: P584895
 CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.1	5.1
10°-20°	591.6	14.2
20°-30°	837.3	20.1
30°-40°	876.0	21.0
40°-50°	730.6	17.5
50°-60°	518.1	12.4
60°-70°	298.4	7.2
70°-80°	96.0	2.3
80°-90°	13.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1639.9	39.3
0°-40°	2515.8	60.3
0°-60°	3764.5	90.2
0°-90°	4172.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4172.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2240	2240	2240	2240	2240	
5°	2324	2294	2226	2160	2133	223
15°	2387	2290	2082	1918	1865	671
25°	2206	2042	1754	1614	1577	1007
35°	1721	1570	1316	1246	1276	1067
45°	1108	1018	867	877	931	859
55°	673	603	522	549	589	608
65°	392	328	268	268	291	391
75°	178	131	64	30	30	192
85°	33	17	3	0	0	42
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584895

CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9
2.5°	2286.8	2283.4	2280.0	2283.4	2280.0	2283.4	2280.0	2280.0	2276.7	2273.4	2273.4
5°	2323.6	2320.2	2320.2	2320.2	2316.8	2313.6	2313.6	2310.2	2303.5	2300.1	2293.5
7.5°	2347.0	2350.4	2350.4	2350.4	2343.6	2343.6	2336.9	2330.3	2323.6	2316.8	2306.8
10°	2373.8	2373.8	2370.5	2367.1	2360.4	2357.1	2353.7	2347.0	2336.9	2323.6	2313.6
12.5°	2383.8	2383.8	2380.4	2373.8	2370.5	2367.1	2363.7	2353.7	2340.3	2323.6	2310.2
15°	2387.2	2380.4	2377.2	2373.8	2367.1	2357.1	2357.1	2343.6	2326.9	2306.8	2290.1
17.5°	2360.4	2363.7	2357.1	2350.4	2340.3	2333.6	2323.6	2313.6	2293.5	2270.0	2253.2
20°	2326.9	2323.6	2320.2	2310.2	2296.7	2293.5	2283.4	2266.7	2249.9	2223.1	2199.7
22.5°	2273.4	2270.0	2263.3	2256.6	2243.2	2236.5	2226.5	2206.4	2183.0	2156.2	2129.3
25°	2206.4	2199.7	2189.7	2176.2	2166.2	2159.5	2146.2	2126.1	2099.3	2069.1	2042.4
27.5°	2099.3	2109.3	2102.6	2082.5	2072.5	2059.1	2055.7	2028.9	2005.5	1975.4	1945.2
30°	1995.5	1995.5	1985.4	1975.4	1958.7	1948.6	1935.2	1915.1	1891.7	1854.9	1831.4
32.5°	1864.9	1861.5	1848.2	1844.8	1831.4	1811.4	1808.0	1781.2	1757.7	1730.9	1700.8
35°	1720.9	1714.2	1700.8	1690.7	1684.1	1674.0	1664.0	1640.6	1617.1	1590.3	1570.2
37.5°	1556.9	1556.9	1553.5	1536.8	1530.1	1523.3	1513.4	1489.9	1476.4	1449.7	1429.7
40°	1399.5	1396.1	1386.1	1382.8	1376.0	1366.0	1359.3	1346.0	1325.9	1305.8	1285.7
42.5°	1245.5	1248.8	1235.4	1238.8	1225.3	1218.7	1215.4	1195.3	1185.2	1165.1	1148.4
45°	1108.2	1104.8	1098.2	1094.8	1088.1	1081.4	1074.8	1064.7	1047.9	1027.9	1017.8
47.5°	981.0	971.0	971.0	967.6	964.2	950.9	947.5	937.4	927.4	907.4	893.9
50°	860.5	860.5	860.5	857.1	847.1	843.7	837.0	827.0	816.9	803.6	783.5
52.5°	763.4	763.4	763.4	760.0	746.6	743.3	740.0	726.5	713.1	703.2	689.7
55°	673.0	676.3	673.0	666.2	656.3	656.3	646.2	639.4	626.1	616.1	602.6
57.5°	596.0	596.0	589.3	585.9	579.2	575.8	569.2	562.5	545.7	535.6	518.9
60°	522.3	518.9	518.9	512.3	505.6	498.8	495.5	485.5	478.8	462.0	448.7
62.5°	455.3	455.3	448.7	448.7	435.2	435.2	431.9	421.9	411.8	395.1	388.3
65°	391.7	391.7	388.3	385.1	375.0	371.6	368.2	358.3	348.2	338.2	328.1
67.5°	334.8	334.8	328.1	324.7	318.1	314.7	308.0	301.4	291.3	281.3	271.2
70°	281.3	277.9	274.6	271.2	264.5	261.2	254.5	247.7	237.7	231.0	220.9
72.5°	227.7	227.7	224.3	217.7	214.3	210.9	207.6	200.8	190.9	180.8	174.1
75°	177.5	177.5	177.5	170.8	164.0	160.7	160.7	154.0	147.3	137.2	130.6
77.5°	137.2	134.0	130.6	130.6	123.9	120.5	117.1	113.9	103.8	100.4	93.8
80°	93.8	97.1	93.8	90.4	87.1	83.7	83.7	77.0	73.6	67.0	60.3
82.5°	63.6	60.3	60.3	56.9	56.9	53.5	53.5	46.9	43.5	40.2	36.8
85°	33.4	33.4	30.2	30.2	30.2	26.8	26.8	23.4	23.4	20.1	16.7
87.5°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584895

CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9
2.5°	2270.0	2263.3	2259.9	2259.9	2256.6	2253.2	2249.9	2246.6	2239.9	2239.9	2233.1
5°	2286.8	2280.0	2276.7	2266.7	2259.9	2259.9	2246.6	2243.2	2233.1	2226.5	2219.8
7.5°	2300.1	2286.8	2276.7	2266.7	2259.9	2253.2	2239.9	2226.5	2213.0	2199.7	2193.0
10°	2300.1	2286.8	2270.0	2253.2	2246.6	2239.9	2223.1	2203.0	2186.3	2172.9	2156.2
12.5°	2293.5	2273.4	2253.2	2239.9	2226.5	2216.4	2196.3	2176.2	2156.2	2129.3	2116.0
15°	2273.4	2246.6	2226.5	2203.0	2193.0	2176.2	2159.5	2129.3	2106.0	2082.5	2065.7
17.5°	2233.1	2199.7	2176.2	2152.8	2136.1	2126.1	2099.3	2072.5	2045.6	2018.9	1998.8
20°	2172.9	2142.8	2116.0	2085.8	2072.5	2059.1	2025.6	1998.8	1972.0	1941.9	1921.8
22.5°	2099.3	2069.1	2032.3	2008.8	1988.7	1972.0	1941.9	1911.8	1885.0	1858.2	1831.4
25°	2008.8	1978.8	1945.2	1908.4	1895.1	1878.2	1844.8	1814.6	1784.5	1754.4	1730.9
27.5°	1911.8	1871.6	1844.8	1804.6	1791.3	1774.5	1737.6	1704.2	1677.4	1653.9	1627.1
30°	1794.5	1764.5	1727.7	1690.7	1677.4	1660.7	1630.5	1600.4	1573.6	1546.8	1520.1
32.5°	1667.3	1637.2	1600.4	1573.6	1553.5	1540.2	1510.0	1483.2	1456.5	1429.7	1406.2
35°	1533.4	1499.9	1473.2	1446.4	1429.7	1412.9	1382.8	1359.3	1339.2	1315.8	1292.3
37.5°	1396.1	1372.8	1346.0	1315.8	1299.1	1285.7	1262.2	1235.4	1218.7	1198.6	1181.9
40°	1262.2	1235.4	1212.0	1185.2	1171.8	1161.8	1138.4	1118.3	1101.5	1084.8	1074.8
42.5°	1124.9	1101.5	1078.1	1061.3	1051.3	1041.2	1024.5	1001.1	991.1	974.2	964.2
45°	997.7	977.6	960.9	937.4	930.8	924.1	904.0	887.3	877.2	867.2	860.5
47.5°	877.2	863.8	843.7	830.3	820.3	813.6	800.2	786.9	776.8	770.0	763.4
50°	773.4	756.7	743.3	729.9	723.1	713.1	699.8	693.1	686.3	679.7	679.7
52.5°	676.3	659.5	646.2	636.2	629.4	622.7	612.7	609.4	602.6	602.6	599.3
55°	585.9	575.8	562.5	549.1	545.7	542.4	535.6	529.0	525.7	522.3	525.7
57.5°	508.9	498.8	485.5	475.4	472.0	468.8	465.4	458.7	455.3	455.3	455.3
60°	438.6	428.6	418.5	408.4	408.4	401.8	398.4	395.1	391.7	388.3	388.3
62.5°	375.0	365.0	354.9	348.2	344.9	341.5	334.8	331.4	328.1	328.1	324.7
65°	318.1	304.6	301.4	291.3	287.9	284.5	281.3	274.6	271.2	267.8	264.5
67.5°	261.2	254.5	244.4	237.7	234.4	231.0	227.7	220.9	217.7	214.3	207.6
70°	210.9	204.2	197.6	190.9	187.5	184.1	177.5	170.8	167.4	160.7	150.7
72.5°	164.0	157.3	150.7	144.0	140.6	137.2	130.6	123.9	117.1	110.5	103.8
75°	123.9	117.1	107.1	100.4	97.1	97.1	87.1	80.3	73.6	63.6	56.9
77.5°	87.1	77.0	73.6	67.0	63.6	56.9	50.3	43.5	36.8	33.4	26.8
80°	56.9	50.3	43.5	40.2	36.8	33.4	30.2	23.4	16.7	13.4	10.1
82.5°	33.4	30.2	26.8	23.4	20.1	16.7	13.4	13.4	10.1	6.7	3.4
85°	16.7	13.4	10.1	10.1	6.7	6.7	6.7	3.4	3.4	3.4	3.4
87.5°	6.7	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584895

CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9
2.5°	2229.9	2226.5	2223.1	2219.8	2219.8	2213.0	2213.0	2209.8	2203.0	2199.7	2199.7
5°	2209.8	2199.7	2193.0	2189.7	2186.3	2176.2	2172.9	2166.2	2159.5	2152.8	2149.4
7.5°	2179.6	2162.9	2156.2	2152.8	2142.8	2132.7	2126.1	2116.0	2106.0	2095.9	2092.5
10°	2142.8	2126.1	2109.3	2102.6	2092.5	2085.8	2072.5	2059.1	2049.0	2039.0	2028.9
12.5°	2095.9	2075.8	2059.1	2052.4	2042.4	2028.9	2008.8	2002.1	1985.4	1978.8	1965.3
15°	2042.4	2018.9	2002.1	1992.1	1982.0	1961.9	1948.6	1935.2	1918.4	1911.8	1898.3
17.5°	1975.4	1948.6	1931.9	1921.8	1915.1	1898.3	1878.2	1861.5	1844.8	1838.1	1828.1
20°	1895.1	1878.2	1854.9	1844.8	1838.1	1818.0	1797.9	1791.3	1777.8	1764.5	1754.4
22.5°	1804.6	1787.9	1764.5	1754.4	1751.0	1734.3	1717.6	1707.6	1697.5	1687.5	1677.4
25°	1710.8	1690.7	1670.7	1664.0	1657.3	1644.0	1630.5	1623.9	1613.8	1607.0	1600.4
27.5°	1610.4	1590.3	1573.6	1563.5	1556.9	1546.8	1540.2	1533.4	1526.7	1520.1	1516.7
30°	1503.3	1483.2	1469.8	1463.1	1456.5	1453.1	1443.0	1439.6	1436.4	1429.7	1433.0
32.5°	1396.1	1379.4	1366.0	1355.9	1355.9	1349.3	1346.0	1346.0	1342.6	1342.6	1342.6
35°	1279.0	1268.9	1258.9	1255.5	1252.2	1248.8	1245.5	1248.8	1245.5	1248.8	1252.2
37.5°	1171.8	1161.8	1155.1	1151.7	1148.4	1151.7	1148.4	1148.4	1151.7	1158.5	1161.8
40°	1061.3	1054.7	1047.9	1051.3	1047.9	1047.9	1047.9	1057.9	1061.3	1064.7	1068.0
42.5°	957.5	950.9	947.5	947.5	950.9	947.5	954.3	957.5	964.2	974.2	981.0
45°	857.1	853.7	853.7	857.1	853.7	860.5	860.5	867.2	877.2	883.9	890.5
47.5°	763.4	763.4	763.4	766.7	766.7	770.0	776.8	780.1	786.9	793.5	800.2
50°	676.3	679.7	683.0	683.0	683.0	689.7	696.4	699.8	703.2	706.4	716.5
52.5°	599.3	602.6	602.6	606.0	609.4	612.7	616.1	622.7	626.1	632.8	636.2
55°	525.7	525.7	532.4	535.6	535.6	535.6	542.4	542.4	549.1	552.5	559.1
57.5°	455.3	458.7	458.7	462.0	462.0	465.4	468.8	472.0	475.4	478.8	482.1
60°	388.3	388.3	388.3	391.7	395.1	398.4	395.1	401.8	401.8	408.4	411.8
62.5°	324.7	328.1	328.1	328.1	328.1	328.1	328.1	331.4	334.8	338.2	341.5
65°	264.5	264.5	264.5	261.2	264.5	261.2	264.5	267.8	267.8	271.2	274.6
67.5°	204.2	204.2	197.6	197.6	200.8	200.8	200.8	200.8	197.6	204.2	204.2
70°	147.3	144.0	140.6	137.2	137.2	134.0	134.0	130.6	130.6	130.6	130.6
72.5°	97.1	90.4	83.7	80.3	77.0	77.0	70.3	67.0	70.3	70.3	70.3
75°	50.3	43.5	40.2	36.8	33.4	33.4	30.2	30.2	30.2	30.2	30.2
77.5°	20.1	16.7	13.4	13.4	10.1	10.1	10.1	10.1	10.1	10.1	10.1
80°	6.7	6.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	3.4	0.0	0.0	3.4	0.0	3.4	3.4	3.4	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584895

CATALOG NUMBER: HCC8S50D010BZ-HM82555935-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9	2239.9
2.5°	2196.3	2196.3	2193.0	2196.3	2189.7	2193.0	2189.7	2189.7
5°	2146.2	2139.4	2139.4	2139.4	2136.1	2136.1	2132.7	2132.7
7.5°	2085.8	2082.5	2079.2	2075.8	2072.5	2069.1	2069.1	2069.1
10°	2025.6	2018.9	2018.9	2015.6	2008.8	2005.5	2005.5	2005.5
12.5°	1955.3	1951.9	1948.6	1948.6	1935.2	1938.6	1935.2	1935.2
15°	1888.3	1885.0	1885.0	1875.0	1868.2	1868.2	1868.2	1864.9
17.5°	1818.0	1814.6	1811.4	1804.6	1797.9	1797.9	1794.5	1797.9
20°	1744.4	1741.0	1734.3	1734.3	1730.9	1727.7	1720.9	1724.3
22.5°	1670.7	1664.0	1660.7	1660.7	1657.3	1657.3	1650.6	1650.6
25°	1593.7	1590.3	1587.0	1590.3	1583.6	1583.6	1577.0	1577.0
27.5°	1513.4	1510.0	1510.0	1510.0	1506.6	1510.0	1506.6	1506.6
30°	1433.0	1433.0	1429.7	1429.7	1433.0	1429.7	1433.0	1436.4
32.5°	1346.0	1346.0	1349.3	1349.3	1352.6	1352.6	1352.6	1352.6
35°	1255.5	1262.2	1262.2	1265.6	1268.9	1272.2	1272.2	1275.6
37.5°	1171.8	1175.2	1178.5	1181.9	1188.5	1188.5	1188.5	1188.5
40°	1081.4	1084.8	1091.5	1088.1	1101.5	1104.8	1101.5	1101.5
42.5°	987.7	994.4	997.7	1004.4	1007.8	1014.5	1017.8	1017.8
45°	900.6	904.0	910.7	917.4	920.7	930.8	930.8	930.8
47.5°	810.2	816.9	820.3	827.0	830.3	840.4	843.7	840.4
50°	723.1	729.9	736.6	736.6	746.6	749.9	756.7	760.0
52.5°	639.4	642.8	649.5	652.9	659.5	666.2	669.6	673.0
55°	559.1	562.5	569.2	569.2	579.2	582.5	589.3	589.3
57.5°	485.5	488.9	495.5	492.1	498.8	505.6	505.6	502.2
60°	415.1	415.1	415.1	421.9	425.2	428.6	431.9	431.9
62.5°	341.5	348.2	351.5	351.5	354.9	358.3	358.3	354.9
65°	274.6	281.3	284.5	284.5	287.9	287.9	287.9	291.3
67.5°	207.6	207.6	207.6	210.9	207.6	207.6	207.6	207.6
70°	130.6	130.6	130.6	130.6	127.2	130.6	130.6	134.0
72.5°	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3
75°	30.2	30.2	30.2	33.4	30.2	30.2	30.2	30.2
77.5°	13.4	10.1	13.4	13.4	10.1	10.1	10.1	10.1
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	0.0	3.4	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)