

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585030

Luminaire Tested: **HCC8W55D010MB-HM82555935-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MB-HM82555935-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5772.8 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585030
CATALOG NUMBER: HCC8W55D010MB-HM82555935-81WDWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585030

CATALOG NUMBER: HCC8W55D010MB-HM82555935-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90																												
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81																												
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73																												
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																												
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59																												
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54																												
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49																												
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																												
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41																												
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101384
5°	100688
10°	100424
15°	103061
20°	111572
25°	119615
30°	116943
35°	97378
40°	59825
45°	41424
50°	31614
55°	20730
60°	12970
65°	9712
70°	9791
75°	11271
80°	12448
85°	11145



TEST NUMBER: P585030
 CATALOG NUMBER: HCC8W55D010MB-HM82555935-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.1	5.4
10°-20°	926.7	16.1
20°-30°	1595.3	27.6
30°-40°	1545.7	26.8
40°-50°	761.3	13.2
50°-60°	359.3	6.2
60°-70°	141.6	2.5
70°-80°	97.6	1.7
80°-90°	36.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2831.1	49.0
0°-40°	4376.8	75.8
0°-60°	5497.4	95.2
0°-90°	5772.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5772.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3288	
5°	3253	309
15°	3228	927
25°	3516	1595
35°	2587	1546
45°	950	761
55°	386	359
65°	133	142
75°	95	98
85°	32	36
90°	0	



TEST NUMBER: P585030

CATALOG NUMBER: HCC8W55D010MB-HM82555935-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3287.8
2.5°	3277.3
5°	3252.8
7.5°	3228.3
10°	3207.2
12.5°	3203.7
15°	3228.3
17.5°	3301.9
20°	3400.0
22.5°	3487.6
25°	3515.6
27.5°	3452.6
30°	3284.3
32.5°	3007.5
35°	2586.8
37.5°	2008.5
40°	1486.2
42.5°	1153.2
45°	949.9
47.5°	799.2
50°	659.0
52.5°	518.7
55°	385.6
57.5°	280.5
60°	210.3
62.5°	164.8
65°	133.1
67.5°	115.7
70°	108.6
72.5°	101.6
75°	94.6
77.5°	84.1
80°	70.1
82.5°	52.6
85°	31.5
87.5°	14.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)