

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584901

Luminaire Tested: **HCC8W50D010MW-HM82555940-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W50D010MW-HM82555940-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5496.3 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584901
CATALOG NUMBER: HCC8W50D010MW-HM82555940-81NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584901

CATALOG NUMBER: HCC8W50D010MW-HM82555940-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1034521
5°	663563
10°	299756
15°	180863
20°	137828
25°	111300
30°	81564
35°	29532
40°	11022
45°	5002
50°	1597
55°	398
60°	228
65°	270
70°	0
75°	0
80°	657
85°	1309



TEST NUMBER: P584901
 CATALOG NUMBER: HCC8W50D010MW-HM82555940-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1635.0	29.7
10°-20°	1660.6	30.2
20°-30°	1486.6	27.0
30°-40°	598.8	10.9
40°-50°	98.2	1.8
50°-60°	8.9	0.2
60°-70°	3.2	0.1
70°-80°	2.5	0.0
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4782.2	87.0
0°-40°	5381.0	97.9
0°-60°	5488.1	99.9
0°-90°	5497.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5496.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	33549	
5°	21437	###
15°	5665	1661
25°	3271	1487
35°	784	599
45°	115	98
55°	7	9
65°	4	3
75°	0	2
85°	4	4
90°	0	



TEST NUMBER: P584901
CATALOG NUMBER: HCC8W50D010MW-HM82555940-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	33548.8
0.5°	33445.2
1°	33012.2
1.5°	32316.5
2°	31261.9
2.5°	30014.8
3°	28453.2
3.5°	26739.8
4°	25045.0
4.5°	23146.7
5°	21437.0
5.5°	19575.7
6°	18065.8
6.5°	16493.2
7°	15257.2
7.5°	13951.0
8°	12899.9
8.5°	11845.4
9°	11053.4
9.5°	10180.1
10°	9573.2
12.5°	7060.5
15°	5665.4
17.5°	4840.2
20°	4200.1
22.5°	3689.4
25°	3271.2
27.5°	2853.1
30°	2290.7
32.5°	1472.8
35°	784.5
37.5°	433.0
40°	273.8
42.5°	181.3
45°	114.7
47.5°	70.3
50°	33.3
52.5°	11.1
55°	7.4
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7



TEST NUMBER: P584901
CATALOG NUMBER: HCC8W50D010MW-HM82555940-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.7
80°	3.7
82.5°	3.7
85°	3.7
87.5°	3.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.7
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)