

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593855

Luminaire Tested: **HCC8W55D010MB-HM82555950-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MB-HM82555950-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5486.1 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593855
CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P593855

CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	84112	84112	84112
5°	87192	83833	80954
10°	89656	83105	77644
15°	91654	81636	74217
20°	91798	78448	71199
25°	90041	74087	68684
30°	85399	68707	65669
35°	77596	62568	62719
40°	67848	56146	59109
45°	58803	50015	55083
50°	51484	44423	50184
55°	45826	39370	45412
60°	41339	35369	39908
65°	37322	31105	34768
70°	33539	26191	25849
75°	29547	20778	19384
80°	24772	17190	18593
85°	19212	15108	16452



TEST NUMBER: P593855
 CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.3	4.7
10°-20°	724.8	13.2
20°-30°	1035.8	18.9
30°-40°	1100.6	20.1
40°-50°	947.6	17.3
50°-60°	708.5	12.9
60°-70°	451.9	8.2
70°-80°	205.7	3.7
80°-90°	54.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2017.9	36.8
0°-40°	3118.5	56.8
0°-60°	4774.6	87.0
0°-90°	5486.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5486.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2728	2728	2728	2728	2728	
5°	2817	2778	2708	2638	2615	270
15°	2871	2774	2557	2383	2325	809
25°	2646	2480	2178	2046	2019	1211
35°	2061	1918	1662	1620	1666	1284
45°	1348	1275	1147	1178	1263	1048
55°	852	783	732	794	845	766
65°	512	453	426	446	476	510
75°	248	213	174	159	163	264
85°	54	46	43	46	46	65
90°	0	0	0	0	0	



TEST NUMBER: P593855

CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7
2.5°	2778.1	2770.3	2774.1	2770.3	2774.1	2774.1	2766.4	2766.4	2766.4	2766.4	2754.8
5°	2816.8	2812.9	2812.9	2809.0	2805.2	2809.0	2805.2	2801.3	2793.6	2789.7	2778.1
7.5°	2840.0	2840.0	2840.0	2840.0	2836.1	2832.3	2828.4	2820.7	2812.9	2805.2	2797.4
10°	2863.3	2867.2	2863.3	2859.4	2855.6	2847.8	2844.0	2836.1	2824.5	2812.9	2805.2
12.5°	2874.9	2874.9	2871.0	2871.0	2863.3	2859.4	2847.8	2836.1	2824.5	2812.9	2793.6
15°	2871.0	2871.0	2867.2	2863.3	2851.7	2847.8	2840.0	2828.4	2809.0	2793.6	2774.1
17.5°	2847.8	2844.0	2836.1	2836.1	2820.7	2816.8	2809.0	2793.6	2774.1	2750.9	2727.7
20°	2797.4	2797.4	2793.6	2789.7	2774.1	2762.5	2754.8	2735.4	2720.0	2692.8	2669.6
22.5°	2727.7	2735.4	2727.7	2720.0	2700.5	2696.7	2685.1	2661.8	2638.5	2607.6	2580.5
25°	2646.4	2642.4	2638.5	2630.8	2615.3	2607.6	2592.1	2568.8	2545.6	2510.7	2479.7
27.5°	2541.7	2526.2	2526.2	2510.7	2499.1	2487.5	2479.7	2456.5	2425.5	2398.4	2359.6
30°	2398.4	2402.2	2382.8	2378.9	2359.6	2351.9	2336.4	2313.1	2286.0	2255.0	2224.0
32.5°	2243.3	2231.7	2231.7	2216.3	2200.8	2189.2	2185.2	2158.1	2134.9	2103.9	2072.9
35°	2061.3	2061.3	2049.6	2045.7	2030.3	2022.5	2010.9	1995.4	1968.3	1941.2	1917.9
37.5°	1883.1	1875.3	1871.4	1863.7	1852.0	1840.4	1840.4	1813.3	1809.5	1778.4	1747.5
40°	1685.5	1693.2	1685.5	1673.9	1670.0	1662.1	1658.3	1642.8	1631.2	1604.1	1584.7
42.5°	1518.8	1511.1	1511.1	1507.2	1491.7	1491.7	1484.0	1476.3	1456.8	1449.1	1425.9
45°	1348.4	1356.1	1344.5	1348.4	1332.8	1332.8	1332.8	1317.3	1301.9	1290.3	1274.8
47.5°	1201.1	1204.9	1204.9	1193.3	1189.5	1189.5	1181.7	1174.0	1162.4	1146.9	1135.2
50°	1073.2	1077.1	1069.3	1065.5	1057.7	1053.9	1053.9	1038.4	1030.7	1015.2	1007.3
52.5°	957.1	957.1	953.2	953.2	941.5	941.5	933.7	922.1	914.4	906.7	887.3
55°	852.4	852.4	848.5	844.7	844.7	833.1	829.2	817.6	809.7	794.3	782.7
57.5°	751.7	755.6	751.7	747.7	743.9	740.0	732.3	720.7	712.9	701.3	693.6
60°	670.3	670.3	666.4	662.5	654.8	650.9	647.1	639.3	627.7	619.9	608.3
62.5°	592.8	588.9	585.1	581.2	573.5	573.5	565.7	558.0	546.3	538.5	530.8
65°	511.5	511.5	507.6	507.6	503.7	496.0	492.1	488.1	472.7	468.8	453.3
67.5°	437.9	441.7	434.0	434.0	426.3	426.3	422.3	410.7	406.8	399.1	391.3
70°	372.0	372.0	372.0	368.1	360.4	356.4	352.5	344.8	340.9	333.2	325.5
72.5°	306.1	306.1	302.3	302.3	298.4	294.5	290.5	282.8	282.8	275.1	267.3
75°	248.0	248.0	244.1	240.3	236.4	236.4	232.5	228.7	220.8	216.9	213.1
77.5°	189.9	189.9	189.9	186.0	182.1	182.1	182.1	174.4	166.7	166.7	162.7
80°	139.5	139.5	135.6	135.6	131.7	131.7	131.7	127.9	124.0	120.1	116.3
82.5°	92.9	92.9	92.9	92.9	89.1	89.1	89.1	85.2	81.3	81.3	81.3
85°	54.3	54.3	54.3	54.3	50.4	50.4	50.4	50.4	50.4	46.5	46.5
87.5°	23.2	19.3	23.2	19.3	23.2	19.3	23.2	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593855

CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7
2.5°	2758.7	2754.8	2750.9	2747.1	2747.1	2743.2	2735.4	2731.6	2727.7	2723.8	2723.8
5°	2774.1	2770.3	2762.5	2754.8	2750.9	2743.2	2735.4	2727.7	2720.0	2708.3	2704.4
7.5°	2785.8	2774.1	2766.4	2750.9	2747.1	2739.3	2727.7	2716.1	2700.5	2685.1	2673.4
10°	2785.8	2770.3	2758.7	2739.3	2731.6	2723.8	2708.3	2688.9	2669.6	2654.1	2634.7
12.5°	2778.1	2758.7	2739.3	2720.0	2708.3	2696.7	2673.4	2654.1	2630.8	2607.6	2592.1
15°	2750.9	2727.7	2704.4	2681.2	2669.6	2654.1	2630.8	2603.7	2580.5	2557.2	2530.1
17.5°	2700.5	2677.3	2650.2	2623.1	2607.6	2596.0	2561.1	2541.7	2506.8	2483.6	2460.4
20°	2634.7	2607.6	2572.7	2545.6	2526.2	2514.6	2487.5	2452.6	2425.5	2390.6	2367.3
22.5°	2549.5	2514.6	2479.7	2452.6	2433.2	2417.7	2382.8	2348.0	2324.8	2293.7	2266.6
25°	2448.7	2413.9	2378.9	2340.2	2320.9	2305.3	2274.4	2243.3	2212.4	2177.5	2154.3
27.5°	2328.6	2289.9	2258.9	2224.0	2204.6	2181.3	2146.5	2115.5	2084.5	2061.3	2030.3
30°	2196.9	2154.3	2123.3	2088.4	2069.0	2049.6	2014.8	1983.7	1956.7	1929.6	1914.0
32.5°	2038.0	2007.0	1976.0	1941.2	1925.6	1914.0	1879.2	1848.1	1817.2	1793.9	1782.3
35°	1886.9	1852.0	1824.9	1793.9	1774.5	1762.9	1732.0	1704.8	1689.3	1662.1	1646.7
37.5°	1728.0	1700.9	1670.0	1638.9	1627.3	1615.7	1592.4	1565.3	1542.1	1522.7	1514.9
40°	1561.5	1538.2	1511.1	1491.7	1480.1	1468.4	1449.1	1429.7	1414.3	1394.8	1387.1
42.5°	1402.5	1387.1	1363.9	1340.7	1328.9	1325.1	1301.9	1286.4	1278.7	1270.8	1263.1
45°	1259.2	1236.0	1220.5	1204.9	1193.3	1185.6	1174.0	1162.4	1154.7	1146.9	1139.1
47.5°	1119.7	1100.4	1084.9	1073.2	1061.6	1057.7	1050.0	1038.4	1030.7	1030.7	1030.7
50°	991.9	976.4	960.9	953.2	949.3	941.5	933.7	929.9	926.0	926.0	926.0
52.5°	879.5	864.0	852.4	844.7	844.7	836.9	829.2	825.3	825.3	825.3	825.3
55°	774.9	763.3	755.6	747.7	740.0	736.1	736.1	736.1	732.3	732.3	736.1
57.5°	681.9	674.1	662.5	654.8	650.9	650.9	647.1	643.2	647.1	650.9	654.8
60°	596.7	588.9	585.1	573.5	573.5	573.5	569.6	569.6	569.6	573.5	577.3
62.5°	519.2	515.3	507.6	503.7	499.9	499.9	496.0	496.0	496.0	496.0	499.9
65°	449.5	441.7	434.0	434.0	434.0	430.1	430.1	422.3	426.3	426.3	422.3
67.5°	383.6	375.9	372.0	368.1	364.3	364.3	360.4	356.4	352.5	352.5	352.5
70°	321.6	313.9	313.9	306.1	306.1	302.3	298.4	298.4	294.5	290.5	286.7
72.5°	259.6	255.7	251.9	248.0	248.0	248.0	244.1	240.3	236.4	232.5	224.7
75°	205.3	205.3	197.6	193.7	193.7	189.9	186.0	182.1	178.3	174.4	170.5
77.5°	158.8	154.9	147.2	143.3	143.3	143.3	139.5	135.6	131.7	127.9	124.0
80°	116.3	112.4	108.5	104.7	104.7	104.7	100.8	100.8	96.8	96.8	96.8
82.5°	77.5	77.5	73.6	73.6	73.6	73.6	69.7	69.7	69.7	69.7	69.7
85°	46.5	46.5	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7
87.5°	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593855

CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7
2.5°	2716.1	2716.1	2708.3	2704.4	2700.5	2704.4	2696.7	2692.8	2688.9	2688.9	2685.1
5°	2692.8	2688.9	2673.4	2669.6	2665.7	2661.8	2654.1	2646.4	2638.5	2634.7	2630.8
7.5°	2661.8	2650.2	2634.7	2630.8	2626.9	2615.3	2603.7	2596.0	2584.4	2580.5	2572.7
10°	2619.2	2603.7	2592.1	2580.5	2572.7	2561.1	2549.5	2537.8	2522.4	2518.5	2506.8
12.5°	2568.8	2549.5	2526.2	2522.4	2510.7	2495.2	2479.7	2468.1	2456.5	2448.7	2437.1
15°	2506.8	2487.5	2464.2	2452.6	2440.9	2429.3	2410.0	2394.5	2382.8	2371.2	2359.6
17.5°	2433.2	2410.0	2390.6	2378.9	2371.2	2351.9	2336.4	2316.9	2305.3	2293.7	2282.1
20°	2344.1	2324.8	2297.6	2286.0	2282.1	2266.6	2247.2	2239.5	2224.0	2212.4	2204.6
22.5°	2243.3	2224.0	2200.8	2193.0	2177.5	2169.7	2150.4	2142.7	2134.9	2123.3	2119.3
25°	2131.0	2111.6	2092.3	2088.4	2076.8	2069.0	2057.4	2045.7	2045.7	2034.1	2034.1
27.5°	2014.8	1995.4	1979.9	1972.1	1968.3	1960.5	1948.9	1945.1	1941.2	1937.3	1937.3
30°	1890.8	1867.6	1859.7	1855.9	1852.0	1844.3	1840.4	1832.7	1836.5	1840.4	1836.5
32.5°	1759.1	1751.3	1735.8	1728.0	1732.0	1728.0	1720.3	1728.0	1724.1	1732.0	1735.8
35°	1631.2	1623.5	1615.7	1615.7	1608.0	1608.0	1608.0	1611.9	1619.6	1623.5	1631.2
37.5°	1507.2	1495.6	1491.7	1487.9	1491.7	1491.7	1491.7	1499.5	1507.2	1514.9	1526.5
40°	1375.5	1367.7	1367.7	1367.7	1367.7	1379.3	1375.5	1383.2	1390.9	1402.5	1414.3
42.5°	1251.5	1251.5	1255.3	1255.3	1255.3	1255.3	1263.1	1274.8	1286.4	1298.0	1309.6
45°	1135.2	1135.2	1135.2	1143.1	1143.1	1146.9	1162.4	1170.1	1177.9	1189.5	1201.1
47.5°	1026.8	1026.8	1030.7	1034.5	1038.4	1046.1	1053.9	1065.5	1077.1	1084.9	1096.5
50°	926.0	929.9	937.6	945.3	945.3	949.3	960.9	968.7	976.4	988.0	991.9
52.5°	829.2	836.9	844.7	848.5	852.4	860.1	864.0	875.6	879.5	891.2	895.1
55°	740.0	743.9	755.6	759.5	759.5	767.2	774.9	782.7	794.3	794.3	802.0
57.5°	658.7	662.5	670.3	674.1	670.3	681.9	685.9	693.6	697.5	705.2	709.1
60°	577.3	585.1	588.9	588.9	592.8	596.7	604.4	604.4	612.1	619.9	619.9
62.5°	499.9	503.7	507.6	511.5	515.3	511.5	523.1	523.1	530.8	534.7	542.4
65°	426.3	430.1	430.1	434.0	434.0	437.9	437.9	441.7	445.6	453.3	457.2
67.5°	352.5	352.5	352.5	356.4	352.5	356.4	356.4	360.4	360.4	368.1	372.0
70°	286.7	282.8	278.9	278.9	278.9	278.9	275.1	278.9	278.9	282.8	282.8
72.5°	220.8	216.9	213.1	209.2	209.2	205.3	201.5	205.3	205.3	209.2	209.2
75°	166.7	158.8	158.8	158.8	154.9	154.9	154.9	158.8	158.8	158.8	162.7
77.5°	124.0	124.0	120.1	120.1	120.1	124.0	124.0	127.9	127.9	127.9	127.9
80°	92.9	96.8	96.8	96.8	96.8	100.8	100.8	100.8	100.8	104.7	104.7
82.5°	69.7	69.7	69.7	69.7	73.6	73.6	73.6	73.6	73.6	73.6	73.6
85°	42.7	46.5	46.5	42.7	46.5	46.5	46.5	46.5	46.5	46.5	46.5
87.5°	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593855

CATALOG NUMBER: HCC8W55D010MB-HM82555950-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7	2727.7
2.5°	2681.2	2681.2	2681.2	2681.2	2677.3	2677.3	2677.3	2673.4
5°	2623.1	2623.1	2623.1	2615.3	2619.2	2619.2	2611.5	2615.3
7.5°	2564.9	2561.1	2557.2	2557.2	2553.3	2549.5	2545.6	2549.5
10°	2499.1	2487.5	2487.5	2483.6	2483.6	2475.8	2475.8	2479.7
12.5°	2425.5	2417.7	2417.7	2413.9	2410.0	2406.1	2402.2	2402.2
15°	2351.9	2344.1	2340.2	2336.4	2332.5	2324.8	2328.6	2324.8
17.5°	2278.3	2266.6	2266.6	2262.8	2258.9	2251.1	2251.1	2247.2
20°	2193.0	2189.2	2181.3	2185.2	2181.3	2173.6	2169.7	2169.7
22.5°	2107.7	2107.7	2103.9	2103.9	2100.0	2096.1	2092.3	2092.3
25°	2026.4	2022.5	2026.4	2026.4	2014.8	2014.8	2014.8	2018.7
27.5°	1933.4	1937.3	1933.4	1933.4	1933.4	1933.4	1937.3	1933.4
30°	1840.4	1840.4	1840.4	1844.3	1852.0	1848.1	1848.1	1844.3
32.5°	1739.7	1743.6	1743.6	1747.5	1751.3	1759.1	1759.1	1762.9
35°	1638.9	1646.7	1650.5	1646.7	1658.3	1658.3	1666.1	1666.1
37.5°	1534.3	1538.2	1546.0	1549.9	1557.6	1561.5	1565.3	1565.3
40°	1422.0	1437.5	1441.3	1445.2	1456.8	1456.8	1460.7	1468.4
42.5°	1317.3	1332.8	1336.7	1340.7	1348.4	1360.0	1356.1	1363.9
45°	1216.7	1228.3	1232.1	1236.0	1247.6	1251.5	1251.5	1263.1
47.5°	1108.1	1115.9	1119.7	1127.5	1135.2	1143.1	1150.8	1146.9
50°	999.6	1011.2	1019.1	1022.9	1034.5	1038.4	1042.3	1046.1
52.5°	902.8	910.5	914.4	918.3	929.9	933.7	937.6	945.3
55°	809.7	813.6	821.5	817.6	829.2	833.1	836.9	844.7
57.5°	716.8	720.7	724.5	724.5	732.3	740.0	743.9	747.7
60°	627.7	635.5	639.3	639.3	639.3	647.1	647.1	647.1
62.5°	546.3	546.3	550.1	550.1	558.0	558.0	558.0	558.0
65°	461.1	464.9	468.8	468.8	476.5	472.7	480.4	476.5
67.5°	372.0	372.0	379.7	379.7	375.9	379.7	379.7	379.7
70°	282.8	282.8	286.7	286.7	286.7	286.7	286.7	286.7
72.5°	209.2	209.2	209.2	213.1	209.2	209.2	213.1	209.2
75°	162.7	162.7	162.7	162.7	162.7	162.7	162.7	162.7
77.5°	127.9	127.9	131.7	131.7	131.7	131.7	131.7	131.7
80°	104.7	104.7	104.7	104.7	108.5	104.7	104.7	104.7
82.5°	77.5	73.6	77.5	73.6	77.5	77.5	77.5	77.5
85°	46.5	46.5	46.5	46.5	46.5	46.5	46.5	46.5
87.5°	19.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)