

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585058

Luminaire Tested: **HCC8S60D010MB-HM86080827-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585058
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MB-HM86080827-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4964.9 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585058
CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77					77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67					67			
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59					59			
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80554	80554	80554
5°	81620	80211	79459
10°	82451	79395	78192
15°	83287	77719	76158
20°	82862	74852	73136
25°	80933	70372	69423
30°	76871	65324	65075
35°	69977	59606	60129
40°	61351	53353	55317
45°	52928	47455	50800
50°	46347	41660	46015
55°	41063	35816	40504
60°	36997	30109	33556
65°	33338	24181	25698
70°	29239	17608	14155
75°	24925	9138	3741
80°	19196	2486	622
85°	12312	0	0



TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.5	5.0
10°-20°	692.9	14.0
20°-30°	983.4	19.8
30°-40°	1035.2	20.9
40°-50°	880.6	17.7
50°-60°	636.4	12.8
60°-70°	362.0	7.3
70°-80°	114.0	2.3
80°-90°	13.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1922.8	38.7
0°-40°	2958.0	59.6
0°-60°	4475.0	90.1
0°-90°	4964.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4964.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2612	2612	2612	2612	2612	
5°	2637	2623	2591	2574	2567	252
15°	2609	2543	2434	2389	2386	735
25°	2379	2260	2068	2033	2040	1089
35°	1859	1751	1583	1573	1597	1157
45°	1214	1168	1088	1116	1165	943
55°	764	708	666	704	753	689
65°	457	394	331	328	352	453
75°	209	160	77	35	31	225
85°	35	21	0	0	0	45
90°	0	0	0	0	0	



TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3
2.5°	2626.3	2629.8	2622.8	2622.8	2629.8	2622.8	2626.3	2626.3	2622.8	2622.8	2619.3
5°	2636.8	2633.2	2633.2	2633.2	2636.8	2629.8	2626.3	2629.8	2622.8	2622.8	2622.8
7.5°	2640.2	2640.2	2636.8	2633.2	2633.2	2633.2	2629.8	2626.3	2622.8	2615.8	2612.3
10°	2633.2	2633.2	2636.8	2629.8	2629.8	2622.8	2622.8	2615.8	2615.8	2608.9	2598.4
12.5°	2626.3	2622.8	2622.8	2615.8	2615.8	2608.9	2608.9	2598.4	2594.9	2584.4	2573.9
15°	2608.9	2605.3	2598.4	2594.9	2591.3	2587.9	2581.0	2577.5	2567.0	2553.1	2542.6
17.5°	2573.9	2570.5	2567.0	2560.0	2553.1	2549.6	2546.0	2535.6	2521.7	2511.2	2493.8
20°	2525.1	2521.7	2521.7	2511.2	2507.7	2497.2	2493.8	2479.8	2469.3	2448.4	2434.5
22.5°	2458.8	2462.4	2455.4	2448.4	2441.4	2430.9	2424.0	2410.0	2392.6	2371.6	2354.2
25°	2378.7	2382.1	2375.2	2368.2	2357.7	2350.7	2343.8	2322.8	2305.4	2281.0	2260.1
27.5°	2277.5	2277.5	2277.5	2270.6	2253.1	2249.6	2242.7	2221.7	2197.2	2176.4	2155.5
30°	2158.9	2155.5	2155.5	2145.0	2137.9	2124.0	2113.6	2096.2	2078.7	2054.3	2029.9
32.5°	2015.9	2019.4	2009.0	2002.0	1991.5	1991.5	1977.5	1963.5	1942.7	1918.2	1893.9
35°	1858.9	1862.5	1855.5	1852.0	1834.6	1831.0	1827.6	1810.1	1796.2	1778.8	1750.9
37.5°	1698.5	1695.0	1691.6	1691.6	1681.1	1674.2	1667.1	1656.6	1635.8	1621.8	1607.8
40°	1524.1	1524.1	1524.1	1520.6	1517.2	1510.1	1506.7	1499.8	1485.8	1471.9	1461.4
42.5°	1367.2	1367.2	1363.7	1360.2	1353.3	1356.7	1349.7	1342.8	1328.8	1318.3	1311.4
45°	1213.7	1213.7	1213.7	1217.2	1210.3	1199.8	1199.8	1192.8	1185.8	1178.9	1168.4
47.5°	1077.7	1088.2	1081.2	1077.7	1081.2	1067.2	1067.2	1060.3	1053.3	1046.4	1032.4
50°	966.1	966.1	966.1	959.2	955.6	955.6	945.2	938.2	934.7	927.8	913.8
52.5°	864.9	858.0	858.0	854.6	851.0	844.1	844.1	837.0	823.1	816.1	805.6
55°	763.8	763.8	760.3	756.9	753.4	749.8	746.4	735.9	728.9	718.5	708.0
57.5°	673.1	680.2	676.6	669.7	662.6	662.6	655.7	648.7	638.3	627.8	617.3
60°	599.9	596.4	596.4	593.0	585.9	582.5	579.0	568.5	558.0	547.6	537.1
62.5°	523.2	523.2	523.2	516.1	509.2	505.8	502.2	495.3	481.3	470.8	463.9
65°	456.9	453.4	449.9	446.5	442.9	436.0	432.5	425.5	415.0	404.6	394.1
67.5°	390.7	387.2	387.2	383.6	373.2	369.7	369.7	359.3	348.8	338.3	327.8
70°	324.3	324.3	324.3	317.4	313.8	310.4	306.9	300.0	289.5	279.0	268.5
72.5°	268.5	265.1	265.1	261.6	251.1	247.6	244.2	237.1	226.8	219.7	212.8
75°	209.2	209.2	205.8	202.3	198.8	195.3	191.8	184.9	174.4	163.9	160.4
77.5°	160.4	157.0	157.0	153.5	146.5	143.0	143.0	136.0	125.6	118.6	111.6
80°	108.1	111.6	108.1	104.6	101.2	97.7	94.1	90.7	83.7	76.7	69.8
82.5°	66.3	69.8	66.3	66.3	62.7	59.3	59.3	52.4	48.8	45.3	41.9
85°	34.8	34.8	34.8	34.8	31.4	31.4	31.4	27.9	24.5	20.9	20.9
87.5°	10.5	14.0	10.5	10.5	10.5	10.5	10.5	10.5	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3
2.5°	2622.8	2619.3	2615.8	2615.8	2615.8	2615.8	2615.8	2612.3	2608.9	2608.9	2608.9
5°	2615.8	2615.8	2615.8	2612.3	2608.9	2608.9	2601.8	2598.4	2594.9	2591.3	2587.9
7.5°	2608.9	2601.8	2598.4	2594.9	2591.3	2591.3	2584.4	2577.5	2577.5	2570.5	2563.5
10°	2587.9	2584.4	2577.5	2570.5	2567.0	2563.5	2556.5	2546.0	2542.6	2535.6	2528.6
12.5°	2563.5	2556.5	2549.6	2535.6	2532.1	2528.6	2514.6	2504.3	2497.2	2493.8	2476.3
15°	2532.1	2518.1	2507.7	2490.3	2486.7	2479.8	2469.3	2458.8	2444.9	2434.5	2427.4
17.5°	2476.3	2462.4	2444.9	2427.4	2420.5	2420.5	2403.1	2389.2	2371.6	2364.7	2350.7
20°	2410.0	2392.6	2378.7	2357.7	2347.3	2336.8	2326.3	2305.4	2291.5	2281.0	2263.5
22.5°	2333.3	2308.9	2291.5	2270.6	2253.1	2242.7	2225.1	2207.7	2190.3	2179.8	2165.9
25°	2235.6	2214.8	2186.8	2165.9	2155.5	2141.5	2120.5	2103.1	2085.7	2068.3	2061.2
27.5°	2127.6	2099.6	2075.2	2050.7	2040.4	2029.9	2005.4	1984.5	1970.6	1953.2	1946.1
30°	2009.0	1981.1	1953.2	1932.2	1921.8	1904.3	1890.3	1866.0	1848.6	1834.6	1817.1
32.5°	1872.9	1852.0	1827.6	1796.2	1789.3	1775.3	1754.3	1743.8	1722.9	1712.5	1698.5
35°	1726.4	1712.5	1688.1	1663.7	1653.2	1646.2	1628.8	1607.8	1593.9	1583.4	1576.5
37.5°	1587.0	1569.4	1545.1	1527.7	1520.6	1510.1	1489.3	1478.8	1464.8	1457.9	1443.9
40°	1436.9	1419.5	1402.1	1391.6	1381.2	1374.2	1360.2	1349.7	1335.8	1325.4	1321.9
42.5°	1290.4	1280.0	1266.1	1252.1	1248.7	1238.2	1231.1	1220.8	1210.3	1206.8	1196.3
45°	1157.9	1147.5	1133.6	1119.6	1116.0	1109.1	1105.6	1095.2	1088.2	1088.2	1088.2
47.5°	1025.4	1015.0	1001.0	994.0	997.5	983.5	983.5	980.0	973.1	973.1	976.6
50°	906.8	892.8	889.4	882.4	875.4	868.4	872.0	861.5	861.5	868.4	864.9
52.5°	795.2	781.3	777.7	770.8	767.4	767.4	763.8	763.8	760.3	763.8	763.8
55°	694.1	683.6	676.6	669.7	666.2	666.2	666.2	662.6	659.2	666.2	669.7
57.5°	603.3	599.9	593.0	582.5	579.0	575.4	572.0	572.0	572.0	572.0	575.4
60°	523.2	516.1	509.2	498.7	498.7	495.3	491.8	488.2	488.2	488.2	488.2
62.5°	453.4	442.9	432.5	425.5	422.0	418.6	415.0	408.1	408.1	408.1	408.1
65°	383.6	373.2	366.2	359.3	352.2	352.2	345.3	341.8	334.8	331.4	324.3
67.5°	317.4	310.4	303.5	293.0	289.5	286.0	279.0	275.5	265.1	261.6	258.1
70°	258.1	247.6	240.6	233.7	230.2	223.2	216.3	209.2	202.3	195.3	188.4
72.5°	202.3	191.8	184.9	177.9	170.9	170.9	160.4	153.5	143.0	136.0	125.6
75°	149.9	139.6	132.5	122.0	118.6	115.1	104.6	97.7	87.2	76.7	69.8
77.5°	101.2	94.1	87.2	76.7	69.8	69.8	59.3	52.4	45.3	34.8	31.4
80°	62.7	55.8	48.8	41.9	41.9	34.8	31.4	24.5	17.4	14.0	10.5
82.5°	34.8	31.4	27.9	20.9	20.9	17.4	14.0	10.5	6.9	3.5	3.5
85°	17.4	14.0	10.5	10.5	6.9	6.9	6.9	3.5	3.5	0.0	0.0
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3
2.5°	2605.3	2605.3	2601.8	2601.8	2601.8	2598.4	2601.8	2598.4	2598.4	2598.4	2601.8
5°	2591.3	2584.4	2584.4	2581.0	2581.0	2577.5	2581.0	2577.5	2573.9	2570.5	2573.9
7.5°	2563.5	2556.5	2553.1	2549.6	2549.6	2549.6	2546.0	2542.6	2546.0	2535.6	2542.6
10°	2525.1	2521.7	2514.6	2511.2	2507.7	2511.2	2507.7	2500.7	2500.7	2500.7	2497.2
12.5°	2476.3	2469.3	2465.9	2462.4	2455.4	2455.4	2458.8	2451.9	2451.9	2444.9	2444.9
15°	2417.1	2410.0	2403.1	2403.1	2396.1	2396.1	2392.6	2392.6	2389.2	2385.6	2385.6
17.5°	2343.8	2333.3	2326.3	2329.9	2326.3	2322.8	2322.8	2315.9	2312.3	2315.9	2315.9
20°	2256.6	2249.6	2242.7	2246.1	2239.1	2235.6	2239.1	2228.7	2232.2	2232.2	2232.2
22.5°	2158.9	2155.5	2145.0	2145.0	2137.9	2134.5	2137.9	2137.9	2141.5	2137.9	2137.9
25°	2050.7	2043.8	2036.9	2036.9	2033.3	2029.9	2033.3	2036.9	2033.3	2036.9	2036.9
27.5°	1935.8	1925.3	1925.3	1918.2	1918.2	1921.8	1918.2	1921.8	1925.3	1925.3	1932.2
30°	1810.1	1806.7	1803.1	1799.7	1799.7	1803.1	1803.1	1803.1	1806.7	1813.6	1813.6
32.5°	1691.6	1684.5	1677.6	1677.6	1684.5	1681.1	1684.5	1684.5	1691.6	1691.6	1698.5
35°	1562.5	1562.5	1555.6	1559.1	1559.1	1559.1	1559.1	1566.0	1573.0	1576.5	1583.4
37.5°	1443.9	1433.4	1436.9	1436.9	1440.5	1436.9	1447.4	1447.4	1454.4	1454.4	1461.4
40°	1314.9	1314.9	1318.3	1314.9	1318.3	1318.3	1325.4	1332.3	1335.8	1342.8	1346.2
42.5°	1192.8	1199.8	1192.8	1196.3	1199.8	1203.2	1206.8	1210.3	1224.2	1231.1	1241.6
45°	1081.2	1084.7	1088.2	1091.7	1088.2	1095.2	1098.6	1105.6	1116.0	1119.6	1123.1
47.5°	973.1	976.6	980.0	983.5	983.5	990.5	994.0	1001.0	1008.0	1011.4	1015.0
50°	868.4	875.4	878.9	878.9	882.4	889.4	896.3	896.3	903.3	913.8	917.3
52.5°	774.3	774.3	781.3	784.8	788.2	788.2	798.7	802.2	805.6	812.7	819.6
55°	669.7	680.2	683.6	683.6	690.5	697.6	701.0	704.5	704.5	718.5	718.5
57.5°	579.0	582.5	589.4	589.4	589.4	599.9	599.9	606.9	610.4	613.8	620.9
60°	488.2	495.3	495.3	498.7	495.3	502.2	505.8	512.7	516.1	519.7	523.2
62.5°	404.6	404.6	408.1	408.1	408.1	408.1	415.0	415.0	422.0	425.5	428.9
65°	324.3	324.3	324.3	324.3	324.3	324.3	324.3	324.3	327.8	327.8	334.8
67.5°	251.1	247.6	240.6	244.2	240.6	240.6	237.1	237.1	240.6	240.6	247.6
70°	181.3	177.9	170.9	170.9	167.4	163.9	160.4	157.0	153.5	153.5	153.5
72.5°	118.6	111.6	101.2	97.7	97.7	90.7	83.7	80.2	80.2	80.2	80.2
75°	59.3	52.4	45.3	41.9	41.9	34.8	38.4	34.8	34.8	34.8	34.8
77.5°	24.5	17.4	14.0	14.0	14.0	10.5	10.5	10.5	10.5	10.5	10.5
80°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585058

CATALOG NUMBER: HCC8S60D010MB-HM86080827-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3	2612.3
2.5°	2598.4	2598.4	2591.3	2594.9	2594.9	2594.9	2594.9	2594.9
5°	2567.0	2570.5	2567.0	2570.5	2570.5	2567.0	2567.0	2567.0
7.5°	2535.6	2539.1	2535.6	2539.1	2539.1	2539.1	2535.6	2535.6
10°	2497.2	2497.2	2497.2	2497.2	2497.2	2493.8	2497.2	2497.2
12.5°	2444.9	2444.9	2444.9	2448.4	2448.4	2444.9	2444.9	2441.4
15°	2389.2	2382.1	2385.6	2389.2	2385.6	2385.6	2385.6	2385.6
17.5°	2312.3	2315.9	2312.3	2312.3	2312.3	2312.3	2315.9	2312.3
20°	2232.2	2232.2	2235.6	2232.2	2232.2	2232.2	2232.2	2228.7
22.5°	2141.5	2137.9	2137.9	2141.5	2141.5	2137.9	2141.5	2141.5
25°	2040.4	2043.8	2040.4	2040.4	2043.8	2043.8	2043.8	2040.4
27.5°	1932.2	1935.8	1939.2	1935.8	1935.8	1935.8	1939.2	1942.7
30°	1820.6	1827.6	1820.6	1820.6	1827.6	1824.1	1827.6	1827.6
32.5°	1702.1	1712.5	1705.5	1712.5	1712.5	1716.0	1712.5	1716.0
35°	1583.4	1593.9	1593.9	1593.9	1597.3	1600.9	1600.9	1597.3
37.5°	1471.9	1475.3	1475.3	1482.3	1485.8	1489.3	1489.3	1485.8
40°	1356.7	1363.7	1367.2	1367.2	1367.2	1374.2	1381.2	1374.2
42.5°	1245.1	1248.7	1252.1	1252.1	1259.1	1262.5	1266.1	1266.1
45°	1137.0	1143.9	1147.5	1151.0	1154.4	1161.5	1157.9	1164.9
47.5°	1025.4	1035.9	1039.3	1042.8	1049.8	1053.3	1056.7	1060.3
50°	924.2	931.3	931.3	938.2	948.7	948.7	955.6	959.2
52.5°	823.1	826.6	830.1	833.6	840.6	847.5	847.5	854.6
55°	725.5	728.9	728.9	732.4	735.9	749.8	753.4	753.4
57.5°	624.3	624.3	631.3	634.7	638.3	645.2	645.2	645.2
60°	526.6	530.1	530.1	533.7	537.1	544.1	547.6	544.1
62.5°	428.9	432.5	432.5	436.0	442.9	446.5	442.9	442.9
65°	338.3	341.8	341.8	345.3	352.2	352.2	348.8	352.2
67.5°	247.6	247.6	247.6	247.6	247.6	247.6	247.6	247.6
70°	157.0	153.5	149.9	153.5	153.5	153.5	149.9	157.0
72.5°	76.7	80.2	80.2	80.2	80.2	80.2	80.2	76.7
75°	34.8	34.8	31.4	31.4	31.4	34.8	34.8	31.4
77.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)