

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585077

Luminaire Tested: **HCC8W60D010BZ-HM86080830-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010BZ-HM86080830-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5185.1 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585077
CATALOG NUMBER: HCC8W60D010BZ-HM86080830-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P585077
 CATALOG NUMBER: HCC8W60D010BZ-HM86080830-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																																				
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																																				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																																				
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																																				
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62																																				
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56																																				
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																																				
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																																				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																																				
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97150
5°	96342
10°	95070
15°	96155
20°	103841
25°	113555
30°	112179
35°	93056
40°	54770
45°	35781
50°	27738
55°	18429
60°	8967
65°	2780
70°	938
75°	822
80°	622
85°	1238



TEST NUMBER: P585077
 CATALOG NUMBER: HCC8W60D010BZ-HM86080830-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.8	5.7
10°-20°	865.3	16.7
20°-30°	1513.0	29.2
30°-40°	1471.7	28.4
40°-50°	669.3	12.9
50°-60°	310.3	6.0
60°-70°	52.0	1.0
70°-80°	6.4	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2673.0	51.6
0°-40°	4144.8	79.9
0°-60°	5124.4	98.8
0°-90°	5185.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5185.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3150	
5°	3112	295
15°	3012	865
25°	3338	1513
35°	2472	1472
45°	820	669
55°	343	310
65°	38	52
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P585077
CATALOG NUMBER: HCC8W60D010BZ-HM86080830-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3150.5
2.5°	3143.6
5°	3112.4
7.5°	3077.7
10°	3036.2
12.5°	3005.1
15°	3012.0
17.5°	3067.4
20°	3164.4
22.5°	3275.1
25°	3337.5
27.5°	3302.9
30°	3150.5
32.5°	2884.0
35°	2472.0
37.5°	1904.1
40°	1360.6
42.5°	1014.4
45°	820.5
47.5°	692.4
50°	578.2
52.5°	460.4
55°	342.8
57.5°	235.4
60°	145.4
62.5°	79.6
65°	38.1
67.5°	17.3
70°	10.4
72.5°	6.9
75°	6.9
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)