

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584929

Luminaire Tested: **HCC8W55D010SL-HM82555827-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010SL-HM82555827-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4524.2 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584929
CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584929

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67		
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59		
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47		
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43		
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39		
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	74898	74898	74898
5°	77995	74732	71588
10°	80600	73780	68097
15°	82639	72091	64560
20°	82803	69099	61358
25°	81403	64727	58185
30°	77049	59727	55457
35°	70252	53711	52073
40°	61089	47351	48083
45°	52409	41006	44015
50°	44759	35356	39539
55°	39235	30450	34354
60°	34931	25970	28881
65°	30988	21189	23050
70°	27499	15715	13091
75°	22923	8221	3896
80°	18042	2575	639
85°	12843	1274	0



TEST NUMBER: P584929
 CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.9	5.1
10°-20°	641.5	14.2
20°-30°	907.9	20.1
30°-40°	949.9	21.0
40°-50°	792.3	17.5
50°-60°	561.8	12.4
60°-70°	323.6	7.2
70°-80°	104.1	2.3
80°-90°	14.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1778.3	39.3
0°-40°	2728.1	60.3
0°-60°	4082.2	90.2
0°-90°	4524.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4524.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2429	2429	2429	2429	2429	
5°	2520	2487	2414	2342	2313	242
15°	2589	2483	2258	2080	2022	728
25°	2392	2215	1902	1750	1710	1092
35°	1866	1703	1427	1351	1383	1157
45°	1202	1104	940	951	1009	931
55°	730	654	566	595	639	659
65°	425	356	290	290	316	425
75°	192	142	69	33	33	209
85°	36	18	4	0	0	45
90°	0	0	0	0	0	



TEST NUMBER: P584929

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9
2.5°	2479.7	2476.1	2472.5	2476.1	2472.5	2476.1	2472.5	2472.5	2468.8	2465.2	2465.2
5°	2519.7	2516.0	2516.0	2516.0	2512.4	2508.8	2508.8	2505.1	2497.9	2494.3	2487.0
7.5°	2545.0	2548.6	2548.6	2548.6	2541.4	2541.4	2534.2	2526.9	2519.7	2512.4	2501.5
10°	2574.1	2574.1	2570.4	2566.8	2559.5	2555.9	2552.3	2545.0	2534.2	2519.7	2508.8
12.5°	2585.0	2585.0	2581.3	2574.1	2570.4	2566.8	2563.2	2552.3	2537.8	2519.7	2505.1
15°	2588.6	2581.3	2577.7	2574.1	2566.8	2555.9	2555.9	2541.4	2523.3	2501.5	2483.4
17.5°	2559.5	2563.2	2555.9	2548.6	2537.8	2530.6	2519.7	2508.8	2487.0	2461.6	2443.4
20°	2523.3	2519.7	2516.0	2505.1	2490.6	2487.0	2476.1	2457.9	2439.8	2410.7	2385.3
22.5°	2465.2	2461.6	2454.3	2447.0	2432.5	2425.2	2414.3	2392.5	2367.2	2338.1	2309.1
25°	2392.5	2385.3	2374.5	2359.9	2349.0	2341.8	2327.2	2305.4	2276.4	2243.7	2214.6
27.5°	2276.4	2287.3	2280.0	2258.2	2247.3	2232.8	2229.1	2200.2	2174.8	2142.1	2109.4
30°	2163.9	2163.9	2153.0	2142.1	2123.9	2113.0	2098.5	2076.7	2051.2	2011.4	1986.0
32.5°	2022.3	2018.7	2004.1	2000.5	1986.0	1964.2	1960.5	1931.5	1906.0	1877.1	1844.4
35°	1866.2	1858.9	1844.4	1833.5	1826.2	1815.3	1804.4	1779.0	1753.5	1724.5	1702.8
37.5°	1688.3	1688.3	1684.6	1666.5	1659.2	1651.9	1641.0	1615.6	1601.1	1572.0	1550.3
40°	1517.6	1514.0	1503.1	1499.5	1492.2	1481.3	1474.0	1459.5	1437.7	1415.9	1394.1
42.5°	1350.6	1354.2	1339.7	1343.3	1328.8	1321.5	1317.9	1296.1	1285.2	1263.4	1245.2
45°	1201.8	1198.1	1190.9	1187.2	1180.0	1172.7	1165.4	1154.5	1136.4	1114.6	1103.7
47.5°	1063.8	1052.9	1052.9	1049.3	1045.7	1031.1	1027.5	1016.6	1005.7	983.9	969.4
50°	933.0	933.0	933.0	929.4	918.5	914.9	907.6	896.8	885.9	871.4	849.6
52.5°	827.8	827.8	827.8	824.2	809.6	806.0	802.4	787.8	773.3	762.4	747.9
55°	729.8	733.4	729.8	722.5	711.6	711.6	700.7	693.5	678.9	668.0	653.5
57.5°	646.2	646.2	639.0	635.3	628.1	624.4	617.2	609.9	591.7	580.8	562.8
60°	566.4	562.8	562.8	555.5	548.3	541.0	537.4	526.5	519.2	501.0	486.5
62.5°	493.8	493.8	486.5	486.5	472.0	472.0	468.3	457.4	446.5	428.4	421.1
65°	424.7	424.7	421.1	417.5	406.7	403.1	399.4	388.5	377.6	366.7	355.8
67.5°	363.1	363.1	355.8	352.2	344.9	341.3	334.0	326.8	315.9	305.0	294.1
70°	305.0	301.3	297.7	294.1	286.8	283.2	275.9	268.6	257.7	250.5	239.7
72.5°	246.8	246.8	243.3	236.0	232.4	228.8	225.1	217.9	207.0	196.1	188.8
75°	192.4	192.4	192.4	185.2	177.9	174.3	174.3	167.0	159.7	148.8	141.6
77.5°	148.8	145.2	141.6	141.6	134.3	130.7	127.0	123.4	112.5	108.9	101.6
80°	101.6	105.2	101.6	98.0	94.3	90.7	90.7	83.4	79.9	72.7	65.4
82.5°	69.0	65.4	65.4	61.8	61.8	58.1	58.1	50.9	47.2	43.6	40.0
85°	36.3	36.3	32.7	32.7	32.7	29.1	29.1	25.4	25.4	21.8	18.2
87.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584929

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9
2.5°	2461.6	2454.3	2450.7	2450.7	2447.0	2443.4	2439.8	2436.1	2428.9	2428.9	2421.6
5°	2479.7	2472.5	2468.8	2457.9	2450.7	2450.7	2436.1	2432.5	2421.6	2414.3	2407.1
7.5°	2494.3	2479.7	2468.8	2457.9	2450.7	2443.4	2428.9	2414.3	2399.8	2385.3	2378.0
10°	2494.3	2479.7	2461.6	2443.4	2436.1	2428.9	2410.7	2388.9	2370.8	2356.3	2338.1
12.5°	2487.0	2465.2	2443.4	2428.9	2414.3	2403.4	2381.6	2359.9	2338.1	2309.1	2294.5
15°	2465.2	2436.1	2414.3	2388.9	2378.0	2359.9	2341.8	2309.1	2283.6	2258.2	2240.0
17.5°	2421.6	2385.3	2359.9	2334.5	2316.3	2305.4	2276.4	2247.3	2218.2	2189.3	2167.5
20°	2356.3	2323.6	2294.5	2261.8	2247.3	2232.8	2196.6	2167.5	2138.4	2105.7	2083.9
22.5°	2276.4	2243.7	2203.8	2178.4	2156.6	2138.4	2105.7	2073.0	2044.1	2015.0	1986.0
25°	2178.4	2145.7	2109.4	2069.4	2054.9	2036.8	2000.5	1967.8	1935.1	1902.4	1877.1
27.5°	2073.0	2029.6	2000.5	1956.9	1942.4	1924.2	1884.2	1848.0	1818.9	1793.5	1764.4
30°	1946.0	1913.3	1873.4	1833.5	1818.9	1800.8	1768.1	1735.4	1706.4	1677.4	1648.3
32.5°	1808.0	1775.3	1735.4	1706.4	1684.6	1670.1	1637.4	1608.3	1579.3	1550.3	1524.9
35°	1662.8	1626.5	1597.4	1568.4	1550.3	1532.2	1499.5	1474.0	1452.2	1426.8	1401.4
37.5°	1514.0	1488.6	1459.5	1426.8	1408.6	1394.1	1368.8	1339.7	1321.5	1299.7	1281.6
40°	1368.8	1339.7	1314.3	1285.2	1270.7	1259.8	1234.4	1212.7	1194.5	1176.3	1165.4
42.5°	1219.9	1194.5	1169.1	1150.9	1140.0	1129.1	1110.9	1085.5	1074.6	1056.6	1045.7
45°	1081.9	1060.2	1042.0	1016.6	1009.3	1002.1	980.3	962.1	951.2	940.3	933.0
47.5°	951.2	936.7	914.9	900.4	889.5	882.3	867.7	853.2	842.3	835.0	827.8
50°	838.7	820.5	806.0	791.5	784.2	773.3	758.8	751.5	744.2	737.0	737.0
52.5°	733.4	715.3	700.7	689.8	682.6	675.3	664.4	660.8	653.5	653.5	649.9
55°	635.3	624.4	609.9	595.4	591.7	588.1	580.8	573.6	570.1	566.4	570.1
57.5°	551.9	541.0	526.5	515.6	511.9	508.3	504.7	497.4	493.8	493.8	493.8
60°	475.6	464.7	453.8	442.9	442.9	435.6	432.0	428.4	424.7	421.1	421.1
62.5°	406.7	395.8	384.9	377.6	374.0	370.4	363.1	359.5	355.8	355.8	352.2
65°	344.9	330.4	326.8	315.9	312.2	308.6	305.0	297.7	294.1	290.4	286.8
67.5°	283.2	275.9	265.0	257.7	254.1	250.5	246.8	239.7	236.0	232.4	225.1
70°	228.8	221.5	214.2	207.0	203.3	199.7	192.4	185.2	181.5	174.3	163.4
72.5°	177.9	170.6	163.4	156.1	152.5	148.8	141.6	134.3	127.0	119.8	112.5
75°	134.3	127.0	116.1	108.9	105.2	105.2	94.3	87.1	79.9	69.0	61.8
77.5°	94.3	83.4	79.9	72.7	69.0	61.8	54.5	47.2	40.0	36.3	29.1
80°	61.8	54.5	47.2	43.6	40.0	36.3	32.7	25.4	18.2	14.5	10.9
82.5°	36.3	32.7	29.1	25.4	21.8	18.2	14.5	14.5	10.9	7.3	3.6
85°	18.2	14.5	10.9	10.9	7.3	7.3	7.3	3.6	3.6	3.6	3.6
87.5°	7.3	3.6	3.6	3.6	3.6	3.6	3.6	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584929

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9
2.5°	2418.0	2414.3	2410.7	2407.1	2407.1	2399.8	2399.8	2396.2	2388.9	2385.3	2385.3
5°	2396.2	2385.3	2378.0	2374.5	2370.8	2359.9	2356.3	2349.0	2341.8	2334.5	2330.9
7.5°	2363.6	2345.4	2338.1	2334.5	2323.6	2312.7	2305.4	2294.5	2283.6	2272.7	2269.1
10°	2323.6	2305.4	2287.3	2280.0	2269.1	2261.8	2247.3	2232.8	2221.9	2211.0	2200.2
12.5°	2272.7	2250.9	2232.8	2225.5	2214.6	2200.2	2178.4	2171.1	2153.0	2145.7	2131.2
15°	2214.6	2189.3	2171.1	2160.2	2149.3	2127.5	2113.0	2098.5	2080.3	2073.0	2058.5
17.5°	2142.1	2113.0	2094.8	2083.9	2076.7	2058.5	2036.8	2018.7	2000.5	1993.2	1982.3
20°	2054.9	2036.8	2011.4	2000.5	1993.2	1971.4	1949.6	1942.4	1927.8	1913.3	1902.4
22.5°	1956.9	1938.7	1913.3	1902.4	1898.8	1880.7	1862.5	1851.6	1840.7	1829.8	1818.9
25°	1855.3	1833.5	1811.7	1804.4	1797.1	1782.6	1768.1	1760.8	1749.9	1742.6	1735.4
27.5°	1746.3	1724.5	1706.4	1695.5	1688.3	1677.4	1670.1	1662.8	1655.6	1648.3	1644.7
30°	1630.1	1608.3	1593.8	1586.5	1579.3	1575.6	1564.7	1561.1	1557.5	1550.3	1554.0
32.5°	1514.0	1495.8	1481.3	1470.4	1470.4	1463.1	1459.5	1459.5	1455.9	1455.9	1455.9
35°	1386.9	1376.0	1365.1	1361.5	1357.9	1354.2	1350.6	1354.2	1350.6	1354.2	1357.9
37.5°	1270.7	1259.8	1252.5	1248.9	1245.2	1248.9	1245.2	1245.2	1248.9	1256.1	1259.8
40°	1150.9	1143.6	1136.4	1140.0	1136.4	1136.4	1136.4	1147.3	1150.9	1154.5	1158.2
42.5°	1038.4	1031.1	1027.5	1027.5	1031.1	1027.5	1034.8	1038.4	1045.7	1056.6	1063.8
45°	929.4	925.8	925.8	929.4	925.8	933.0	933.0	940.3	951.2	958.5	965.7
47.5°	827.8	827.8	827.8	831.4	831.4	835.0	842.3	845.9	853.2	860.5	867.7
50°	733.4	737.0	740.6	740.6	740.6	747.9	755.1	758.8	762.4	766.0	776.9
52.5°	649.9	653.5	653.5	657.1	660.8	664.4	668.0	675.3	678.9	686.2	689.8
55°	570.1	570.1	577.2	580.8	580.8	580.8	588.1	588.1	595.4	599.0	606.3
57.5°	493.8	497.4	497.4	501.0	501.0	504.7	508.3	511.9	515.6	519.2	522.8
60°	421.1	421.1	421.1	424.7	428.4	432.0	428.4	435.6	435.6	442.9	446.5
62.5°	352.2	355.8	355.8	355.8	355.8	355.8	355.8	359.5	363.1	366.7	370.4
65°	286.8	286.8	286.8	283.2	286.8	283.2	286.8	290.4	290.4	294.1	297.7
67.5°	221.5	221.5	214.2	214.2	217.9	217.9	217.9	217.9	214.2	221.5	221.5
70°	159.7	156.1	152.5	148.8	148.8	145.2	145.2	141.6	141.6	141.6	141.6
72.5°	105.2	98.0	90.7	87.1	83.4	83.4	76.3	72.7	76.3	76.3	76.3
75°	54.5	47.2	43.6	40.0	36.3	36.3	32.7	32.7	32.7	32.7	32.7
77.5°	21.8	18.2	14.5	14.5	10.9	10.9	10.9	10.9	10.9	10.9	10.9
80°	7.3	7.3	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	3.6	0.0	0.0	3.6	0.0	3.6	3.6	3.6	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584929

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9	2428.9
2.5°	2381.6	2381.6	2378.0	2381.6	2374.5	2378.0	2374.5	2374.5
5°	2327.2	2320.0	2320.0	2320.0	2316.3	2316.3	2312.7	2312.7
7.5°	2261.8	2258.2	2254.6	2250.9	2247.3	2243.7	2243.7	2243.7
10°	2196.6	2189.3	2189.3	2185.7	2178.4	2174.8	2174.8	2174.8
12.5°	2120.3	2116.6	2113.0	2113.0	2098.5	2102.1	2098.5	2098.5
15°	2047.6	2044.1	2044.1	2033.2	2025.9	2025.9	2025.9	2022.3
17.5°	1971.4	1967.8	1964.2	1956.9	1949.6	1949.6	1946.0	1949.6
20°	1891.5	1887.9	1880.7	1880.7	1877.1	1873.4	1866.2	1869.8
22.5°	1811.7	1804.4	1800.8	1800.8	1797.1	1797.1	1789.9	1789.9
25°	1728.1	1724.5	1720.8	1724.5	1717.3	1717.3	1710.1	1710.1
27.5°	1641.0	1637.4	1637.4	1637.4	1633.8	1637.4	1633.8	1633.8
30°	1554.0	1554.0	1550.3	1550.3	1554.0	1550.3	1554.0	1557.5
32.5°	1459.5	1459.5	1463.1	1463.1	1466.8	1466.8	1466.8	1466.8
35°	1361.5	1368.8	1368.8	1372.4	1376.0	1379.7	1379.7	1383.3
37.5°	1270.7	1274.3	1277.9	1281.6	1288.8	1288.8	1288.8	1288.8
40°	1172.7	1176.3	1183.6	1180.0	1194.5	1198.1	1194.5	1194.5
42.5°	1071.0	1078.2	1081.9	1089.1	1092.8	1100.0	1103.7	1103.7
45°	976.6	980.3	987.5	994.8	998.4	1009.3	1009.3	1009.3
47.5°	878.6	885.9	889.5	896.8	900.4	911.2	914.9	911.2
50°	784.2	791.5	798.7	798.7	809.6	813.3	820.5	824.2
52.5°	693.5	697.1	704.4	708.0	715.3	722.5	726.2	729.8
55°	606.3	609.9	617.2	617.2	628.1	631.7	639.0	639.0
57.5°	526.5	530.1	537.4	533.7	541.0	548.3	548.3	544.6
60°	450.2	450.2	450.2	457.4	461.1	464.7	468.3	468.3
62.5°	370.4	377.6	381.3	381.3	384.9	388.5	388.5	384.9
65°	297.7	305.0	308.6	308.6	312.2	312.2	312.2	315.9
67.5°	225.1	225.1	225.1	228.8	225.1	225.1	225.1	225.1
70°	141.6	141.6	141.6	141.6	137.9	141.6	141.6	145.2
72.5°	76.3	76.3	76.3	76.3	76.3	76.3	76.3	76.3
75°	32.7	32.7	32.7	36.3	32.7	32.7	32.7	32.7
77.5°	14.5	10.9	14.5	14.5	10.9	10.9	10.9	10.9
80°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	0.0	3.6	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)