

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585071

Luminaire Tested: **HCC8W60D010MW-HM86080830-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585071  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010MW-HM86080830-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5140.2 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585071  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P585071

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	967465
5°	620552
10°	280327
15°	169143
20°	128892
25°	104087
30°	76273
35°	27620
40°	10309
45°	4679
50°	1492
55°	371
60°	216
65°	255
70°	0
75°	0
80°	622
85°	1238



TEST NUMBER: P585071  
 CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1529.0	29.7
10°-20°	1553.0	30.2
20°-30°	1390.2	27.0
30°-40°	560.0	10.9
40°-50°	91.8	1.8
50°-60°	8.4	0.2
60°-70°	3.0	0.1
70°-80°	2.3	0.0
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4472.2	87.0
0°-40°	5032.2	97.9
0°-60°	5132.4	99.8
0°-90°	5141.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5140.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	31374	
5°	20048	###
15°	5298	1553
25°	3059	1390
35°	734	560
45°	107	92
55°	7	8
65°	4	3
75°	0	2
85°	4	3
90°	0	



TEST NUMBER: P585071  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	31374.2
0.5°	31277.3
1°	30872.4
1.5°	30221.8
2°	29235.6
2.5°	28069.3
3°	26608.9
3.5°	25006.6
4°	23421.6
4.5°	21646.3
5°	20047.5
5.5°	18306.8
6°	16894.9
6.5°	15424.1
7°	14268.3
7.5°	13046.7
8°	12063.8
8.5°	11077.5
9°	10337.0
9.5°	9520.3
10°	8952.7
12.5°	6602.9
15°	5298.3
17.5°	4526.5
20°	3927.8
22.5°	3450.3
25°	3059.2
27.5°	2668.2
30°	2142.1
32.5°	1377.4
35°	733.7
37.5°	404.8
40°	256.1
42.5°	169.5
45°	107.3
47.5°	65.7
50°	31.1
52.5°	10.4
55°	6.9
57.5°	3.5
60°	3.5
62.5°	3.5
65°	3.5



TEST NUMBER: P585071  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	3.5
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.5
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)