

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585075

Luminaire Tested: **HCC8W60D010MW-HM86080830-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010MW-HM86080830-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4928.9 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585075
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P585075

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79971	79971	79971
5°	81025	79636	78883
10°	81856	78819	77626
15°	82683	77154	75609
20°	82261	74310	72607
25°	80348	69862	68919
30°	76312	64847	64601
35°	69476	59177	59696
40°	60908	52966	54914
45°	52549	47111	50434
50°	46015	41362	45675
55°	40762	35558	40208
60°	36726	29899	33309
65°	33097	23998	25516
70°	29031	17482	14047
75°	24746	9067	3705
80°	19072	2451	622
85°	12242	0	0



TEST NUMBER: P585075
 CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.7	5.0
10°-20°	687.9	14.0
20°-30°	976.3	19.8
30°-40°	1027.7	20.9
40°-50°	874.3	17.7
50°-60°	631.8	12.8
60°-70°	359.3	7.3
70°-80°	113.2	2.3
80°-90°	13.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1908.9	38.7
0°-40°	2936.6	59.6
0°-60°	4442.6	90.1
0°-90°	4928.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4928.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2593	2593	2593	2593	2593	
5°	2618	2604	2573	2555	2548	250
15°	2590	2524	2417	2372	2368	729
25°	2362	2244	2053	2019	2026	1082
35°	1846	1738	1572	1562	1586	1148
45°	1205	1160	1080	1108	1156	937
55°	758	703	661	699	748	684
65°	454	391	329	326	350	450
75°	208	159	76	35	31	224
85°	35	21	0	0	0	45
90°	0	0	0	0	0	



TEST NUMBER: P585075

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4
2.5°	2607.3	2610.7	2603.8	2603.8	2610.7	2603.8	2607.3	2607.3	2603.8	2603.8	2600.3
5°	2617.6	2614.2	2614.2	2614.2	2617.6	2610.7	2607.3	2610.7	2603.8	2603.8	2603.8
7.5°	2621.1	2621.1	2617.6	2614.2	2614.2	2614.2	2610.7	2607.3	2603.8	2596.9	2593.4
10°	2614.2	2614.2	2617.6	2610.7	2610.7	2603.8	2603.8	2596.9	2596.9	2590.0	2579.6
12.5°	2607.3	2603.8	2603.8	2596.9	2596.9	2590.0	2590.0	2579.6	2576.1	2565.7	2555.4
15°	2590.0	2586.5	2579.6	2576.1	2572.7	2569.2	2562.3	2558.8	2548.4	2534.6	2524.1
17.5°	2555.4	2551.9	2548.4	2541.5	2534.6	2531.1	2527.7	2517.2	2503.3	2493.0	2475.7
20°	2506.8	2503.3	2503.3	2493.0	2489.5	2479.1	2475.7	2461.8	2451.4	2430.7	2416.8
22.5°	2441.1	2444.5	2437.6	2430.7	2423.8	2413.4	2406.5	2392.6	2375.3	2354.6	2337.1
25°	2361.5	2364.9	2358.0	2351.0	2340.6	2333.7	2326.8	2306.0	2288.7	2264.5	2243.7
27.5°	2261.0	2261.0	2261.0	2254.1	2236.8	2233.3	2226.4	2205.6	2181.4	2160.5	2139.8
30°	2143.2	2139.8	2139.8	2129.4	2122.5	2108.6	2098.3	2081.0	2063.7	2039.4	2015.2
32.5°	2001.3	2004.8	1994.3	1987.4	1977.0	1977.0	1963.2	1949.4	1928.6	1904.4	1880.2
35°	1845.6	1849.0	1842.1	1838.6	1821.2	1817.8	1814.3	1797.0	1783.2	1765.9	1738.2
37.5°	1686.3	1682.8	1679.4	1679.4	1669.0	1662.0	1655.1	1644.6	1623.9	1610.0	1596.2
40°	1513.1	1513.1	1513.1	1509.7	1506.2	1499.3	1495.8	1488.9	1475.0	1461.1	1450.7
42.5°	1357.3	1357.3	1353.9	1350.4	1343.5	1346.9	1340.0	1333.1	1319.3	1308.9	1301.8
45°	1205.0	1205.0	1205.0	1208.4	1201.5	1191.1	1191.1	1184.2	1177.3	1170.4	1160.0
47.5°	1069.9	1080.3	1073.4	1069.9	1073.4	1059.5	1059.5	1052.6	1045.7	1038.8	1024.9
50°	959.2	959.2	959.2	952.1	948.7	948.7	938.3	931.4	927.9	921.0	907.1
52.5°	858.7	851.8	851.8	848.3	844.9	837.9	837.9	831.0	817.2	810.3	799.9
55°	758.2	758.2	754.8	751.3	747.9	744.4	740.9	730.6	723.6	713.3	702.9
57.5°	668.3	675.2	671.7	664.8	657.9	657.9	651.0	644.1	633.7	623.3	612.9
60°	595.5	592.0	592.0	588.6	581.7	578.2	574.7	564.4	554.0	543.6	533.2
62.5°	519.4	519.4	519.4	512.5	505.5	502.1	498.6	491.7	477.9	467.5	460.6
65°	453.6	450.2	446.7	443.3	439.8	432.8	429.3	422.4	412.0	401.6	391.2
67.5°	387.8	384.3	384.3	380.9	370.5	367.0	367.0	356.6	346.3	335.9	325.5
70°	322.0	322.0	322.0	315.1	311.6	308.2	304.7	297.8	287.4	277.0	266.7
72.5°	266.7	263.2	263.2	259.6	249.2	245.8	242.3	235.4	225.0	218.1	211.2
75°	207.7	207.7	204.3	200.8	197.3	193.9	190.4	183.5	173.1	162.7	159.3
77.5°	159.3	155.8	155.8	152.4	145.4	142.0	142.0	135.1	124.7	117.8	110.8
80°	107.4	110.8	107.4	103.9	100.5	97.0	93.5	90.1	83.0	76.1	69.2
82.5°	65.7	69.2	65.7	65.7	62.3	58.8	58.8	51.9	48.4	45.0	41.5
85°	34.6	34.6	34.6	34.6	31.1	31.1	31.1	27.7	24.2	20.8	20.8
87.5°	10.4	13.8	10.4	10.4	10.4	10.4	10.4	10.4	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585075

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4
2.5°	2603.8	2600.3	2596.9	2596.9	2596.9	2596.9	2596.9	2593.4	2590.0	2590.0	2590.0
5°	2596.9	2596.9	2596.9	2593.4	2590.0	2590.0	2583.0	2579.6	2576.1	2572.7	2569.2
7.5°	2590.0	2583.0	2579.6	2576.1	2572.7	2572.7	2565.7	2558.8	2558.8	2551.9	2545.0
10°	2569.2	2565.7	2558.8	2551.9	2548.4	2545.0	2538.1	2527.7	2524.1	2517.2	2510.3
12.5°	2545.0	2538.1	2531.1	2517.2	2513.7	2510.3	2496.4	2486.0	2479.1	2475.7	2458.4
15°	2513.7	2499.9	2489.5	2472.2	2468.7	2461.8	2451.4	2441.1	2427.2	2416.8	2409.9
17.5°	2458.4	2444.5	2427.2	2409.9	2403.0	2403.0	2385.7	2371.9	2354.6	2347.5	2333.7
20°	2392.6	2375.3	2361.5	2340.6	2330.2	2319.8	2309.5	2288.7	2274.9	2264.5	2247.2
22.5°	2316.4	2292.2	2274.9	2254.1	2236.8	2226.4	2209.1	2191.8	2174.4	2164.0	2150.2
25°	2219.5	2198.7	2170.9	2150.2	2139.8	2125.9	2105.2	2087.9	2070.6	2053.3	2046.4
27.5°	2112.1	2084.4	2060.2	2036.0	2025.6	2015.2	1990.9	1970.1	1956.3	1939.0	1932.1
30°	1994.3	1966.7	1939.0	1918.2	1907.8	1890.5	1876.7	1852.5	1835.2	1821.2	1803.9
32.5°	1859.4	1838.6	1814.3	1783.2	1776.2	1762.4	1741.6	1731.3	1710.5	1700.1	1686.3
35°	1714.0	1700.1	1675.9	1651.6	1641.2	1634.3	1617.0	1596.2	1582.3	1572.0	1565.0
37.5°	1575.4	1558.1	1533.9	1516.6	1509.7	1499.3	1478.4	1468.0	1454.2	1447.3	1433.4
40°	1426.5	1409.2	1391.9	1381.5	1371.2	1364.2	1350.4	1340.0	1326.2	1315.8	1312.3
42.5°	1281.1	1270.7	1256.9	1243.0	1239.6	1229.2	1222.3	1211.9	1201.5	1198.0	1187.7
45°	1149.6	1139.2	1125.3	1111.4	1108.0	1101.0	1097.6	1087.2	1080.3	1080.3	1080.3
47.5°	1018.0	1007.6	993.8	986.8	990.3	976.5	976.5	973.0	966.1	966.1	969.5
50°	900.2	886.4	882.9	876.0	869.1	862.2	865.6	855.2	855.2	862.2	858.7
52.5°	789.5	775.5	772.1	765.2	761.7	761.7	758.2	758.2	754.8	758.2	758.2
55°	689.0	678.7	671.7	664.8	661.4	661.4	661.4	657.9	654.4	661.4	664.8
57.5°	599.0	595.5	588.6	578.2	574.7	571.3	567.8	567.8	567.8	567.8	571.3
60°	519.4	512.5	505.5	495.2	495.2	491.7	488.2	484.8	484.8	484.8	484.8
62.5°	450.2	439.8	429.3	422.4	418.9	415.5	412.0	405.1	405.1	405.1	405.1
65°	380.9	370.5	363.6	356.6	349.7	349.7	342.8	339.3	332.4	328.9	322.0
67.5°	315.1	308.2	301.3	290.9	287.4	284.0	277.0	273.6	263.2	259.6	256.2
70°	256.2	245.8	238.9	231.9	228.5	221.6	214.6	207.7	200.8	193.9	187.0
72.5°	200.8	190.4	183.5	176.6	169.7	169.7	159.3	152.4	142.0	135.1	124.7
75°	148.9	138.5	131.6	121.2	117.8	114.3	103.9	97.0	86.5	76.1	69.2
77.5°	100.5	93.5	86.5	76.1	69.2	69.2	58.8	51.9	45.0	34.6	31.1
80°	62.3	55.4	48.4	41.5	41.5	34.6	31.1	24.2	17.3	13.8	10.4
82.5°	34.6	31.1	27.7	20.8	20.8	17.3	13.8	10.4	6.9	3.5	3.5
85°	17.3	13.8	10.4	10.4	6.9	6.9	6.9	3.5	3.5	0.0	0.0
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585075

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4
2.5°	2586.5	2586.5	2583.0	2583.0	2583.0	2579.6	2583.0	2579.6	2579.6	2579.6	2583.0
5°	2572.7	2565.7	2565.7	2562.3	2562.3	2558.8	2562.3	2558.8	2555.4	2551.9	2555.4
7.5°	2545.0	2538.1	2534.6	2531.1	2531.1	2531.1	2527.7	2524.1	2527.7	2517.2	2524.1
10°	2506.8	2503.3	2496.4	2493.0	2489.5	2493.0	2489.5	2482.6	2482.6	2482.6	2479.1
12.5°	2458.4	2451.4	2448.0	2444.5	2437.6	2437.6	2441.1	2434.1	2434.1	2427.2	2427.2
15°	2399.5	2392.6	2385.7	2385.7	2378.8	2378.8	2375.3	2375.3	2371.9	2368.4	2368.4
17.5°	2326.8	2316.4	2309.5	2312.9	2309.5	2306.0	2306.0	2299.1	2295.6	2299.1	2299.1
20°	2240.2	2233.3	2226.4	2229.9	2222.9	2219.5	2222.9	2212.6	2216.0	2216.0	2216.0
22.5°	2143.2	2139.8	2129.4	2129.4	2122.5	2119.0	2122.5	2122.5	2125.9	2122.5	2122.5
25°	2036.0	2029.1	2022.1	2022.1	2018.7	2015.2	2018.7	2022.1	2018.7	2022.1	2022.1
27.5°	1921.7	1911.3	1911.3	1904.4	1904.4	1907.8	1904.4	1907.8	1911.3	1911.3	1918.2
30°	1797.0	1793.5	1790.1	1786.6	1786.6	1790.1	1790.1	1790.1	1793.5	1800.5	1800.5
32.5°	1679.4	1672.4	1665.5	1665.5	1672.4	1669.0	1672.4	1672.4	1679.4	1679.4	1686.3
35°	1551.2	1551.2	1544.3	1547.7	1547.7	1547.7	1547.7	1554.7	1561.6	1565.0	1572.0
37.5°	1433.4	1423.1	1426.5	1426.5	1430.0	1426.5	1436.9	1436.9	1443.8	1443.8	1450.7
40°	1305.3	1305.3	1308.9	1305.3	1308.9	1308.9	1315.8	1322.7	1326.2	1333.1	1336.6
42.5°	1184.2	1191.1	1184.2	1187.7	1191.1	1194.6	1198.0	1201.5	1215.3	1222.3	1232.6
45°	1073.4	1076.8	1080.3	1083.7	1080.3	1087.2	1090.7	1097.6	1108.0	1111.4	1114.9
47.5°	966.1	969.5	973.0	976.5	976.5	983.4	986.8	993.8	1000.7	1004.2	1007.6
50°	862.2	869.1	872.5	872.5	876.0	882.9	889.8	889.8	896.8	907.1	910.6
52.5°	768.6	768.6	775.5	779.0	782.5	782.5	793.0	796.4	799.9	806.8	813.7
55°	664.8	675.2	678.7	678.7	685.6	692.5	696.0	699.4	699.4	713.3	713.3
57.5°	574.7	578.2	585.1	585.1	585.1	595.5	595.5	602.4	605.9	609.3	616.4
60°	484.8	491.7	491.7	495.2	491.7	498.6	502.1	509.0	512.5	515.9	519.4
62.5°	401.6	401.6	405.1	405.1	405.1	405.1	412.0	412.0	418.9	422.4	425.8
65°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	325.5	325.5	332.4
67.5°	249.2	245.8	238.9	242.3	238.9	238.9	235.4	235.4	238.9	238.9	245.8
70°	180.0	176.6	169.7	169.7	166.2	162.7	159.3	155.8	152.4	152.4	152.4
72.5°	117.8	110.8	100.5	97.0	97.0	90.1	83.0	79.6	79.6	79.6	79.6
75°	58.8	51.9	45.0	41.5	41.5	34.6	38.1	34.6	34.6	34.6	34.6
77.5°	24.2	17.3	13.8	13.8	13.8	10.4	10.4	10.4	10.4	10.4	10.4
80°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585075

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4	2593.4
2.5°	2579.6	2579.6	2572.7	2576.1	2576.1	2576.1	2576.1	2576.1
5°	2548.4	2551.9	2548.4	2551.9	2551.9	2548.4	2548.4	2548.4
7.5°	2517.2	2520.6	2517.2	2520.6	2520.6	2520.6	2517.2	2517.2
10°	2479.1	2479.1	2479.1	2479.1	2479.1	2475.7	2479.1	2479.1
12.5°	2427.2	2427.2	2427.2	2430.7	2430.7	2427.2	2427.2	2423.8
15°	2371.9	2364.9	2368.4	2371.9	2368.4	2368.4	2368.4	2368.4
17.5°	2295.6	2299.1	2295.6	2295.6	2295.6	2295.6	2299.1	2295.6
20°	2216.0	2216.0	2219.5	2216.0	2216.0	2216.0	2216.0	2212.6
22.5°	2125.9	2122.5	2122.5	2125.9	2125.9	2122.5	2125.9	2125.9
25°	2025.6	2029.1	2025.6	2025.6	2029.1	2029.1	2029.1	2025.6
27.5°	1918.2	1921.7	1925.1	1921.7	1921.7	1921.7	1925.1	1928.6
30°	1807.4	1814.3	1807.4	1807.4	1814.3	1810.8	1814.3	1814.3
32.5°	1689.7	1700.1	1693.2	1700.1	1700.1	1703.6	1700.1	1703.6
35°	1572.0	1582.3	1582.3	1582.3	1585.8	1589.3	1589.3	1585.8
37.5°	1461.1	1464.6	1464.6	1471.5	1475.0	1478.4	1478.4	1475.0
40°	1346.9	1353.9	1357.3	1357.3	1357.3	1364.2	1371.2	1364.2
42.5°	1236.1	1239.6	1243.0	1243.0	1249.9	1253.4	1256.9	1256.9
45°	1128.7	1135.8	1139.2	1142.7	1146.1	1153.1	1149.6	1156.5
47.5°	1018.0	1028.4	1031.8	1035.3	1042.2	1045.7	1049.1	1052.6
50°	917.5	924.5	924.5	931.4	941.8	941.8	948.7	952.1
52.5°	817.2	820.6	824.1	827.6	834.5	841.4	841.4	848.3
55°	720.2	723.6	723.6	727.1	730.6	744.4	747.9	747.9
57.5°	619.8	619.8	626.8	630.2	633.7	640.6	640.6	640.6
60°	522.8	526.3	526.3	529.8	533.2	540.1	543.6	540.1
62.5°	425.8	429.3	429.3	432.8	439.8	443.3	439.8	439.8
65°	335.9	339.3	339.3	342.8	349.7	349.7	346.3	349.7
67.5°	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8
70°	155.8	152.4	148.9	152.4	152.4	152.4	148.9	155.8
72.5°	76.1	79.6	79.6	79.6	79.6	79.6	79.6	76.1
75°	34.6	34.6	31.1	31.1	31.1	34.6	34.6	31.1
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)