

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584931

Luminaire Tested: **HCC8W55D010SL-HM82555827-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584931
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010SL-HM82555827-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5141.5 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584931
CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584931

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87				
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57				
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50				
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45				
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37				
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33				
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78830	78830	78830
5°	81716	78568	75872
10°	84026	77882	72769
15°	85898	76509	69553
20°	86035	73523	66730
25°	84383	69436	64367
30°	80037	64391	61546
35°	72721	58642	58781
40°	63585	52620	55402
45°	55109	46871	51620
50°	48251	41636	47033
55°	42945	36896	42558
60°	38743	33143	37398
65°	34972	29142	32586
70°	31430	24559	24226
75°	27689	19468	18169
80°	23210	16124	17421
85°	18009	14152	15426



TEST NUMBER: P584931
 CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.2	4.7
10°-20°	679.3	13.2
20°-30°	970.8	18.9
30°-40°	1031.5	20.1
40°-50°	888.1	17.3
50°-60°	664.0	12.9
60°-70°	423.5	8.2
70°-80°	192.7	3.7
80°-90°	50.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1891.2	36.8
0°-40°	2922.7	56.8
0°-60°	4474.7	87.0
0°-90°	5141.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5141.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2556	2556	2556	2556	2556	
5°	2640	2604	2538	2473	2451	253
15°	2691	2600	2397	2233	2179	758
25°	2480	2324	2041	1917	1892	1135
35°	1932	1798	1558	1518	1562	1203
45°	1264	1195	1075	1104	1184	982
55°	799	734	686	744	792	718
65°	479	425	399	418	447	478
75°	232	200	163	149	152	247
85°	51	44	40	44	44	61
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584931

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4
2.5°	2603.6	2596.3	2600.0	2596.3	2600.0	2600.0	2592.7	2592.7	2592.7	2592.7	2581.8
5°	2639.9	2636.3	2636.3	2632.7	2629.0	2632.7	2629.0	2625.4	2618.1	2614.5	2603.6
7.5°	2661.7	2661.7	2661.7	2661.7	2658.1	2654.5	2650.8	2643.6	2636.3	2629.0	2621.8
10°	2683.5	2687.0	2683.5	2679.9	2676.3	2669.0	2665.4	2658.1	2647.2	2636.3	2629.0
12.5°	2694.3	2694.3	2690.7	2690.7	2683.5	2679.9	2669.0	2658.1	2647.2	2636.3	2618.1
15°	2690.7	2690.7	2687.0	2683.5	2672.6	2669.0	2661.7	2650.8	2632.7	2618.1	2600.0
17.5°	2669.0	2665.4	2658.1	2658.1	2643.6	2639.9	2632.7	2618.1	2600.0	2578.2	2556.4
20°	2621.8	2621.8	2618.1	2614.5	2600.0	2589.1	2581.8	2563.6	2549.1	2523.7	2501.9
22.5°	2556.4	2563.6	2556.4	2549.1	2530.9	2527.3	2516.4	2494.6	2472.8	2443.9	2418.4
25°	2480.1	2476.4	2472.8	2465.7	2451.1	2443.9	2429.3	2407.5	2385.7	2353.0	2324.0
27.5°	2382.1	2367.6	2367.6	2353.0	2342.1	2331.2	2324.0	2302.2	2273.1	2247.8	2211.4
30°	2247.8	2251.4	2233.2	2229.6	2211.4	2204.2	2189.6	2167.8	2142.4	2113.4	2084.3
32.5°	2102.5	2091.6	2091.6	2077.0	2062.5	2051.6	2048.0	2022.6	2000.8	1971.8	1942.7
35°	1931.8	1931.8	1920.9	1917.3	1902.7	1895.5	1884.6	1870.0	1844.6	1819.3	1797.5
37.5°	1764.8	1757.5	1753.9	1746.6	1735.7	1724.8	1724.8	1699.4	1695.8	1666.7	1637.6
40°	1579.6	1586.9	1579.6	1568.7	1565.1	1557.8	1554.2	1539.7	1528.8	1503.3	1485.2
42.5°	1423.4	1416.1	1416.1	1412.5	1398.0	1398.0	1390.8	1383.5	1365.4	1358.1	1336.3
45°	1263.7	1270.9	1260.0	1263.7	1249.1	1249.1	1249.1	1234.6	1220.1	1209.2	1194.6
47.5°	1125.7	1129.3	1129.3	1118.4	1114.8	1114.8	1107.5	1100.3	1089.4	1074.8	1063.9
50°	1005.8	1009.4	1002.2	998.5	991.3	987.6	987.6	973.1	966.0	951.4	944.2
52.5°	896.9	896.9	893.3	893.3	882.4	882.4	875.1	864.2	857.0	849.7	831.5
55°	798.8	798.8	795.2	791.6	791.6	780.7	777.0	766.1	758.9	744.5	733.6
57.5°	704.5	708.1	704.5	700.9	697.2	693.6	686.3	675.4	668.2	657.3	650.0
60°	628.2	628.2	624.6	620.9	613.7	610.0	606.4	599.1	588.2	581.0	570.1
62.5°	555.5	551.9	548.3	544.6	537.4	537.4	530.2	522.9	512.0	504.8	497.5
65°	479.3	479.3	475.7	475.7	472.1	464.8	461.2	457.5	443.0	439.4	424.8
67.5°	410.3	414.0	406.7	406.7	399.4	399.4	395.8	384.9	381.3	374.0	366.7
70°	348.6	348.6	348.6	344.9	337.7	334.0	330.4	323.1	319.6	312.3	305.1
72.5°	286.9	286.9	283.3	283.3	279.6	276.0	272.4	265.1	265.1	257.8	250.6
75°	232.4	232.4	228.8	225.1	221.5	221.5	217.9	214.2	207.0	203.3	199.7
77.5°	177.9	177.9	177.9	174.3	170.6	170.6	170.6	163.4	156.1	156.1	152.5
80°	130.7	130.7	127.0	127.0	123.4	123.4	123.4	119.8	116.1	112.5	108.9
82.5°	87.2	87.2	87.2	87.2	83.6	83.6	83.6	79.9	76.3	76.3	76.3
85°	50.9	50.9	50.9	50.9	47.2	47.2	47.2	47.2	47.2	43.6	43.6
87.5°	21.8	18.2	21.8	18.2	21.8	18.2	21.8	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584931

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4
2.5°	2585.4	2581.8	2578.2	2574.5	2574.5	2570.9	2563.6	2560.0	2556.4	2552.7	2552.7
5°	2600.0	2596.3	2589.1	2581.8	2578.2	2570.9	2563.6	2556.4	2549.1	2538.2	2534.6
7.5°	2610.9	2600.0	2592.7	2578.2	2574.5	2567.3	2556.4	2545.5	2530.9	2516.4	2505.5
10°	2610.9	2596.3	2585.4	2567.3	2560.0	2552.7	2538.2	2520.0	2501.9	2487.3	2469.3
12.5°	2603.6	2585.4	2567.3	2549.1	2538.2	2527.3	2505.5	2487.3	2465.7	2443.9	2429.3
15°	2578.2	2556.4	2534.6	2512.8	2501.9	2487.3	2465.7	2440.2	2418.4	2396.6	2371.2
17.5°	2530.9	2509.1	2483.7	2458.4	2443.9	2433.0	2400.3	2382.1	2349.4	2327.6	2305.8
20°	2469.3	2443.9	2411.2	2385.7	2367.6	2356.7	2331.2	2298.5	2273.1	2240.5	2218.7
22.5°	2389.4	2356.7	2324.0	2298.5	2280.4	2265.8	2233.2	2200.5	2178.7	2149.7	2124.2
25°	2294.9	2262.2	2229.6	2193.3	2175.1	2160.6	2131.5	2102.5	2073.4	2040.8	2019.0
27.5°	2182.4	2146.0	2117.0	2084.3	2066.1	2044.3	2011.7	1982.7	1953.6	1931.8	1902.7
30°	2058.9	2019.0	1989.9	1957.2	1939.1	1920.9	1888.2	1859.1	1833.7	1808.4	1793.9
32.5°	1910.0	1880.9	1851.9	1819.3	1804.8	1793.9	1761.2	1732.1	1703.0	1681.2	1670.3
35°	1768.4	1735.7	1710.3	1681.2	1663.1	1652.2	1623.1	1597.8	1583.3	1557.8	1543.3
37.5°	1619.5	1594.2	1565.1	1536.0	1525.1	1514.2	1492.4	1467.0	1445.2	1427.0	1419.8
40°	1463.4	1441.6	1416.1	1398.0	1387.2	1376.3	1358.1	1339.9	1325.4	1307.2	1300.0
42.5°	1314.5	1300.0	1278.2	1256.4	1245.5	1241.9	1220.1	1205.5	1198.3	1191.0	1183.7
45°	1180.2	1158.4	1143.9	1129.3	1118.4	1111.2	1100.3	1089.4	1082.1	1074.8	1067.6
47.5°	1049.4	1031.2	1016.7	1005.8	994.9	991.3	984.0	973.1	966.0	966.0	966.0
50°	929.6	915.1	900.6	893.3	889.7	882.4	875.1	871.5	867.9	867.9	867.9
52.5°	824.3	809.7	798.8	791.6	791.6	784.3	777.0	773.4	773.4	773.4	773.4
55°	726.3	715.4	708.1	700.9	693.6	690.0	690.0	690.0	686.3	686.3	690.0
57.5°	639.1	631.8	620.9	613.7	610.0	610.0	606.4	602.8	606.4	610.0	613.7
60°	559.2	551.9	548.3	537.4	537.4	537.4	533.8	533.8	533.8	537.4	541.0
62.5°	486.6	483.0	475.7	472.1	468.4	468.4	464.8	464.8	464.8	464.8	468.4
65°	421.2	414.0	406.7	406.7	406.7	403.1	403.1	395.8	399.4	399.4	395.8
67.5°	359.5	352.2	348.6	344.9	341.3	341.3	337.7	334.0	330.4	330.4	330.4
70°	301.4	294.2	294.2	286.9	286.9	283.3	279.6	279.6	276.0	272.4	268.7
72.5°	243.3	239.7	236.0	232.4	232.4	232.4	228.8	225.1	221.5	217.9	210.6
75°	192.4	192.4	185.2	181.5	181.5	177.9	174.3	170.6	167.0	163.4	159.7
77.5°	148.8	145.2	137.9	134.3	134.3	134.3	130.7	127.0	123.4	119.8	116.1
80°	108.9	105.4	101.7	98.1	98.1	98.1	94.5	94.5	90.8	90.8	90.8
82.5°	72.7	72.7	69.0	69.0	69.0	69.0	65.4	65.4	65.4	65.4	65.4
85°	43.6	43.6	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0	40.0
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P584931

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4
2.5°	2545.5	2545.5	2538.2	2534.6	2530.9	2534.6	2527.3	2523.7	2520.0	2520.0	2516.4
5°	2523.7	2520.0	2505.5	2501.9	2498.2	2494.6	2487.3	2480.1	2472.8	2469.3	2465.7
7.5°	2494.6	2483.7	2469.3	2465.7	2462.0	2451.1	2440.2	2433.0	2422.1	2418.4	2411.2
10°	2454.8	2440.2	2429.3	2418.4	2411.2	2400.3	2389.4	2378.5	2363.9	2360.3	2349.4
12.5°	2407.5	2389.4	2367.6	2363.9	2353.0	2338.5	2324.0	2313.1	2302.2	2294.9	2284.0
15°	2349.4	2331.2	2309.4	2298.5	2287.6	2276.7	2258.6	2244.1	2233.2	2222.3	2211.4
17.5°	2280.4	2258.6	2240.5	2229.6	2222.3	2204.2	2189.6	2171.5	2160.6	2149.7	2138.8
20°	2196.9	2178.7	2153.3	2142.4	2138.8	2124.2	2106.1	2098.8	2084.3	2073.4	2066.1
22.5°	2102.5	2084.3	2062.5	2055.2	2040.8	2033.5	2015.4	2008.1	2000.8	1989.9	1986.3
25°	1997.2	1979.0	1960.9	1957.2	1946.3	1939.1	1928.2	1917.3	1917.3	1906.4	1906.4
27.5°	1888.2	1870.0	1855.5	1848.2	1844.6	1837.3	1826.6	1822.9	1819.3	1815.7	1815.7
30°	1772.1	1750.3	1743.0	1739.4	1735.7	1728.5	1724.8	1717.6	1721.2	1724.8	1721.2
32.5°	1648.5	1641.3	1626.7	1619.5	1623.1	1619.5	1612.2	1619.5	1615.8	1623.1	1626.7
35°	1528.8	1521.5	1514.2	1514.2	1507.0	1507.0	1507.0	1510.6	1517.9	1521.5	1528.8
37.5°	1412.5	1401.6	1398.0	1394.4	1398.0	1398.0	1398.0	1405.2	1412.5	1419.8	1430.7
40°	1289.1	1281.8	1281.8	1281.8	1281.8	1292.7	1289.1	1296.3	1303.6	1314.5	1325.4
42.5°	1172.9	1172.9	1176.6	1176.6	1176.6	1176.6	1183.7	1194.6	1205.5	1216.4	1227.3
45°	1063.9	1063.9	1063.9	1071.2	1071.2	1074.8	1089.4	1096.6	1103.9	1114.8	1125.7
47.5°	962.3	962.3	966.0	969.5	973.1	980.4	987.6	998.5	1009.4	1016.7	1027.6
50°	867.9	871.5	878.8	886.0	886.0	889.7	900.6	907.8	915.1	926.0	929.6
52.5°	777.0	784.3	791.6	795.2	798.8	806.1	809.7	820.6	824.3	835.2	838.8
55°	693.6	697.2	708.1	711.8	711.8	719.0	726.3	733.6	744.5	744.5	751.7
57.5°	617.3	620.9	628.2	631.8	628.2	639.1	642.7	650.0	653.6	660.9	664.5
60°	541.0	548.3	551.9	551.9	555.5	559.2	566.4	566.4	573.7	581.0	581.0
62.5°	468.4	472.1	475.7	479.3	483.0	479.3	490.2	490.2	497.5	501.1	508.4
65°	399.4	403.1	403.1	406.7	406.7	410.3	410.3	414.0	417.6	424.8	428.5
67.5°	330.4	330.4	330.4	334.0	330.4	334.0	334.0	337.7	337.7	344.9	348.6
70°	268.7	265.1	261.5	261.5	261.5	261.5	257.8	261.5	261.5	265.1	265.1
72.5°	207.0	203.3	199.7	196.1	196.1	192.4	188.8	192.4	192.4	196.1	196.1
75°	156.1	148.8	148.8	148.8	145.2	145.2	145.2	148.8	148.8	148.8	152.5
77.5°	116.1	116.1	112.5	112.5	112.5	116.1	116.1	119.8	119.8	119.8	119.8
80°	87.2	90.8	90.8	90.8	90.8	94.5	94.5	94.5	94.5	98.1	98.1
82.5°	65.4	65.4	65.4	65.4	69.0	69.0	69.0	69.0	69.0	69.0	69.0
85°	40.0	43.6	43.6	40.0	43.6	43.6	43.6	43.6	43.6	43.6	43.6
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584931

CATALOG NUMBER: HCC8W55D010SL-HM82555827-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4	2556.4
2.5°	2512.8	2512.8	2512.8	2512.8	2509.1	2509.1	2509.1	2505.5
5°	2458.4	2458.4	2458.4	2451.1	2454.8	2454.8	2447.5	2451.1
7.5°	2403.9	2400.3	2396.6	2396.6	2393.0	2389.4	2385.7	2389.4
10°	2342.1	2331.2	2331.2	2327.6	2327.6	2320.3	2320.3	2324.0
12.5°	2273.1	2265.8	2265.8	2262.2	2258.6	2255.0	2251.4	2251.4
15°	2204.2	2196.9	2193.3	2189.6	2186.0	2178.7	2182.4	2178.7
17.5°	2135.1	2124.2	2124.2	2120.6	2117.0	2109.7	2109.7	2106.1
20°	2055.2	2051.6	2044.3	2048.0	2044.3	2037.2	2033.5	2033.5
22.5°	1975.4	1975.4	1971.8	1971.8	1968.1	1964.5	1960.9	1960.9
25°	1899.1	1895.5	1899.1	1899.1	1888.2	1888.2	1888.2	1891.8
27.5°	1812.0	1815.7	1812.0	1812.0	1812.0	1812.0	1815.7	1812.0
30°	1724.8	1724.8	1724.8	1728.5	1735.7	1732.1	1732.1	1728.5
32.5°	1630.4	1634.0	1634.0	1637.6	1641.3	1648.5	1648.5	1652.2
35°	1536.0	1543.3	1546.9	1543.3	1554.2	1554.2	1561.5	1561.5
37.5°	1437.9	1441.6	1448.8	1452.5	1459.7	1463.4	1467.0	1467.0
40°	1332.7	1347.2	1350.8	1354.5	1365.4	1365.4	1369.0	1376.3
42.5°	1234.6	1249.1	1252.8	1256.4	1263.7	1274.6	1270.9	1278.2
45°	1140.2	1151.1	1154.8	1158.4	1169.3	1172.9	1172.9	1183.7
47.5°	1038.5	1045.8	1049.4	1056.7	1063.9	1071.2	1078.5	1074.8
50°	936.9	947.8	955.1	958.7	969.5	973.1	976.7	980.4
52.5°	846.1	853.3	857.0	860.6	871.5	875.1	878.8	886.0
55°	758.9	762.5	769.8	766.1	777.0	780.7	784.3	791.6
57.5°	671.8	675.4	679.1	679.1	686.3	693.6	697.2	700.9
60°	588.2	595.5	599.1	599.1	599.1	606.4	606.4	606.4
62.5°	512.0	512.0	515.7	515.7	522.9	522.9	522.9	522.9
65°	432.1	435.7	439.4	439.4	446.6	443.0	450.3	446.6
67.5°	348.6	348.6	355.8	355.8	352.2	355.8	355.8	355.8
70°	265.1	265.1	268.7	268.7	268.7	268.7	268.7	268.7
72.5°	196.1	196.1	196.1	199.7	196.1	196.1	199.7	196.1
75°	152.5	152.5	152.5	152.5	152.5	152.5	152.5	152.5
77.5°	119.8	119.8	123.4	123.4	123.4	123.4	123.4	123.4
80°	98.1	98.1	98.1	98.1	101.7	98.1	98.1	98.1
82.5°	72.7	69.0	72.7	69.0	72.7	72.7	72.7	72.7
85°	43.6	43.6	43.6	43.6	43.6	43.6	43.6	43.6
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)