

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585081

Luminaire Tested: **HCC8S60D010MB-HM86080830-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585081  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MB-HM86080830-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5700.7 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585081  
CATALOG NUMBER: HCC8S60D010MB-HM86080830-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P585081  
 CATALOG NUMBER: HCC8S60D010MB-HM86080830-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90						90													
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81						81													
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73						73													
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65						65													
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59						59													
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54						54													
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49						49													
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45						45													
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41						41													
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38						38													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100119
5°	99431
10°	99171
15°	101774
20°	110177
25°	118125
30°	115487
35°	96166
40°	59081
45°	40910
50°	31216
55°	20467
60°	12809
65°	9595
70°	9674
75°	11128
80°	12288
85°	11003



TEST NUMBER: P585081  
 CATALOG NUMBER: HCC8S60D010MB-HM86080830-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	305.2	5.4
10°-20°	915.2	16.1
20°-30°	1575.5	27.6
30°-40°	1526.4	26.8
40°-50°	751.8	13.2
50°-60°	354.8	6.2
60°-70°	139.8	2.5
70°-80°	96.4	1.7
80°-90°	35.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2795.8	49.0
0°-40°	4322.2	75.8
0°-60°	5428.8	95.2
0°-90°	5700.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5700.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3247	
5°	3212	305
15°	3188	915
25°	3472	1575
35°	2555	1526
45°	938	752
55°	381	355
65°	132	140
75°	93	96
85°	31	36
90°	0	



TEST NUMBER: P585081

CATALOG NUMBER: HCC8S60D010MB-HM86080830-81WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3246.8
2.5°	3236.4
5°	3212.2
7.5°	3188.0
10°	3167.2
12.5°	3163.8
15°	3188.0
17.5°	3260.7
20°	3357.5
22.5°	3444.2
25°	3471.8
27.5°	3409.5
30°	3243.4
32.5°	2969.9
35°	2554.6
37.5°	1983.4
40°	1467.7
42.5°	1138.8
45°	938.1
47.5°	789.2
50°	650.7
52.5°	512.3
55°	380.7
57.5°	276.9
60°	207.7
62.5°	162.6
65°	131.5
67.5°	114.2
70°	107.3
72.5°	100.3
75°	93.4
77.5°	83.0
80°	69.2
82.5°	51.9
85°	31.1
87.5°	13.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)