

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585100

Luminaire Tested: **HCC8S60D010SL-HM86080835-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010SL-HM86080835-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5661.7 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585100
CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P585100

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66		
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51		
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41		
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38		
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34		
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	94600	94600	94600
5°	97923	94057	90324
10°	100101	92408	85241
15°	101525	89298	79596
20°	101216	84965	73897
25°	98714	79453	67841
30°	93521	73069	62248
35°	85083	66126	56564
40°	74731	58811	51102
45°	65165	51734	45558
50°	56709	45329	40139
55°	50573	39832	34913
60°	45952	34913	29776
65°	41305	30375	27034
70°	36785	25894	24397
75°	32240	21827	20838
80°	27347	17740	18468
85°	20592	13268	14718



TEST NUMBER: P585100
 CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.3	5.1
10°-20°	791.7	14.0
20°-30°	1099.0	19.4
30°-40°	1136.2	20.1
40°-50°	951.4	16.8
50°-60°	690.6	12.2
60°-70°	435.9	7.7
70°-80°	215.9	3.8
80°-90°	53.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2178.1	38.5
0°-40°	3314.3	58.5
0°-60°	4956.3	87.5
0°-90°	5661.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5661.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3068	3068	3068	3068	3068	
5°	3164	3126	3039	2955	2918	303
15°	3180	3060	2797	2572	2493	895
25°	2901	2714	2335	2081	1994	1330
35°	2260	2094	1757	1557	1503	1408
45°	1494	1386	1186	1070	1045	1156
55°	941	857	741	678	649	849
65°	566	495	416	366	370	564
75°	271	225	183	175	175	290
85°	58	46	38	42	42	71
90°	0	0	0	0	0	



TEST NUMBER: P585100

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8
2.5°	3117.8	3117.8	3121.9	3117.8	3117.8	3117.8	3113.6	3113.6	3109.5	3109.5	3101.0
5°	3163.5	3155.2	3163.5	3155.2	3155.2	3155.2	3151.1	3142.7	3138.5	3130.2	3126.1
7.5°	3184.3	3180.2	3180.2	3176.0	3176.0	3171.8	3167.7	3163.5	3146.8	3142.7	3130.2
10°	3196.9	3192.6	3192.6	3188.5	3180.2	3180.2	3171.8	3167.7	3146.8	3138.5	3121.9
12.5°	3192.6	3192.6	3192.6	3188.5	3176.0	3171.8	3163.5	3151.1	3134.4	3117.8	3101.0
15°	3180.2	3180.2	3171.8	3167.7	3155.2	3146.8	3142.7	3121.9	3105.3	3084.4	3059.5
17.5°	3138.5	3138.5	3134.4	3126.1	3113.6	3105.3	3096.9	3076.1	3059.5	3026.2	3001.1
20°	3084.4	3080.3	3076.1	3063.7	3051.1	3046.9	3034.5	3005.3	2984.5	2959.5	2926.3
22.5°	3005.3	3001.1	2997.0	2988.7	2967.9	2959.5	2951.2	2930.4	2893.0	2867.9	2826.4
25°	2901.3	2901.3	2893.0	2880.5	2859.6	2851.3	2838.9	2818.0	2784.8	2747.3	2714.0
27.5°	2780.6	2776.5	2763.9	2755.6	2739.0	2726.4	2705.6	2680.6	2647.4	2618.2	2576.6
30°	2626.5	2626.5	2618.2	2605.8	2584.9	2576.6	2560.0	2530.8	2497.6	2460.1	2430.9
32.5°	2451.8	2451.8	2439.2	2430.9	2418.4	2397.6	2393.4	2360.2	2331.0	2301.8	2268.6
35°	2260.2	2264.5	2256.1	2239.4	2218.7	2218.7	2210.3	2181.2	2147.9	2118.7	2093.8
37.5°	2068.7	2056.3	2052.1	2043.8	2031.4	2014.6	2006.3	1993.9	1964.7	1943.9	1906.5
40°	1856.5	1860.7	1852.4	1844.1	1839.8	1827.3	1823.2	1802.4	1781.5	1756.6	1739.9
42.5°	1665.0	1665.0	1665.0	1656.7	1648.3	1635.9	1631.7	1619.3	1594.2	1577.6	1552.6
45°	1494.3	1481.9	1481.9	1477.7	1473.6	1465.2	1452.7	1444.4	1427.8	1415.2	1386.2
47.5°	1327.8	1332.1	1327.8	1323.6	1311.2	1307.0	1302.9	1286.3	1269.5	1257.1	1236.3
50°	1182.1	1190.5	1182.1	1182.1	1173.8	1169.7	1161.4	1148.9	1136.3	1115.6	1094.7
52.5°	1061.5	1061.5	1057.3	1053.2	1040.6	1032.3	1028.1	1024.0	1003.2	986.5	969.9
55°	940.7	944.9	944.9	932.4	928.3	920.0	915.8	903.2	894.9	870.0	857.4
57.5°	836.7	832.5	836.7	828.4	820.1	811.6	807.5	799.2	786.7	770.1	753.4
60°	745.1	736.8	736.8	732.6	724.3	720.1	711.8	699.3	686.8	670.1	657.7
62.5°	653.5	649.4	645.2	641.1	632.8	628.5	624.3	611.9	599.4	587.0	574.4
65°	566.1	566.1	561.9	553.6	549.5	545.3	541.2	532.8	516.1	507.8	495.4
67.5°	487.0	482.8	482.8	474.5	466.2	462.1	462.1	453.7	441.2	428.7	420.4
70°	408.0	412.1	408.0	403.8	395.4	395.4	387.1	382.9	366.3	362.2	349.6
72.5°	337.1	337.1	333.0	333.0	324.7	320.5	320.5	312.2	303.9	295.5	287.2
75°	270.6	270.6	270.6	266.4	262.3	253.9	253.9	249.7	241.4	233.1	224.8
77.5°	212.3	208.1	208.1	203.9	199.8	195.6	195.6	191.5	183.2	179.0	170.7
80°	154.0	149.8	149.8	149.8	141.5	145.7	141.5	137.4	133.2	129.1	124.9
82.5°	99.9	104.0	104.0	99.9	95.7	95.7	95.7	91.6	91.6	87.4	83.3
85°	58.2	58.2	58.2	58.2	54.1	54.1	54.1	49.9	49.9	49.9	45.8
87.5°	25.0	25.0	25.0	25.0	25.0	25.0	20.8	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585100

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8
2.5°	3101.0	3092.7	3088.6	3084.4	3084.4	3080.3	3076.1	3067.8	3067.8	3059.5	3055.4
5°	3117.8	3105.3	3096.9	3088.6	3084.4	3076.1	3067.8	3055.4	3051.1	3038.6	3026.2
7.5°	3121.9	3101.0	3092.7	3076.1	3067.8	3059.5	3042.8	3030.3	3013.7	3001.1	2984.5
10°	3105.3	3088.6	3067.8	3046.9	3042.8	3030.3	3005.3	2988.7	2967.9	2951.2	2926.3
12.5°	3080.3	3055.4	3034.5	3009.6	2997.0	2984.5	2959.5	2934.6	2905.4	2876.3	2851.3
15°	3038.6	3009.6	2980.4	2951.2	2934.6	2922.1	2893.0	2863.8	2834.7	2797.2	2772.2
17.5°	2976.2	2942.9	2913.7	2876.3	2859.6	2847.2	2809.7	2776.5	2739.0	2701.5	2676.5
20°	2897.1	2855.5	2822.3	2780.6	2768.0	2747.3	2709.8	2672.3	2630.7	2589.2	2560.0
22.5°	2793.1	2751.4	2714.0	2672.3	2651.6	2630.7	2593.3	2547.5	2505.9	2472.5	2443.4
25°	2672.3	2634.8	2589.2	2551.7	2526.6	2501.7	2460.1	2422.6	2385.1	2335.2	2306.0
27.5°	2539.1	2493.3	2460.1	2410.1	2385.1	2368.5	2322.7	2272.8	2239.4	2193.7	2160.3
30°	2389.3	2347.6	2310.3	2260.2	2235.3	2218.7	2177.0	2131.3	2097.9	2052.1	2018.8
32.5°	2231.1	2185.3	2139.6	2106.2	2077.2	2060.4	2014.6	1985.6	1943.9	1906.5	1869.0
35°	2060.4	2014.6	1981.3	1935.6	1918.9	1902.3	1864.8	1827.3	1789.8	1756.6	1727.4
37.5°	1877.3	1844.1	1806.6	1773.2	1760.8	1744.1	1698.3	1665.0	1635.9	1602.5	1577.6
40°	1698.3	1669.2	1644.2	1611.0	1590.1	1577.6	1544.3	1515.1	1481.9	1461.0	1436.1
42.5°	1536.0	1502.6	1477.7	1452.7	1431.9	1419.4	1390.3	1369.4	1344.5	1323.6	1294.6
45°	1365.3	1348.7	1319.5	1298.7	1286.3	1269.5	1248.8	1223.8	1203.0	1186.3	1165.5
47.5°	1215.5	1198.8	1178.0	1153.1	1144.7	1132.2	1111.4	1094.7	1078.1	1061.5	1040.6
50°	1078.1	1057.3	1040.6	1024.0	1015.7	1003.2	982.4	974.0	961.6	944.9	932.4
52.5°	953.2	936.6	920.0	899.1	894.9	886.6	874.2	857.4	845.0	836.7	828.4
55°	840.8	824.2	811.6	795.0	790.9	782.6	765.9	757.6	749.2	740.9	732.6
57.5°	740.9	724.3	707.6	699.3	691.0	682.7	678.5	666.0	657.7	653.5	645.2
60°	649.4	632.8	620.2	607.7	603.6	599.4	591.1	582.7	574.4	566.1	561.9
62.5°	561.9	545.3	537.0	528.6	520.3	520.3	512.0	503.7	495.4	491.2	482.8
65°	482.8	474.5	462.1	449.6	445.4	445.4	432.9	428.7	424.6	416.3	408.0
67.5°	408.0	399.7	387.1	382.9	378.8	374.6	370.5	362.2	353.9	349.6	341.3
70°	341.3	333.0	324.7	320.5	316.4	312.2	303.9	299.7	291.3	287.2	283.0
72.5°	274.7	270.6	262.3	258.1	253.9	249.7	245.6	241.4	233.1	228.9	224.8
75°	220.6	216.5	208.1	203.9	199.8	199.8	195.6	187.3	183.2	183.2	179.0
77.5°	166.6	162.3	158.1	154.0	149.8	149.8	145.7	141.5	137.4	137.4	133.2
80°	120.8	116.5	112.3	112.3	112.3	108.2	104.0	104.0	99.9	99.9	95.7
82.5°	79.1	79.1	75.0	75.0	75.0	70.8	70.8	66.6	66.6	66.6	66.6
85°	45.8	45.8	45.8	41.6	41.6	41.6	41.6	41.6	41.6	37.5	41.6
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585100

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8
2.5°	3051.1	3046.9	3038.6	3038.6	3030.3	3030.3	3026.2	3022.0	3017.9	3013.7	3009.6
5°	3022.0	3005.3	2997.0	2992.8	2984.5	2980.4	2967.9	2959.5	2955.4	2947.1	2938.7
7.5°	2967.9	2951.2	2934.6	2930.4	2926.3	2909.6	2897.1	2884.7	2876.3	2867.9	2859.6
10°	2905.4	2888.8	2867.9	2859.6	2851.3	2830.6	2813.8	2801.4	2784.8	2768.0	2763.9
12.5°	2830.6	2805.5	2780.6	2772.2	2759.7	2739.0	2722.3	2701.5	2689.0	2668.2	2664.0
15°	2743.1	2714.0	2693.2	2672.3	2664.0	2643.2	2614.1	2597.5	2572.4	2564.1	2543.4
17.5°	2639.1	2609.9	2580.7	2572.4	2560.0	2530.8	2501.7	2480.8	2455.9	2443.4	2430.9
20°	2530.8	2493.3	2464.2	2455.9	2439.2	2414.3	2385.1	2364.4	2343.5	2318.6	2306.0
22.5°	2406.0	2364.4	2339.3	2318.6	2314.4	2285.2	2251.9	2235.3	2218.7	2197.8	2181.2
25°	2268.6	2231.1	2202.0	2185.3	2177.0	2152.0	2127.1	2106.2	2081.3	2068.7	2048.0
27.5°	2127.1	2102.1	2064.6	2048.0	2035.5	2014.6	1985.6	1973.0	1948.1	1931.4	1918.9
30°	1989.7	1952.2	1931.4	1910.6	1898.2	1877.3	1852.4	1839.8	1819.0	1802.4	1789.8
32.5°	1839.8	1814.9	1785.7	1777.4	1760.8	1739.9	1723.3	1702.5	1685.8	1669.2	1665.0
35°	1702.5	1669.2	1640.0	1631.7	1619.3	1598.4	1590.1	1577.6	1556.7	1552.6	1536.0
37.5°	1552.6	1536.0	1502.6	1490.2	1486.0	1469.4	1452.7	1444.4	1431.9	1419.4	1415.2
40°	1411.1	1390.3	1373.6	1361.1	1352.8	1340.4	1323.6	1319.5	1311.2	1294.6	1290.4
42.5°	1277.9	1257.1	1240.5	1236.3	1223.8	1211.3	1203.0	1190.5	1186.3	1182.1	1173.8
45°	1148.9	1136.3	1119.7	1115.6	1111.4	1094.7	1086.4	1078.1	1069.8	1065.6	1057.3
47.5°	1032.3	1019.8	1007.4	1003.2	994.8	990.7	978.2	974.0	961.6	957.4	953.2
50°	920.0	911.6	903.2	899.1	890.8	886.6	878.3	870.0	861.6	857.4	853.3
52.5°	820.1	811.6	803.3	799.2	795.0	786.7	778.4	770.1	765.9	761.7	757.6
55°	724.3	715.9	711.8	707.6	703.5	699.3	686.8	682.7	678.5	674.3	666.0
57.5°	636.9	628.5	620.2	620.2	616.0	611.9	603.6	595.3	595.3	587.0	578.5
60°	557.8	549.5	541.2	537.0	532.8	524.5	520.3	516.1	512.0	507.8	499.5
62.5°	474.5	470.4	462.1	462.1	453.7	449.6	445.4	441.2	437.0	428.7	424.6
65°	403.8	399.7	391.2	387.1	387.1	382.9	374.6	370.5	366.3	366.3	362.2
67.5°	337.1	333.0	324.7	320.5	320.5	316.4	312.2	312.2	308.1	303.9	308.1
70°	278.9	270.6	270.6	266.4	266.4	262.3	258.1	258.1	258.1	262.3	262.3
72.5°	220.6	216.5	212.3	212.3	212.3	212.3	208.1	208.1	212.3	216.5	216.5
75°	174.9	170.7	170.7	170.7	166.6	166.6	170.7	170.7	174.9	174.9	174.9
77.5°	129.1	129.1	129.1	129.1	129.1	129.1	133.2	133.2	137.4	137.4	137.4
80°	95.7	95.7	95.7	95.7	95.7	99.9	99.9	99.9	99.9	99.9	104.0
82.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	70.8	70.8	70.8	70.8
85°	37.5	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585100

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8	3067.8
2.5°	3005.3	3005.3	3005.3	3009.6	3001.1	3001.1	3001.1	3001.1
5°	2934.6	2930.4	2926.3	2930.4	2922.1	2922.1	2918.0	2918.0
7.5°	2847.2	2843.0	2838.9	2838.9	2830.6	2830.6	2826.4	2822.3
10°	2751.4	2743.1	2747.3	2739.0	2734.8	2730.7	2726.4	2722.3
12.5°	2647.4	2639.1	2634.8	2626.5	2618.2	2614.1	2618.2	2609.9
15°	2534.9	2522.5	2518.3	2510.0	2501.7	2497.6	2497.6	2493.3
17.5°	2410.1	2401.7	2397.6	2389.3	2385.1	2376.8	2372.7	2368.5
20°	2293.5	2272.8	2276.9	2268.6	2264.5	2247.7	2247.7	2251.9
22.5°	2164.5	2152.0	2143.7	2135.4	2131.3	2122.9	2122.9	2118.7
25°	2035.5	2022.9	2018.8	2010.5	2006.3	1998.0	1993.9	1993.9
27.5°	1910.6	1894.0	1894.0	1885.6	1877.3	1873.1	1869.0	1864.8
30°	1777.4	1764.9	1760.8	1760.8	1756.6	1756.6	1744.1	1748.2
32.5°	1652.5	1644.2	1640.0	1631.7	1631.7	1627.6	1627.6	1615.1
35°	1527.7	1515.1	1519.4	1511.0	1506.8	1502.6	1506.8	1502.6
37.5°	1406.9	1398.6	1398.6	1390.3	1390.3	1386.2	1382.0	1390.3
40°	1286.3	1282.0	1277.9	1273.7	1277.9	1273.7	1265.4	1269.5
42.5°	1165.5	1165.5	1161.4	1161.4	1157.2	1157.2	1157.2	1157.2
45°	1057.3	1053.2	1053.2	1048.9	1048.9	1048.9	1048.9	1044.7
47.5°	949.0	944.9	944.9	944.9	940.7	940.7	936.6	940.7
50°	845.0	845.0	840.8	840.8	845.0	840.8	836.7	836.7
52.5°	749.2	749.2	745.1	745.1	740.9	736.8	740.9	740.9
55°	661.8	657.7	653.5	653.5	649.4	645.2	645.2	649.4
57.5°	578.5	574.4	570.2	570.2	561.9	557.8	557.8	557.8
60°	499.5	491.2	491.2	487.0	487.0	482.8	482.8	482.8
62.5°	424.6	420.4	420.4	420.4	420.4	416.3	416.3	416.3
65°	362.2	362.2	362.2	366.3	366.3	370.5	370.5	370.5
67.5°	312.2	316.4	316.4	316.4	320.5	320.5	320.5	316.4
70°	266.4	266.4	266.4	270.6	270.6	270.6	270.6	270.6
72.5°	220.6	220.6	220.6	220.6	220.6	220.6	220.6	220.6
75°	174.9	179.0	179.0	179.0	174.9	179.0	179.0	174.9
77.5°	137.4	137.4	137.4	137.4	137.4	137.4	137.4	137.4
80°	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0
82.5°	70.8	70.8	70.8	70.8	70.8	70.8	70.8	70.8
85°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)