

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584945

Luminaire Tested: **HCC8S55D010BZ-HM82555830-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S55D010BZ-HM82555830-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5839.8 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584945  
CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P584945  
 CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98		98	97	95		95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86		90	87	84		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62		71	66	62		69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43		53	47	43		52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40		49	44	40		48	43	40	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	102562
5°	101854
10°	101589
15°	104255
20°	112868
25°	121003
30°	118300
35°	98507
40°	60518
45°	41904
50°	31979
55°	20967
60°	13118
65°	9836
70°	9909
75°	11414
80°	12590
85°	11286



TEST NUMBER: P584945  
 CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.7	5.4
10°-20°	937.5	16.1
20°-30°	1613.9	27.6
30°-40°	1563.6	26.8
40°-50°	770.1	13.2
50°-60°	363.4	6.2
60°-70°	143.2	2.5
70°-80°	98.8	1.7
80°-90°	36.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2864.0	49.0
0°-40°	4427.6	75.8
0°-60°	5561.1	95.2
0°-90°	5839.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5839.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3326	
5°	3290	313
15°	3266	937
25°	3556	1614
35°	2617	1564
45°	961	770
55°	390	363
65°	135	143
75°	96	99
85°	32	37
90°	0	



TEST NUMBER: P584945  
CATALOG NUMBER: HCC8S55D010BZ-HM82555830-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3326.0
2.5°	3315.4
5°	3290.5
7.5°	3265.7
10°	3244.4
12.5°	3240.9
15°	3265.7
17.5°	3340.2
20°	3439.5
22.5°	3528.1
25°	3556.4
27.5°	3492.7
30°	3322.4
32.5°	3042.3
35°	2616.8
37.5°	2031.8
40°	1503.4
42.5°	1166.6
45°	960.9
47.5°	808.4
50°	666.6
52.5°	524.8
55°	390.0
57.5°	283.6
60°	212.7
62.5°	166.7
65°	134.8
67.5°	117.0
70°	109.9
72.5°	102.8
75°	95.8
77.5°	85.1
80°	70.9
82.5°	53.2
85°	31.9
87.5°	14.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)