

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584950

Luminaire Tested: **HCC8S55D010SL-HM82555835-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S55D010SL-HM82555835-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5551.4 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584950  
CATALOG NUMBER: HCC8S55D010SL-HM82555835-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584950

CATALOG NUMBER: HCC8S55D010SL-HM82555835-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	253878
5°	231354
10°	197670
15°	172384
20°	153641
25°	136290
30°	111588
35°	64078
40°	28439
45°	16550
50°	9551
55°	5457
60°	3016
65°	1919
70°	1352
75°	894
80°	675
85°	1344



TEST NUMBER: P584950  
 CATALOG NUMBER: HCC8S55D010SL-HM82555835-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	676.5	12.2
10°-20°	1517.8	27.3
20°-30°	1816.9	32.7
30°-40°	1099.1	19.8
40°-50°	308.0	5.5
50°-60°	95.6	1.7
60°-70°	27.3	0.5
70°-80°	7.4	0.1
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4011.3	72.3
0°-40°	5110.4	92.1
0°-60°	5514.1	99.3
0°-90°	5551.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5551.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8233	
5°	7474	677
15°	5400	1518
25°	4006	1817
35°	1702	1099
45°	380	308
55°	102	96
65°	26	27
75°	8	7
85°	4	3
90°	0	



TEST NUMBER: P584950  
CATALOG NUMBER: HCC8S55D010SL-HM82555835-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8233.1
2.5°	8000.1
5°	7474.1
7.5°	6880.3
10°	6312.9
12.5°	5816.9
15°	5399.8
17.5°	5031.5
20°	4682.0
22.5°	4358.9
25°	4005.7
27.5°	3607.4
30°	3133.9
32.5°	2521.4
35°	1702.2
37.5°	1059.7
40°	706.5
42.5°	507.2
45°	379.5
47.5°	278.1
50°	199.1
52.5°	139.0
55°	101.5
57.5°	67.6
60°	48.9
62.5°	33.9
65°	26.3
67.5°	18.8
70°	15.0
72.5°	7.5
75°	7.5
77.5°	3.8
80°	3.8
82.5°	3.8
85°	3.8
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)