

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584969

Luminaire Tested: **HCC8S55D010MB-HM82555840-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S55D010MB-HM82555840-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6045.1 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584969
CATALOG NUMBER: HCC8S55D010MB-HM82555840-81NDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584969

CATALOG NUMBER: HCC8S55D010MB-HM82555840-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96																																				
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																																				
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87																																				
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83																																				
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80																																				
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76																																				
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73																																				
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71																																				
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68																																				
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1137789
5°	729802
10°	329678
15°	198922
20°	151584
25°	122412
30°	89700
35°	32479
40°	12124
45°	5503
50°	1761
55°	435
60°	253
65°	299
70°	0
75°	0
80°	728
85°	1451



TEST NUMBER: P584969
 CATALOG NUMBER: HCC8S55D010MB-HM82555840-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1798.2	29.7
10°-20°	1826.4	30.2
20°-30°	1635.0	27.0
30°-40°	658.6	10.9
40°-50°	108.0	1.8
50°-60°	9.8	0.2
60°-70°	3.5	0.1
70°-80°	2.7	0.0
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5259.6	87.0
0°-40°	5918.1	97.9
0°-60°	6036.0	99.8
0°-90°	6046.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6045.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	36898	
5°	23577	###
15°	6231	1826
25°	3598	1635
35°	863	659
45°	126	108
55°	8	10
65°	4	4
75°	0	3
85°	4	4
90°	0	



TEST NUMBER: P584969
CATALOG NUMBER: HCC8S55D010MB-HM82555840-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	36897.7
0.5°	36783.7
1°	36307.5
1.5°	35542.4
2°	34382.5
2.5°	33010.9
3°	31293.5
3.5°	29409.1
4°	27545.0
4.5°	25457.2
5°	23576.9
5.5°	21529.8
6°	19869.3
6.5°	18139.5
7°	16780.2
7.5°	15343.5
8°	14187.6
8.5°	13027.7
9°	12156.8
9.5°	11196.2
10°	10528.8
12.5°	7765.3
15°	6231.1
17.5°	5323.5
20°	4619.3
22.5°	4057.7
25°	3597.8
27.5°	3137.9
30°	2519.2
32.5°	1619.8
35°	862.8
37.5°	476.2
40°	301.2
42.5°	199.5
45°	126.2
47.5°	77.4
50°	36.7
52.5°	12.2
55°	8.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1



TEST NUMBER: P584969
CATALOG NUMBER: HCC8S55D010MB-HM82555840-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	4.1
80°	4.1
82.5°	4.1
85°	4.1
87.5°	4.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		4.1
70°		0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)