

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593838

Luminaire Tested: **HCC8W55D010MW-HM82555850-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010MW-HM82555850-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5764.1 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593838
CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88374	88374	88374
5°	91609	88083	85059
10°	94199	87314	81580
15°	96302	85774	77978
20°	96454	82422	74812
25°	94604	77844	72165
30°	89725	72185	68999
35°	81526	65742	65896
40°	71286	58996	62108
45°	61781	52553	57878
50°	54099	46678	52727
55°	48149	41364	47708
60°	43436	37158	41931
65°	39211	32674	36534
70°	35243	27526	27156
75°	31037	21827	20373
80°	26015	18060	19516
85°	20167	15851	17301



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.4	4.7
10°-20°	761.5	13.2
20°-30°	1088.3	18.9
30°-40°	1156.4	20.1
40°-50°	995.6	17.3
50°-60°	744.4	12.9
60°-70°	474.8	8.2
70°-80°	216.1	3.7
80°-90°	56.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2120.2	36.8
0°-40°	3276.6	56.8
0°-60°	5016.6	87.0
0°-90°	5764.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5764.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2866	2866	2866	2866	2866	
5°	2960	2919	2846	2772	2748	284
15°	3017	2915	2687	2504	2443	850
25°	2780	2605	2288	2149	2121	1273
35°	2166	2015	1746	1702	1750	1349
45°	1417	1339	1205	1238	1327	1101
55°	896	822	769	835	887	805
65°	537	476	448	468	501	536
75°	260	224	183	167	171	277
85°	57	49	45	49	49	69
90°	0	0	0	0	0	



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9
2.5°	2918.9	2910.8	2914.8	2910.8	2914.8	2914.8	2906.7	2906.7	2906.7	2906.7	2894.5
5°	2959.5	2955.5	2955.5	2951.4	2947.3	2951.4	2947.3	2943.2	2935.2	2931.1	2918.9
7.5°	2984.0	2984.0	2984.0	2984.0	2979.9	2975.8	2971.8	2963.6	2955.5	2947.3	2939.3
10°	3008.4	3012.5	3008.4	3004.3	3000.3	2992.1	2988.0	2979.9	2967.7	2955.5	2947.3
12.5°	3020.6	3020.6	3016.6	3016.6	3008.4	3004.3	2992.1	2979.9	2967.7	2955.5	2935.2
15°	3016.6	3016.6	3012.5	3008.4	2996.2	2992.1	2984.0	2971.8	2951.4	2935.2	2914.8
17.5°	2992.1	2988.0	2979.9	2979.9	2963.6	2959.5	2951.4	2935.2	2914.8	2890.4	2865.9
20°	2939.3	2939.3	2935.2	2931.1	2914.8	2902.6	2894.5	2874.1	2857.8	2829.3	2804.8
22.5°	2865.9	2874.1	2865.9	2857.8	2837.4	2833.4	2821.1	2796.7	2772.4	2739.8	2711.3
25°	2780.5	2776.4	2772.4	2764.2	2747.9	2739.8	2723.5	2699.0	2674.6	2637.9	2605.4
27.5°	2670.5	2654.2	2654.2	2637.9	2625.7	2613.6	2605.4	2581.0	2548.4	2519.9	2479.2
30°	2519.9	2524.0	2503.6	2499.5	2479.2	2471.0	2454.8	2430.4	2401.9	2369.3	2336.7
32.5°	2357.1	2344.8	2344.8	2328.5	2312.2	2300.0	2296.1	2267.5	2243.1	2210.5	2177.9
35°	2165.7	2165.7	2153.5	2149.4	2133.2	2125.1	2112.8	2096.6	2068.0	2039.5	2015.1
37.5°	1978.5	1970.4	1966.3	1958.2	1945.9	1933.7	1933.7	1905.2	1901.1	1868.5	1835.9
40°	1770.9	1779.0	1770.9	1758.7	1754.6	1746.4	1742.4	1726.1	1713.8	1685.3	1665.1
42.5°	1595.8	1587.7	1587.7	1583.6	1567.3	1567.3	1559.2	1551.0	1530.6	1522.5	1498.1
45°	1416.7	1424.8	1412.6	1416.7	1400.4	1400.4	1400.4	1384.1	1367.8	1355.7	1339.4
47.5°	1262.0	1266.1	1266.1	1253.8	1249.8	1249.8	1241.6	1233.5	1221.2	1205.1	1192.7
50°	1127.7	1131.7	1123.6	1119.5	1111.4	1107.3	1107.3	1091.0	1082.9	1066.6	1058.4
52.5°	1005.6	1005.6	1001.5	1001.5	989.3	989.3	981.1	968.9	960.7	952.6	932.2
55°	895.6	895.6	891.5	887.4	887.4	875.2	871.1	859.0	850.9	834.6	822.3
57.5°	789.8	793.8	789.8	785.7	781.6	777.5	769.4	757.2	749.0	736.8	728.7
60°	704.3	704.3	700.2	696.2	688.0	683.9	679.9	671.7	659.5	651.4	639.1
62.5°	622.8	618.8	614.7	610.6	602.5	602.5	594.3	586.2	574.0	565.8	557.8
65°	537.4	537.4	533.3	533.3	529.3	521.1	517.0	513.0	496.7	492.6	476.3
67.5°	460.0	464.1	455.9	455.9	447.8	447.8	443.7	431.5	427.4	419.3	411.1
70°	390.9	390.9	390.9	386.8	378.6	374.6	370.5	362.3	358.3	350.1	342.0
72.5°	321.6	321.6	317.5	317.5	313.5	309.4	305.3	297.2	297.2	289.0	280.9
75°	260.5	260.5	256.4	252.4	248.3	248.3	244.2	240.1	232.1	228.0	223.9
77.5°	199.5	199.5	199.5	195.4	191.4	191.4	191.4	183.2	175.1	175.1	171.0
80°	146.5	146.5	142.5	142.5	138.4	138.4	138.4	134.3	130.3	126.2	122.1
82.5°	97.7	97.7	97.7	97.7	93.6	93.6	93.6	89.5	85.4	85.4	85.4
85°	57.0	57.0	57.0	57.0	53.0	53.0	53.0	53.0	53.0	48.9	48.9
87.5°	24.4	20.4	24.4	20.4	24.4	20.4	24.4	20.4	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9
2.5°	2898.5	2894.5	2890.4	2886.3	2886.3	2882.2	2874.1	2870.0	2865.9	2861.9	2861.9
5°	2914.8	2910.8	2902.6	2894.5	2890.4	2882.2	2874.1	2865.9	2857.8	2845.6	2841.5
7.5°	2927.0	2914.8	2906.7	2890.4	2886.3	2878.2	2865.9	2853.7	2837.4	2821.1	2808.9
10°	2927.0	2910.8	2898.5	2878.2	2870.0	2861.9	2845.6	2825.2	2804.8	2788.5	2768.3
12.5°	2918.9	2898.5	2878.2	2857.8	2845.6	2833.4	2808.9	2788.5	2764.2	2739.8	2723.5
15°	2890.4	2865.9	2841.5	2817.1	2804.8	2788.5	2764.2	2735.7	2711.3	2686.8	2658.3
17.5°	2837.4	2813.0	2784.6	2756.1	2739.8	2727.5	2690.9	2670.5	2634.0	2609.5	2585.1
20°	2768.3	2739.8	2703.1	2674.6	2654.2	2642.0	2613.6	2576.9	2548.4	2511.7	2487.3
22.5°	2678.7	2642.0	2605.4	2576.9	2556.6	2540.3	2503.6	2466.9	2442.6	2410.0	2381.5
25°	2572.9	2536.2	2499.5	2458.9	2438.5	2422.2	2389.6	2357.1	2324.5	2287.9	2263.5
27.5°	2446.7	2405.9	2373.3	2336.7	2316.3	2292.0	2255.3	2222.7	2190.1	2165.7	2133.2
30°	2308.3	2263.5	2230.9	2194.2	2173.8	2153.5	2116.9	2084.3	2055.8	2027.3	2011.0
32.5°	2141.4	2108.8	2076.2	2039.5	2023.2	2011.0	1974.4	1941.9	1909.3	1884.8	1872.6
35°	1982.6	1945.9	1917.4	1884.8	1864.5	1852.2	1819.8	1791.2	1774.9	1746.4	1730.1
37.5°	1815.7	1787.2	1754.6	1722.0	1709.8	1697.5	1673.1	1644.7	1620.3	1599.9	1591.7
40°	1640.6	1616.2	1587.7	1567.3	1555.1	1542.9	1522.5	1502.2	1485.9	1465.6	1457.4
42.5°	1473.7	1457.4	1433.0	1408.5	1396.3	1392.2	1367.8	1351.6	1343.5	1335.3	1327.2
45°	1323.1	1298.6	1282.4	1266.1	1253.8	1245.7	1233.5	1221.2	1213.1	1205.1	1196.8
47.5°	1176.5	1156.2	1139.9	1127.7	1115.4	1111.4	1103.2	1091.0	1082.9	1082.9	1082.9
50°	1042.1	1025.9	1009.6	1001.5	997.4	989.3	981.1	977.0	973.0	973.0	973.0
52.5°	924.1	907.8	895.6	887.4	887.4	879.4	871.1	867.2	867.2	867.2	867.2
55°	814.2	802.0	793.8	785.7	777.5	773.5	773.5	773.5	769.4	769.4	773.5
57.5°	716.4	708.4	696.2	688.0	683.9	683.9	679.9	675.8	679.9	683.9	688.0
60°	626.9	618.8	614.7	602.5	602.5	602.5	598.4	598.4	598.4	602.5	606.6
62.5°	545.4	541.5	533.3	529.3	525.2	525.2	521.1	521.1	521.1	521.1	525.2
65°	472.2	464.1	455.9	455.9	455.9	451.9	451.9	443.7	447.8	447.8	443.7
67.5°	403.1	394.8	390.9	386.8	382.7	382.7	378.6	374.6	370.5	370.5	370.5
70°	337.9	329.8	329.8	321.6	321.6	317.5	313.5	313.5	309.4	305.3	301.2
72.5°	272.7	268.7	264.6	260.5	260.5	260.5	256.4	252.4	248.3	244.2	236.2
75°	215.8	215.8	207.6	203.6	203.6	199.5	195.4	191.4	187.3	183.2	179.1
77.5°	166.9	162.8	154.7	150.6	150.6	150.6	146.5	142.5	138.4	134.3	130.3
80°	122.1	118.0	114.0	109.9	109.9	109.9	105.8	105.8	101.7	101.7	101.7
82.5°	81.5	81.5	77.4	77.4	77.4	77.4	73.2	73.2	73.2	73.2	73.2
85°	48.9	48.9	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8
87.5°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9
2.5°	2853.7	2853.7	2845.6	2841.5	2837.4	2841.5	2833.4	2829.3	2825.2	2825.2	2821.1
5°	2829.3	2825.2	2808.9	2804.8	2800.8	2796.7	2788.5	2780.5	2772.4	2768.3	2764.2
7.5°	2796.7	2784.6	2768.3	2764.2	2760.1	2747.9	2735.7	2727.5	2715.3	2711.3	2703.1
10°	2752.0	2735.7	2723.5	2711.3	2703.1	2690.9	2678.7	2666.4	2650.1	2646.1	2634.0
12.5°	2699.0	2678.7	2654.2	2650.1	2637.9	2621.6	2605.4	2593.2	2581.0	2572.9	2560.6
15°	2634.0	2613.6	2589.1	2576.9	2564.7	2552.5	2532.1	2515.8	2503.6	2491.4	2479.2
17.5°	2556.6	2532.1	2511.7	2499.5	2491.4	2471.0	2454.8	2434.5	2422.2	2410.0	2397.8
20°	2463.0	2442.6	2414.1	2401.9	2397.8	2381.5	2361.1	2353.0	2336.7	2324.5	2316.3
22.5°	2357.1	2336.7	2312.2	2304.2	2287.9	2279.8	2259.4	2251.2	2243.1	2230.9	2226.8
25°	2239.0	2218.7	2198.3	2194.2	2182.0	2173.8	2161.6	2149.4	2149.4	2137.3	2137.3
27.5°	2116.9	2096.6	2080.3	2072.1	2068.0	2059.9	2047.7	2043.6	2039.5	2035.4	2035.4
30°	1986.7	1962.2	1954.1	1950.0	1945.9	1937.8	1933.7	1925.6	1929.6	1933.7	1929.6
32.5°	1848.2	1840.0	1823.7	1815.7	1819.8	1815.7	1807.5	1815.7	1811.6	1819.8	1823.7
35°	1713.8	1705.7	1697.5	1697.5	1689.4	1689.4	1689.4	1693.5	1701.6	1705.7	1713.8
37.5°	1583.6	1571.4	1567.3	1563.2	1567.3	1567.3	1567.3	1575.4	1583.6	1591.7	1604.0
40°	1445.2	1437.0	1437.0	1437.0	1437.0	1449.3	1445.2	1453.3	1461.5	1473.7	1485.9
42.5°	1314.9	1314.9	1319.0	1319.0	1319.0	1319.0	1327.2	1339.4	1351.6	1363.7	1375.9
45°	1192.7	1192.7	1192.7	1200.9	1200.9	1205.1	1221.2	1229.4	1237.5	1249.8	1262.0
47.5°	1078.8	1078.8	1082.9	1086.9	1091.0	1099.1	1107.3	1119.5	1131.7	1139.9	1152.1
50°	973.0	977.0	985.2	993.3	993.3	997.4	1009.6	1017.8	1025.9	1038.0	1042.1
52.5°	871.1	879.4	887.4	891.5	895.6	903.7	907.8	920.0	924.1	936.3	940.4
55°	777.5	781.6	793.8	797.9	797.9	806.1	814.2	822.3	834.6	834.6	842.7
57.5°	692.1	696.2	704.3	708.4	704.3	716.4	720.5	728.7	732.7	740.9	745.0
60°	606.6	614.7	618.8	618.8	622.8	626.9	635.1	635.1	643.2	651.4	651.4
62.5°	525.2	529.3	533.3	537.4	541.5	537.4	549.6	549.6	557.8	561.7	569.9
65°	447.8	451.9	451.9	455.9	455.9	460.0	460.0	464.1	468.2	476.3	480.4
67.5°	370.5	370.5	370.5	374.6	370.5	374.6	374.6	378.6	378.6	386.8	390.9
70°	301.2	297.2	293.1	293.1	293.1	293.1	289.0	293.1	293.1	297.2	297.2
72.5°	232.1	228.0	223.9	219.9	219.9	215.8	211.7	215.8	215.8	219.9	219.9
75°	175.1	166.9	166.9	166.9	162.8	162.8	162.8	166.9	166.9	166.9	171.0
77.5°	130.3	130.3	126.2	126.2	126.2	130.3	130.3	134.3	134.3	134.3	134.3
80°	97.7	101.7	101.7	101.7	101.7	105.8	105.8	105.8	105.8	109.9	109.9
82.5°	73.2	73.2	73.2	73.2	77.4	77.4	77.4	77.4	77.4	77.4	77.4
85°	44.8	48.9	48.9	44.8	48.9	48.9	48.9	48.9	48.9	48.9	48.9
87.5°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593838

CATALOG NUMBER: HCC8W55D010MW-HM82555850-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9	2865.9
2.5°	2817.1	2817.1	2817.1	2817.1	2813.0	2813.0	2813.0	2808.9
5°	2756.1	2756.1	2756.1	2747.9	2752.0	2752.0	2743.8	2747.9
7.5°	2695.0	2690.9	2686.8	2686.8	2682.7	2678.7	2674.6	2678.7
10°	2625.7	2613.6	2613.6	2609.5	2609.5	2601.4	2601.4	2605.4
12.5°	2548.4	2540.3	2540.3	2536.2	2532.1	2528.0	2524.0	2524.0
15°	2471.0	2463.0	2458.9	2454.8	2450.7	2442.6	2446.7	2442.6
17.5°	2393.7	2381.5	2381.5	2377.4	2373.3	2365.2	2365.2	2361.1
20°	2304.2	2300.0	2292.0	2296.1	2292.0	2283.8	2279.8	2279.8
22.5°	2214.6	2214.6	2210.5	2210.5	2206.4	2202.4	2198.3	2198.3
25°	2129.1	2125.1	2129.1	2129.1	2116.9	2116.9	2116.9	2121.0
27.5°	2031.4	2035.4	2031.4	2031.4	2031.4	2031.4	2035.4	2031.4
30°	1933.7	1933.7	1933.7	1937.8	1945.9	1941.9	1941.9	1937.8
32.5°	1827.9	1832.0	1832.0	1835.9	1840.0	1848.2	1848.2	1852.2
35°	1722.0	1730.1	1734.2	1730.1	1742.4	1742.4	1750.5	1750.5
37.5°	1612.1	1616.2	1624.3	1628.4	1636.5	1640.6	1644.7	1644.7
40°	1494.1	1510.4	1514.3	1518.4	1530.6	1530.6	1534.7	1542.9
42.5°	1384.1	1400.4	1404.5	1408.5	1416.7	1428.9	1424.8	1433.0
45°	1278.3	1290.5	1294.6	1298.6	1310.9	1314.9	1314.9	1327.2
47.5°	1164.3	1172.5	1176.5	1184.7	1192.7	1200.9	1209.0	1205.1
50°	1050.3	1062.5	1070.6	1074.7	1086.9	1091.0	1095.1	1099.1
52.5°	948.5	956.7	960.7	964.8	977.0	981.1	985.2	993.3
55°	850.9	854.9	863.1	859.0	871.1	875.2	879.4	887.4
57.5°	753.1	757.2	761.2	761.2	769.4	777.5	781.6	785.7
60°	659.5	667.7	671.7	671.7	671.7	679.9	679.9	679.9
62.5°	574.0	574.0	578.0	578.0	586.2	586.2	586.2	586.2
65°	484.4	488.5	492.6	492.6	500.7	496.7	504.8	500.7
67.5°	390.9	390.9	398.9	398.9	394.8	398.9	398.9	398.9
70°	297.2	297.2	301.2	301.2	301.2	301.2	301.2	301.2
72.5°	219.9	219.9	219.9	223.9	219.9	219.9	223.9	219.9
75°	171.0	171.0	171.0	171.0	171.0	171.0	171.0	171.0
77.5°	134.3	134.3	138.4	138.4	138.4	138.4	138.4	138.4
80°	109.9	109.9	109.9	109.9	114.0	109.9	109.9	109.9
82.5°	81.5	77.4	81.5	77.4	81.5	81.5	81.5	81.5
85°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9
87.5°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)