

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585147

Luminaire Tested: **HCC8W60D010SL-HM86080930-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585147  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010SL-HM86080930-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5168.7 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585147  
CATALOG NUMBER: HCC8W60D010SL-HM86080930-81WDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585147

CATALOG NUMBER: HCC8W60D010SL-HM86080930-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			92	
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83	
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75	
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			68	
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			62	
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			57	
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			52	
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48	
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			44	
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			41	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118331
5°	115666
10°	112119
15°	109848
20°	108865
25°	107237
30°	101579
35°	84398
40°	49702
45°	32877
50°	25872
55°	19042
60°	13223
65°	8063
70°	3516
75°	1549
80°	1154
85°	0



TEST NUMBER: P585147  
 CATALOG NUMBER: HCC8W60D010SL-HM86080930-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	351.9	6.8
10°-20°	972.8	18.8
20°-30°	1441.3	27.9
30°-40°	1331.8	25.8
40°-50°	614.1	11.9
50°-60°	323.0	6.2
60°-70°	114.1	2.2
70°-80°	17.9	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2766.0	53.5
0°-40°	4097.8	79.3
0°-60°	5034.8	97.4
0°-90°	5168.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5168.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3837	
5°	3737	352
15°	3441	973
25°	3152	1441
35°	2242	1332
45°	754	614
55°	354	323
65°	110	114
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P585147  
CATALOG NUMBER: HCC8W60D010SL-HM86080930-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3837.4
2.5°	3805.0
5°	3736.7
7.5°	3661.9
10°	3580.7
12.5°	3502.8
15°	3440.9
17.5°	3385.7
20°	3317.5
22.5°	3242.8
25°	3151.8
27.5°	3028.4
30°	2852.8
32.5°	2602.6
35°	2242.0
37.5°	1722.1
40°	1234.7
42.5°	926.1
45°	753.9
47.5°	640.1
50°	539.3
52.5°	441.9
55°	354.2
57.5°	279.5
60°	214.4
62.5°	162.5
65°	110.5
67.5°	64.9
70°	39.0
72.5°	22.7
75°	13.0
77.5°	9.8
80°	6.5
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)