

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585157

Luminaire Tested: **HCC8S60D010SL-HM86080935-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010SL-HM86080935-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5001.5 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585157
CATALOG NUMBER: HCC8S60D010SL-HM86080935-81NDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585157

CATALOG NUMBER: HCC8S60D010SL-HM86080935-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	397973
5°	337168
10°	244631
15°	183707
20°	144952
25°	116920
30°	86642
35°	35103
40°	14805
45°	7937
50°	3564
55°	1796
60°	1147
65°	817
70°	667
75°	441
80°	657
85°	1309



TEST NUMBER: P585157
 CATALOG NUMBER: HCC8S60D010SL-HM86080935-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	935.2	18.7
10°-20°	1616.3	32.3
20°-30°	1562.6	31.2
30°-40°	686.3	13.7
40°-50°	148.4	3.0
50°-60°	33.3	0.7
60°-70°	11.5	0.2
70°-80°	4.4	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4114.1	82.3
0°-40°	4800.5	96.0
0°-60°	4982.1	99.6
0°-90°	5001.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5001.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12906	
5°	10892	935
15°	5754	1616
25°	3436	1563
35°	932	686
45°	182	148
55°	33	33
65°	11	11
75°	4	4
85°	4	4
90°	0	



TEST NUMBER: P585157
CATALOG NUMBER: HCC8S60D010SL-HM86080935-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	12906.0
1°	12809.4
2°	12545.6
3°	12070.1
4°	11501.7
5°	10892.5
6°	10227.4
7°	9558.7
8°	8930.9
9°	8347.6
10°	7812.7
11°	7307.5
12°	6854.2
13°	6441.9
14°	6077.7
15°	5754.5
17.5°	5030.1
20°	4417.2
22.5°	3878.4
25°	3436.4
27.5°	2986.8
30°	2433.3
32.5°	1653.2
35°	932.5
37.5°	549.8
40°	367.8
42.5°	260.1
45°	182.0
47.5°	118.9
50°	74.3
52.5°	44.6
55°	33.4
57.5°	26.0
60°	18.6
62.5°	14.9
65°	11.2
67.5°	7.4
70°	7.4
72.5°	3.7
75°	3.7
77.5°	3.7
80°	3.7
82.5°	3.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585157
CATALOG NUMBER: HCC8S60D010SL-HM86080935-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	3.7
87.5°	3.7

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)