

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584985

Luminaire Tested: **HCC8W55D010MB-HM82555927-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584985  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W55D010MB-HM82555927-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4335.9 lumens  
Efficiency: N/A  
Efficacy: 83.4 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584985  
CATALOG NUMBER: HCC8W55D010MB-HM82555927-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584985

CATALOG NUMBER: HCC8W55D010MB-HM82555927-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110866
5°	107847
10°	101482
15°	96085
20°	92428
25°	88857
30°	78919
35°	50259
40°	28053
45°	23497
50°	21209
55°	19994
60°	18237
65°	16454
70°	14516
75°	12903
80°	11454
85°	10367



TEST NUMBER: P584985  
 CATALOG NUMBER: HCC8W55D010MB-HM82555927-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.8	7.5
10°-20°	848.8	19.6
20°-30°	1184.2	27.3
30°-40°	852.1	19.7
40°-50°	422.3	9.7
50°-60°	330.4	7.6
60°-70°	223.7	5.2
70°-80°	116.2	2.7
80°-90°	33.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2357.8	54.4
0°-40°	3209.9	74.0
0°-60°	3962.6	91.4
0°-90°	4335.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4335.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3595	
5°	3484	325
15°	3010	849
25°	2612	1184
35°	1335	852
45°	539	422
55°	372	330
65°	226	224
75°	108	116
85°	29	33
90°	0	



TEST NUMBER: P584985  
CATALOG NUMBER: HCC8W55D010MB-HM82555927-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3595.3
2.5°	3563.1
5°	3484.1
7.5°	3372.9
10°	3241.0
12.5°	3118.1
15°	3009.8
17.5°	2907.4
20°	2816.6
22.5°	2725.8
25°	2611.6
27.5°	2447.6
30°	2216.4
32.5°	1853.3
35°	1335.1
37.5°	910.5
40°	696.9
42.5°	600.2
45°	538.8
47.5°	486.0
50°	442.1
52.5°	404.0
55°	371.9
57.5°	333.8
60°	295.7
62.5°	257.6
65°	225.5
67.5°	193.3
70°	161.0
72.5°	134.7
75°	108.3
77.5°	84.9
80°	64.5
82.5°	46.9
85°	29.3
87.5°	14.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)