

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585024

Luminaire Tested: **HCC8W55D010BZ-HM82555935-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W55D010BZ-HM82555935-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4991.2 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585024
CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P585024

CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80982	80982	80982
5°	82050	80639	79880
10°	82889	79814	78606
15°	83727	78131	76564
20°	83305	75246	73523
25°	81358	70743	69787
30°	77277	65669	65417
35°	70353	59922	60453
40°	61681	53630	55607
45°	53212	47704	51071
50°	46591	41880	46255
55°	41283	36004	40714
60°	37195	30269	33735
65°	33513	24305	25844
70°	29401	17698	14227
75°	25068	9186	3753
80°	19285	2504	622
85°	12383	0	0



TEST NUMBER: P585024
 CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.8	5.0
10°-20°	696.5	14.0
20°-30°	988.6	19.8
30°-40°	1040.7	20.9
40°-50°	885.3	17.7
50°-60°	639.8	12.8
60°-70°	363.9	7.3
70°-80°	114.6	2.3
80°-90°	13.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1933.0	38.7
0°-40°	2973.7	59.6
0°-60°	4498.7	90.1
0°-90°	4991.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4991.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2626	2626	2626	2626	2626	
5°	2651	2637	2605	2588	2581	253
15°	2623	2556	2447	2402	2398	739
25°	2391	2272	2079	2044	2051	1095
35°	1869	1760	1592	1581	1606	1163
45°	1220	1175	1094	1122	1171	948
55°	768	712	670	708	757	692
65°	459	396	333	330	354	456
75°	210	161	77	35	32	226
85°	35	21	0	0	0	45
90°	0	0	0	0	0	



TEST NUMBER: P585024

CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2
2.5°	2640.2	2643.7	2636.6	2636.6	2643.7	2636.6	2640.2	2640.2	2636.6	2636.6	2633.1
5°	2650.7	2647.2	2647.2	2647.2	2650.7	2643.7	2640.2	2643.7	2636.6	2636.6	2636.6
7.5°	2654.2	2654.2	2650.7	2647.2	2647.2	2647.2	2643.7	2640.2	2636.6	2629.6	2626.2
10°	2647.2	2647.2	2650.7	2643.7	2643.7	2636.6	2636.6	2629.6	2629.6	2622.7	2612.2
12.5°	2640.2	2636.6	2636.6	2629.6	2629.6	2622.7	2622.7	2612.2	2608.6	2598.1	2587.5
15°	2622.7	2619.2	2612.2	2608.6	2605.1	2601.6	2594.6	2591.1	2580.6	2566.6	2556.0
17.5°	2587.5	2584.1	2580.6	2573.6	2566.6	2563.0	2559.5	2549.0	2535.0	2524.5	2506.9
20°	2538.6	2535.0	2535.0	2524.5	2521.0	2510.4	2506.9	2493.0	2482.4	2461.3	2447.4
22.5°	2471.9	2475.4	2468.3	2461.3	2454.4	2443.9	2436.8	2422.8	2405.3	2384.2	2366.7
25°	2391.2	2394.7	2387.7	2380.7	2370.3	2363.2	2356.2	2335.1	2317.6	2293.0	2272.0
27.5°	2289.6	2289.6	2289.6	2282.6	2265.0	2261.5	2254.5	2233.5	2208.9	2187.9	2166.8
30°	2170.3	2166.8	2166.8	2156.4	2149.3	2135.3	2124.7	2107.3	2089.7	2065.2	2040.6
32.5°	2026.6	2030.1	2019.6	2012.6	2002.0	2002.0	1988.1	1974.0	1953.0	1928.4	1903.9
35°	1868.9	1872.3	1865.4	1861.8	1844.3	1840.7	1837.2	1819.8	1805.7	1788.1	1760.1
37.5°	1707.5	1704.0	1700.6	1700.6	1690.0	1683.0	1676.0	1665.4	1644.4	1630.4	1616.4
40°	1532.3	1532.3	1532.3	1528.8	1525.2	1518.2	1514.7	1507.7	1493.6	1479.6	1469.1
42.5°	1374.4	1374.4	1370.9	1367.4	1360.5	1364.0	1356.9	1349.9	1335.8	1325.3	1318.4
45°	1220.2	1220.2	1220.2	1223.7	1216.7	1206.1	1206.1	1199.1	1192.2	1185.1	1174.6
47.5°	1083.4	1093.9	1086.9	1083.4	1086.9	1072.8	1072.8	1065.9	1058.9	1051.9	1037.8
50°	971.2	971.2	971.2	964.2	960.7	960.7	950.1	943.2	939.7	932.7	918.6
52.5°	869.5	862.5	862.5	859.1	855.6	848.5	848.5	841.5	827.4	820.4	810.0
55°	767.9	767.9	764.4	760.9	757.3	753.8	750.3	739.8	732.9	722.3	711.8
57.5°	676.7	683.7	680.2	673.2	666.2	666.2	659.1	652.1	641.7	631.1	620.6
60°	603.1	599.6	599.6	596.1	589.0	585.5	582.0	571.5	561.0	550.5	539.9
62.5°	525.9	525.9	525.9	519.0	511.9	508.4	504.9	497.9	483.8	473.4	466.3
65°	459.3	455.8	452.3	448.8	445.2	438.3	434.8	427.8	417.2	406.7	396.3
67.5°	392.7	389.2	389.2	385.7	375.2	371.6	371.6	361.1	350.7	340.1	329.6
70°	326.1	326.1	326.1	319.0	315.5	312.1	308.6	301.6	291.0	280.5	270.0
72.5°	270.0	266.5	266.5	263.0	252.4	248.9	245.4	238.4	228.0	220.9	213.9
75°	210.4	210.4	206.9	203.3	199.8	196.3	192.8	185.9	175.3	164.8	161.3
77.5°	161.3	157.8	157.8	154.2	147.2	143.8	143.8	136.8	126.2	119.2	112.2
80°	108.6	112.2	108.6	105.1	101.7	98.2	94.7	91.2	84.1	77.1	70.1
82.5°	66.6	70.1	66.6	66.6	63.1	59.7	59.7	52.6	49.1	45.6	42.1
85°	35.0	35.0	35.0	35.0	31.5	31.5	31.5	28.0	24.5	21.0	21.0
87.5°	10.5	14.1	10.5	10.5	10.5	10.5	10.5	10.5	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585024

CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2
2.5°	2636.6	2633.1	2629.6	2629.6	2629.6	2629.6	2629.6	2626.2	2622.7	2622.7	2622.7
5°	2629.6	2629.6	2629.6	2626.2	2622.7	2622.7	2615.7	2612.2	2608.6	2605.1	2601.6
7.5°	2622.7	2615.7	2612.2	2608.6	2605.1	2605.1	2598.1	2591.1	2591.1	2584.1	2577.1
10°	2601.6	2598.1	2591.1	2584.1	2580.6	2577.1	2570.1	2559.5	2556.0	2549.0	2542.1
12.5°	2577.1	2570.1	2563.0	2549.0	2545.5	2542.1	2528.0	2517.5	2510.4	2506.9	2489.4
15°	2545.5	2531.5	2521.0	2503.4	2500.0	2493.0	2482.4	2471.9	2457.9	2447.4	2440.3
17.5°	2489.4	2475.4	2457.9	2440.3	2433.3	2433.3	2415.8	2401.8	2384.2	2377.2	2363.2
20°	2422.8	2405.3	2391.2	2370.3	2359.7	2349.2	2338.6	2317.6	2303.6	2293.0	2275.6
22.5°	2345.6	2321.1	2303.6	2282.6	2265.0	2254.5	2237.0	2219.4	2202.0	2191.4	2177.3
25°	2247.5	2226.4	2198.4	2177.3	2166.8	2152.8	2131.8	2114.3	2096.7	2079.2	2072.2
27.5°	2138.8	2110.8	2086.2	2061.7	2051.1	2040.6	2016.1	1995.1	1981.0	1963.5	1956.4
30°	2019.6	1991.6	1963.5	1942.5	1931.9	1914.3	1900.4	1875.8	1858.3	1844.3	1826.8
32.5°	1882.8	1861.8	1837.2	1805.7	1798.7	1784.7	1763.6	1753.1	1732.1	1721.6	1707.5
35°	1735.6	1721.6	1697.1	1672.4	1661.9	1655.0	1637.4	1616.4	1602.4	1591.8	1584.8
37.5°	1595.3	1577.7	1553.3	1535.7	1528.8	1518.2	1497.1	1486.7	1472.6	1465.6	1451.5
40°	1444.6	1427.0	1409.4	1399.0	1388.5	1381.4	1367.4	1356.9	1342.9	1332.3	1328.8
42.5°	1297.3	1286.7	1272.8	1258.7	1255.2	1244.7	1237.7	1227.2	1216.7	1213.1	1202.6
45°	1164.0	1153.6	1139.5	1125.5	1122.0	1114.9	1111.5	1101.0	1093.9	1093.9	1093.9
47.5°	1030.8	1020.3	1006.3	999.2	1002.8	988.7	988.7	985.3	978.3	978.3	981.8
50°	911.6	897.6	894.1	887.1	880.1	873.0	876.5	866.0	866.0	873.0	869.5
52.5°	799.4	785.4	781.8	774.9	771.4	771.4	767.9	767.9	764.4	767.9	767.9
55°	697.7	687.3	680.2	673.2	669.7	669.7	669.7	666.2	662.6	669.7	673.2
57.5°	606.6	603.1	596.1	585.5	582.0	578.5	575.0	575.0	575.0	575.0	578.5
60°	525.9	519.0	511.9	501.4	501.4	497.9	494.3	490.8	490.8	490.8	490.8
62.5°	455.8	445.2	434.8	427.8	424.3	420.7	417.2	410.2	410.2	410.2	410.2
65°	385.7	375.2	368.1	361.1	354.2	354.2	347.1	343.6	336.6	333.1	326.1
67.5°	319.0	312.1	305.1	294.5	291.0	287.5	280.5	276.9	266.5	263.0	259.5
70°	259.5	248.9	241.9	234.9	231.4	224.4	217.4	210.4	203.3	196.3	189.3
72.5°	203.3	192.8	185.9	178.8	171.8	171.8	161.3	154.2	143.8	136.8	126.2
75°	150.7	140.3	133.3	122.7	119.2	115.7	105.1	98.2	87.7	77.1	70.1
77.5°	101.7	94.7	87.7	77.1	70.1	70.1	59.7	52.6	45.6	35.0	31.5
80°	63.1	56.1	49.1	42.1	42.1	35.0	31.5	24.5	17.6	14.1	10.5
82.5°	35.0	31.5	28.0	21.0	21.0	17.6	14.1	10.5	7.0	3.5	3.5
85°	17.6	14.1	10.5	10.5	7.0	7.0	7.0	3.5	3.5	0.0	0.0
87.5°	7.0	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585024

CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2
2.5°	2619.2	2619.2	2615.7	2615.7	2615.7	2612.2	2615.7	2612.2	2612.2	2612.2	2615.7
5°	2605.1	2598.1	2598.1	2594.6	2594.6	2591.1	2594.6	2591.1	2587.5	2584.1	2587.5
7.5°	2577.1	2570.1	2566.6	2563.0	2563.0	2563.0	2559.5	2556.0	2559.5	2549.0	2556.0
10°	2538.6	2535.0	2528.0	2524.5	2521.0	2524.5	2521.0	2513.9	2513.9	2513.9	2510.4
12.5°	2489.4	2482.4	2478.9	2475.4	2468.3	2468.3	2471.9	2464.8	2464.8	2457.9	2457.9
15°	2429.8	2422.8	2415.8	2415.8	2408.8	2408.8	2405.3	2405.3	2401.8	2398.3	2398.3
17.5°	2356.2	2345.6	2338.6	2342.1	2338.6	2335.1	2335.1	2328.2	2324.7	2328.2	2328.2
20°	2268.5	2261.5	2254.5	2258.0	2250.9	2247.5	2250.9	2240.5	2244.0	2244.0	2244.0
22.5°	2170.3	2166.8	2156.4	2156.4	2149.3	2145.8	2149.3	2149.3	2152.8	2149.3	2149.3
25°	2061.7	2054.6	2047.6	2047.6	2044.1	2040.6	2044.1	2047.6	2044.1	2047.6	2047.6
27.5°	1946.0	1935.4	1935.4	1928.4	1928.4	1931.9	1928.4	1931.9	1935.4	1935.4	1942.5
30°	1819.8	1816.2	1812.7	1809.2	1809.2	1812.7	1812.7	1812.7	1816.2	1823.3	1823.3
32.5°	1700.6	1693.5	1686.5	1686.5	1693.5	1690.0	1693.5	1693.5	1700.6	1700.6	1707.5
35°	1570.8	1570.8	1563.8	1567.3	1567.3	1567.3	1567.3	1574.3	1581.3	1584.8	1591.8
37.5°	1451.5	1441.1	1444.6	1444.6	1448.1	1444.6	1455.0	1455.0	1462.1	1462.1	1469.1
40°	1321.9	1321.9	1325.3	1321.9	1325.3	1325.3	1332.3	1339.4	1342.9	1349.9	1353.4
42.5°	1199.1	1206.1	1199.1	1202.6	1206.1	1209.6	1213.1	1216.7	1230.7	1237.7	1248.2
45°	1086.9	1090.4	1093.9	1097.5	1093.9	1101.0	1104.5	1111.5	1122.0	1125.5	1129.0
47.5°	978.3	981.8	985.3	988.7	988.7	995.7	999.2	1006.3	1013.3	1016.8	1020.3
50°	873.0	880.1	883.6	883.6	887.1	894.1	901.2	901.2	908.1	918.6	922.1
52.5°	778.3	778.3	785.4	788.9	792.4	792.4	802.9	806.5	810.0	817.0	823.9
55°	673.2	683.7	687.3	687.3	694.2	701.2	704.7	708.2	708.2	722.3	722.3
57.5°	582.0	585.5	592.6	592.6	592.6	603.1	603.1	610.0	613.5	617.1	624.1
60°	490.8	497.9	497.9	501.4	497.9	504.9	508.4	515.4	519.0	522.5	525.9
62.5°	406.7	406.7	410.2	410.2	410.2	410.2	417.2	417.2	424.3	427.8	431.3
65°	326.1	326.1	326.1	326.1	326.1	326.1	326.1	326.1	329.6	329.6	336.6
67.5°	252.4	248.9	241.9	245.4	241.9	241.9	238.4	238.4	241.9	241.9	248.9
70°	182.4	178.8	171.8	171.8	168.3	164.8	161.3	157.8	154.2	154.2	154.2
72.5°	119.2	112.2	101.7	98.2	98.2	91.2	84.1	80.6	80.6	80.6	80.6
75°	59.7	52.6	45.6	42.1	42.1	35.0	38.6	35.0	35.0	35.0	35.0
77.5°	24.5	17.6	14.1	14.1	14.1	10.5	10.5	10.5	10.5	10.5	10.5
80°	7.0	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585024

CATALOG NUMBER: HCC8W55D010BZ-HM82555935-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2	2626.2
2.5°	2612.2	2612.2	2605.1	2608.6	2608.6	2608.6	2608.6	2608.6
5°	2580.6	2584.1	2580.6	2584.1	2584.1	2580.6	2580.6	2580.6
7.5°	2549.0	2552.5	2549.0	2552.5	2552.5	2552.5	2549.0	2549.0
10°	2510.4	2510.4	2510.4	2510.4	2510.4	2506.9	2510.4	2510.4
12.5°	2457.9	2457.9	2457.9	2461.3	2461.3	2457.9	2457.9	2454.4
15°	2401.8	2394.7	2398.3	2401.8	2398.3	2398.3	2398.3	2398.3
17.5°	2324.7	2328.2	2324.7	2324.7	2324.7	2324.7	2328.2	2324.7
20°	2244.0	2244.0	2247.5	2244.0	2244.0	2244.0	2244.0	2240.5
22.5°	2152.8	2149.3	2149.3	2152.8	2152.8	2149.3	2152.8	2152.8
25°	2051.1	2054.6	2051.1	2051.1	2054.6	2054.6	2054.6	2051.1
27.5°	1942.5	1946.0	1949.5	1946.0	1946.0	1946.0	1949.5	1953.0
30°	1830.2	1837.2	1830.2	1830.2	1837.2	1833.7	1837.2	1837.2
32.5°	1711.0	1721.6	1714.5	1721.6	1721.6	1725.1	1721.6	1725.1
35°	1591.8	1602.4	1602.4	1602.4	1605.9	1609.4	1609.4	1605.9
37.5°	1479.6	1483.2	1483.2	1490.2	1493.6	1497.1	1497.1	1493.6
40°	1364.0	1370.9	1374.4	1374.4	1374.4	1381.4	1388.5	1381.4
42.5°	1251.7	1255.2	1258.7	1258.7	1265.8	1269.3	1272.8	1272.8
45°	1143.1	1150.1	1153.6	1157.0	1160.5	1167.5	1164.0	1171.1
47.5°	1030.8	1041.3	1044.8	1048.4	1055.4	1058.9	1062.4	1065.9
50°	929.2	936.2	936.2	943.2	953.7	953.7	960.7	964.2
52.5°	827.4	830.9	834.5	838.0	845.0	852.0	852.0	859.1
55°	729.3	732.9	732.9	736.3	739.8	753.8	757.3	757.3
57.5°	627.6	627.6	634.6	638.2	641.7	648.7	648.7	648.7
60°	529.4	532.9	532.9	536.4	539.9	547.0	550.5	547.0
62.5°	431.3	434.8	434.8	438.3	445.2	448.8	445.2	445.2
65°	340.1	343.6	343.6	347.1	354.2	354.2	350.7	354.2
67.5°	248.9	248.9	248.9	248.9	248.9	248.9	248.9	248.9
70°	157.8	154.2	150.7	154.2	154.2	154.2	150.7	157.8
72.5°	77.1	80.6	80.6	80.6	80.6	80.6	80.6	77.1
75°	35.0	35.0	31.5	31.5	31.5	35.0	35.0	31.5
77.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)