

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593874

Luminaire Tested: **HCC8S60D010MB-HM86080950-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593874  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MB-HM86080950-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6275.4 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593874  
CATALOG NUMBER: HCC8S60D010MB-HM86080950-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P593874  
 CATALOG NUMBER: HCC8S60D010MB-HM86080950-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90	90	90	90	90	90	90	90	90	90	90																
	2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81	81	81	81	81	81	81	81	81	81	81																
	3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73	73	73	73	73	73	73	73	73	73	73																
	4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65	65	65	65	65	65	65	65	65	65	65																
	5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59	59	59	59	59	59	59	59																
	6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54	54	54	54	54	54	54	54	54	54	54																
	7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49	49	49	49	49	49	49	49	49	49	49																
	8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45	45	45	45	45	45	45	45	45	45	45																
	9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41	41	41	41	41	41	41	41	41	41	41																
	10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38	38	38	38	38	38	38	38	38	38	38																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	110209
	5°	109454
	10°	109166
	15°	112031
	20°	121285
	25°	130030
	30°	127123
	35°	105855
	40°	65034
	45°	45031
	50°	34368
	55°	22531
	60°	14098
	65°	10565
	70°	10648
	75°	12260
	80°	13532
	85°	12136



TEST NUMBER: P593874  
 CATALOG NUMBER: HCC8S60D010MB-HM86080950-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.0	5.4
10°-20°	1007.4	16.1
20°-30°	1734.2	27.6
30°-40°	1680.2	26.8
40°-50°	827.6	13.2
50°-60°	390.5	6.2
60°-70°	153.9	2.5
70°-80°	106.2	1.7
80°-90°	39.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3077.6	49.0
0°-40°	4757.8	75.8
0°-60°	5975.9	95.2
0°-90°	6275.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6275.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3574	
5°	3536	336
15°	3509	1007
25°	3822	1734
35°	2812	1680
45°	1033	828
55°	419	391
65°	145	154
75°	103	106
85°	34	39
90°	0	



TEST NUMBER: P593874  
CATALOG NUMBER: HCC8S60D010MB-HM86080950-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3574.0
2.5°	3562.6
5°	3536.0
7.5°	3509.3
10°	3486.4
12.5°	3482.6
15°	3509.3
17.5°	3589.3
20°	3696.0
22.5°	3791.2
25°	3821.7
27.5°	3753.2
30°	3570.2
32.5°	3269.2
35°	2812.0
37.5°	2183.3
40°	1615.6
42.5°	1253.6
45°	1032.6
47.5°	868.7
50°	716.4
52.5°	563.9
55°	419.1
57.5°	304.8
60°	228.6
62.5°	179.1
65°	144.8
67.5°	125.7
70°	118.1
72.5°	110.5
75°	102.9
77.5°	91.5
80°	76.2
82.5°	57.2
85°	34.3
87.5°	15.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)