

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585196

Luminaire Tested: **HCC8W80D010SL-HM86080827-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585196  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010SL-HM86080827-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6238.7 lumens  
Efficiency: N/A  
Efficacy: 89.1 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585196  
CATALOG NUMBER: HCC8W80D010SL-HM86080827-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P585196

CATALOG NUMBER: HCC8W80D010SL-HM86080827-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116891
5°	115920
10°	114389
15°	115696
20°	124938
25°	136627
30°	134974
35°	111961
40°	65896
45°	43051
50°	33375
55°	22166
60°	10787
65°	3342
70°	1127
75°	989
80°	746
85°	1486



TEST NUMBER: P585196  
 CATALOG NUMBER: HCC8W80D010SL-HM86080827-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	354.6	5.7
10°-20°	1041.2	16.7
20°-30°	1820.4	29.2
30°-40°	1770.8	28.4
40°-50°	805.3	12.9
50°-60°	373.4	6.0
60°-70°	62.5	1.0
70°-80°	7.7	0.1
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3216.2	51.6
0°-40°	4986.9	79.9
0°-60°	6165.6	98.8
0°-90°	6238.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6238.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3791	
5°	3745	355
15°	3624	1041
25°	4016	1820
35°	2974	1771
45°	987	805
55°	412	373
65°	46	63
75°	8	8
85°	4	3
90°	0	



TEST NUMBER: P585196  
CATALOG NUMBER: HCC8W80D010SL-HM86080827-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3790.7
2.5°	3782.3
5°	3744.9
7.5°	3703.1
10°	3653.2
12.5°	3615.7
15°	3624.1
17.5°	3690.7
20°	3807.3
22.5°	3940.6
25°	4015.6
27.5°	3974.0
30°	3790.7
32.5°	3470.0
35°	2974.2
37.5°	2291.1
40°	1637.0
42.5°	1220.5
45°	987.2
47.5°	833.1
50°	695.7
52.5°	554.1
55°	412.3
57.5°	283.2
60°	174.9
62.5°	95.8
65°	45.8
67.5°	20.8
70°	12.5
72.5°	8.3
75°	8.3
77.5°	4.2
80°	4.2
82.5°	4.2
85°	4.2
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)