

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585202

Luminaire Tested: **HCC8S80D010MB-HM86080827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010MB-HM86080827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5663.9 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585202
CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585202

CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	94637	94637	94637
5°	97964	94094	90358
10°	100139	92446	85275
15°	101563	89333	79628
20°	101258	84995	73926
25°	98755	79484	67868
30°	93560	73097	62273
35°	85117	66148	56591
40°	74760	58835	51127
45°	65191	51751	45580
50°	56733	45349	40158
55°	50595	39848	34929
60°	45971	34925	29794
65°	41320	30383	27041
70°	36794	25912	24397
75°	32240	21827	20838
80°	27365	17758	18504
85°	20627	13268	14718



TEST NUMBER: P585202
 CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.5	5.1
10°-20°	792.0	14.0
20°-30°	1099.4	19.4
30°-40°	1136.7	20.1
40°-50°	951.8	16.8
50°-60°	690.9	12.2
60°-70°	436.0	7.7
70°-80°	216.0	3.8
80°-90°	53.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2178.9	38.5
0°-40°	3315.6	58.5
0°-60°	4958.3	87.5
0°-90°	5663.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5663.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3069	3069	3069	3069	3069	
5°	3165	3127	3040	2957	2919	303
15°	3181	3061	2798	2574	2494	895
25°	2902	2715	2336	2082	1995	1330
35°	2261	2094	1757	1557	1503	1408
45°	1495	1387	1187	1070	1045	1156
55°	941	858	741	679	650	849
65°	566	496	416	366	371	565
75°	271	225	183	175	175	290
85°	58	46	38	42	42	71
90°	0	0	0	0	0	



TEST NUMBER: P585202

CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0
2.5°	3119.0	3119.0	3123.1	3119.0	3119.0	3119.0	3114.8	3114.8	3110.7	3110.7	3102.3
5°	3164.8	3156.4	3164.8	3156.4	3156.4	3156.4	3152.3	3144.0	3139.8	3131.5	3127.3
7.5°	3185.6	3181.4	3181.4	3177.2	3177.2	3173.1	3168.9	3164.8	3148.1	3144.0	3131.5
10°	3198.1	3193.9	3193.9	3189.7	3181.4	3181.4	3173.1	3168.9	3148.1	3139.8	3123.1
12.5°	3193.9	3193.9	3193.9	3189.7	3177.2	3173.1	3164.8	3152.3	3135.6	3119.0	3102.3
15°	3181.4	3181.4	3173.1	3168.9	3156.4	3148.1	3144.0	3123.1	3106.5	3085.7	3060.7
17.5°	3139.8	3139.8	3135.6	3127.3	3114.8	3106.5	3098.2	3077.4	3060.7	3027.3	3002.3
20°	3085.7	3081.5	3077.4	3064.9	3052.3	3048.1	3035.6	3006.5	2985.7	2960.7	2927.4
22.5°	3006.5	3002.3	2998.2	2989.9	2969.1	2960.7	2952.4	2931.6	2894.1	2869.2	2827.4
25°	2902.5	2902.5	2894.1	2881.7	2860.7	2852.4	2839.9	2819.1	2785.8	2748.4	2715.1
27.5°	2781.7	2777.5	2765.0	2756.7	2740.1	2727.6	2706.8	2681.7	2648.4	2619.2	2577.6
30°	2627.6	2627.6	2619.2	2606.8	2586.0	2577.6	2561.0	2531.9	2498.6	2461.0	2431.9
32.5°	2452.7	2452.7	2440.2	2431.9	2419.4	2398.6	2394.4	2361.1	2332.0	2302.7	2269.4
35°	2261.1	2265.3	2257.0	2240.3	2219.5	2219.5	2211.2	2182.1	2148.8	2119.5	2094.5
37.5°	2069.6	2057.1	2052.9	2044.6	2032.1	2015.5	2007.2	1994.7	1965.5	1944.7	1907.2
40°	1857.2	1861.4	1853.1	1844.7	1840.6	1828.1	1823.9	1803.1	1782.3	1757.2	1740.6
42.5°	1665.7	1665.7	1665.7	1657.3	1649.0	1636.5	1632.4	1619.9	1594.9	1578.3	1553.2
45°	1494.9	1482.4	1482.4	1478.3	1474.1	1465.8	1453.3	1445.0	1428.3	1415.9	1386.6
47.5°	1328.4	1332.5	1328.4	1324.2	1311.7	1307.5	1303.4	1286.7	1270.1	1257.6	1236.8
50°	1182.6	1190.9	1182.6	1182.6	1174.3	1170.1	1161.8	1149.3	1136.8	1116.0	1095.2
52.5°	1061.9	1061.9	1057.7	1053.6	1041.1	1032.8	1028.6	1024.4	1003.5	986.9	970.2
55°	941.1	945.3	945.3	932.8	928.6	920.3	916.1	903.6	895.3	870.3	857.9
57.5°	837.1	832.9	837.1	828.6	820.3	812.0	807.8	799.5	787.0	770.4	753.7
60°	745.4	737.1	737.1	732.9	724.6	720.4	712.1	699.6	687.1	670.5	658.0
62.5°	653.8	649.7	645.4	641.2	632.9	628.7	624.6	612.1	599.6	587.1	574.6
65°	566.3	566.3	562.2	553.8	549.7	545.5	541.4	533.0	516.4	508.1	495.6
67.5°	487.3	483.1	483.1	474.8	466.4	462.2	462.2	453.8	441.4	428.9	420.5
70°	408.1	412.2	408.1	403.9	395.6	395.6	387.3	383.1	366.4	362.3	349.8
72.5°	337.3	337.3	333.2	333.2	324.8	320.7	320.7	312.4	304.0	295.7	287.4
75°	270.6	270.6	270.6	266.5	262.3	254.0	254.0	249.8	241.5	233.2	224.8
77.5°	212.4	208.2	208.2	204.0	199.9	195.7	195.7	191.5	183.2	179.1	170.7
80°	154.1	149.9	149.9	149.9	141.6	145.8	141.6	137.4	133.3	129.1	125.0
82.5°	100.0	104.2	104.2	100.0	95.8	95.8	95.8	91.6	91.6	87.4	83.2
85°	58.3	58.3	58.3	58.3	54.1	54.1	54.1	49.9	49.9	49.9	45.8
87.5°	25.0	25.0	25.0	25.0	25.0	25.0	20.8	20.8	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585202

CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0
2.5°	3102.3	3094.0	3089.9	3085.7	3085.7	3081.5	3077.4	3069.0	3069.0	3060.7	3056.6
5°	3119.0	3106.5	3098.2	3089.9	3085.7	3077.4	3069.0	3056.6	3052.3	3039.8	3027.3
7.5°	3123.1	3102.3	3094.0	3077.4	3069.0	3060.7	3044.0	3031.5	3014.8	3002.3	2985.7
10°	3106.5	3089.9	3069.0	3048.1	3044.0	3031.5	3006.5	2989.9	2969.1	2952.4	2927.4
12.5°	3081.5	3056.6	3035.6	3010.7	2998.2	2985.7	2960.7	2935.8	2906.6	2877.5	2852.4
15°	3039.8	3010.7	2981.5	2952.4	2935.8	2923.3	2894.1	2864.9	2835.8	2798.3	2773.3
17.5°	2977.4	2944.1	2915.0	2877.5	2860.7	2848.2	2810.8	2777.5	2740.1	2702.6	2677.5
20°	2898.3	2856.6	2823.3	2781.7	2769.2	2748.4	2710.9	2673.3	2631.7	2590.1	2561.0
22.5°	2794.2	2752.5	2715.1	2673.3	2652.5	2631.7	2594.3	2548.5	2506.9	2473.5	2444.3
25°	2673.3	2635.9	2590.1	2552.7	2527.7	2502.7	2461.0	2423.5	2386.1	2336.1	2306.9
27.5°	2540.2	2494.3	2461.0	2411.1	2386.1	2369.4	2323.7	2273.6	2240.3	2194.5	2161.2
30°	2390.2	2348.6	2311.1	2261.1	2236.2	2219.5	2177.9	2132.1	2098.7	2052.9	2019.6
32.5°	2232.0	2186.2	2140.4	2107.0	2077.9	2061.3	2015.5	1986.3	1944.7	1907.2	1869.7
35°	2061.3	2015.5	1982.2	1936.3	1919.6	1903.0	1865.5	1828.1	1790.6	1757.2	1728.1
37.5°	1878.0	1844.7	1807.3	1774.0	1761.5	1744.7	1699.0	1665.7	1636.5	1603.2	1578.3
40°	1699.0	1669.8	1644.9	1611.6	1590.8	1578.3	1544.9	1515.7	1482.4	1461.6	1436.7
42.5°	1536.5	1503.3	1478.3	1453.3	1432.5	1420.0	1390.9	1370.0	1345.0	1324.2	1295.1
45°	1365.8	1349.2	1320.0	1299.2	1286.7	1270.1	1249.3	1224.3	1203.5	1186.7	1165.9
47.5°	1216.0	1199.2	1178.4	1153.4	1145.1	1132.6	1111.8	1095.2	1078.5	1061.9	1041.1
50°	1078.5	1057.7	1041.1	1024.4	1016.0	1003.5	982.7	974.4	961.9	945.3	932.8
52.5°	953.6	936.9	920.3	899.5	895.3	887.0	874.5	857.9	845.4	837.1	828.6
55°	841.2	824.5	812.0	795.3	791.2	782.8	766.2	757.9	749.5	741.2	732.9
57.5°	741.2	724.6	707.9	699.6	691.3	683.0	678.8	666.3	658.0	653.8	645.4
60°	649.7	632.9	620.4	607.9	603.8	599.6	591.3	583.0	574.6	566.3	562.2
62.5°	562.2	545.5	537.2	528.9	520.5	520.5	512.2	503.9	495.6	491.4	483.1
65°	483.1	474.8	462.2	449.7	445.5	445.5	433.0	428.9	424.7	416.4	408.1
67.5°	408.1	399.7	387.3	383.1	378.9	374.8	370.6	362.3	354.0	349.8	341.5
70°	341.5	333.2	324.8	320.7	316.5	312.4	304.0	299.9	291.5	287.4	283.2
72.5°	274.8	270.6	262.3	258.1	254.0	249.8	245.6	241.5	233.2	229.0	224.8
75°	220.7	216.5	208.2	204.0	199.9	199.9	195.7	187.4	183.2	183.2	179.1
77.5°	166.6	162.4	158.3	154.1	149.9	149.9	145.8	141.6	137.4	137.4	133.3
80°	120.8	116.6	112.5	112.5	112.5	108.3	104.2	104.2	100.0	100.0	95.8
82.5°	79.1	79.1	74.9	74.9	74.9	70.7	70.7	66.6	66.6	66.6	66.6
85°	45.8	45.8	45.8	41.6	41.6	41.6	41.6	41.6	41.6	37.5	41.6
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585202

CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0
2.5°	3052.3	3048.1	3039.8	3039.8	3031.5	3031.5	3027.3	3023.2	3019.0	3014.8	3010.7
5°	3023.2	3006.5	2998.2	2994.0	2985.7	2981.5	2969.1	2960.7	2956.6	2948.2	2939.9
7.5°	2969.1	2952.4	2935.8	2931.6	2927.4	2910.8	2898.3	2885.8	2877.5	2869.2	2860.7
10°	2906.6	2890.0	2869.2	2860.7	2852.4	2831.6	2815.0	2802.5	2785.8	2769.2	2765.0
12.5°	2831.6	2806.6	2781.7	2773.3	2760.9	2740.1	2723.4	2702.6	2690.1	2669.2	2665.0
15°	2744.2	2715.1	2694.3	2673.3	2665.0	2644.2	2615.1	2598.4	2573.5	2565.1	2544.3
17.5°	2640.1	2610.9	2581.8	2573.5	2561.0	2531.9	2502.7	2481.8	2456.8	2444.3	2431.9
20°	2531.9	2494.3	2465.2	2456.8	2440.2	2415.2	2386.1	2365.3	2344.5	2319.5	2306.9
22.5°	2406.9	2365.3	2340.3	2319.5	2315.3	2286.1	2252.8	2236.2	2219.5	2198.7	2182.1
25°	2269.4	2232.0	2202.9	2186.2	2177.9	2152.9	2127.8	2107.0	2082.1	2069.6	2048.8
27.5°	2127.8	2102.9	2065.4	2048.8	2036.3	2015.5	1986.3	1973.9	1948.9	1932.1	1919.6
30°	1990.5	1953.1	1932.1	1911.3	1898.8	1878.0	1853.1	1840.6	1819.8	1803.1	1790.6
32.5°	1840.6	1815.6	1786.5	1778.1	1761.5	1740.6	1723.9	1703.1	1686.5	1669.8	1665.7
35°	1703.1	1669.8	1640.7	1632.4	1619.9	1599.1	1590.8	1578.3	1557.4	1553.2	1536.5
37.5°	1553.2	1536.5	1503.3	1490.8	1486.6	1470.0	1453.3	1445.0	1432.5	1420.0	1415.9
40°	1411.7	1390.9	1374.1	1361.6	1353.3	1340.8	1324.2	1320.0	1311.7	1295.1	1290.9
42.5°	1278.4	1257.6	1241.0	1236.8	1224.3	1211.8	1203.5	1190.9	1186.7	1182.6	1174.3
45°	1149.3	1136.8	1120.2	1116.0	1111.8	1095.2	1086.9	1078.5	1070.2	1066.1	1057.7
47.5°	1032.8	1020.3	1007.7	1003.5	995.2	991.0	978.5	974.4	961.9	957.7	953.6
50°	920.3	912.0	903.6	899.5	891.2	887.0	878.7	870.3	862.0	857.9	853.7
52.5°	820.3	812.0	803.6	799.5	795.3	787.0	778.7	770.4	766.2	762.0	757.9
55°	724.6	716.3	712.1	707.9	703.8	699.6	687.1	683.0	678.8	674.6	666.3
57.5°	637.1	628.7	620.4	620.4	616.3	612.1	603.8	595.5	595.5	587.1	578.8
60°	558.0	549.7	541.4	537.2	533.0	524.7	520.5	516.4	512.2	508.1	499.7
62.5°	474.8	470.6	462.2	462.2	453.8	449.7	445.5	441.4	437.2	428.9	424.7
65°	403.9	399.7	391.4	387.3	387.3	383.1	374.8	370.6	366.4	366.4	362.3
67.5°	337.3	333.2	324.8	320.7	320.7	316.5	312.4	312.4	308.2	304.0	308.2
70°	279.1	270.6	270.6	266.5	266.5	262.3	258.1	258.1	258.1	262.3	262.3
72.5°	220.7	216.5	212.4	212.4	212.4	212.4	208.2	208.2	212.4	216.5	216.5
75°	174.9	170.7	170.7	170.7	166.6	166.6	170.7	170.7	174.9	174.9	174.9
77.5°	129.1	129.1	129.1	129.1	129.1	129.1	133.3	133.3	137.4	137.4	137.4
80°	95.8	95.8	95.8	95.8	95.8	100.0	100.0	100.0	100.0	100.0	104.2
82.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	70.7	70.7	70.7	70.7
85°	37.5	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585202

CATALOG NUMBER: HCC8S80D010MB-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0	3069.0
2.5°	3006.5	3006.5	3006.5	3010.7	3002.3	3002.3	3002.3	3002.3
5°	2935.8	2931.6	2927.4	2931.6	2923.3	2923.3	2919.1	2919.1
7.5°	2848.2	2844.1	2839.9	2839.9	2831.6	2831.6	2827.4	2823.3
10°	2752.5	2744.2	2748.4	2740.1	2735.9	2731.7	2727.6	2723.4
12.5°	2648.4	2640.1	2635.9	2627.6	2619.2	2615.1	2619.2	2610.9
15°	2536.0	2523.5	2519.4	2511.0	2502.7	2498.6	2498.6	2494.3
17.5°	2411.1	2402.7	2398.6	2390.2	2386.1	2377.8	2373.6	2369.4
20°	2294.4	2273.6	2277.8	2269.4	2265.3	2248.6	2248.6	2252.8
22.5°	2165.4	2152.9	2144.6	2136.3	2132.1	2123.7	2123.7	2119.5
25°	2036.3	2023.8	2019.6	2011.3	2007.2	1998.8	1994.7	1994.7
27.5°	1911.3	1894.7	1894.7	1886.3	1878.0	1873.9	1869.7	1865.5
30°	1778.1	1765.7	1761.5	1761.5	1757.2	1757.2	1744.7	1748.9
32.5°	1653.2	1644.9	1640.7	1632.4	1632.4	1628.2	1628.2	1615.7
35°	1528.2	1515.7	1519.9	1511.6	1507.4	1503.3	1507.4	1503.3
37.5°	1407.5	1399.2	1399.2	1390.9	1390.9	1386.6	1382.5	1390.9
40°	1286.7	1282.6	1278.4	1274.3	1278.4	1274.3	1265.9	1270.1
42.5°	1165.9	1165.9	1161.8	1161.8	1157.6	1157.6	1157.6	1157.6
45°	1057.7	1053.6	1053.6	1049.4	1049.4	1049.4	1049.4	1045.2
47.5°	949.4	945.3	945.3	945.3	941.1	941.1	936.9	941.1
50°	845.4	845.4	841.2	841.2	845.4	841.2	837.1	837.1
52.5°	749.5	749.5	745.4	745.4	741.2	737.1	741.2	741.2
55°	662.2	658.0	653.8	653.8	649.7	645.4	645.4	649.7
57.5°	578.8	574.6	570.5	570.5	562.2	558.0	558.0	558.0
60°	499.7	491.4	491.4	487.3	487.3	483.1	483.1	483.1
62.5°	424.7	420.5	420.5	420.5	420.5	416.4	416.4	416.4
65°	362.3	362.3	362.3	366.4	366.4	370.6	370.6	370.6
67.5°	312.4	316.5	316.5	316.5	320.7	320.7	320.7	316.5
70°	266.5	266.5	266.5	270.6	270.6	270.6	270.6	270.6
72.5°	220.7	220.7	220.7	220.7	220.7	220.7	220.7	220.7
75°	174.9	179.1	179.1	179.1	174.9	179.1	179.1	174.9
77.5°	137.4	137.4	137.4	137.4	137.4	137.4	137.4	137.4
80°	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2
82.5°	70.7	70.7	70.7	70.7	70.7	70.7	70.7	70.7
85°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)