

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585065

Luminaire Tested: **HCC8S60D010MW-HM86080827-81WWBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585065  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MW-HM86080827-81WWBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4344.3 lumens  
Efficiency: N/A  
Efficacy: 77.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585065  
CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585065

CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	71920	71920	71920
5°	74890	71761	68743
10°	77394	70843	65386
15°	79354	69224	61993
20°	79508	66353	58917
25°	78164	62155	55868
30°	73980	57348	53253
35°	67455	51576	50003
40°	58658	45467	46167
45°	50325	39375	42266
50°	42984	33950	37961
55°	37671	29235	32988
60°	33538	24940	27734
65°	29755	20350	22130
70°	26399	15093	12568
75°	22018	7887	3741
80°	17332	2486	622
85°	12312	1238	0



TEST NUMBER: P585065  
 CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.8	5.1
10°-20°	616.0	14.2
20°-30°	871.8	20.1
30°-40°	912.1	21.0
40°-50°	760.7	17.5
50°-60°	539.5	12.4
60°-70°	310.7	7.2
70°-80°	100.0	2.3
80°-90°	13.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1707.5	39.3
0°-40°	2619.6	60.3
0°-60°	3919.8	90.2
0°-90°	4344.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4344.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2332	2332	2332	2332	2332	
5°	2419	2388	2318	2249	2221	232
15°	2486	2384	2168	1998	1942	699
25°	2297	2126	1827	1680	1642	1048
35°	1792	1635	1370	1297	1328	1111
45°	1154	1060	903	913	969	894
55°	701	628	544	572	614	633
65°	408	342	279	279	303	408
75°	185	136	66	31	31	200
85°	35	17	4	0	0	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585065

CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3
2.5°	2381.1	2377.6	2374.0	2377.6	2374.0	2377.6	2374.0	2374.0	2370.6	2367.1	2367.1
5°	2419.4	2415.9	2415.9	2415.9	2412.5	2409.0	2409.0	2405.4	2398.5	2395.0	2388.0
7.5°	2443.8	2447.3	2447.3	2447.3	2440.4	2440.4	2433.3	2426.4	2419.4	2412.5	2402.0
10°	2471.7	2471.7	2468.3	2464.7	2457.8	2454.3	2450.7	2443.8	2433.3	2419.4	2409.0
12.5°	2482.1	2482.1	2478.7	2471.7	2468.3	2464.7	2461.2	2450.7	2436.9	2419.4	2405.4
15°	2485.7	2478.7	2475.2	2471.7	2464.7	2454.3	2454.3	2440.4	2422.9	2402.0	2384.5
17.5°	2457.8	2461.2	2454.3	2447.3	2436.9	2429.9	2419.4	2409.0	2388.0	2363.7	2346.2
20°	2422.9	2419.4	2415.9	2405.4	2391.6	2388.0	2377.6	2360.2	2342.7	2314.9	2290.4
22.5°	2367.1	2363.7	2356.6	2349.7	2335.8	2328.8	2318.3	2297.3	2273.0	2245.1	2217.2
25°	2297.3	2290.4	2279.9	2266.0	2255.6	2248.6	2234.6	2213.7	2185.8	2154.4	2126.5
27.5°	2185.8	2196.3	2189.4	2168.4	2157.9	2144.1	2140.5	2112.7	2088.2	2056.9	2025.5
30°	2077.7	2077.7	2067.4	2056.9	2039.4	2028.9	2015.0	1994.1	1969.7	1931.4	1906.9
32.5°	1941.9	1938.3	1924.3	1920.9	1906.9	1886.0	1882.6	1854.7	1830.2	1802.4	1770.9
35°	1791.9	1784.9	1770.9	1760.5	1753.5	1743.1	1732.6	1708.2	1683.8	1655.9	1635.1
37.5°	1621.1	1621.1	1617.6	1600.1	1593.2	1586.3	1575.8	1551.3	1537.4	1509.6	1488.6
40°	1457.2	1453.7	1443.2	1439.8	1432.9	1422.4	1415.3	1401.5	1380.5	1359.6	1338.8
42.5°	1296.9	1300.3	1286.4	1289.8	1275.9	1269.0	1265.5	1244.5	1234.1	1213.1	1195.7
45°	1154.0	1150.4	1143.5	1140.0	1133.0	1126.1	1119.0	1108.6	1091.2	1070.2	1059.9
47.5°	1021.5	1011.0	1011.0	1007.5	1004.0	990.1	986.6	976.1	965.6	944.7	930.8
50°	896.0	896.0	896.0	892.5	882.0	878.5	871.5	861.1	850.6	836.7	815.8
52.5°	794.8	794.8	794.8	791.3	777.4	773.9	770.5	756.5	742.6	732.1	718.1
55°	700.7	704.3	700.7	693.8	683.3	683.3	672.8	665.9	651.9	641.4	627.6
57.5°	620.5	620.5	613.6	610.0	603.1	599.7	592.6	585.7	568.3	557.8	540.4
60°	543.8	540.4	540.4	533.3	526.4	519.5	515.9	505.5	498.5	481.1	467.1
62.5°	474.2	474.2	467.1	467.1	453.2	453.2	449.7	439.2	428.8	411.4	404.4
65°	407.8	407.8	404.4	400.9	390.4	387.0	383.5	373.0	362.5	352.1	341.6
67.5°	348.7	348.7	341.6	338.2	331.1	327.7	320.8	313.7	303.3	292.8	282.4
70°	292.8	289.4	285.8	282.4	275.4	272.0	264.9	258.0	247.5	240.6	230.1
72.5°	237.0	237.0	233.6	226.6	223.1	219.6	216.1	209.2	198.7	188.2	181.3
75°	184.8	184.8	184.8	177.7	170.8	167.4	167.4	160.3	153.4	142.9	136.0
77.5°	142.9	139.4	136.0	136.0	129.0	125.5	122.0	118.6	108.1	104.6	97.6
80°	97.6	101.2	97.6	94.1	90.7	87.2	87.2	80.2	76.7	69.8	62.7
82.5°	66.2	62.7	62.7	59.3	59.3	55.8	55.8	48.8	45.3	41.9	38.3
85°	34.8	34.8	31.4	31.4	31.4	27.9	27.9	24.5	24.5	20.9	17.4
87.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585065

CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3
2.5°	2363.7	2356.6	2353.2	2353.2	2349.7	2346.2	2342.7	2339.2	2332.3	2332.3	2325.3
5°	2381.1	2374.0	2370.6	2360.2	2353.2	2353.2	2339.2	2335.8	2325.3	2318.3	2311.3
7.5°	2395.0	2381.1	2370.6	2360.2	2353.2	2346.2	2332.3	2318.3	2304.4	2290.4	2283.5
10°	2395.0	2381.1	2363.7	2346.2	2339.2	2332.3	2314.9	2293.9	2276.5	2262.5	2245.1
12.5°	2388.0	2367.1	2346.2	2332.3	2318.3	2307.8	2287.0	2266.0	2245.1	2217.2	2203.2
15°	2367.1	2339.2	2318.3	2293.9	2283.5	2266.0	2248.6	2217.2	2192.8	2168.4	2151.0
17.5°	2325.3	2290.4	2266.0	2241.6	2224.2	2213.7	2185.8	2157.9	2130.1	2102.2	2081.3
20°	2262.5	2231.1	2203.2	2171.9	2157.9	2144.1	2109.1	2081.3	2053.4	2022.0	2001.0
22.5°	2185.8	2154.4	2116.1	2091.7	2070.8	2053.4	2022.0	1990.7	1962.7	1934.8	1906.9
25°	2091.7	2060.3	2025.5	1987.1	1973.2	1955.7	1920.9	1889.5	1858.1	1826.8	1802.4
27.5°	1990.7	1948.8	1920.9	1879.0	1865.2	1847.6	1809.3	1774.5	1746.6	1722.1	1694.3
30°	1868.6	1837.3	1798.8	1760.5	1746.6	1729.2	1697.8	1666.4	1638.5	1610.6	1582.7
32.5°	1736.1	1704.7	1666.4	1638.5	1617.6	1603.7	1572.3	1544.4	1516.5	1488.6	1464.2
35°	1596.7	1561.8	1533.9	1506.0	1488.6	1471.2	1439.8	1415.3	1394.5	1370.1	1345.7
37.5°	1453.7	1429.3	1401.5	1370.1	1352.6	1338.8	1314.3	1286.4	1269.0	1248.1	1230.7
40°	1314.3	1286.4	1262.1	1234.1	1220.2	1209.7	1185.3	1164.4	1146.9	1129.5	1119.0
42.5°	1171.4	1146.9	1122.6	1105.1	1094.7	1084.2	1066.8	1042.3	1031.9	1014.5	1004.0
45°	1038.9	1018.0	1000.6	976.1	969.2	962.2	941.3	923.9	913.4	902.9	896.0
47.5°	913.4	899.4	878.5	864.6	854.1	847.2	833.2	819.3	808.8	801.8	794.8
50°	805.3	787.9	773.9	760.0	753.1	742.6	728.6	721.7	714.6	707.7	707.7
52.5°	704.3	686.7	672.8	662.4	655.4	648.4	637.9	634.5	627.6	627.6	624.0
55°	610.0	599.7	585.7	571.7	568.3	564.8	557.8	550.9	547.3	543.8	547.3
57.5°	529.9	519.5	505.5	495.0	491.6	488.1	484.5	477.6	474.2	474.2	474.2
60°	456.7	446.3	435.8	425.3	425.3	418.3	414.9	411.4	407.8	404.4	404.4
62.5°	390.4	380.0	369.5	362.5	359.1	355.6	348.7	345.1	341.6	341.6	338.2
65°	331.1	317.3	313.7	303.3	299.8	296.3	292.8	285.8	282.4	278.9	275.4
67.5°	272.0	264.9	254.4	247.5	244.1	240.6	237.0	230.1	226.6	223.1	216.1
70°	219.6	212.7	205.7	198.7	195.3	191.7	184.8	177.7	174.3	167.4	156.9
72.5°	170.8	163.9	156.9	149.9	146.4	142.9	136.0	129.0	122.0	115.0	108.1
75°	129.0	122.0	111.5	104.6	101.2	101.2	90.7	83.6	76.7	66.2	59.3
77.5°	90.7	80.2	76.7	69.8	66.2	59.3	52.2	45.3	38.3	34.8	27.9
80°	59.3	52.2	45.3	41.9	38.3	34.8	31.4	24.5	17.4	14.0	10.5
82.5°	34.8	31.4	27.9	24.5	20.9	17.4	14.0	14.0	10.5	6.9	3.5
85°	17.4	14.0	10.5	10.5	6.9	6.9	6.9	3.5	3.5	3.5	3.5
87.5°	6.9	3.5	3.5	3.5	3.5	3.5	3.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585065

CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3
2.5°	2321.8	2318.3	2314.9	2311.3	2311.3	2304.4	2304.4	2300.9	2293.9	2290.4	2290.4
5°	2300.9	2290.4	2283.5	2279.9	2276.5	2266.0	2262.5	2255.6	2248.6	2241.6	2238.2
7.5°	2269.5	2252.1	2245.1	2241.6	2231.1	2220.8	2213.7	2203.2	2192.8	2182.3	2178.9
10°	2231.1	2213.7	2196.3	2189.4	2178.9	2171.9	2157.9	2144.1	2133.6	2123.1	2112.7
12.5°	2182.3	2161.5	2144.1	2137.0	2126.5	2112.7	2091.7	2084.8	2067.4	2060.3	2046.4
15°	2126.5	2102.2	2084.8	2074.3	2063.8	2042.9	2028.9	2015.0	1997.6	1990.7	1976.7
17.5°	2056.9	2028.9	2011.5	2001.0	1994.1	1976.7	1955.7	1938.3	1920.9	1914.0	1903.5
20°	1973.2	1955.7	1931.4	1920.9	1914.0	1893.0	1872.1	1865.2	1851.2	1837.3	1826.8
22.5°	1879.0	1861.6	1837.3	1826.8	1823.3	1805.9	1788.5	1778.0	1767.5	1757.1	1746.6
25°	1781.4	1760.5	1739.6	1732.6	1725.7	1711.8	1697.8	1690.8	1680.4	1673.4	1666.4
27.5°	1676.8	1655.9	1638.5	1628.0	1621.1	1610.6	1603.7	1596.7	1589.7	1582.7	1579.2
30°	1565.3	1544.4	1530.4	1523.4	1516.5	1513.0	1502.5	1499.1	1495.6	1488.6	1492.0
32.5°	1453.7	1436.3	1422.4	1411.9	1411.9	1405.0	1401.5	1401.5	1397.9	1397.9	1397.9
35°	1331.7	1321.2	1310.8	1307.4	1303.8	1300.3	1296.9	1300.3	1296.9	1300.3	1303.8
37.5°	1220.2	1209.7	1202.8	1199.3	1195.7	1199.3	1195.7	1195.7	1199.3	1206.2	1209.7
40°	1105.1	1098.2	1091.2	1094.7	1091.2	1091.2	1091.2	1101.6	1105.1	1108.6	1112.1
42.5°	997.0	990.1	986.6	986.6	990.1	986.6	993.5	997.0	1004.0	1014.5	1021.5
45°	892.5	888.9	888.9	892.5	888.9	896.0	896.0	902.9	913.4	920.3	927.3
47.5°	794.8	794.8	794.8	798.4	798.4	801.8	808.8	812.3	819.3	826.2	833.2
50°	704.3	707.7	711.2	711.2	711.2	718.1	725.1	728.6	732.1	735.6	746.0
52.5°	624.0	627.6	627.6	631.0	634.5	637.9	641.4	648.4	651.9	658.9	662.4
55°	547.3	547.3	554.3	557.8	557.8	557.8	564.8	564.8	571.7	575.2	582.2
57.5°	474.2	477.6	477.6	481.1	481.1	484.5	488.1	491.6	495.0	498.5	502.0
60°	404.4	404.4	404.4	407.8	411.4	414.9	411.4	418.3	418.3	425.3	428.8
62.5°	338.2	341.6	341.6	341.6	341.6	341.6	341.6	345.1	348.7	352.1	355.6
65°	275.4	275.4	275.4	272.0	275.4	272.0	275.4	278.9	278.9	282.4	285.8
67.5°	212.7	212.7	205.7	205.7	209.2	209.2	209.2	209.2	205.7	212.7	212.7
70°	153.4	149.9	146.4	142.9	142.9	139.4	139.4	136.0	136.0	136.0	136.0
72.5°	101.2	94.1	87.2	83.6	80.2	80.2	73.2	69.8	73.2	73.2	73.2
75°	52.2	45.3	41.9	38.3	34.8	34.8	31.4	31.4	31.4	31.4	31.4
77.5°	20.9	17.4	14.0	14.0	10.5	10.5	10.5	10.5	10.5	10.5	10.5
80°	6.9	6.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	3.5	0.0	0.0	3.5	0.0	3.5	3.5	3.5	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585065

CATALOG NUMBER: HCC8S60D010MW-HM86080827-81WWBB

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3	2332.3
2.5°	2287.0	2287.0	2283.5	2287.0	2279.9	2283.5	2279.9	2279.9
5°	2234.6	2227.7	2227.7	2227.7	2224.2	2224.2	2220.8	2220.8
7.5°	2171.9	2168.4	2164.9	2161.5	2157.9	2154.4	2154.4	2154.4
10°	2109.1	2102.2	2102.2	2098.7	2091.7	2088.2	2088.2	2088.2
12.5°	2036.0	2032.4	2028.9	2028.9	2015.0	2018.4	2015.0	2015.0
15°	1966.2	1962.7	1962.7	1952.2	1945.3	1945.3	1945.3	1941.9
17.5°	1893.0	1889.5	1886.0	1879.0	1872.1	1872.1	1868.6	1872.1
20°	1816.3	1812.8	1805.9	1805.9	1802.4	1798.8	1791.9	1795.4
22.5°	1739.6	1732.6	1729.2	1729.2	1725.7	1725.7	1718.7	1718.7
25°	1659.4	1655.9	1652.5	1655.9	1649.0	1649.0	1642.0	1642.0
27.5°	1575.8	1572.3	1572.3	1572.3	1568.7	1572.3	1568.7	1568.7
30°	1492.0	1492.0	1488.6	1488.6	1492.0	1488.6	1492.0	1495.6
32.5°	1401.5	1401.5	1405.0	1405.0	1408.4	1408.4	1408.4	1408.4
35°	1307.4	1314.3	1314.3	1317.8	1321.2	1324.8	1324.8	1328.3
37.5°	1220.2	1223.6	1227.1	1230.7	1237.6	1237.6	1237.6	1237.6
40°	1126.1	1129.5	1136.4	1133.0	1146.9	1150.4	1146.9	1146.9
42.5°	1028.4	1035.4	1038.9	1045.9	1049.4	1056.3	1059.9	1059.9
45°	937.8	941.3	948.2	955.2	958.7	969.2	969.2	969.2
47.5°	843.7	850.6	854.1	861.1	864.6	875.1	878.5	875.1
50°	753.1	760.0	767.0	767.0	777.4	780.9	787.9	791.3
52.5°	665.9	669.3	676.4	679.8	686.7	693.8	697.2	700.7
55°	582.2	585.7	592.6	592.6	603.1	606.6	613.6	613.6
57.5°	505.5	509.0	515.9	512.5	519.5	526.4	526.4	523.0
60°	432.3	432.3	432.3	439.2	442.8	446.3	449.7	449.7
62.5°	355.6	362.5	366.1	366.1	369.5	373.0	373.0	369.5
65°	285.8	292.8	296.3	296.3	299.8	299.8	299.8	303.3
67.5°	216.1	216.1	216.1	219.6	216.1	216.1	216.1	216.1
70°	136.0	136.0	136.0	136.0	132.5	136.0	136.0	139.4
72.5°	73.2	73.2	73.2	73.2	73.2	73.2	73.2	73.2
75°	31.4	31.4	31.4	34.8	31.4	31.4	31.4	31.4
77.5°	14.0	10.5	14.0	14.0	10.5	10.5	10.5	10.5
80°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	0.0	3.5	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)