

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585066

Luminaire Tested: **HCC8W60D010SL-HM86080827-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010SL-HM86080827-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4741.7 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585066
CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P585066

CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79228	79228	79228
5°	82013	78775	75646
10°	83835	77394	71388
15°	85027	74789	66664
20°	84772	71157	61890
25°	82675	66541	56817
30°	78328	61197	52135
35°	71260	55382	47375
40°	62587	49255	42802
45°	54581	43326	38162
50°	47498	37961	33615
55°	42359	33359	29235
60°	38484	29245	24940
65°	34600	25443	22641
70°	30798	21692	20430
75°	26998	18276	17442
80°	22908	14846	15485
85°	17266	11110	12312



TEST NUMBER: P585066
 CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.7	5.1
10°-20°	663.1	14.0
20°-30°	920.4	19.4
30°-40°	951.6	20.1
40°-50°	796.8	16.8
50°-60°	578.4	12.2
60°-70°	365.0	7.7
70°-80°	180.8	3.8
80°-90°	44.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1824.1	38.5
0°-40°	2775.7	58.5
0°-60°	4151.0	87.5
0°-90°	4741.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4741.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2569	2569	2569	2569	2569	
5°	2650	2618	2545	2475	2444	253
15°	2663	2562	2343	2154	2088	750
25°	2430	2273	1956	1743	1670	1114
35°	1893	1754	1471	1304	1258	1179
45°	1252	1161	994	896	875	968
55°	788	718	620	568	544	711
65°	474	415	349	307	310	473
75°	227	188	153	146	146	243
85°	49	38	31	35	35	59
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585066

CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3
2.5°	2611.2	2611.2	2614.6	2611.2	2611.2	2611.2	2607.6	2607.6	2604.1	2604.1	2597.2
5°	2649.5	2642.6	2649.5	2642.6	2642.6	2642.6	2639.0	2632.1	2628.6	2621.6	2618.1
7.5°	2666.9	2663.4	2663.4	2660.0	2660.0	2656.5	2652.9	2649.5	2635.5	2632.1	2621.6
10°	2677.4	2673.9	2673.9	2670.4	2663.4	2663.4	2656.5	2652.9	2635.5	2628.6	2614.6
12.5°	2673.9	2673.9	2673.9	2670.4	2660.0	2656.5	2649.5	2639.0	2625.1	2611.2	2597.2
15°	2663.4	2663.4	2656.5	2652.9	2642.6	2635.5	2632.1	2614.6	2600.7	2583.3	2562.3
17.5°	2628.6	2628.6	2625.1	2618.1	2607.6	2600.7	2593.7	2576.2	2562.3	2534.5	2513.5
20°	2583.3	2579.8	2576.2	2565.9	2555.4	2551.9	2541.4	2517.1	2499.5	2478.7	2450.7
22.5°	2517.1	2513.5	2510.0	2503.1	2485.7	2478.7	2471.7	2454.2	2422.8	2402.0	2367.1
25°	2429.9	2429.9	2422.8	2412.5	2395.0	2388.0	2377.6	2360.1	2332.3	2300.9	2273.0
27.5°	2328.7	2325.3	2314.8	2307.8	2293.9	2283.4	2266.0	2245.1	2217.2	2192.8	2157.9
30°	2199.8	2199.8	2192.8	2182.3	2164.9	2157.9	2143.9	2119.6	2091.7	2060.3	2035.9
32.5°	2053.4	2053.4	2042.9	2035.9	2025.5	2008.1	2004.5	1976.7	1952.2	1927.8	1900.0
35°	1893.0	1896.4	1889.5	1875.5	1858.1	1858.1	1851.2	1826.8	1798.8	1774.5	1753.5
37.5°	1732.6	1722.1	1718.7	1711.8	1701.3	1687.3	1680.4	1669.9	1645.4	1628.0	1596.7
40°	1554.8	1558.4	1551.3	1544.4	1540.8	1530.4	1527.0	1509.5	1492.0	1471.2	1457.2
42.5°	1394.5	1394.5	1394.5	1387.5	1380.5	1370.0	1366.5	1356.2	1335.2	1321.2	1300.3
45°	1251.6	1241.1	1241.1	1237.6	1234.1	1227.1	1216.7	1209.7	1195.7	1185.3	1160.9
47.5°	1112.1	1115.6	1112.1	1108.6	1098.2	1094.7	1091.1	1077.3	1063.3	1052.8	1035.4
50°	990.1	997.0	990.1	990.1	983.0	979.6	972.7	962.2	951.7	934.3	916.8
52.5°	888.9	888.9	885.5	882.0	871.5	864.6	861.1	857.6	840.1	826.2	812.2
55°	787.9	791.3	791.3	780.9	777.4	770.5	767.0	756.5	749.5	728.6	718.1
57.5°	700.7	697.2	700.7	693.8	686.7	679.8	676.4	669.3	658.9	645.0	631.0
60°	624.0	617.1	617.1	613.6	606.6	603.1	596.1	585.7	575.2	561.2	550.9
62.5°	547.3	543.8	540.4	536.9	529.9	526.4	523.0	512.5	502.0	491.6	481.1
65°	474.2	474.2	470.6	463.7	460.2	456.6	453.2	446.3	432.3	425.3	414.9
67.5°	407.8	404.4	404.4	397.5	390.4	387.0	387.0	380.0	369.5	359.1	352.1
70°	341.6	345.1	341.6	338.2	331.1	331.1	324.2	320.8	306.8	303.3	292.8
72.5°	282.4	282.4	278.9	278.9	272.0	268.4	268.4	261.5	254.4	247.5	240.6
75°	226.6	226.6	226.6	223.1	219.6	212.7	212.7	209.2	202.2	195.3	188.2
77.5°	177.7	174.3	174.3	170.8	167.4	163.9	163.9	160.3	153.4	149.9	142.9
80°	129.0	125.5	125.5	125.5	118.6	122.0	118.6	115.0	111.5	108.1	104.6
82.5°	83.6	87.2	87.2	83.6	80.2	80.2	80.2	76.7	76.7	73.2	69.8
85°	48.8	48.8	48.8	48.8	45.3	45.3	45.3	41.9	41.9	41.9	38.3
87.5°	20.9	20.9	20.9	20.9	20.9	20.9	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585066

CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3
2.5°	2597.2	2590.2	2586.7	2583.3	2583.3	2579.8	2576.2	2569.3	2569.3	2562.3	2558.8
5°	2611.2	2600.7	2593.7	2586.7	2583.3	2576.2	2569.3	2558.8	2555.4	2544.9	2534.5
7.5°	2614.6	2597.2	2590.2	2576.2	2569.3	2562.3	2548.4	2537.9	2524.0	2513.5	2499.5
10°	2600.7	2586.7	2569.3	2551.9	2548.4	2537.9	2517.1	2503.1	2485.7	2471.7	2450.7
12.5°	2579.8	2558.8	2541.4	2520.5	2510.0	2499.5	2478.7	2457.8	2433.3	2409.0	2388.0
15°	2544.9	2520.5	2496.1	2471.7	2457.8	2447.3	2422.8	2398.5	2374.0	2342.7	2321.8
17.5°	2492.6	2464.7	2440.4	2409.0	2395.0	2384.5	2353.2	2325.3	2293.9	2262.5	2241.6
20°	2426.4	2391.5	2363.7	2328.7	2318.3	2300.9	2269.5	2238.2	2203.2	2168.4	2143.9
22.5°	2339.2	2304.4	2273.0	2238.2	2220.6	2203.2	2171.9	2133.6	2098.7	2070.8	2046.4
25°	2238.2	2206.7	2168.4	2137.0	2116.1	2095.2	2060.3	2028.9	1997.6	1955.7	1931.4
27.5°	2126.5	2088.2	2060.3	2018.4	1997.6	1983.6	1945.3	1903.5	1875.5	1837.3	1809.3
30°	2001.0	1966.2	1934.8	1893.0	1872.1	1858.1	1823.3	1784.9	1757.0	1718.7	1690.8
32.5°	1868.6	1830.2	1791.9	1764.0	1739.6	1725.6	1687.3	1662.9	1628.0	1596.7	1565.3
35°	1725.6	1687.3	1659.4	1621.1	1607.1	1593.2	1561.8	1530.4	1499.1	1471.2	1446.7
37.5°	1572.3	1544.4	1513.0	1485.1	1474.6	1460.7	1422.4	1394.5	1370.0	1342.2	1321.2
40°	1422.4	1397.9	1377.0	1349.1	1331.7	1321.2	1293.4	1269.0	1241.1	1223.6	1202.8
42.5°	1286.4	1258.5	1237.6	1216.7	1199.2	1188.8	1164.4	1146.9	1126.1	1108.6	1084.2
45°	1143.5	1129.5	1105.1	1087.7	1077.3	1063.3	1045.9	1024.9	1007.5	993.5	976.1
47.5°	1018.0	1004.0	986.6	965.6	958.7	948.2	930.8	916.8	902.9	888.9	871.5
50°	902.9	885.5	871.5	857.6	850.6	840.1	822.7	815.8	805.3	791.3	780.9
52.5°	798.4	784.4	770.5	753.1	749.5	742.6	732.1	718.1	707.7	700.7	693.8
55°	704.2	690.3	679.8	665.9	662.4	655.4	641.4	634.5	627.6	620.5	613.6
57.5°	620.5	606.6	592.6	585.7	578.7	571.7	568.3	557.8	550.9	547.3	540.4
60°	543.8	529.9	519.5	509.0	505.5	502.0	495.0	488.1	481.1	474.2	470.6
62.5°	470.6	456.6	449.7	442.8	435.8	435.8	428.8	421.8	414.9	411.4	404.4
65°	404.4	397.5	387.0	376.5	373.0	373.0	362.5	359.1	355.6	348.7	341.6
67.5°	341.6	334.7	324.2	320.8	317.2	313.7	310.3	303.3	296.3	292.8	285.8
70°	285.8	278.9	272.0	268.4	264.9	261.5	254.4	251.0	244.1	240.6	237.0
72.5°	230.1	226.6	219.6	216.1	212.7	209.2	205.7	202.2	195.3	191.7	188.2
75°	184.8	181.3	174.3	170.8	167.4	167.4	163.9	156.9	153.4	153.4	149.9
77.5°	139.4	136.0	132.5	129.0	125.5	125.5	122.0	118.6	115.0	115.0	111.5
80°	101.2	97.6	94.1	94.1	94.1	90.7	87.2	87.2	83.6	83.6	80.2
82.5°	66.2	66.2	62.7	62.7	62.7	59.3	59.3	55.8	55.8	55.8	55.8
85°	38.3	38.3	38.3	34.8	34.8	34.8	34.8	34.8	34.8	31.4	34.8
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	14.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585066

CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3
2.5°	2555.4	2551.9	2544.9	2544.9	2537.9	2537.9	2534.5	2530.9	2527.4	2524.0	2520.5
5°	2530.9	2517.1	2510.0	2506.6	2499.5	2496.1	2485.7	2478.7	2475.2	2468.2	2461.2
7.5°	2485.7	2471.7	2457.8	2454.2	2450.7	2436.8	2426.4	2415.9	2409.0	2402.0	2395.0
10°	2433.3	2419.4	2402.0	2395.0	2388.0	2370.6	2356.6	2346.1	2332.3	2318.3	2314.8
12.5°	2370.6	2349.7	2328.7	2321.8	2311.3	2293.9	2279.9	2262.5	2252.0	2234.6	2231.1
15°	2297.3	2273.0	2255.6	2238.2	2231.1	2213.7	2189.3	2175.3	2154.4	2147.5	2130.1
17.5°	2210.3	2185.8	2161.5	2154.4	2143.9	2119.6	2095.2	2077.7	2056.9	2046.4	2035.9
20°	2119.6	2088.2	2063.8	2056.9	2042.9	2022.0	1997.6	1980.2	1962.7	1941.7	1931.4
22.5°	2015.0	1980.2	1959.3	1941.7	1938.3	1914.0	1886.0	1872.1	1858.1	1840.7	1826.8
25°	1900.0	1868.6	1844.2	1830.2	1823.3	1802.3	1781.4	1764.0	1743.1	1732.6	1715.2
27.5°	1781.4	1760.5	1729.2	1715.2	1704.7	1687.3	1662.9	1652.5	1631.5	1617.5	1607.1
30°	1666.4	1635.1	1617.5	1600.1	1589.7	1572.3	1551.3	1540.8	1523.4	1509.5	1499.1
32.5°	1540.8	1520.0	1495.6	1488.6	1474.6	1457.2	1443.2	1425.8	1411.9	1397.9	1394.5
35°	1425.8	1397.9	1373.6	1366.5	1356.2	1338.6	1331.7	1321.2	1303.8	1300.3	1286.4
37.5°	1300.3	1286.4	1258.5	1248.1	1244.5	1230.6	1216.7	1209.7	1199.2	1188.8	1185.3
40°	1181.8	1164.4	1150.4	1140.0	1133.0	1122.5	1108.6	1105.1	1098.2	1084.2	1080.7
42.5°	1070.2	1052.8	1038.9	1035.4	1024.9	1014.5	1007.5	997.0	993.5	990.1	983.0
45°	962.2	951.7	937.8	934.3	930.8	916.8	909.9	902.9	896.0	892.5	885.5
47.5°	864.6	854.1	843.6	840.1	833.2	829.8	819.3	815.8	805.3	801.8	798.4
50°	770.5	763.4	756.5	753.1	746.0	742.6	735.5	728.6	721.7	718.1	714.6
52.5°	686.7	679.8	672.8	669.3	665.9	658.9	651.9	645.0	641.4	637.9	634.5
55°	606.6	599.7	596.1	592.6	589.2	585.7	575.2	571.7	568.3	564.7	557.8
57.5°	533.3	526.4	519.5	519.5	515.9	512.5	505.5	498.5	498.5	491.6	484.5
60°	467.1	460.2	453.2	449.7	446.3	439.2	435.8	432.3	428.8	425.3	418.3
62.5°	397.5	393.9	387.0	387.0	380.0	376.5	373.0	369.5	366.1	359.1	355.6
65°	338.2	334.7	327.7	324.2	324.2	320.8	313.7	310.3	306.8	306.8	303.3
67.5°	282.4	278.9	272.0	268.4	268.4	264.9	261.5	261.5	258.0	254.4	258.0
70°	233.6	226.6	226.6	223.1	223.1	219.6	216.1	216.1	216.1	219.6	219.6
72.5°	184.8	181.3	177.7	177.7	177.7	177.7	174.3	174.3	177.7	181.3	181.3
75°	146.4	142.9	142.9	142.9	139.4	139.4	142.9	142.9	146.4	146.4	146.4
77.5°	108.1	108.1	108.1	108.1	108.1	108.1	111.5	111.5	115.0	115.0	115.0
80°	80.2	80.2	80.2	80.2	80.2	83.6	83.6	83.6	83.6	83.6	87.2
82.5°	55.8	55.8	55.8	55.8	55.8	55.8	55.8	59.3	59.3	59.3	59.3
85°	31.4	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
87.5°	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585066

CATALOG NUMBER: HCC8W60D010SL-HM86080827-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3	2569.3
2.5°	2517.1	2517.1	2517.1	2520.5	2513.5	2513.5	2513.5	2513.5
5°	2457.8	2454.2	2450.7	2454.2	2447.3	2447.3	2443.8	2443.8
7.5°	2384.5	2381.1	2377.6	2377.6	2370.6	2370.6	2367.1	2363.7
10°	2304.4	2297.3	2300.9	2293.9	2290.4	2287.0	2283.4	2279.9
12.5°	2217.2	2210.3	2206.7	2199.8	2192.8	2189.3	2192.8	2185.8
15°	2123.1	2112.6	2109.1	2102.2	2095.2	2091.7	2091.7	2088.2
17.5°	2018.4	2011.5	2008.1	2001.0	1997.6	1990.7	1987.1	1983.6
20°	1920.9	1903.5	1906.9	1900.0	1896.4	1882.6	1882.6	1886.0
22.5°	1812.8	1802.3	1795.4	1788.3	1784.9	1778.0	1778.0	1774.5
25°	1704.7	1694.2	1690.8	1683.8	1680.4	1673.4	1669.9	1669.9
27.5°	1600.1	1586.2	1586.2	1579.2	1572.3	1568.7	1565.3	1561.8
30°	1488.6	1478.1	1474.6	1474.6	1471.2	1471.2	1460.7	1464.2
32.5°	1384.0	1377.0	1373.6	1366.5	1366.5	1363.1	1363.1	1352.6
35°	1279.5	1269.0	1272.4	1265.5	1261.9	1258.5	1261.9	1258.5
37.5°	1178.3	1171.4	1171.4	1164.4	1164.4	1160.9	1157.4	1164.4
40°	1077.3	1073.7	1070.2	1066.8	1070.2	1066.8	1059.7	1063.3
42.5°	976.1	976.1	972.7	972.7	969.2	969.2	969.2	969.2
45°	885.5	882.0	882.0	878.5	878.5	878.5	878.5	875.1
47.5°	794.8	791.3	791.3	791.3	787.9	787.9	784.4	787.9
50°	707.7	707.7	704.2	704.2	707.7	704.2	700.7	700.7
52.5°	627.6	627.6	624.0	624.0	620.5	617.1	620.5	620.5
55°	554.3	550.9	547.3	547.3	543.8	540.4	540.4	543.8
57.5°	484.5	481.1	477.6	477.6	470.6	467.1	467.1	467.1
60°	418.3	411.4	411.4	407.8	407.8	404.4	404.4	404.4
62.5°	355.6	352.1	352.1	352.1	352.1	348.7	348.7	348.7
65°	303.3	303.3	303.3	306.8	306.8	310.3	310.3	310.3
67.5°	261.5	264.9	264.9	264.9	268.4	268.4	268.4	264.9
70°	223.1	223.1	223.1	226.6	226.6	226.6	226.6	226.6
72.5°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8
75°	146.4	149.9	149.9	149.9	146.4	149.9	149.9	146.4
77.5°	115.0	115.0	115.0	115.0	115.0	115.0	115.0	115.0
80°	87.2	87.2	87.2	87.2	87.2	87.2	87.2	87.2
82.5°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
85°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
87.5°	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)