

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585218

Luminaire Tested: **HCC8S80D010MW-HM86080830-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010MW-HM86080830-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5151.6 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585218
CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585218

CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85284	85284	85284
5°	88810	85096	81515
10°	91776	84010	77538
15°	94096	82086	73508
20°	94285	78681	69864
25°	92695	73703	66248
30°	87728	68005	63148
35°	79990	61157	59293
40°	69559	53916	54749
45°	59675	46692	50120
50°	50971	40259	45022
55°	44676	34671	39111
60°	39773	29572	32890
65°	35293	24137	26245
70°	31312	17888	14912
75°	26104	9365	4432
80°	20564	2930	746
85°	14648	1486	0



TEST NUMBER: P585218
 CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.6	5.1
10°-20°	730.4	14.2
20°-30°	1033.8	20.1
30°-40°	1081.6	21.0
40°-50°	902.1	17.5
50°-60°	639.7	12.4
60°-70°	368.4	7.2
70°-80°	118.6	2.3
80°-90°	16.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2024.8	39.3
0°-40°	3106.4	60.3
0°-60°	4648.3	90.2
0°-90°	5151.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5151.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2766	2766	2766	2766	2766	
5°	2869	2832	2749	2666	2633	275
15°	2948	2828	2571	2369	2303	829
25°	2724	2522	2166	1993	1947	1243
35°	2125	1939	1625	1538	1575	1317
45°	1368	1257	1071	1083	1149	1060
55°	831	744	645	678	728	751
65°	484	405	331	331	360	483
75°	219	161	79	37	37	238
85°	41	21	4	0	0	52
90°	0	0	0	0	0	



TEST NUMBER: P585218

CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7
2.5°	2823.5	2819.5	2815.3	2819.5	2815.3	2819.5	2815.3	2815.3	2811.2	2807.0	2807.0
5°	2869.1	2864.9	2864.9	2864.9	2860.7	2856.6	2856.6	2852.5	2844.2	2840.0	2831.8
7.5°	2897.9	2902.1	2902.1	2902.1	2893.8	2893.8	2885.6	2877.3	2869.1	2860.7	2848.4
10°	2931.0	2931.0	2927.0	2922.8	2914.5	2910.3	2906.3	2897.9	2885.6	2869.1	2856.6
12.5°	2943.5	2943.5	2939.3	2931.0	2927.0	2922.8	2918.6	2906.3	2889.7	2869.1	2852.5
15°	2947.5	2939.3	2935.2	2931.0	2922.8	2910.3	2910.3	2893.8	2873.2	2848.4	2827.7
17.5°	2914.5	2918.6	2910.3	2902.1	2889.7	2881.4	2869.1	2856.6	2831.8	2802.8	2782.3
20°	2873.2	2869.1	2864.9	2852.5	2836.0	2831.8	2819.5	2798.8	2778.1	2745.0	2716.0
22.5°	2807.0	2802.8	2794.6	2786.3	2769.8	2761.6	2749.1	2724.4	2695.3	2662.3	2629.2
25°	2724.4	2716.0	2703.7	2687.1	2674.8	2666.5	2649.9	2625.1	2592.0	2554.8	2521.8
27.5°	2592.0	2604.5	2596.2	2571.3	2559.0	2542.4	2538.3	2505.2	2476.3	2439.1	2401.9
30°	2463.8	2463.8	2451.5	2439.1	2418.4	2406.1	2389.5	2364.7	2335.8	2290.3	2261.4
32.5°	2302.6	2298.6	2282.0	2277.9	2261.4	2236.5	2232.3	2199.3	2170.4	2137.3	2100.1
35°	2124.9	2116.7	2100.1	2087.6	2079.4	2067.1	2054.6	2025.7	1996.7	1963.6	1938.9
37.5°	1922.4	1922.4	1918.2	1897.5	1889.2	1881.0	1868.6	1839.6	1823.1	1790.0	1765.2
40°	1728.0	1723.9	1711.4	1707.4	1699.1	1686.7	1678.4	1661.9	1637.1	1612.3	1587.4
42.5°	1537.9	1542.0	1525.5	1529.6	1513.1	1504.8	1500.6	1475.9	1463.4	1438.7	1418.0
45°	1368.4	1364.3	1355.9	1351.9	1343.6	1335.2	1327.0	1314.7	1294.0	1269.1	1256.8
47.5°	1211.2	1198.9	1198.9	1194.7	1190.7	1174.0	1170.0	1157.5	1145.1	1120.3	1103.7
50°	1062.5	1062.5	1062.5	1058.3	1046.0	1041.8	1033.5	1021.1	1008.7	992.2	967.4
52.5°	942.5	942.5	942.5	938.5	922.0	917.8	913.6	897.1	880.6	868.2	851.6
55°	831.0	835.0	831.0	822.7	810.3	810.3	797.8	789.6	773.1	760.7	744.1
57.5°	735.9	735.9	727.5	723.5	715.2	711.0	702.8	694.5	673.8	661.4	640.8
60°	644.9	640.8	640.8	632.5	624.2	616.0	611.9	599.5	591.2	570.5	554.0
62.5°	562.3	562.3	554.0	554.0	537.4	537.4	533.3	520.9	508.5	487.8	479.5
65°	483.7	483.7	479.5	475.4	463.0	458.8	454.8	442.3	429.9	417.6	405.1
67.5°	413.4	413.4	405.1	401.0	392.7	388.6	380.4	372.0	359.7	347.3	334.8
70°	347.3	343.1	339.0	334.8	326.6	322.5	314.1	305.9	293.6	285.2	272.9
72.5°	281.1	281.1	277.0	268.7	264.6	260.4	256.3	248.0	235.7	223.3	215.0
75°	219.1	219.1	219.1	210.8	202.6	198.4	198.4	190.1	181.9	169.6	161.2
77.5°	169.6	165.4	161.2	161.2	152.9	148.9	144.7	140.5	128.2	124.0	115.8
80°	115.8	119.9	115.8	111.6	107.5	103.3	103.3	95.1	91.0	82.6	74.4
82.5°	78.6	74.4	74.4	70.3	70.3	66.1	66.1	57.9	53.7	49.6	45.4
85°	41.4	41.4	37.2	37.2	37.2	33.1	33.1	28.9	28.9	24.9	20.7
87.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585218

CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7
2.5°	2802.8	2794.6	2790.5	2790.5	2786.3	2782.3	2778.1	2773.9	2765.7	2765.7	2757.4
5°	2823.5	2815.3	2811.2	2798.8	2790.5	2790.5	2773.9	2769.8	2757.4	2749.1	2740.9
7.5°	2840.0	2823.5	2811.2	2798.8	2790.5	2782.3	2765.7	2749.1	2732.6	2716.0	2707.8
10°	2840.0	2823.5	2802.8	2782.3	2773.9	2765.7	2745.0	2720.2	2699.5	2683.0	2662.3
12.5°	2831.8	2807.0	2782.3	2765.7	2749.1	2736.7	2712.0	2687.1	2662.3	2629.2	2612.7
15°	2807.0	2773.9	2749.1	2720.2	2707.8	2687.1	2666.5	2629.2	2600.3	2571.3	2550.8
17.5°	2757.4	2716.0	2687.1	2658.2	2637.6	2625.1	2592.0	2559.0	2525.9	2492.9	2468.0
20°	2683.0	2645.8	2612.7	2575.5	2559.0	2542.4	2501.1	2468.0	2435.0	2397.7	2372.9
22.5°	2592.0	2554.8	2509.4	2480.4	2455.6	2435.0	2397.7	2360.5	2327.5	2294.4	2261.4
25°	2480.4	2443.3	2401.9	2356.4	2339.8	2319.1	2277.9	2240.7	2203.5	2166.2	2137.3
27.5°	2360.5	2310.9	2277.9	2228.3	2211.7	2191.1	2145.6	2104.2	2071.1	2042.2	2009.2
30°	2215.8	2178.6	2133.2	2087.6	2071.1	2050.4	2013.3	1976.1	1942.9	1909.9	1876.8
32.5°	2058.8	2021.5	1976.1	1942.9	1918.2	1901.7	1864.5	1831.4	1798.4	1765.2	1736.3
35°	1893.4	1852.1	1818.9	1785.9	1765.2	1744.6	1707.4	1678.4	1653.7	1624.6	1595.8
37.5°	1723.9	1694.9	1661.9	1624.6	1604.0	1587.4	1558.5	1525.5	1504.8	1479.9	1459.4
40°	1558.5	1525.5	1496.5	1463.4	1446.9	1434.5	1405.6	1380.8	1360.1	1339.4	1327.0
42.5°	1389.0	1360.1	1331.2	1310.5	1298.2	1285.7	1265.0	1236.1	1223.7	1203.0	1190.7
45°	1231.9	1207.2	1186.5	1157.5	1149.3	1141.0	1116.2	1095.5	1083.2	1070.7	1062.5
47.5°	1083.2	1066.5	1041.8	1025.3	1012.8	1004.6	988.1	971.5	959.0	950.8	942.5
50°	955.0	934.3	917.8	901.3	892.9	880.6	864.0	855.7	847.5	839.2	839.2
52.5°	835.0	814.5	797.8	785.5	777.2	768.9	756.6	752.4	744.1	744.1	740.0
55°	723.5	711.0	694.5	678.0	673.8	669.8	661.4	653.2	649.1	644.9	649.1
57.5°	628.4	616.0	599.5	587.0	582.8	578.8	574.6	566.3	562.3	562.3	562.3
60°	541.6	529.1	516.7	504.4	504.4	496.1	492.0	487.8	483.7	479.5	479.5
62.5°	463.0	450.6	438.3	429.9	425.8	421.6	413.4	409.3	405.1	405.1	401.0
65°	392.7	376.2	372.0	359.7	355.5	351.3	347.3	339.0	334.8	330.8	326.6
67.5°	322.5	314.1	301.8	293.6	289.4	285.2	281.1	272.9	268.7	264.6	256.3
70°	260.4	252.2	243.9	235.7	231.5	227.3	219.1	210.8	206.6	198.4	186.1
72.5°	202.6	194.3	186.1	177.8	173.6	169.6	161.2	152.9	144.7	136.4	128.2
75°	152.9	144.7	132.3	124.0	119.9	119.9	107.5	99.2	91.0	78.6	70.3
77.5°	107.5	95.1	91.0	82.6	78.6	70.3	62.1	53.7	45.4	41.4	33.1
80°	70.3	62.1	53.7	49.6	45.4	41.4	37.2	28.9	20.7	16.5	12.4
82.5°	41.4	37.2	33.1	28.9	24.9	20.7	16.5	16.5	12.4	8.3	4.2
85°	20.7	16.5	12.4	12.4	8.3	8.3	8.3	4.2	4.2	4.2	4.2
87.5°	8.3	4.2	4.2	4.2	4.2	4.2	4.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585218

CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7
2.5°	2753.2	2749.1	2745.0	2740.9	2740.9	2732.6	2732.6	2728.5	2720.2	2716.0	2716.0
5°	2728.5	2716.0	2707.8	2703.7	2699.5	2687.1	2683.0	2674.8	2666.5	2658.2	2654.1
7.5°	2691.3	2670.6	2662.3	2658.2	2645.8	2633.4	2625.1	2612.7	2600.3	2587.9	2583.8
10°	2645.8	2625.1	2604.5	2596.2	2583.8	2575.5	2559.0	2542.4	2530.1	2517.6	2505.2
12.5°	2587.9	2563.1	2542.4	2534.1	2521.8	2505.2	2480.4	2472.2	2451.5	2443.3	2426.6
15°	2521.8	2492.9	2472.2	2459.8	2447.3	2422.6	2406.1	2389.5	2368.8	2360.5	2344.0
17.5°	2439.1	2406.1	2385.4	2372.9	2364.7	2344.0	2319.1	2298.6	2277.9	2269.6	2257.2
20°	2339.8	2319.1	2290.3	2277.9	2269.6	2244.8	2220.0	2211.7	2195.1	2178.6	2166.2
22.5°	2228.3	2207.6	2178.6	2166.2	2162.1	2141.4	2120.8	2108.3	2096.0	2083.6	2071.1
25°	2112.5	2087.6	2062.9	2054.6	2046.4	2029.9	2013.3	2005.0	1992.6	1984.3	1976.1
27.5°	1988.5	1963.6	1942.9	1930.6	1922.4	1909.9	1901.7	1893.4	1885.2	1876.8	1872.7
30°	1856.1	1831.4	1814.9	1806.6	1798.4	1794.2	1781.7	1777.7	1773.5	1765.2	1769.4
32.5°	1723.9	1703.2	1686.7	1674.2	1674.2	1666.0	1661.9	1661.9	1657.7	1657.7	1657.7
35°	1579.2	1566.7	1554.4	1550.2	1546.2	1542.0	1537.9	1542.0	1537.9	1542.0	1546.2
37.5°	1446.9	1434.5	1426.2	1422.2	1418.0	1422.2	1418.0	1418.0	1422.2	1430.4	1434.5
40°	1310.5	1302.2	1294.0	1298.2	1294.0	1294.0	1294.0	1306.4	1310.5	1314.7	1318.7
42.5°	1182.3	1174.0	1170.0	1170.0	1174.0	1170.0	1178.2	1182.3	1190.7	1203.0	1211.2
45°	1058.3	1054.2	1054.2	1058.3	1054.2	1062.5	1062.5	1070.7	1083.2	1091.4	1099.7
47.5°	942.5	942.5	942.5	946.7	946.7	950.8	959.0	963.2	971.5	979.7	988.1
50°	835.0	839.2	843.4	843.4	843.4	851.6	859.9	864.0	868.2	872.3	884.7
52.5°	740.0	744.1	744.1	748.2	752.4	756.6	760.7	768.9	773.1	781.3	785.5
55°	649.1	649.1	657.3	661.4	661.4	661.4	669.8	669.8	678.0	682.1	690.3
57.5°	562.3	566.3	566.3	570.5	570.5	574.6	578.8	582.8	587.0	591.2	595.3
60°	479.5	479.5	479.5	483.7	487.8	492.0	487.8	496.1	496.1	504.4	508.5
62.5°	401.0	405.1	405.1	405.1	405.1	405.1	405.1	409.3	413.4	417.6	421.6
65°	326.6	326.6	326.6	322.5	326.6	322.5	326.6	330.8	330.8	334.8	339.0
67.5°	252.2	252.2	243.9	243.9	248.0	248.0	248.0	248.0	243.9	252.2	252.2
70°	181.9	177.8	173.6	169.6	169.6	165.4	165.4	161.2	161.2	161.2	161.2
72.5°	119.9	111.6	103.3	99.2	95.1	95.1	86.8	82.6	86.8	86.8	86.8
75°	62.1	53.7	49.6	45.4	41.4	41.4	37.2	37.2	37.2	37.2	37.2
77.5°	24.9	20.7	16.5	16.5	12.4	12.4	12.4	12.4	12.4	12.4	12.4
80°	8.3	8.3	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
82.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
85°	4.2	0.0	0.0	4.2	0.0	4.2	4.2	4.2	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585218

CATALOG NUMBER: HCC8S80D010MW-HM86080830-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7	2765.7
2.5°	2712.0	2712.0	2707.8	2712.0	2703.7	2707.8	2703.7	2703.7
5°	2649.9	2641.6	2641.6	2641.6	2637.6	2637.6	2633.4	2633.4
7.5°	2575.5	2571.3	2567.3	2563.1	2559.0	2554.8	2554.8	2554.8
10°	2501.1	2492.9	2492.9	2488.7	2480.4	2476.3	2476.3	2476.3
12.5°	2414.3	2410.1	2406.1	2406.1	2389.5	2393.6	2389.5	2389.5
15°	2331.6	2327.5	2327.5	2315.1	2306.8	2306.8	2306.8	2302.6
17.5°	2244.8	2240.7	2236.5	2228.3	2220.0	2220.0	2215.8	2220.0
20°	2153.9	2149.7	2141.4	2141.4	2137.3	2133.2	2124.9	2129.0
22.5°	2062.9	2054.6	2050.4	2050.4	2046.4	2046.4	2038.1	2038.1
25°	1967.8	1963.6	1959.6	1963.6	1955.4	1955.4	1947.1	1947.1
27.5°	1868.6	1864.5	1864.5	1864.5	1860.3	1864.5	1860.3	1860.3
30°	1769.4	1769.4	1765.2	1765.2	1769.4	1765.2	1769.4	1773.5
32.5°	1661.9	1661.9	1666.0	1666.0	1670.2	1670.2	1670.2	1670.2
35°	1550.2	1558.5	1558.5	1562.7	1566.7	1570.9	1570.9	1575.1
37.5°	1446.9	1451.1	1455.2	1459.4	1467.6	1467.6	1467.6	1467.6
40°	1335.2	1339.4	1347.7	1343.6	1360.1	1364.3	1360.1	1360.1
42.5°	1219.6	1227.8	1231.9	1240.2	1244.4	1252.6	1256.8	1256.8
45°	1112.1	1116.2	1124.4	1132.8	1136.9	1149.3	1149.3	1149.3
47.5°	1000.4	1008.7	1012.8	1021.1	1025.3	1037.6	1041.8	1037.6
50°	892.9	901.3	909.5	909.5	922.0	926.0	934.3	938.5
52.5°	789.6	793.8	802.0	806.1	814.5	822.7	826.8	831.0
55°	690.3	694.5	702.8	702.8	715.2	719.3	727.5	727.5
57.5°	599.5	603.5	611.9	607.7	616.0	624.2	624.2	620.1
60°	512.6	512.6	512.6	520.9	525.1	529.1	533.3	533.3
62.5°	421.6	429.9	434.1	434.1	438.3	442.3	442.3	438.3
65°	339.0	347.3	351.3	351.3	355.5	355.5	355.5	359.7
67.5°	256.3	256.3	256.3	260.4	256.3	256.3	256.3	256.3
70°	161.2	161.2	161.2	161.2	157.1	161.2	161.2	165.4
72.5°	86.8	86.8	86.8	86.8	86.8	86.8	86.8	86.8
75°	37.2	37.2	37.2	41.4	37.2	37.2	37.2	37.2
77.5°	16.5	12.4	16.5	16.5	12.4	12.4	12.4	12.4
80°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
82.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
85°	0.0	4.2	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)