

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585072

Luminaire Tested: **HCC8W60D010MW-HM86080830-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585072  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010MW-HM86080830-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4686.7 lumens  
Efficiency: N/A  
Efficacy: 83.7 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585072  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585072

CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	95	95	95	93	94	92	91	89																					
	1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	93	94	92	91	89	89	89	87	90	88	86	84																					
	2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	87	90	88	86	84	84	84	82	85	82	86	83	81	80																			
	3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	82	84	82	81	79	75	75	77	77	77	75	75																					
	4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	77	82	79	77	75	75	75	77	77	75	75	75																					
	5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	77	77	75	75	75	75	75	77	77	75	75	75																					
	6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	73	73	73	72	72	72	73	73	72	72	72	72																					
	7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	70	70	69	68	68	68	69	69	68	68	68	68																					
	8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	66	66	66	66	66	66	66	66	66	66	66	66																					
	9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	63	63	63	63	63	63	63	63	63	63	63	63																					
	10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	60	60	60	60	60	60	60	60	60	60	60	60																					

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	372916
5°	315939
10°	229226
15°	172144
20°	135826
25°	109561
30°	81190
35°	32893
40°	13872
45°	7440
50°	3344
55°	1688
60°	1073
65°	766
70°	622
75°	417
80°	622
85°	1238



TEST NUMBER: P585072  
 CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	876.3	18.7
10°-20°	1514.5	32.3
20°-30°	1464.3	31.2
30°-40°	643.1	13.7
40°-50°	139.0	3.0
50°-60°	31.2	0.7
60°-70°	10.7	0.2
70°-80°	4.1	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3855.1	82.3
0°-40°	4498.2	96.0
0°-60°	4668.5	99.6
0°-90°	4686.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4686.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12093	
5°	10207	876
15°	5392	1515
25°	3220	1464
35°	874	643
45°	171	139
55°	31	31
65°	10	11
75°	4	4
85°	4	3
90°	0	



TEST NUMBER: P585072  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12093.4
1°	12002.9
2°	11755.7
3°	11310.1
4°	10777.5
5°	10206.7
6°	9583.5
7°	8957.0
8°	8368.6
9°	7822.0
10°	7320.7
11°	6847.4
12°	6422.7
13°	6036.2
14°	5695.1
15°	5392.3
17.5°	4713.5
20°	4139.1
22.5°	3634.2
25°	3220.1
27.5°	2798.8
30°	2280.2
32.5°	1549.1
35°	873.8
37.5°	515.2
40°	344.6
42.5°	243.7
45°	170.6
47.5°	111.4
50°	69.7
52.5°	41.8
55°	31.4
57.5°	24.3
60°	17.4
62.5°	14.0
65°	10.5
67.5°	6.9
70°	6.9
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	3.5

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585072  
CATALOG NUMBER: HCC8W60D010MW-HM86080830-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	3.5
87.5°	3.5

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)