

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585230

Luminaire Tested: **HCC8W80D010SL-HM86080835-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585230  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010SL-HM86080835-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7449.2 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585230  
CATALOG NUMBER: HCC8W80D010SL-HM86080835-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P585230  
 CATALOG NUMBER: HCC8W80D010SL-HM86080835-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			92	
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83	
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75	
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			68	
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			62	
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			56	
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51	
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			47	
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43	
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			40	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	139571
5°	138408
10°	136583
15°	138139
20°	149178
25°	163132
30°	161163
35°	133686
40°	78684
45°	51406
50°	39846
55°	26472
60°	12883
65°	3991
70°	1343
75°	1191
80°	888
85°	1769



TEST NUMBER: P585230  
 CATALOG NUMBER: HCC8W80D010SL-HM86080835-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	423.5	5.7
10°-20°	1243.2	16.7
20°-30°	2173.5	29.2
30°-40°	2114.3	28.4
40°-50°	961.5	12.9
50°-60°	445.9	6.0
60°-70°	74.7	1.0
70°-80°	9.2	0.1
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3840.2	51.6
0°-40°	5954.5	79.9
0°-60°	7361.9	98.8
0°-90°	7449.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7449.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4526	
5°	4471	423
15°	4327	1243
25°	4795	2174
35°	3551	2114
45°	1179	962
55°	492	446
65°	55	75
75°	10	9
85°	5	3
90°	0	



TEST NUMBER: P585230  
CATALOG NUMBER: HCC8W80D010SL-HM86080835-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4526.2
2.5°	4516.2
5°	4471.4
7.5°	4421.7
10°	4362.0
12.5°	4317.3
15°	4327.1
17.5°	4406.8
20°	4546.0
22.5°	4705.2
25°	4794.6
27.5°	4744.9
30°	4526.2
32.5°	4143.2
35°	3551.3
37.5°	2735.5
40°	1954.7
42.5°	1457.4
45°	1178.8
47.5°	994.7
50°	830.6
52.5°	661.6
55°	492.4
57.5°	338.3
60°	208.9
62.5°	114.4
65°	54.7
67.5°	24.9
70°	14.9
72.5°	10.0
75°	10.0
77.5°	5.0
80°	5.0
82.5°	5.0
85°	5.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)