

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585098

Luminaire Tested: **HCC8S60D010SL-HM86080835-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010SL-HM86080835-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6856.6 lumens  
Efficiency: N/A  
Efficacy: 122.4 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585098  
CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P585098

CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90					90			
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81					81			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73					73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65					65			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54					54			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49					49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45					45			
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41					41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38					38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120419
5°	119588
10°	119277
15°	122403
20°	132518
25°	142074
30°	138898
35°	115658
40°	71056
45°	49204
50°	37548
55°	24617
60°	15406
65°	11543
70°	11640
75°	13404
80°	14792
85°	13268



TEST NUMBER: P585098  
 CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	367.1	5.4
10°-20°	1100.7	16.1
20°-30°	1894.8	27.6
30°-40°	1835.8	26.8
40°-50°	904.3	13.2
50°-60°	426.7	6.2
60°-70°	168.1	2.5
70°-80°	116.0	1.7
80°-90°	43.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3362.6	49.0
0°-40°	5198.4	75.8
0°-60°	6529.4	95.2
0°-90°	6856.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6856.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3905	
5°	3863	367
15°	3834	1101
25°	4176	1895
35°	3072	1836
45°	1128	904
55°	458	427
65°	158	168
75°	112	116
85°	38	43
90°	0	



TEST NUMBER: P585098  
CATALOG NUMBER: HCC8S60D010SL-HM86080835-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3905.1
2.5°	3892.5
5°	3863.4
7.5°	3834.2
10°	3809.3
12.5°	3805.1
15°	3834.2
17.5°	3921.7
20°	4038.3
22.5°	4142.3
25°	4175.7
27.5°	4100.7
30°	3900.9
32.5°	3572.0
35°	3072.4
37.5°	2385.5
40°	1765.2
42.5°	1369.7
45°	1128.3
47.5°	949.2
50°	782.7
52.5°	616.1
55°	457.9
57.5°	333.1
60°	249.8
62.5°	195.6
65°	158.2
67.5°	137.4
70°	129.1
72.5°	120.8
75°	112.5
77.5°	99.9
80°	83.3
82.5°	62.4
85°	37.5
87.5°	16.6
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)