

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585237

Luminaire Tested: **HCC8W80D010MW-HM86080835-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010MW-HM86080835-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7041.3 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585237
CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	107958	107958	107958
5°	111911	107603	103907
10°	115075	106664	99657
15°	117637	104778	95255
20°	117823	100687	91387
25°	115563	95094	88153
30°	109608	88184	84288
35°	99591	80310	80498
40°	87081	72067	75871
45°	75470	64193	70699
50°	66083	57016	64413
55°	58815	50530	58283
60°	53063	45391	51219
65°	47894	39919	44625
70°	43042	33629	33179
75°	37923	26664	24889
80°	31804	22091	23831
85°	24660	19353	21122



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.3	4.7
10°-20°	930.3	13.2
20°-30°	1329.5	18.9
30°-40°	1412.6	20.1
40°-50°	1216.2	17.3
50°-60°	909.3	12.9
60°-70°	580.0	8.2
70°-80°	264.0	3.7
80°-90°	69.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2590.0	36.8
0°-40°	4002.6	56.8
0°-60°	6128.1	87.0
0°-90°	7041.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7041.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3501	3501	3501	3501	3501	
5°	3615	3566	3476	3387	3357	346
15°	3685	3561	3282	3058	2984	1038
25°	3396	3183	2795	2626	2591	1555
35°	2646	2462	2133	2079	2138	1648
45°	1731	1636	1472	1512	1621	1345
55°	1094	1005	940	1019	1084	984
65°	656	582	547	572	612	655
75°	318	274	224	204	209	338
85°	70	60	55	60	60	84
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0
2.5°	3565.6	3555.7	3560.7	3555.7	3560.7	3560.7	3550.7	3550.7	3550.7	3550.7	3535.7
5°	3615.4	3610.4	3610.4	3605.4	3600.4	3605.4	3600.4	3595.4	3585.5	3580.6	3565.6
7.5°	3645.2	3645.2	3645.2	3645.2	3640.2	3635.2	3630.3	3620.3	3610.4	3600.4	3590.5
10°	3675.1	3680.0	3675.1	3670.1	3665.1	3655.1	3650.1	3640.2	3625.3	3610.4	3600.4
12.5°	3689.9	3689.9	3684.9	3684.9	3675.1	3670.1	3655.1	3640.2	3625.3	3610.4	3585.5
15°	3684.9	3684.9	3680.0	3675.1	3660.1	3655.1	3645.2	3630.3	3605.4	3585.5	3560.7
17.5°	3655.1	3650.1	3640.2	3640.2	3620.3	3615.4	3605.4	3585.5	3560.7	3530.9	3501.0
20°	3590.5	3590.5	3585.5	3580.6	3560.7	3545.7	3535.7	3510.9	3491.0	3456.2	3426.3
22.5°	3501.0	3510.9	3501.0	3491.0	3466.2	3461.2	3446.3	3416.5	3386.6	3346.8	3312.0
25°	3396.5	3391.6	3386.6	3376.6	3356.8	3346.8	3326.9	3297.1	3267.3	3222.5	3182.7
27.5°	3262.3	3242.4	3242.4	3222.5	3207.6	3192.7	3182.7	3152.9	3113.0	3078.3	3028.5
30°	3078.3	3083.2	3058.3	3053.4	3028.5	3018.6	2998.7	2968.8	2934.1	2894.3	2854.4
32.5°	2879.4	2864.4	2864.4	2844.6	2824.7	2809.7	2804.7	2769.9	2740.1	2700.3	2660.5
35°	2645.6	2645.6	2630.7	2625.8	2605.8	2595.9	2581.0	2561.1	2526.3	2491.4	2461.6
37.5°	2416.9	2406.9	2401.9	2392.0	2377.0	2362.2	2362.2	2327.3	2322.4	2282.6	2242.8
40°	2163.3	2173.1	2163.3	2148.3	2143.4	2133.4	2128.4	2108.6	2093.6	2058.8	2033.9
42.5°	1949.4	1939.5	1939.5	1934.5	1914.6	1914.6	1904.7	1894.7	1869.8	1859.8	1830.1
45°	1730.6	1740.6	1725.6	1730.6	1710.7	1710.7	1710.7	1690.8	1670.9	1656.0	1636.1
47.5°	1541.7	1546.7	1546.7	1531.7	1526.7	1526.7	1516.8	1506.8	1491.8	1472.0	1457.1
50°	1377.5	1382.5	1372.6	1367.6	1357.6	1352.6	1352.6	1332.8	1322.8	1302.9	1292.9
52.5°	1228.4	1228.4	1223.4	1223.4	1208.4	1208.4	1198.5	1183.5	1173.7	1163.7	1138.8
55°	1094.0	1094.0	1089.1	1084.1	1084.1	1069.1	1064.3	1049.3	1039.3	1019.4	1004.6
57.5°	964.8	969.7	964.8	959.8	954.8	949.9	939.9	924.9	915.1	900.1	890.2
60°	860.4	860.4	855.4	850.4	840.4	835.5	830.5	820.5	805.7	795.7	780.8
62.5°	760.8	755.8	751.0	746.0	736.0	736.0	726.0	716.1	701.2	691.3	681.3
65°	656.4	656.4	651.5	651.5	646.5	636.6	631.6	626.6	606.7	601.8	581.9
67.5°	561.9	566.9	556.9	556.9	547.1	547.1	542.1	527.1	522.2	512.2	502.2
70°	477.4	477.4	477.4	472.4	462.5	457.5	452.5	442.5	437.7	427.7	417.7
72.5°	392.8	392.8	387.9	387.9	383.0	378.0	373.0	363.0	363.0	353.1	343.1
75°	318.3	318.3	313.3	308.3	303.3	303.3	298.3	293.4	283.5	278.5	273.5
77.5°	243.6	243.6	243.6	238.8	233.8	233.8	233.8	223.8	213.8	213.8	208.9
80°	179.1	179.1	174.1	174.1	169.1	169.1	169.1	164.1	159.1	154.2	149.2
82.5°	119.4	119.4	119.4	119.4	114.4	114.4	114.4	109.4	104.4	104.4	104.4
85°	69.7	69.7	69.7	69.7	64.7	64.7	64.7	64.7	64.7	59.7	59.7
87.5°	29.8	24.9	29.8	24.9	29.8	24.9	29.8	24.9	24.9	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0
2.5°	3540.7	3535.7	3530.9	3525.9	3525.9	3520.9	3510.9	3506.0	3501.0	3496.0	3496.0
5°	3560.7	3555.7	3545.7	3535.7	3530.9	3520.9	3510.9	3501.0	3491.0	3476.2	3471.2
7.5°	3575.6	3560.7	3550.7	3530.9	3525.9	3515.9	3501.0	3486.0	3466.2	3446.3	3431.3
10°	3575.6	3555.7	3540.7	3515.9	3506.0	3496.0	3476.2	3451.2	3426.3	3406.5	3381.6
12.5°	3565.6	3540.7	3515.9	3491.0	3476.2	3461.2	3431.3	3406.5	3376.6	3346.8	3326.9
15°	3530.9	3501.0	3471.2	3441.3	3426.3	3406.5	3376.6	3341.8	3312.0	3282.1	3247.4
17.5°	3466.2	3436.3	3401.5	3366.7	3346.8	3331.9	3287.1	3262.3	3217.6	3187.7	3157.9
20°	3381.6	3346.8	3302.1	3267.3	3242.4	3227.4	3192.7	3147.9	3113.0	3068.3	3038.5
22.5°	3272.2	3227.4	3182.7	3147.9	3123.0	3103.2	3058.3	3013.6	2983.8	2944.0	2909.2
25°	3142.9	3098.2	3053.4	3003.7	2978.8	2958.9	2919.1	2879.4	2839.6	2794.9	2765.0
27.5°	2988.8	2939.0	2899.3	2854.4	2829.6	2799.7	2755.0	2715.2	2675.5	2645.6	2605.8
30°	2819.7	2765.0	2725.2	2680.5	2655.5	2630.7	2586.0	2546.1	2511.4	2476.6	2456.6
32.5°	2615.8	2576.0	2536.3	2491.4	2471.6	2456.6	2411.9	2372.1	2332.3	2302.5	2287.5
35°	2421.9	2377.0	2342.3	2302.5	2277.6	2262.7	2223.0	2188.1	2168.3	2133.4	2113.6
37.5°	2218.0	2183.1	2143.4	2103.6	2088.6	2073.7	2043.9	2009.1	1979.2	1954.4	1944.5
40°	2004.1	1974.2	1939.5	1914.6	1899.7	1884.8	1859.8	1835.0	1815.1	1790.3	1780.3
42.5°	1800.3	1780.3	1750.4	1720.6	1705.7	1700.7	1670.9	1651.0	1641.1	1631.2	1621.2
45°	1616.2	1586.4	1566.5	1546.7	1531.7	1521.7	1506.8	1491.8	1482.0	1472.0	1462.1
47.5°	1437.1	1412.3	1392.4	1377.5	1362.6	1357.6	1347.7	1332.8	1322.8	1322.8	1322.8
50°	1273.1	1253.2	1233.3	1223.4	1218.4	1208.4	1198.5	1193.5	1188.5	1188.5	1188.5
52.5°	1128.8	1109.0	1094.0	1084.1	1084.1	1074.1	1064.3	1059.3	1059.3	1059.3	1059.3
55°	994.6	979.6	969.7	959.8	949.9	944.9	944.9	944.9	939.9	939.9	944.9
57.5°	875.2	865.4	850.4	840.4	835.5	835.5	830.5	825.5	830.5	835.5	840.4
60°	765.8	755.8	751.0	736.0	736.0	736.0	731.0	731.0	731.0	736.0	741.0
62.5°	666.4	661.4	651.5	646.5	641.5	641.5	636.6	636.6	636.6	636.6	641.5
65°	576.9	566.9	556.9	556.9	556.9	552.1	552.1	542.1	547.1	547.1	542.1
67.5°	492.4	482.4	477.4	472.4	467.5	467.5	462.5	457.5	452.5	452.5	452.5
70°	412.7	402.8	402.8	392.8	392.8	387.9	383.0	383.0	378.0	373.0	368.0
72.5°	333.2	328.2	323.3	318.3	318.3	318.3	313.3	308.3	303.3	298.3	288.5
75°	263.6	263.6	253.6	248.6	248.6	243.6	238.8	233.8	228.8	223.8	218.8
77.5°	203.9	198.9	188.9	184.1	184.1	184.1	179.1	174.1	169.1	164.1	159.1
80°	149.2	144.2	139.2	134.2	134.2	134.2	129.2	129.2	124.4	124.4	124.4
82.5°	99.4	99.4	94.5	94.5	94.5	94.5	89.5	89.5	89.5	89.5	89.5
85°	59.7	59.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7
87.5°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0
2.5°	3486.0	3486.0	3476.2	3471.2	3466.2	3471.2	3461.2	3456.2	3451.2	3451.2	3446.3
5°	3456.2	3451.2	3431.3	3426.3	3421.3	3416.5	3406.5	3396.5	3386.6	3381.6	3376.6
7.5°	3416.5	3401.5	3381.6	3376.6	3371.6	3356.8	3341.8	3331.9	3317.0	3312.0	3302.1
10°	3361.8	3341.8	3326.9	3312.0	3302.1	3287.1	3272.2	3257.3	3237.4	3232.4	3217.6
12.5°	3297.1	3272.2	3242.4	3237.4	3222.5	3202.6	3182.7	3167.7	3152.9	3142.9	3128.0
15°	3217.6	3192.7	3162.9	3147.9	3133.0	3118.0	3093.2	3073.3	3058.3	3043.5	3028.5
17.5°	3123.0	3093.2	3068.3	3053.4	3043.5	3018.6	2998.7	2973.8	2958.9	2944.0	2929.1
20°	3008.6	2983.8	2949.0	2934.1	2929.1	2909.2	2884.3	2874.4	2854.4	2839.6	2829.6
22.5°	2879.4	2854.4	2824.7	2814.7	2794.9	2784.9	2760.0	2750.0	2740.1	2725.2	2720.2
25°	2735.2	2710.3	2685.4	2680.5	2665.5	2655.5	2640.7	2625.8	2625.8	2610.8	2610.8
27.5°	2586.0	2561.1	2541.2	2531.3	2526.3	2516.3	2501.4	2496.4	2491.4	2486.4	2486.4
30°	2426.9	2397.0	2387.0	2382.0	2377.0	2367.2	2362.2	2352.2	2357.2	2362.2	2357.2
32.5°	2257.7	2247.8	2227.9	2218.0	2223.0	2218.0	2208.0	2218.0	2213.0	2223.0	2227.9
35°	2093.6	2083.7	2073.7	2073.7	2063.7	2063.7	2063.7	2068.7	2078.7	2083.7	2093.6
37.5°	1934.5	1919.5	1914.6	1909.7	1914.6	1914.6	1914.6	1924.5	1934.5	1944.5	1959.4
40°	1765.4	1755.4	1755.4	1755.4	1755.4	1770.4	1765.4	1775.3	1785.3	1800.3	1815.1
42.5°	1606.2	1606.2	1611.2	1611.2	1611.2	1611.2	1621.2	1636.1	1651.0	1665.9	1680.9
45°	1457.1	1457.1	1457.1	1467.0	1467.0	1472.0	1491.8	1501.8	1511.8	1526.7	1541.7
47.5°	1317.9	1317.9	1322.8	1327.8	1332.8	1342.7	1352.6	1367.6	1382.5	1392.4	1407.3
50°	1188.5	1193.5	1203.5	1213.4	1213.4	1218.4	1233.3	1243.2	1253.2	1268.1	1273.1
52.5°	1064.3	1074.1	1084.1	1089.1	1094.0	1104.0	1109.0	1123.8	1128.8	1143.8	1148.8
55°	949.9	954.8	969.7	974.7	974.7	984.6	994.6	1004.6	1019.4	1019.4	1029.4
57.5°	845.4	850.4	860.4	865.4	860.4	875.2	880.2	890.2	895.1	905.1	910.1
60°	741.0	751.0	755.8	755.8	760.8	765.8	775.8	775.8	785.7	795.7	795.7
62.5°	641.5	646.5	651.5	656.4	661.4	656.4	671.3	671.3	681.3	686.3	696.2
65°	547.1	552.1	552.1	556.9	556.9	561.9	561.9	566.9	571.9	581.9	586.8
67.5°	452.5	452.5	452.5	457.5	452.5	457.5	457.5	462.5	462.5	472.4	477.4
70°	368.0	363.0	358.0	358.0	358.0	358.0	353.1	358.0	358.0	363.0	363.0
72.5°	283.5	278.5	273.5	268.6	268.6	263.6	258.6	263.6	263.6	268.6	268.6
75°	213.8	203.9	203.9	203.9	198.9	198.9	198.9	203.9	203.9	203.9	208.9
77.5°	159.1	159.1	154.2	154.2	154.2	159.1	159.1	164.1	164.1	164.1	164.1
80°	119.4	124.4	124.4	124.4	124.4	129.2	129.2	129.2	129.2	134.2	134.2
82.5°	89.5	89.5	89.5	89.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5
85°	54.7	59.7	59.7	54.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7
87.5°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585237

CATALOG NUMBER: HCC8W80D010MW-HM86080835-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0	3501.0
2.5°	3441.3	3441.3	3441.3	3441.3	3436.3	3436.3	3436.3	3431.3
5°	3366.7	3366.7	3366.7	3356.8	3361.8	3361.8	3351.8	3356.8
7.5°	3292.1	3287.1	3282.1	3282.1	3277.2	3272.2	3267.3	3272.2
10°	3207.6	3192.7	3192.7	3187.7	3187.7	3177.7	3177.7	3182.7
12.5°	3113.0	3103.2	3103.2	3098.2	3093.2	3088.2	3083.2	3083.2
15°	3018.6	3008.6	3003.7	2998.7	2993.8	2983.8	2988.8	2983.8
17.5°	2924.1	2909.2	2909.2	2904.3	2899.3	2889.3	2889.3	2884.3
20°	2814.7	2809.7	2799.7	2804.7	2799.7	2789.9	2784.9	2784.9
22.5°	2705.3	2705.3	2700.3	2700.3	2695.3	2690.4	2685.4	2685.4
25°	2600.8	2595.9	2600.8	2600.8	2586.0	2586.0	2586.0	2590.9
27.5°	2481.6	2486.4	2481.6	2481.6	2481.6	2481.6	2486.4	2481.6
30°	2362.2	2362.2	2362.2	2367.2	2377.0	2372.1	2372.1	2367.2
32.5°	2232.8	2237.8	2237.8	2242.8	2247.8	2257.7	2257.7	2262.7
35°	2103.6	2113.6	2118.4	2113.6	2128.4	2128.4	2138.4	2138.4
37.5°	1969.3	1974.2	1984.2	1989.2	1999.2	2004.1	2009.1	2009.1
40°	1825.1	1845.0	1850.0	1855.0	1869.8	1869.8	1874.8	1884.8
42.5°	1690.8	1710.7	1715.7	1720.6	1730.6	1745.6	1740.6	1750.4
45°	1561.5	1576.4	1581.4	1586.4	1601.3	1606.2	1606.2	1621.2
47.5°	1422.3	1432.3	1437.1	1447.1	1457.1	1467.0	1477.0	1472.0
50°	1283.0	1297.9	1307.9	1312.9	1327.8	1332.8	1337.7	1342.7
52.5°	1158.7	1168.7	1173.7	1178.5	1193.5	1198.5	1203.5	1213.4
55°	1039.3	1044.3	1054.3	1049.3	1064.3	1069.1	1074.1	1084.1
57.5°	920.0	924.9	929.9	929.9	939.9	949.9	954.8	959.8
60°	805.7	815.5	820.5	820.5	820.5	830.5	830.5	830.5
62.5°	701.2	701.2	706.1	706.1	716.1	716.1	716.1	716.1
65°	591.8	596.8	601.8	601.8	611.6	606.7	616.6	611.6
67.5°	477.4	477.4	487.4	487.4	482.4	487.4	487.4	487.4
70°	363.0	363.0	368.0	368.0	368.0	368.0	368.0	368.0
72.5°	268.6	268.6	268.6	273.5	268.6	268.6	273.5	268.6
75°	208.9	208.9	208.9	208.9	208.9	208.9	208.9	208.9
77.5°	164.1	164.1	169.1	169.1	169.1	169.1	169.1	169.1
80°	134.2	134.2	134.2	134.2	139.2	134.2	134.2	134.2
82.5°	99.4	94.5	99.4	94.5	99.4	99.4	99.4	99.4
85°	59.7	59.7	59.7	59.7	59.7	59.7	59.7	59.7
87.5°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)