

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585247

Luminaire Tested: **HCC8W80D010BZ-HM86080840-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585247  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010BZ-HM86080840-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7801.1 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585247  
CATALOG NUMBER: HCC8W80D010BZ-HM86080840-81WDBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585247

CATALOG NUMBER: HCC8W80D010BZ-HM86080840-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146161
5°	144946
10°	143033
15°	144667
20°	156227
25°	170845
30°	168772
35°	140003
40°	82400
45°	53831
50°	41732
55°	27725
60°	13494
65°	4181
70°	1406
75°	1251
80°	923
85°	1840



TEST NUMBER: P585247  
 CATALOG NUMBER: HCC8W80D010BZ-HM86080840-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.5	5.7
10°-20°	1301.9	16.7
20°-30°	2276.3	29.2
30°-40°	2214.2	28.4
40°-50°	1007.0	12.9
50°-60°	466.9	6.0
60°-70°	78.3	1.0
70°-80°	9.6	0.1
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4021.6	51.6
0°-40°	6235.8	79.9
0°-60°	7709.7	98.8
0°-90°	7801.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7801.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4740	
5°	4683	443
15°	4532	1302
25°	5021	2276
35°	3719	2214
45°	1234	1007
55°	516	467
65°	57	78
75°	10	10
85°	5	4
90°	0	



TEST NUMBER: P585247  
CATALOG NUMBER: HCC8W80D010BZ-HM86080840-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4739.9
2.5°	4729.5
5°	4682.6
7.5°	4630.6
10°	4568.0
12.5°	4521.2
15°	4531.6
17.5°	4615.0
20°	4760.8
22.5°	4927.5
25°	5021.3
27.5°	4969.2
30°	4739.9
32.5°	4338.9
35°	3719.1
37.5°	2864.8
40°	2047.0
42.5°	1526.2
45°	1234.4
47.5°	1041.8
50°	869.9
52.5°	692.7
55°	515.7
57.5°	354.2
60°	218.8
62.5°	119.9
65°	57.3
67.5°	26.0
70°	15.6
72.5°	10.5
75°	10.5
77.5°	5.2
80°	5.2
82.5°	5.2
85°	5.2
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)