

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585126

Luminaire Tested: **HCC8W60D010SL-HM86080927-81RWWC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585126  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010SL-HM86080927-81RWWC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4324.3 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585126  
CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P585126  
 CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77			77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			67
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59			59
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52			52
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	70162	70162	70162
5°	71086	69867	69207
10°	71814	69149	68104
15°	72538	67689	66335
20°	72171	65194	63701
25°	70488	61291	60461
30°	66955	56892	56679
35°	60950	51915	52371
40°	53433	46465	48180
45°	46099	41328	44246
50°	40364	36287	40076
55°	35768	31192	35278
60°	32224	26229	29227
65°	29033	21058	22386
70°	25470	15336	12325
75°	21708	7959	3253
80°	16710	2149	533
85°	10720	0	0



TEST NUMBER: P585126  
 CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.7	5.0
10°-20°	603.5	14.0
20°-30°	856.6	19.8
30°-40°	901.6	20.9
40°-50°	767.0	17.7
50°-60°	554.3	12.8
60°-70°	315.3	7.3
70°-80°	99.3	2.3
80°-90°	12.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1674.7	38.7
0°-40°	2576.3	59.6
0°-60°	3897.6	90.1
0°-90°	4324.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4324.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2275	2275	2275	2275	2275	
5°	2296	2284	2257	2242	2236	219
15°	2272	2214	2120	2081	2078	640
25°	2072	1968	1801	1771	1777	949
35°	1619	1525	1379	1370	1391	1007
45°	1057	1018	948	972	1015	822
55°	665	617	580	614	656	600
65°	398	343	289	286	307	395
75°	182	140	67	30	27	196
85°	30	18	0	0	0	39
90°	0	0	0	0	0	



TEST NUMBER: P585126

CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3
2.5°	2287.4	2290.4	2284.4	2284.4	2290.4	2284.4	2287.4	2287.4	2284.4	2284.4	2281.3
5°	2296.5	2293.5	2293.5	2293.5	2296.5	2290.4	2287.4	2290.4	2284.4	2284.4	2284.4
7.5°	2299.5	2299.5	2296.5	2293.5	2293.5	2293.5	2290.4	2287.4	2284.4	2278.3	2275.3
10°	2293.5	2293.5	2296.5	2290.4	2290.4	2284.4	2284.4	2278.3	2278.3	2272.2	2263.1
12.5°	2287.4	2284.4	2284.4	2278.3	2278.3	2272.2	2272.2	2263.1	2260.1	2251.0	2241.9
15°	2272.2	2269.2	2263.1	2260.1	2257.1	2254.0	2248.0	2244.9	2235.8	2223.6	2214.5
17.5°	2241.9	2238.9	2235.8	2229.8	2223.6	2220.6	2217.5	2208.4	2196.3	2187.2	2172.0
20°	2199.3	2196.3	2196.3	2187.2	2184.1	2175.0	2172.0	2159.9	2150.7	2132.5	2120.3
22.5°	2141.6	2144.6	2138.5	2132.5	2126.4	2117.3	2111.2	2099.1	2083.8	2065.6	2050.5
25°	2071.7	2074.7	2068.7	2062.6	2053.5	2047.4	2041.4	2023.2	2008.0	1986.7	1968.5
27.5°	1983.6	1983.6	1983.6	1977.6	1962.4	1959.4	1953.3	1935.1	1913.7	1895.5	1877.3
30°	1880.4	1877.3	1877.3	1868.2	1862.2	1849.9	1840.8	1825.7	1810.5	1789.3	1767.9
32.5°	1755.8	1758.8	1749.7	1743.7	1734.6	1734.6	1722.4	1710.3	1692.0	1670.7	1649.5
35°	1619.1	1622.1	1616.0	1613.0	1597.8	1594.8	1591.8	1576.6	1564.5	1549.2	1524.9
37.5°	1479.4	1476.4	1473.4	1473.4	1464.2	1458.1	1452.0	1442.9	1424.7	1412.6	1400.3
40°	1327.4	1327.4	1327.4	1324.4	1321.5	1315.3	1312.3	1306.2	1294.1	1281.9	1272.8
42.5°	1190.8	1190.8	1187.8	1184.8	1178.7	1181.7	1175.7	1169.5	1157.3	1148.2	1142.2
45°	1057.1	1057.1	1057.1	1060.2	1054.1	1045.0	1045.0	1038.9	1032.9	1026.8	1017.6
47.5°	938.6	947.7	941.8	938.6	941.8	929.5	929.5	923.5	917.4	911.3	899.2
50°	841.4	841.4	841.4	835.4	832.3	832.3	823.2	817.2	814.1	808.1	795.8
52.5°	753.4	747.3	747.3	744.3	741.2	735.2	735.2	729.1	717.0	710.8	701.7
55°	665.3	665.3	662.3	659.2	656.2	653.2	650.1	640.9	634.8	625.7	616.6
57.5°	586.3	592.4	589.3	583.3	577.2	577.2	571.0	565.1	555.9	546.8	537.7
60°	522.5	519.5	519.5	516.4	510.4	507.3	504.3	495.2	486.0	476.9	467.8
62.5°	455.7	455.7	455.7	449.6	443.5	440.5	437.5	431.4	419.3	410.1	404.0
65°	397.9	394.9	391.9	388.8	385.8	379.7	376.7	370.6	361.5	352.4	343.3
67.5°	340.3	337.1	337.1	334.1	325.0	322.0	322.0	312.9	303.8	294.7	285.6
70°	282.5	282.5	282.5	276.5	273.4	270.4	267.4	261.2	252.1	243.0	233.9
72.5°	233.9	230.9	230.9	227.8	218.7	215.7	212.7	206.6	197.5	191.3	185.4
75°	182.2	182.2	179.2	176.2	173.1	170.1	167.1	161.0	151.9	142.8	139.8
77.5°	139.8	136.7	136.7	133.7	127.6	124.6	124.6	118.5	109.3	103.2	97.2
80°	94.1	97.2	94.1	91.1	88.1	85.0	82.0	79.0	72.9	66.8	60.8
82.5°	57.7	60.8	57.7	57.7	54.7	51.7	51.7	45.6	42.6	39.4	36.4
85°	30.3	30.3	30.3	30.3	27.3	27.3	27.3	24.3	21.2	18.2	18.2
87.5°	9.1	12.1	9.1	9.1	9.1	9.1	9.1	9.1	6.1	6.1	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585126

CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3
2.5°	2284.4	2281.3	2278.3	2278.3	2278.3	2278.3	2278.3	2275.3	2272.2	2272.2	2272.2
5°	2278.3	2278.3	2278.3	2275.3	2272.2	2272.2	2266.2	2263.1	2260.1	2257.1	2254.0
7.5°	2272.2	2266.2	2263.1	2260.1	2257.1	2257.1	2251.0	2244.9	2244.9	2238.9	2232.8
10°	2254.0	2251.0	2244.9	2238.9	2235.8	2232.8	2226.6	2217.5	2214.5	2208.4	2202.4
12.5°	2232.8	2226.6	2220.6	2208.4	2205.4	2202.4	2190.2	2181.1	2175.0	2172.0	2156.7
15°	2205.4	2193.3	2184.1	2169.0	2165.9	2159.9	2150.7	2141.6	2129.4	2120.3	2114.3
17.5°	2156.7	2144.6	2129.4	2114.3	2108.2	2108.2	2093.0	2080.8	2065.6	2059.6	2047.4
20°	2099.1	2083.8	2071.7	2053.5	2044.4	2035.3	2026.2	2008.0	1995.8	1986.7	1971.5
22.5°	2032.3	2011.0	1995.8	1977.6	1962.4	1953.3	1938.1	1922.8	1907.7	1898.6	1886.4
25°	1947.2	1928.9	1904.6	1886.4	1877.3	1865.2	1846.9	1831.7	1816.6	1801.4	1795.3
27.5°	1853.1	1828.7	1807.5	1786.2	1777.0	1767.9	1746.7	1728.5	1716.4	1701.1	1695.0
30°	1749.7	1725.5	1701.1	1682.9	1673.8	1658.6	1646.5	1625.1	1610.0	1597.8	1582.7
32.5°	1631.3	1613.0	1591.8	1564.5	1558.4	1546.2	1528.0	1518.9	1500.7	1491.6	1479.4
35°	1503.7	1491.6	1470.2	1449.0	1439.9	1433.8	1418.7	1400.3	1388.2	1379.1	1373.0
37.5°	1382.1	1367.0	1345.7	1330.6	1324.4	1315.3	1297.1	1288.0	1275.9	1269.8	1257.7
40°	1251.6	1236.3	1221.2	1212.1	1203.0	1196.9	1184.8	1175.7	1163.4	1154.3	1151.3
42.5°	1124.0	1114.9	1102.7	1090.5	1087.5	1078.4	1072.3	1063.2	1054.1	1051.1	1042.0
45°	1008.5	999.4	987.3	975.1	972.1	966.0	963.0	953.9	947.7	947.7	947.7
47.5°	893.1	884.0	871.9	865.7	868.7	856.6	856.6	853.6	847.5	847.5	850.5
50°	789.8	777.6	774.6	768.5	762.5	756.4	759.4	750.3	750.3	756.4	753.4
52.5°	692.6	680.5	677.4	671.4	668.3	668.3	665.3	665.3	662.3	665.3	665.3
55°	604.5	595.4	589.3	583.3	580.2	580.2	580.2	577.2	574.2	580.2	583.3
57.5°	525.5	522.5	516.4	507.3	504.3	501.3	498.2	498.2	498.2	498.2	501.3
60°	455.7	449.6	443.5	434.4	434.4	431.4	428.4	425.3	425.3	425.3	425.3
62.5°	394.9	385.8	376.7	370.6	367.6	364.5	361.5	355.4	355.4	355.4	355.4
65°	334.1	325.0	318.9	312.9	306.8	306.8	300.7	297.7	291.6	288.6	282.5
67.5°	276.5	270.4	264.2	255.1	252.1	249.1	243.0	240.0	230.9	227.8	224.8
70°	224.8	215.7	209.6	203.6	200.5	194.5	188.4	182.2	176.2	170.1	164.0
72.5°	176.2	167.1	161.0	154.9	148.9	148.9	139.8	133.7	124.6	118.5	109.3
75°	130.7	121.5	115.5	106.3	103.2	100.2	91.1	85.0	75.9	66.8	60.8
77.5°	88.1	82.0	75.9	66.8	60.8	60.8	51.7	45.6	39.4	30.3	27.3
80°	54.7	48.6	42.6	36.4	36.4	30.3	27.3	21.2	15.2	12.1	9.1
82.5°	30.3	27.3	24.3	18.2	18.2	15.2	12.1	9.1	6.1	3.0	3.0
85°	15.2	12.1	9.1	9.1	6.1	6.1	6.1	3.0	3.0	0.0	0.0
87.5°	6.1	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585126

CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3
2.5°	2269.2	2269.2	2266.2	2266.2	2266.2	2263.1	2266.2	2263.1	2263.1	2263.1	2266.2
5°	2257.1	2251.0	2251.0	2248.0	2248.0	2244.9	2248.0	2244.9	2241.9	2238.9	2241.9
7.5°	2232.8	2226.6	2223.6	2220.6	2220.6	2220.6	2217.5	2214.5	2217.5	2208.4	2214.5
10°	2199.3	2196.3	2190.2	2187.2	2184.1	2187.2	2184.1	2178.1	2178.1	2178.1	2175.0
12.5°	2156.7	2150.7	2147.6	2144.6	2138.5	2138.5	2141.6	2135.5	2135.5	2129.4	2129.4
15°	2105.2	2099.1	2093.0	2093.0	2087.0	2087.0	2083.8	2083.8	2080.8	2077.9	2077.9
17.5°	2041.4	2032.3	2026.2	2029.2	2026.2	2023.2	2023.2	2017.1	2014.1	2017.1	2017.1
20°	1965.4	1959.4	1953.3	1956.3	1950.3	1947.2	1950.3	1941.2	1944.2	1944.2	1944.2
22.5°	1880.4	1877.3	1868.2	1868.2	1862.2	1859.1	1862.2	1862.2	1865.2	1862.2	1862.2
25°	1786.2	1780.2	1774.0	1774.0	1771.0	1767.9	1771.0	1774.0	1771.0	1774.0	1774.0
27.5°	1685.9	1676.8	1676.8	1670.7	1670.7	1673.8	1670.7	1673.8	1676.8	1676.8	1682.9
30°	1576.6	1573.6	1570.5	1567.5	1567.5	1570.5	1570.5	1570.5	1573.6	1579.6	1579.6
32.5°	1473.4	1467.2	1461.1	1461.1	1467.2	1464.2	1467.2	1467.2	1473.4	1473.4	1479.4
35°	1360.9	1360.9	1354.8	1357.9	1357.9	1357.9	1357.9	1363.9	1370.0	1373.0	1379.1
37.5°	1257.7	1248.6	1251.6	1251.6	1254.6	1251.6	1260.7	1260.7	1266.8	1266.8	1272.8
40°	1145.2	1145.2	1148.2	1145.2	1148.2	1148.2	1154.3	1160.4	1163.4	1169.5	1172.5
42.5°	1038.9	1045.0	1038.9	1042.0	1045.0	1048.0	1051.1	1054.1	1066.2	1072.3	1081.4
45°	941.8	944.7	947.7	950.9	947.7	953.9	956.9	963.0	972.1	975.1	978.2
47.5°	847.5	850.5	853.6	856.6	856.6	862.7	865.7	871.9	877.9	881.0	884.0
50°	756.4	762.5	765.5	765.5	768.5	774.6	780.7	780.7	786.7	795.8	799.0
52.5°	674.4	674.4	680.5	683.5	686.5	686.5	695.6	698.7	701.7	707.8	713.8
55°	583.3	592.4	595.4	595.4	601.5	607.5	610.6	613.6	613.6	625.7	625.7
57.5°	504.3	507.3	513.4	513.4	513.4	522.5	522.5	528.6	531.6	534.6	540.7
60°	425.3	431.4	431.4	434.4	431.4	437.5	440.5	446.6	449.6	452.6	455.7
62.5°	352.4	352.4	355.4	355.4	355.4	355.4	361.5	361.5	367.6	370.6	373.6
65°	282.5	282.5	282.5	282.5	282.5	282.5	282.5	282.5	285.6	285.6	291.6
67.5°	218.7	215.7	209.6	212.7	209.6	209.6	206.6	206.6	209.6	209.6	215.7
70°	158.0	154.9	148.9	148.9	145.8	142.8	139.8	136.7	133.7	133.7	133.7
72.5°	103.2	97.2	88.1	85.0	85.0	79.0	72.9	69.9	69.9	69.9	69.9
75°	51.7	45.6	39.4	36.4	36.4	30.3	33.4	30.3	30.3	30.3	30.3
77.5°	21.2	15.2	12.1	12.1	12.1	9.1	9.1	9.1	9.1	9.1	9.1
80°	6.1	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P585126

CATALOG NUMBER: HCC8W60D010SL-HM86080927-81RWWC

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3	2275.3
2.5°	2263.1	2263.1	2257.1	2260.1	2260.1	2260.1	2260.1	2260.1
5°	2235.8	2238.9	2235.8	2238.9	2238.9	2235.8	2235.8	2235.8
7.5°	2208.4	2211.5	2208.4	2211.5	2211.5	2211.5	2208.4	2208.4
10°	2175.0	2175.0	2175.0	2175.0	2175.0	2172.0	2175.0	2175.0
12.5°	2129.4	2129.4	2129.4	2132.5	2132.5	2129.4	2129.4	2126.4
15°	2080.8	2074.7	2077.9	2080.8	2077.9	2077.9	2077.9	2077.9
17.5°	2014.1	2017.1	2014.1	2014.1	2014.1	2014.1	2017.1	2014.1
20°	1944.2	1944.2	1947.2	1944.2	1944.2	1944.2	1944.2	1941.2
22.5°	1865.2	1862.2	1862.2	1865.2	1865.2	1862.2	1865.2	1865.2
25°	1777.0	1780.2	1777.0	1777.0	1780.2	1780.2	1780.2	1777.0
27.5°	1682.9	1685.9	1689.0	1685.9	1685.9	1685.9	1689.0	1692.0
30°	1585.7	1591.8	1585.7	1585.7	1591.8	1588.7	1591.8	1591.8
32.5°	1482.5	1491.6	1485.5	1491.6	1491.6	1494.6	1491.6	1494.6
35°	1379.1	1388.2	1388.2	1388.2	1391.2	1394.3	1394.3	1391.2
37.5°	1281.9	1285.0	1285.0	1291.0	1294.1	1297.1	1297.1	1294.1
40°	1181.7	1187.8	1190.8	1190.8	1190.8	1196.9	1203.0	1196.9
42.5°	1084.4	1087.5	1090.5	1090.5	1096.7	1099.7	1102.7	1102.7
45°	990.3	996.4	999.4	1002.4	1005.5	1011.5	1008.5	1014.6
47.5°	893.1	902.2	905.3	908.3	914.4	917.4	920.4	923.5
50°	805.0	811.1	811.1	817.2	826.3	826.3	832.3	835.4
52.5°	717.0	720.0	723.0	726.1	732.1	738.2	738.2	744.3
55°	631.8	634.8	634.8	637.9	640.9	653.2	656.2	656.2
57.5°	543.7	543.7	549.8	552.8	555.9	561.9	561.9	561.9
60°	458.7	461.7	461.7	464.8	467.8	473.9	476.9	473.9
62.5°	373.6	376.7	376.7	379.7	385.8	388.8	385.8	385.8
65°	294.7	297.7	297.7	300.7	306.8	306.8	303.8	306.8
67.5°	215.7	215.7	215.7	215.7	215.7	215.7	215.7	215.7
70°	136.7	133.7	130.7	133.7	133.7	133.7	130.7	136.7
72.5°	66.8	69.9	69.9	69.9	69.9	69.9	69.9	66.8
75°	30.3	30.3	27.3	27.3	27.3	30.3	30.3	27.3
77.5°	9.1	9.1	9.1	9.1	9.1	9.1	9.1	9.1
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)