

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585262

Luminaire Tested: **HCC8S80D010SL-HM86080927-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010SL-HM86080927-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5165.3 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585262
CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P585262

CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	82	79	77								
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67								
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59								
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83807	83807	83807
5°	84910	83455	82666
10°	85782	82598	81352
15°	86645	80854	79232
20°	86209	77871	76089
25°	84199	73210	72223
30°	79973	67959	67699
35°	72804	62015	62561
40°	63831	55506	57551
45°	55065	49366	52850
50°	48217	43343	47867
55°	42719	37262	42138
60°	38490	31324	34913
65°	34688	25151	26734
70°	30420	18320	14714
75°	25937	9508	3896
80°	19978	2575	657
85°	12843	0	0



TEST NUMBER: P585262
 CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	5.0
10°-20°	720.8	14.0
20°-30°	1023.1	19.8
30°-40°	1077.0	20.9
40°-50°	916.2	17.7
50°-60°	662.1	12.8
60°-70°	376.6	7.3
70°-80°	118.7	2.3
80°-90°	14.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2000.4	38.7
0°-40°	3077.4	59.6
0°-60°	4655.7	90.1
0°-90°	5165.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5165.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2718	2718	2718	2718	2718	
5°	2743	2729	2696	2678	2671	262
15°	2714	2645	2533	2486	2482	764
25°	2475	2351	2152	2116	2123	1133
35°	1934	1822	1647	1636	1662	1203
45°	1263	1216	1132	1161	1212	982
55°	795	737	693	733	784	716
65°	475	410	345	341	366	471
75°	218	167	80	36	33	234
85°	36	22	0	0	0	47
90°	0	0	0	0	0	



TEST NUMBER: P585262

CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8
2.5°	2732.3	2735.9	2728.6	2728.6	2735.9	2728.6	2732.3	2732.3	2728.6	2728.6	2725.1
5°	2743.1	2739.6	2739.6	2739.6	2743.1	2735.9	2732.3	2735.9	2728.6	2728.6	2728.6
7.5°	2746.8	2746.8	2743.1	2739.6	2739.6	2739.6	2735.9	2732.3	2728.6	2721.4	2717.8
10°	2739.6	2739.6	2743.1	2735.9	2735.9	2728.6	2728.6	2721.4	2721.4	2714.1	2703.3
12.5°	2732.3	2728.6	2728.6	2721.4	2721.4	2714.1	2714.1	2703.3	2699.6	2688.8	2677.9
15°	2714.1	2710.6	2703.3	2699.6	2696.1	2692.4	2685.1	2681.4	2670.6	2656.1	2645.2
17.5°	2677.9	2674.2	2670.6	2663.4	2656.1	2652.4	2648.9	2637.9	2623.4	2612.6	2594.4
20°	2627.1	2623.4	2623.4	2612.6	2608.9	2598.1	2594.4	2579.9	2569.0	2547.2	2532.7
22.5°	2558.1	2561.7	2554.4	2547.2	2539.9	2529.1	2521.9	2507.4	2489.2	2467.4	2449.2
25°	2474.7	2478.4	2471.0	2463.7	2452.9	2445.7	2438.4	2416.6	2398.5	2373.0	2351.2
27.5°	2369.4	2369.4	2369.4	2362.2	2344.0	2340.4	2333.2	2311.4	2286.0	2264.2	2242.5
30°	2246.0	2242.5	2242.5	2231.5	2224.3	2209.8	2198.9	2180.7	2162.6	2137.2	2111.8
32.5°	2097.3	2101.0	2090.0	2082.8	2072.0	2072.0	2057.3	2042.8	2021.1	1995.7	1970.3
35°	1934.0	1937.6	1930.3	1926.8	1908.6	1905.0	1901.3	1883.3	1868.8	1850.6	1821.5
37.5°	1767.1	1763.5	1759.8	1759.8	1748.9	1741.6	1734.4	1723.6	1701.8	1687.3	1672.8
40°	1585.7	1585.7	1585.7	1582.1	1578.4	1571.1	1567.6	1560.3	1545.7	1531.2	1520.4
42.5°	1422.4	1422.4	1418.7	1415.1	1407.9	1411.5	1404.2	1397.0	1382.5	1371.6	1364.4
45°	1262.7	1262.7	1262.7	1266.4	1259.2	1248.2	1248.2	1241.0	1233.7	1226.5	1215.5
47.5°	1121.2	1132.0	1124.8	1121.2	1124.8	1110.3	1110.3	1103.0	1095.8	1088.5	1074.0
50°	1005.1	1005.1	1005.1	997.8	994.2	994.2	983.3	976.1	972.5	965.2	950.7
52.5°	899.8	892.6	892.6	889.0	885.3	878.1	878.1	870.8	856.3	849.1	838.2
55°	794.6	794.6	791.0	787.4	783.8	780.1	776.5	765.6	758.3	747.5	736.6
57.5°	700.3	707.6	703.9	696.6	689.4	689.4	682.1	674.9	664.1	653.1	642.3
60°	624.1	620.5	620.5	616.9	609.6	605.9	602.3	591.4	580.6	569.6	558.8
62.5°	544.3	544.3	544.3	537.1	529.8	526.1	522.6	515.2	500.7	489.9	482.6
65°	475.4	471.7	468.1	464.4	460.9	453.6	449.9	442.7	431.8	420.9	410.0
67.5°	406.4	402.7	402.7	399.1	388.2	384.6	384.6	373.7	362.9	351.9	341.1
70°	337.4	337.4	337.4	330.2	326.6	322.9	319.4	312.1	301.2	290.2	279.4
72.5°	279.4	275.7	275.7	272.2	261.2	257.7	254.0	246.7	235.9	228.6	221.4
75°	217.7	217.7	214.1	210.5	206.9	203.2	199.5	192.3	181.4	170.5	166.9
77.5°	166.9	163.2	163.2	159.7	152.4	148.7	148.7	141.5	130.7	123.4	116.2
80°	112.5	116.2	112.5	108.9	105.2	101.5	98.0	94.3	87.0	79.8	72.5
82.5°	69.0	72.5	69.0	69.0	65.3	61.7	61.7	54.5	50.8	47.2	43.5
85°	36.3	36.3	36.3	36.3	32.7	32.7	32.7	29.0	25.4	21.8	21.8
87.5°	10.9	14.5	10.9	10.9	10.9	10.9	10.9	10.9	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585262

CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8
2.5°	2728.6	2725.1	2721.4	2721.4	2721.4	2721.4	2721.4	2717.8	2714.1	2714.1	2714.1
5°	2721.4	2721.4	2721.4	2717.8	2714.1	2714.1	2706.9	2703.3	2699.6	2696.1	2692.4
7.5°	2714.1	2706.9	2703.3	2699.6	2696.1	2696.1	2688.8	2681.4	2681.4	2674.2	2666.9
10°	2692.4	2688.8	2681.4	2674.2	2670.6	2666.9	2659.7	2648.9	2645.2	2637.9	2630.7
12.5°	2666.9	2659.7	2652.4	2637.9	2634.3	2630.7	2616.2	2605.3	2598.1	2594.4	2576.2
15°	2634.3	2619.8	2608.9	2590.8	2587.1	2579.9	2569.0	2558.1	2543.6	2532.7	2525.4
17.5°	2576.2	2561.7	2543.6	2525.4	2518.2	2518.2	2500.1	2485.6	2467.4	2460.2	2445.7
20°	2507.4	2489.2	2474.7	2452.9	2442.0	2431.1	2420.2	2398.5	2383.9	2373.0	2354.9
22.5°	2427.5	2402.1	2383.9	2362.2	2344.0	2333.2	2315.0	2296.9	2278.7	2267.8	2253.3
25°	2325.9	2304.2	2275.2	2253.3	2242.5	2227.9	2206.2	2188.0	2169.9	2151.7	2144.5
27.5°	2213.4	2184.4	2159.0	2133.5	2122.7	2111.8	2086.5	2064.7	2050.1	2032.0	2024.7
30°	2090.0	2061.0	2032.0	2010.2	1999.3	1981.2	1966.7	1941.3	1923.1	1908.6	1890.5
32.5°	1948.5	1926.8	1901.3	1868.8	1861.5	1846.9	1825.1	1814.3	1792.5	1781.6	1767.1
35°	1796.1	1781.6	1756.3	1730.8	1719.9	1712.6	1694.6	1672.8	1658.3	1647.4	1640.1
37.5°	1650.9	1632.9	1607.4	1589.3	1582.1	1571.1	1549.4	1538.4	1523.9	1516.7	1502.2
40°	1494.9	1476.9	1458.7	1447.8	1436.9	1429.7	1415.1	1404.2	1389.7	1378.9	1375.2
42.5°	1342.6	1331.7	1317.2	1302.7	1299.0	1288.2	1280.9	1270.0	1259.2	1255.5	1244.6
45°	1204.7	1193.8	1179.3	1164.7	1161.2	1153.9	1150.2	1139.4	1132.0	1132.0	1132.0
47.5°	1066.8	1056.0	1041.4	1034.2	1037.8	1023.3	1023.3	1019.6	1012.3	1012.3	1016.0
50°	943.5	928.8	925.3	918.0	910.8	903.5	907.1	896.3	896.3	903.5	899.8
52.5°	827.3	812.8	809.1	801.9	798.3	798.3	794.6	794.6	791.0	794.6	794.6
55°	722.1	711.1	703.9	696.6	693.1	693.1	693.1	689.4	685.8	693.1	696.6
57.5°	627.8	624.1	616.9	605.9	602.3	598.7	595.1	595.1	595.1	595.1	598.7
60°	544.3	537.1	529.8	518.9	518.9	515.2	511.6	507.9	507.9	507.9	507.9
62.5°	471.7	460.9	449.9	442.7	439.1	435.4	431.8	424.6	424.6	424.6	424.6
65°	399.1	388.2	381.0	373.7	366.4	366.4	359.2	355.6	348.4	344.7	337.4
67.5°	330.2	322.9	315.7	304.7	301.2	297.5	290.2	286.7	275.7	272.2	268.5
70°	268.5	257.7	250.4	243.2	239.5	232.2	225.0	217.7	210.5	203.2	195.9
72.5°	210.5	199.5	192.3	185.0	177.8	177.8	166.9	159.7	148.7	141.5	130.7
75°	156.0	145.2	137.9	127.0	123.4	119.7	108.9	101.5	90.7	79.8	72.5
77.5°	105.2	98.0	90.7	79.8	72.5	72.5	61.7	54.5	47.2	36.3	32.7
80°	65.3	58.0	50.8	43.5	43.5	36.3	32.7	25.4	18.2	14.5	10.9
82.5°	36.3	32.7	29.0	21.8	21.8	18.2	14.5	10.9	7.3	3.7	3.7
85°	18.2	14.5	10.9	10.9	7.3	7.3	7.3	3.7	3.7	0.0	0.0
87.5°	7.3	3.7	3.7	3.7	3.7	3.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585262

CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8
2.5°	2710.6	2710.6	2706.9	2706.9	2706.9	2703.3	2706.9	2703.3	2703.3	2703.3	2706.9
5°	2696.1	2688.8	2688.8	2685.1	2685.1	2681.4	2685.1	2681.4	2677.9	2674.2	2677.9
7.5°	2666.9	2659.7	2656.1	2652.4	2652.4	2652.4	2648.9	2645.2	2648.9	2637.9	2645.2
10°	2627.1	2623.4	2616.2	2612.6	2608.9	2612.6	2608.9	2601.7	2601.7	2601.7	2598.1
12.5°	2576.2	2569.0	2565.4	2561.7	2554.4	2554.4	2558.1	2550.9	2550.9	2543.6	2543.6
15°	2514.6	2507.4	2500.1	2500.1	2492.9	2492.9	2489.2	2489.2	2485.6	2481.9	2481.9
17.5°	2438.4	2427.5	2420.2	2423.9	2420.2	2416.6	2416.6	2409.4	2405.7	2409.4	2409.4
20°	2347.7	2340.4	2333.2	2336.7	2329.5	2325.9	2329.5	2318.7	2322.2	2322.2	2322.2
22.5°	2246.0	2242.5	2231.5	2231.5	2224.3	2220.7	2224.3	2224.3	2227.9	2224.3	2224.3
25°	2133.5	2126.3	2119.0	2119.0	2115.5	2111.8	2115.5	2119.0	2115.5	2119.0	2119.0
27.5°	2013.8	2003.0	2003.0	1995.7	1995.7	1999.3	1995.7	1999.3	2003.0	2003.0	2010.2
30°	1883.3	1879.6	1876.0	1872.3	1872.3	1876.0	1876.0	1876.0	1879.6	1886.8	1886.8
32.5°	1759.8	1752.6	1745.3	1745.3	1752.6	1748.9	1752.6	1752.6	1759.8	1759.8	1767.1
35°	1625.6	1625.6	1618.3	1621.9	1621.9	1621.9	1621.9	1629.2	1636.4	1640.1	1647.4
37.5°	1502.2	1491.4	1494.9	1494.9	1498.6	1494.9	1505.9	1505.9	1513.1	1513.1	1520.4
40°	1367.9	1367.9	1371.6	1367.9	1371.6	1371.6	1378.9	1386.1	1389.7	1397.0	1400.6
42.5°	1241.0	1248.2	1241.0	1244.6	1248.2	1251.9	1255.5	1259.2	1273.7	1280.9	1291.7
45°	1124.8	1128.5	1132.0	1135.7	1132.0	1139.4	1143.0	1150.2	1161.2	1164.7	1168.4
47.5°	1012.3	1016.0	1019.6	1023.3	1023.3	1030.5	1034.2	1041.4	1048.7	1052.3	1056.0
50°	903.5	910.8	914.3	914.3	918.0	925.3	932.5	932.5	939.8	950.7	954.3
52.5°	805.5	805.5	812.8	816.4	820.1	820.1	831.0	834.6	838.2	845.5	852.8
55°	696.6	707.6	711.1	711.1	718.4	725.8	729.3	733.0	733.0	747.5	747.5
57.5°	602.3	605.9	613.2	613.2	613.2	624.1	624.1	631.4	635.0	638.6	645.9
60°	507.9	515.2	515.2	518.9	515.2	522.6	526.1	533.4	537.1	540.6	544.3
62.5°	420.9	420.9	424.6	424.6	424.6	424.6	431.8	431.8	439.1	442.7	446.4
65°	337.4	337.4	337.4	337.4	337.4	337.4	337.4	337.4	341.1	341.1	348.4
67.5°	261.2	257.7	250.4	254.0	250.4	250.4	246.7	246.7	250.4	250.4	257.7
70°	188.7	185.0	177.8	177.8	174.2	170.5	166.9	163.2	159.7	159.7	159.7
72.5°	123.4	116.2	105.2	101.5	101.5	94.3	87.0	83.5	83.5	83.5	83.5
75°	61.7	54.5	47.2	43.5	43.5	36.3	40.0	36.3	36.3	36.3	36.3
77.5°	25.4	18.2	14.5	14.5	14.5	10.9	10.9	10.9	10.9	10.9	10.9
80°	7.3	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585262

CATALOG NUMBER: HCC8S80D010SL-HM86080927-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8	2717.8
2.5°	2703.3	2703.3	2696.1	2699.6	2699.6	2699.6	2699.6	2699.6
5°	2670.6	2674.2	2670.6	2674.2	2674.2	2670.6	2670.6	2670.6
7.5°	2637.9	2641.6	2637.9	2641.6	2641.6	2641.6	2637.9	2637.9
10°	2598.1	2598.1	2598.1	2598.1	2598.1	2594.4	2598.1	2598.1
12.5°	2543.6	2543.6	2543.6	2547.2	2547.2	2543.6	2543.6	2539.9
15°	2485.6	2478.4	2481.9	2485.6	2481.9	2481.9	2481.9	2481.9
17.5°	2405.7	2409.4	2405.7	2405.7	2405.7	2405.7	2409.4	2405.7
20°	2322.2	2322.2	2325.9	2322.2	2322.2	2322.2	2322.2	2318.7
22.5°	2227.9	2224.3	2224.3	2227.9	2227.9	2224.3	2227.9	2227.9
25°	2122.7	2126.3	2122.7	2122.7	2126.3	2126.3	2126.3	2122.7
27.5°	2010.2	2013.8	2017.5	2013.8	2013.8	2013.8	2017.5	2021.1
30°	1894.1	1901.3	1894.1	1894.1	1901.3	1897.8	1901.3	1901.3
32.5°	1770.8	1781.6	1774.3	1781.6	1781.6	1785.3	1781.6	1785.3
35°	1647.4	1658.3	1658.3	1658.3	1661.9	1665.6	1665.6	1661.9
37.5°	1531.2	1534.9	1534.9	1542.1	1545.7	1549.4	1549.4	1545.7
40°	1411.5	1418.7	1422.4	1422.4	1422.4	1429.7	1436.9	1429.7
42.5°	1295.4	1299.0	1302.7	1302.7	1309.9	1313.5	1317.2	1317.2
45°	1182.9	1190.2	1193.8	1197.4	1201.0	1208.3	1204.7	1211.9
47.5°	1066.8	1077.7	1081.3	1085.0	1092.2	1095.8	1099.5	1103.0
50°	961.5	968.8	968.8	976.1	987.0	987.0	994.2	997.8
52.5°	856.3	860.0	863.6	867.3	874.5	881.8	881.8	889.0
55°	754.8	758.3	758.3	762.0	765.6	780.1	783.8	783.8
57.5°	649.6	649.6	656.8	660.4	664.1	671.3	671.3	671.3
60°	547.9	551.6	551.6	555.1	558.8	566.1	569.6	566.1
62.5°	446.4	449.9	449.9	453.6	460.9	464.4	460.9	460.9
65°	351.9	355.6	355.6	359.2	366.4	366.4	362.9	366.4
67.5°	257.7	257.7	257.7	257.7	257.7	257.7	257.7	257.7
70°	163.2	159.7	156.0	159.7	159.7	159.7	156.0	163.2
72.5°	79.8	83.5	83.5	83.5	83.5	83.5	83.5	79.8
75°	36.3	36.3	32.7	32.7	32.7	36.3	36.3	32.7
77.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
80°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)