

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585280

Luminaire Tested: **HCC8W80D010BZ-HM86080930-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010BZ-HM86080930-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5370.7 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585280
CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P585280

CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88343	88343	88343
5°	90002	87959	85916
10°	91406	86421	82776
15°	92325	84270	79188
20°	91971	81014	75538
25°	89551	76343	71321
30°	85282	70768	67176
35°	77012	64590	62399
40°	67663	57974	57817
45°	58406	50953	53160
50°	50842	44696	47675
55°	45079	38821	41531
60°	40223	32798	34469
65°	36256	26625	27187
70°	32205	19952	16102
75°	27748	11557	6946
80°	21363	4138	2078
85°	13728	1380	1380



TEST NUMBER: P585280
 CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.9	5.0
10°-20°	748.7	13.9
20°-30°	1058.9	19.7
30°-40°	1115.8	20.8
40°-50°	948.3	17.7
50°-60°	682.9	12.7
60°-70°	393.9	7.3
70°-80°	134.8	2.5
80°-90°	18.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2076.5	38.7
0°-40°	3192.3	59.4
0°-60°	4823.4	89.8
0°-90°	5370.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5370.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2865	2865	2865	2865	2865	
5°	2908	2888	2842	2791	2776	278
15°	2892	2803	2640	2523	2480	814
25°	2632	2496	2244	2127	2096	1207
35°	2046	1926	1716	1654	1658	1274
45°	1339	1277	1168	1176	1219	1040
55°	838	772	722	749	772	755
65°	497	427	365	357	373	494
75°	233	175	97	62	58	246
85°	39	23	4	4	4	52
90°	0	0	0	0	0	



TEST NUMBER: P585280

CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9
2.5°	2892.0	2895.9	2892.0	2892.0	2888.1	2884.3	2880.4	2876.4	2868.7	2861.0	2861.0
5°	2907.6	2915.3	2907.6	2907.6	2895.9	2888.1	2880.4	2868.7	2853.2	2841.6	2841.6
7.5°	2919.2	2919.2	2919.2	2907.6	2899.7	2888.1	2868.7	2849.3	2829.9	2810.4	2802.7
10°	2919.2	2919.2	2915.3	2899.7	2892.0	2868.7	2849.3	2822.1	2795.0	2767.8	2760.0
12.5°	2907.6	2911.4	2903.7	2888.1	2868.7	2841.6	2814.4	2779.4	2748.4	2717.3	2701.8
15°	2892.0	2888.1	2880.4	2861.0	2837.7	2802.7	2775.6	2736.7	2694.0	2655.3	2639.7
17.5°	2853.2	2853.2	2841.6	2822.1	2791.1	2752.3	2709.6	2666.8	2620.3	2577.6	2558.1
20°	2802.7	2802.7	2787.3	2763.9	2732.8	2682.4	2635.8	2585.4	2531.0	2488.3	2468.8
22.5°	2729.0	2732.8	2713.4	2686.3	2651.4	2593.1	2546.5	2484.4	2430.1	2379.5	2364.1
25°	2632.0	2639.7	2620.3	2593.1	2546.5	2496.1	2437.8	2379.5	2317.5	2267.1	2243.8
27.5°	2519.4	2523.2	2503.8	2476.7	2430.1	2375.7	2317.5	2255.4	2197.2	2142.8	2119.5
30°	2395.1	2379.5	2371.8	2336.9	2286.4	2239.8	2173.8	2123.4	2061.3	2014.8	1987.5
32.5°	2220.5	2228.2	2204.9	2177.8	2138.9	2084.6	2030.2	1972.0	1913.8	1878.9	1859.5
35°	2045.8	2053.5	2041.9	2014.8	1972.0	1925.5	1871.1	1828.3	1777.9	1735.2	1715.8
37.5°	1863.3	1863.3	1855.6	1840.0	1808.9	1766.3	1711.9	1669.2	1626.6	1591.6	1579.9
40°	1680.9	1673.0	1669.2	1657.6	1630.4	1591.6	1556.6	1521.7	1479.0	1455.7	1440.2
42.5°	1502.3	1502.3	1494.6	1482.9	1455.7	1436.3	1401.4	1362.6	1331.4	1308.3	1308.3
45°	1339.3	1343.1	1331.4	1323.7	1308.3	1277.1	1246.1	1219.0	1191.7	1176.2	1168.4
47.5°	1195.7	1195.7	1184.0	1176.2	1160.7	1133.5	1106.4	1083.1	1063.7	1052.0	1048.1
50°	1059.8	1059.8	1059.8	1040.4	1021.0	1001.5	982.1	955.0	943.4	935.5	931.7
52.5°	943.4	939.4	939.4	923.9	904.5	881.2	861.8	838.5	826.8	819.1	822.9
55°	838.5	838.5	834.6	815.2	795.8	772.5	753.1	733.7	725.9	718.2	722.1
56°	795.8	795.8	791.9	776.4	753.1	733.7	710.4	690.9	679.3	683.2	683.2
57°	764.8	756.9	756.9	737.5	718.2	690.9	671.5	652.2	644.4	640.5	640.5
58°	725.9	722.1	718.2	698.8	679.3	656.1	636.6	617.2	605.6	605.6	601.8
59°	687.1	687.1	679.3	663.8	644.4	621.1	601.8	582.3	570.6	566.8	566.8
60°	652.2	656.1	644.4	628.9	613.3	586.2	562.9	547.3	535.6	531.8	531.8
61°	621.1	621.1	613.3	593.9	574.5	555.1	531.8	512.5	504.6	496.9	496.9
62°	593.9	586.2	582.3	562.9	543.5	520.2	500.8	481.3	469.7	461.9	465.9
63°	558.9	555.1	547.3	531.8	512.5	489.2	465.9	450.3	438.6	427.0	430.9
64°	531.8	527.9	516.3	500.8	481.3	458.1	434.8	419.2	411.5	399.9	395.9
65°	496.9	493.0	489.2	469.7	450.3	427.0	407.6	392.0	380.5	372.6	364.9
66°	465.9	469.7	461.9	446.5	423.2	403.7	376.6	361.0	353.3	341.6	333.9
67°	438.6	438.6	430.9	415.3	392.0	372.6	353.3	333.9	322.2	310.6	306.6
67.5°	423.2	423.2	415.3	395.9	380.5	357.2	337.7	322.2	306.6	298.9	291.2
68°	407.6	407.6	403.7	388.2	368.8	345.5	326.0	306.6	291.2	279.5	275.6
69°	380.5	384.3	376.6	361.0	341.6	318.3	298.9	283.3	267.9	256.2	248.4
70°	357.2	353.3	345.5	329.9	310.6	295.0	275.6	256.2	240.7	225.2	221.3
71°	326.0	326.0	318.3	306.6	287.3	267.9	248.4	232.9	217.3	198.0	194.0
72°	302.8	302.8	295.0	279.5	264.0	244.6	225.2	205.7	194.0	174.7	166.9
72.5°	287.3	291.2	283.3	267.9	252.3	229.0	213.5	198.0	178.6	163.0	155.3
73°	279.5	275.6	271.7	256.2	236.8	221.3	201.9	186.3	166.9	151.4	143.6



TEST NUMBER: P585280
 CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	174.7	174.7	170.9	155.3	139.7	124.3	108.7	93.2	77.6	62.1	54.3
80°	120.3	124.3	116.4	108.7	97.0	81.6	66.0	54.3	38.8	31.0	23.3
82.5°	77.6	77.6	73.7	66.0	58.3	46.6	38.8	27.2	19.4	15.6	11.7
85°	38.8	42.7	38.8	35.0	27.2	23.3	19.4	11.7	7.7	3.9	3.9
87.5°	15.6	15.6	15.6	11.7	11.7	7.7	3.9	3.9	3.9	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585280

CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9	2864.9
2.5°	2853.2	2853.2	2845.4	2841.6	2837.7	2833.7	2829.9	2826.0	2826.0	2829.9
5°	2829.9	2822.1	2806.6	2802.7	2791.1	2787.3	2779.4	2775.6	2779.4	2775.6
7.5°	2795.0	2779.4	2760.0	2752.3	2736.7	2729.0	2717.3	2717.3	2709.6	2713.4
10°	2748.4	2725.1	2701.8	2686.3	2674.7	2663.0	2655.3	2647.4	2643.6	2643.6
12.5°	2690.1	2663.0	2639.7	2616.4	2597.0	2589.2	2573.7	2573.7	2566.0	2562.1
15°	2624.1	2589.2	2562.1	2538.8	2523.2	2507.7	2496.1	2488.3	2480.5	2480.5
17.5°	2538.8	2507.7	2480.5	2453.4	2430.1	2418.4	2406.8	2395.1	2395.1	2387.4
20°	2445.5	2410.7	2387.4	2360.2	2340.8	2321.4	2305.8	2305.8	2298.1	2301.9
22.5°	2340.8	2298.1	2274.8	2255.4	2235.9	2220.5	2204.9	2204.9	2201.1	2197.2
25°	2224.4	2189.4	2162.2	2138.9	2127.2	2111.8	2107.9	2100.1	2096.2	2096.2
27.5°	2100.1	2072.9	2037.9	2026.3	2010.8	2003.1	2003.1	1999.2	1991.5	1995.3
30°	1968.2	1937.1	1917.6	1909.9	1894.3	1894.3	1890.5	1882.7	1882.7	1886.6
32.5°	1840.0	1808.9	1793.5	1789.6	1774.0	1774.0	1770.2	1774.0	1774.0	1777.9
35°	1700.3	1673.0	1669.2	1657.6	1653.7	1653.7	1653.7	1661.5	1669.2	1657.6
37.5°	1568.3	1548.9	1537.3	1533.3	1537.3	1537.3	1541.1	1552.7	1548.9	1545.0
40°	1432.4	1416.9	1409.1	1409.1	1416.9	1424.7	1424.7	1436.3	1440.2	1436.3
42.5°	1296.6	1285.0	1285.0	1288.8	1296.6	1300.4	1312.1	1323.7	1327.6	1331.4
45°	1168.4	1168.4	1168.4	1172.4	1176.2	1184.0	1199.5	1211.1	1215.0	1219.0
47.5°	1044.2	1040.4	1052.0	1055.8	1067.5	1071.4	1083.1	1098.5	1102.4	1106.4
50°	927.8	935.5	939.4	951.1	958.8	958.8	974.4	982.1	993.8	993.8
52.5°	819.1	830.8	834.6	846.2	850.1	854.1	861.8	873.4	881.2	881.2
55°	722.1	725.9	733.7	737.5	749.2	753.1	760.8	764.8	776.4	772.5
56°	679.3	687.1	690.9	698.8	706.5	710.4	718.2	722.1	729.8	733.7
57°	640.5	644.4	656.1	659.9	667.7	667.7	671.5	683.2	683.2	687.1
58°	601.8	609.5	613.3	617.2	624.9	628.9	636.6	640.5	644.4	640.5
59°	566.8	570.6	574.5	574.5	582.3	582.3	593.9	601.8	605.6	605.6
60°	531.8	531.8	535.6	539.6	547.3	551.2	551.2	558.9	558.9	558.9
61°	496.9	496.9	500.8	504.6	508.5	508.5	516.3	516.3	520.2	524.1
62°	465.9	461.9	461.9	465.9	465.9	473.6	477.5	481.3	485.2	481.3
63°	430.9	427.0	427.0	427.0	427.0	434.8	434.8	438.6	446.5	442.5
64°	392.0	392.0	392.0	392.0	395.9	395.9	403.7	407.6	411.5	415.3
65°	364.9	357.2	353.3	353.3	357.2	361.0	364.9	368.8	372.6	372.6
66°	333.9	326.0	322.2	322.2	322.2	322.2	329.9	329.9	337.7	337.7
67°	298.9	291.2	287.3	283.3	283.3	283.3	295.0	291.2	291.2	291.2
67.5°	287.3	275.6	271.7	267.9	264.0	271.7	267.9	271.7	271.7	267.9
68°	271.7	264.0	256.2	248.4	248.4	248.4	252.3	256.2	252.3	248.4
69°	240.7	236.8	225.2	217.3	213.5	217.3	213.5	217.3	213.5	217.3
70°	213.5	201.9	190.2	186.3	182.4	182.4	182.4	178.6	182.4	178.6
71°	186.3	174.7	163.0	155.3	151.4	151.4	147.6	151.4	147.6	151.4
72°	159.2	147.6	132.0	124.3	124.3	124.3	124.3	120.3	124.3	120.3
72.5°	147.6	132.0	120.3	112.6	108.7	108.7	108.7	108.7	104.9	108.7
73°	135.9	120.3	104.9	100.9	100.9	100.9	97.0	93.2	97.0	97.0



TEST NUMBER: P585280
CATALOG NUMBER: HCC8W80D010BZ-HM86080930-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	46.6	35.0	31.0	31.0	31.0	31.0	31.0	31.0	27.2	27.2
80°	19.4	15.6	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7
82.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
85°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	252.3	252.3	244.6	232.9	213.5	194.0	178.6	163.0	143.6	124.3	116.4
75°	232.9	229.0	221.3	209.6	194.0	174.7	159.2	139.7	124.3	104.9	97.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



74°	112.6	93.2	85.4	77.6	77.6	77.6	73.7	73.7	73.7	77.6
75°	89.3	73.7	66.0	58.3	62.1	58.3	62.1	58.3	58.3	58.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)