

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585125

Luminaire Tested: **HCC8W60D010MB-HM86080927-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585125  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W60D010MB-HM86080927-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4515.6 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585125  
CATALOG NUMBER: HCC8W60D010MB-HM86080927-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585125

CATALOG NUMBER: HCC8W60D010MB-HM86080927-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	105997
5°	104616
10°	100784
15°	96839
20°	94164
25°	91331
30°	81956
35°	53726
40°	29699
45°	24761
50°	22581
55°	21548
60°	20037
65°	18168
70°	16427
75°	14833
80°	13478
85°	12879



TEST NUMBER: P585125  
 CATALOG NUMBER: HCC8W60D010MB-HM86080927-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	317.5	7.0
10°-20°	855.8	19.0
20°-30°	1218.0	27.0
30°-40°	901.5	20.0
40°-50°	446.5	9.9
50°-60°	356.3	7.9
60°-70°	247.4	5.5
70°-80°	133.3	3.0
80°-90°	39.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2391.4	53.0
0°-40°	3292.8	72.9
0°-60°	4095.6	90.7
0°-90°	4515.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4515.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3437	
5°	3380	318
15°	3033	856
25°	2684	1218
35°	1427	901
45°	568	446
55°	401	356
65°	249	247
75°	124	133
85°	36	39
90°	0	



TEST NUMBER: P585125  
CATALOG NUMBER: HCC8W60D010MB-HM86080927-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3437.4
2.5°	3422.1
5°	3379.7
7.5°	3312.9
10°	3218.7
12.5°	3121.6
15°	3033.4
17.5°	2948.4
20°	2869.5
22.5°	2790.5
25°	2684.3
27.5°	2529.4
30°	2301.7
32.5°	1952.5
35°	1427.2
37.5°	974.7
40°	737.8
42.5°	631.6
45°	567.8
47.5°	516.3
50°	470.7
52.5°	431.1
55°	400.8
57.5°	364.4
60°	324.9
62.5°	285.5
65°	249.0
67.5°	212.6
70°	182.2
72.5°	151.8
75°	124.5
77.5°	100.2
80°	75.9
82.5°	54.7
85°	36.4
87.5°	15.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)