

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585278

Luminaire Tested: **HCC8S80D010SL-HM86080930-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010SL-HM86080930-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5770.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585278
CATALOG NUMBER: HCC8S80D010SL-HM86080930-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P585278
 CATALOG NUMBER: HCC8S80D010SL-HM86080930-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89					89			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79					79			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71					71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64					64			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58					58			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53					53			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49					49			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45					45			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42					42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135449
5°	133685
10°	128789
15°	123751
20°	120330
25°	116706
30°	104726
35°	68652
40°	37955
45°	31643
50°	28851
55°	27537
60°	25606
65°	23217
70°	20989
75°	18956
80°	17225
85°	16487



TEST NUMBER: P585278
 CATALOG NUMBER: HCC8S80D010SL-HM86080930-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	405.8	7.0
10°-20°	1093.7	19.0
20°-30°	1556.4	27.0
30°-40°	1151.9	20.0
40°-50°	570.6	9.9
50°-60°	455.4	7.9
60°-70°	316.1	5.5
70°-80°	170.4	3.0
80°-90°	50.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3055.8	53.0
0°-40°	4207.8	72.9
0°-60°	5233.7	90.7
0°-90°	5770.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5770.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4392	
5°	4319	406
15°	3876	1094
25°	3430	1556
35°	1824	1152
45°	726	571
55°	512	455
65°	318	316
75°	159	170
85°	47	50
90°	0	



TEST NUMBER: P585278
CATALOG NUMBER: HCC8S80D010SL-HM86080930-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4392.5
2.5°	4373.0
5°	4318.8
7.5°	4233.4
10°	4113.1
12.5°	3989.0
15°	3876.4
17.5°	3767.7
20°	3666.9
22.5°	3565.9
25°	3430.1
27.5°	3232.3
30°	2941.2
32.5°	2495.0
35°	1823.7
37.5°	1245.6
40°	942.9
42.5°	807.1
45°	725.6
47.5°	659.7
50°	601.4
52.5°	551.0
55°	512.2
57.5°	465.6
60°	415.2
62.5°	364.8
65°	318.2
67.5°	271.6
70°	232.8
72.5°	194.0
75°	159.1
77.5°	128.1
80°	97.0
82.5°	69.8
85°	46.6
87.5°	19.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)