

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585290

Luminaire Tested: **HCC8W80D010MB-HM86080935-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585290  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010MB-HM86080935-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6517.0 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585290  
CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585290

CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			58
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			55
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	298036
5°	271594
10°	232053
15°	202367
20°	180369
25°	159998
30°	130997
35°	75228
40°	33383
45°	19428
50°	11216
55°	6403
60°	3534
65°	2255
70°	1587
75°	1048
80°	781
85°	1557



TEST NUMBER: P585290  
 CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	794.2	12.2
10°-20°	1781.9	27.3
20°-30°	2132.9	32.7
30°-40°	1290.3	19.8
40°-50°	361.6	5.5
50°-60°	112.3	1.7
60°-70°	32.1	0.5
70°-80°	8.7	0.1
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4709.0	72.3
0°-40°	5999.3	92.1
0°-60°	6473.2	99.3
0°-90°	6517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6517.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9665	
5°	8774	794
15°	6339	1782
25°	4702	2133
35°	1998	1290
45°	446	362
55°	119	112
65°	31	32
75°	9	9
85°	4	3
90°	0	



TEST NUMBER: P585290  
CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9665.1
2.5°	9391.7
5°	8774.1
7.5°	8077.1
10°	7411.0
12.5°	6828.7
15°	6339.0
17.5°	5906.7
20°	5496.5
22.5°	5117.1
25°	4702.5
27.5°	4234.9
30°	3679.0
32.5°	2960.0
35°	1998.4
37.5°	1244.1
40°	829.3
42.5°	595.6
45°	445.5
47.5°	326.4
50°	233.8
52.5°	163.2
55°	119.1
57.5°	79.4
60°	57.3
62.5°	39.7
65°	30.9
67.5°	22.1
70°	17.6
72.5°	8.8
75°	8.8
77.5°	4.4
80°	4.4
82.5°	4.4
85°	4.4
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)