

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585142

Luminaire Tested: **HCC8S60D010MW-HM86080930-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585142  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MW-HM86080930-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4830.8 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585142  
CATALOG NUMBER: HCC8S60D010MW-HM86080930-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585142

CATALOG NUMBER: HCC8S60D010MW-HM86080930-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89					89			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79					79			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71					71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64					64			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58					58			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53					53			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49					49			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45					45			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42					42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39					39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113394
5°	111918
10°	107820
15°	103600
20°	100736
25°	97704
30°	87678
35°	57475
40°	31776
45°	26493
50°	24154
55°	23053
60°	21437
65°	19431
70°	17572
75°	15870
80°	14419
85°	13798



TEST NUMBER: P585142  
 CATALOG NUMBER: HCC8S60D010MW-HM86080930-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	339.7	7.0
10°-20°	915.6	19.0
20°-30°	1303.0	27.0
30°-40°	964.4	20.0
40°-50°	477.7	9.9
50°-60°	381.2	7.9
60°-70°	264.6	5.5
70°-80°	142.6	3.0
80°-90°	42.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2558.3	53.0
0°-40°	3522.7	72.9
0°-60°	4381.5	90.7
0°-90°	4830.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4830.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3677	
5°	3616	340
15°	3245	916
25°	2872	1303
35°	1527	964
45°	608	478
55°	429	381
65°	266	265
75°	133	143
85°	39	42
90°	0	



TEST NUMBER: P585142  
CATALOG NUMBER: HCC8S60D010MW-HM86080930-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3677.3
2.5°	3661.0
5°	3615.6
7.5°	3544.1
10°	3443.4
12.5°	3339.4
15°	3245.2
17.5°	3154.3
20°	3069.8
22.5°	2985.3
25°	2871.6
27.5°	2706.0
30°	2462.4
32.5°	2088.8
35°	1526.8
37.5°	1042.8
40°	789.4
42.5°	675.7
45°	607.5
47.5°	552.2
50°	503.5
52.5°	461.2
55°	428.8
57.5°	389.8
60°	347.6
62.5°	305.3
65°	266.3
67.5°	227.5
70°	194.9
72.5°	162.4
75°	133.2
77.5°	107.2
80°	81.2
82.5°	58.5
85°	39.0
87.5°	16.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)