

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585305

Luminaire Tested: **HCC8S80D010BZ-HM86080935-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S80D010BZ-HM86080935-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6247.8 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585305
CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P585305

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75								
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65								
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57								
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50								
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45								
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40								
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33								
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	95793	95793	95793
5°	99298	95475	92194
10°	102102	94644	88425
15°	104385	92973	84519
20°	104546	89343	81090
25°	102542	84376	78218
30°	97256	78246	74788
35°	88366	71260	71426
40°	77267	63943	67317
45°	66966	56958	62732
50°	58637	50592	57155
55°	52192	44837	51713
60°	47075	40278	45447
65°	42502	35410	39605
70°	38192	29834	29437
75°	33646	23662	22089
80°	28217	19587	21150
85°	21865	17160	18716



TEST NUMBER: P585305
 CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	4.7
10°-20°	825.4	13.2
20°-30°	1179.6	18.9
30°-40°	1253.4	20.1
40°-50°	1079.2	17.3
50°-60°	806.8	12.9
60°-70°	514.6	8.2
70°-80°	234.2	3.7
80°-90°	61.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2298.1	36.8
0°-40°	3551.5	56.8
0°-60°	5437.5	87.0
0°-90°	6247.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6247.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3106	3106	3106	3106	3106	
5°	3208	3164	3084	3005	2978	307
15°	3270	3159	2912	2714	2648	921
25°	3014	2824	2480	2330	2299	1380
35°	2347	2184	1893	1844	1897	1462
45°	1536	1452	1306	1341	1438	1194
55°	971	891	834	905	962	873
65°	582	516	485	508	543	581
75°	282	243	199	181	185	300
85°	62	53	48	53	53	74
90°	0	0	0	0	0	



TEST NUMBER: P585305

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5
2.5°	3163.8	3155.0	3159.4	3155.0	3159.4	3159.4	3150.6	3150.6	3150.6	3150.6	3137.3
5°	3207.9	3203.5	3203.5	3199.1	3194.7	3199.1	3194.7	3190.3	3181.4	3177.0	3163.8
7.5°	3234.4	3234.4	3234.4	3234.4	3230.0	3225.6	3221.1	3212.3	3203.5	3194.7	3185.9
10°	3260.8	3265.4	3260.8	3256.4	3252.0	3243.2	3238.8	3230.0	3216.7	3203.5	3194.7
12.5°	3274.1	3274.1	3269.8	3269.8	3260.8	3256.4	3243.2	3230.0	3216.7	3203.5	3181.4
15°	3269.8	3269.8	3265.4	3260.8	3247.6	3243.2	3234.4	3221.1	3199.1	3181.4	3159.4
17.5°	3243.2	3238.8	3230.0	3230.0	3212.3	3207.9	3199.1	3181.4	3159.4	3132.9	3106.5
20°	3185.9	3185.9	3181.4	3177.0	3159.4	3146.2	3137.3	3115.3	3097.6	3066.8	3040.3
22.5°	3106.5	3115.3	3106.5	3097.6	3075.6	3071.2	3057.9	3031.5	3005.0	2969.6	2938.7
25°	3013.8	3009.4	3005.0	2996.2	2978.4	2969.6	2952.0	2925.5	2899.0	2859.3	2824.0
27.5°	2894.6	2877.0	2877.0	2859.3	2846.1	2832.9	2824.0	2797.6	2762.3	2731.4	2687.3
30°	2731.4	2735.8	2713.8	2709.4	2687.3	2678.5	2660.7	2634.3	2603.4	2568.1	2532.8
32.5°	2554.9	2541.6	2541.6	2524.0	2506.3	2493.1	2488.7	2457.8	2431.4	2396.1	2360.8
35°	2347.4	2347.4	2334.2	2329.8	2312.1	2303.3	2290.1	2272.4	2241.6	2210.7	2184.2
37.5°	2144.5	2135.7	2131.3	2122.5	2109.2	2096.0	2096.0	2065.1	2060.7	2025.3	1990.0
40°	1919.5	1928.3	1919.5	1906.2	1901.8	1893.0	1888.6	1870.9	1857.7	1826.8	1804.8
42.5°	1729.8	1721.0	1721.0	1716.4	1698.8	1698.8	1690.0	1681.2	1659.1	1650.3	1623.8
45°	1535.6	1544.4	1531.2	1535.6	1517.9	1517.9	1517.9	1500.3	1482.7	1469.4	1451.8
47.5°	1367.9	1372.3	1372.3	1359.0	1354.6	1354.6	1345.8	1337.0	1323.7	1306.1	1292.9
50°	1222.3	1226.7	1217.9	1213.5	1204.6	1200.2	1200.2	1182.6	1173.8	1156.1	1147.3
52.5°	1090.0	1090.0	1085.4	1085.4	1072.2	1072.2	1063.4	1050.2	1041.3	1032.5	1010.5
55°	970.8	970.8	966.3	961.9	961.9	948.7	944.3	931.1	922.2	904.6	891.4
57.5°	856.1	860.5	856.1	851.7	847.2	842.8	834.0	820.8	812.0	798.7	789.9
60°	763.3	763.3	758.9	754.5	745.7	741.3	736.9	728.0	714.8	706.0	692.8
62.5°	675.1	670.7	666.3	661.9	653.1	653.1	644.2	635.4	622.2	613.4	604.5
65°	582.5	582.5	578.1	578.1	573.7	564.8	560.4	556.0	538.4	534.0	516.3
67.5°	498.7	503.1	494.3	494.3	485.3	485.3	481.0	467.8	463.4	454.4	445.6
70°	423.6	423.6	423.6	419.2	410.3	405.9	401.5	392.7	388.3	379.5	370.6
72.5°	348.6	348.6	344.2	344.2	339.8	335.3	330.9	322.1	322.1	313.3	304.5
75°	282.4	282.4	278.0	273.6	269.2	269.2	264.8	260.4	251.5	247.1	242.7
77.5°	216.2	216.2	216.2	211.8	207.4	207.4	207.4	198.6	189.8	189.8	185.4
80°	158.9	158.9	154.5	154.5	150.1	150.1	150.1	145.7	141.3	136.7	132.3
82.5°	105.9	105.9	105.9	105.9	101.5	101.5	101.5	97.0	92.6	92.6	92.6
85°	61.8	61.8	61.8	61.8	57.3	57.3	57.3	57.3	57.3	52.9	52.9
87.5°	26.5	22.1	26.5	22.1	26.5	22.1	26.5	22.1	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585305

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5
2.5°	3141.7	3137.3	3132.9	3128.5	3128.5	3124.1	3115.3	3110.9	3106.5	3102.0	3102.0
5°	3159.4	3155.0	3146.2	3137.3	3132.9	3124.1	3115.3	3106.5	3097.6	3084.4	3080.0
7.5°	3172.6	3159.4	3150.6	3132.9	3128.5	3119.7	3106.5	3093.2	3075.6	3057.9	3044.7
10°	3172.6	3155.0	3141.7	3119.7	3110.9	3102.0	3084.4	3062.3	3040.3	3022.6	3000.6
12.5°	3163.8	3141.7	3119.7	3097.6	3084.4	3071.2	3044.7	3022.6	2996.2	2969.6	2952.0
15°	3132.9	3106.5	3080.0	3053.5	3040.3	3022.6	2996.2	2965.2	2938.7	2912.3	2881.4
17.5°	3075.6	3049.1	3018.2	2987.4	2969.6	2956.4	2916.7	2894.6	2854.9	2828.5	2802.0
20°	3000.6	2969.6	2929.9	2899.0	2877.0	2863.7	2832.9	2793.2	2762.3	2722.6	2696.1
22.5°	2903.4	2863.7	2824.0	2793.2	2771.1	2753.5	2713.8	2674.1	2647.5	2612.2	2581.3
25°	2788.8	2749.1	2709.4	2665.1	2643.1	2625.4	2590.2	2554.9	2519.6	2479.9	2453.4
27.5°	2651.9	2607.8	2572.5	2532.8	2510.8	2484.3	2444.6	2409.3	2374.0	2347.4	2312.1
30°	2501.9	2453.4	2418.1	2378.4	2356.4	2334.2	2294.5	2259.2	2228.3	2197.5	2179.8
32.5°	2321.0	2285.7	2250.4	2210.7	2193.0	2179.8	2140.1	2104.8	2069.5	2043.1	2029.7
35°	2148.9	2109.2	2078.4	2043.1	2020.9	2007.7	1972.4	1941.5	1923.9	1893.0	1875.3
37.5°	1968.0	1937.1	1901.8	1866.5	1853.3	1840.1	1813.6	1782.7	1756.2	1734.2	1725.4
40°	1778.3	1751.8	1721.0	1698.8	1685.6	1672.3	1650.3	1628.2	1610.6	1588.5	1579.7
42.5°	1597.3	1579.7	1553.2	1526.8	1513.5	1509.1	1482.7	1465.0	1456.2	1447.4	1438.5
45°	1434.1	1407.7	1389.9	1372.3	1359.0	1350.2	1337.0	1323.7	1314.9	1306.1	1297.3
47.5°	1275.2	1253.2	1235.5	1222.3	1209.1	1204.6	1195.8	1182.6	1173.8	1173.8	1173.8
50°	1129.7	1112.0	1094.4	1085.4	1081.0	1072.2	1063.4	1059.0	1054.6	1054.6	1054.6
52.5°	1001.6	984.0	970.8	961.9	961.9	953.1	944.3	939.9	939.9	939.9	939.9
55°	882.5	869.3	860.5	851.7	842.8	838.4	838.4	838.4	834.0	834.0	838.4
57.5°	776.7	767.7	754.5	745.7	741.3	741.3	736.9	732.5	736.9	741.3	745.7
60°	679.5	670.7	666.3	653.1	653.1	653.1	648.6	648.6	648.6	653.1	657.5
62.5°	591.3	586.9	578.1	573.7	569.2	569.2	564.8	564.8	564.8	564.8	569.2
65°	511.9	503.1	494.3	494.3	494.3	489.7	489.7	481.0	485.3	485.3	481.0
67.5°	436.8	428.0	423.6	419.2	414.7	414.7	410.3	405.9	401.5	401.5	401.5
70°	366.2	357.4	357.4	348.6	348.6	344.2	339.8	339.8	335.3	330.9	326.5
72.5°	295.6	291.2	286.8	282.4	282.4	282.4	278.0	273.6	269.2	264.8	255.9
75°	233.9	233.9	225.1	220.7	220.7	216.2	211.8	207.4	203.0	198.6	194.2
77.5°	181.0	176.4	167.6	163.2	163.2	163.2	158.9	154.5	150.1	145.7	141.3
80°	132.3	127.9	123.5	119.1	119.1	119.1	114.7	114.7	110.3	110.3	110.3
82.5°	88.2	88.2	83.8	83.8	83.8	83.8	79.4	79.4	79.4	79.4	79.4
85°	52.9	52.9	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
87.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585305

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5
2.5°	3093.2	3093.2	3084.4	3080.0	3075.6	3080.0	3071.2	3066.8	3062.3	3062.3	3057.9
5°	3066.8	3062.3	3044.7	3040.3	3035.9	3031.5	3022.6	3013.8	3005.0	3000.6	2996.2
7.5°	3031.5	3018.2	3000.6	2996.2	2991.8	2978.4	2965.2	2956.4	2943.1	2938.7	2929.9
10°	2982.8	2965.2	2952.0	2938.7	2929.9	2916.7	2903.4	2890.2	2872.6	2868.2	2854.9
12.5°	2925.5	2903.4	2877.0	2872.6	2859.3	2841.7	2824.0	2810.8	2797.6	2788.8	2775.5
15°	2854.9	2832.9	2806.4	2793.2	2779.9	2766.7	2744.6	2727.0	2713.8	2700.5	2687.3
17.5°	2771.1	2744.6	2722.6	2709.4	2700.5	2678.5	2660.7	2638.7	2625.4	2612.2	2599.0
20°	2669.7	2647.5	2616.6	2603.4	2599.0	2581.3	2559.3	2550.5	2532.8	2519.6	2510.8
22.5°	2554.9	2532.8	2506.3	2497.5	2479.9	2471.1	2449.0	2440.2	2431.4	2418.1	2413.7
25°	2426.9	2404.9	2382.8	2378.4	2365.2	2356.4	2343.0	2329.8	2329.8	2316.6	2316.6
27.5°	2294.5	2272.4	2254.8	2246.0	2241.6	2232.7	2219.5	2215.1	2210.7	2206.3	2206.3
30°	2153.3	2126.9	2118.1	2113.6	2109.2	2100.4	2096.0	2087.2	2091.6	2096.0	2091.6
32.5°	2003.3	1994.4	1976.8	1968.0	1972.4	1968.0	1959.2	1968.0	1963.6	1972.4	1976.8
35°	1857.7	1848.9	1840.1	1840.1	1831.2	1831.2	1831.2	1835.6	1844.5	1848.9	1857.7
37.5°	1716.4	1703.2	1698.8	1694.4	1698.8	1698.8	1698.8	1707.6	1716.4	1725.4	1738.6
40°	1566.5	1557.6	1557.6	1557.6	1557.6	1570.9	1566.5	1575.3	1584.1	1597.3	1610.6
42.5°	1425.3	1425.3	1429.7	1429.7	1429.7	1429.7	1438.5	1451.8	1465.0	1478.2	1491.5
45°	1292.9	1292.9	1292.9	1301.7	1301.7	1306.1	1323.7	1332.6	1341.4	1354.6	1367.9
47.5°	1169.4	1169.4	1173.8	1178.2	1182.6	1191.4	1200.2	1213.5	1226.7	1235.5	1248.8
50°	1054.6	1059.0	1067.8	1076.6	1076.6	1081.0	1094.4	1103.2	1112.0	1125.2	1129.7
52.5°	944.3	953.1	961.9	966.3	970.8	979.6	984.0	997.2	1001.6	1014.9	1019.3
55°	842.8	847.2	860.5	864.9	864.9	873.7	882.5	891.4	904.6	904.6	913.4
57.5°	750.1	754.5	763.3	767.7	763.3	776.7	781.1	789.9	794.3	803.1	807.4
60°	657.5	666.3	670.7	670.7	675.1	679.5	688.3	688.3	697.2	706.0	706.0
62.5°	569.2	573.7	578.1	582.5	586.9	582.5	595.7	595.7	604.5	608.9	617.8
65°	485.3	489.7	489.7	494.3	494.3	498.7	498.7	503.1	507.5	516.3	520.7
67.5°	401.5	401.5	401.5	405.9	401.5	405.9	405.9	410.3	410.3	419.2	423.6
70°	326.5	322.1	317.7	317.7	317.7	317.7	313.3	317.7	317.7	322.1	322.1
72.5°	251.5	247.1	242.7	238.3	238.3	233.9	229.5	233.9	233.9	238.3	238.3
75°	189.8	181.0	181.0	181.0	176.4	176.4	176.4	181.0	181.0	181.0	185.4
77.5°	141.3	141.3	136.7	136.7	136.7	141.3	141.3	145.7	145.7	145.7	145.7
80°	105.9	110.3	110.3	110.3	110.3	114.7	114.7	114.7	114.7	119.1	119.1
82.5°	79.4	79.4	79.4	79.4	83.8	83.8	83.8	83.8	83.8	83.8	83.8
85°	48.5	52.9	52.9	48.5	52.9	52.9	52.9	52.9	52.9	52.9	52.9
87.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585305

CATALOG NUMBER: HCC8S80D010BZ-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5	3106.5
2.5°	3053.5	3053.5	3053.5	3053.5	3049.1	3049.1	3049.1	3044.7
5°	2987.4	2987.4	2987.4	2978.4	2982.8	2982.8	2974.0	2978.4
7.5°	2921.1	2916.7	2912.3	2912.3	2907.9	2903.4	2899.0	2903.4
10°	2846.1	2832.9	2832.9	2828.5	2828.5	2819.6	2819.6	2824.0
12.5°	2762.3	2753.5	2753.5	2749.1	2744.6	2740.2	2735.8	2735.8
15°	2678.5	2669.7	2665.1	2660.7	2656.3	2647.5	2651.9	2647.5
17.5°	2594.6	2581.3	2581.3	2576.9	2572.5	2563.7	2563.7	2559.3
20°	2497.5	2493.1	2484.3	2488.7	2484.3	2475.5	2471.1	2471.1
22.5°	2400.5	2400.5	2396.1	2396.1	2391.7	2387.2	2382.8	2382.8
25°	2307.7	2303.3	2307.7	2307.7	2294.5	2294.5	2294.5	2298.9
27.5°	2201.9	2206.3	2201.9	2201.9	2201.9	2201.9	2206.3	2201.9
30°	2096.0	2096.0	2096.0	2100.4	2109.2	2104.8	2104.8	2100.4
32.5°	1981.2	1985.6	1985.6	1990.0	1994.4	2003.3	2003.3	2007.7
35°	1866.5	1875.3	1879.8	1875.3	1888.6	1888.6	1897.4	1897.4
37.5°	1747.4	1751.8	1760.7	1765.1	1773.9	1778.3	1782.7	1782.7
40°	1619.4	1637.0	1641.5	1645.9	1659.1	1659.1	1663.5	1672.3
42.5°	1500.3	1517.9	1522.4	1526.8	1535.6	1548.8	1544.4	1553.2
45°	1385.5	1398.7	1403.1	1407.7	1420.9	1425.3	1425.3	1438.5
47.5°	1262.0	1270.8	1275.2	1284.0	1292.9	1301.7	1310.5	1306.1
50°	1138.5	1151.7	1160.5	1164.9	1178.2	1182.6	1187.0	1191.4
52.5°	1028.1	1036.9	1041.3	1045.7	1059.0	1063.4	1067.8	1076.6
55°	922.2	926.6	935.5	931.1	944.3	948.7	953.1	961.9
57.5°	816.4	820.8	825.2	825.2	834.0	842.8	847.2	851.7
60°	714.8	723.6	728.0	728.0	728.0	736.9	736.9	736.9
62.5°	622.2	622.2	626.6	626.6	635.4	635.4	635.4	635.4
65°	525.1	529.5	534.0	534.0	542.8	538.4	547.2	542.8
67.5°	423.6	423.6	432.4	432.4	428.0	432.4	432.4	432.4
70°	322.1	322.1	326.5	326.5	326.5	326.5	326.5	326.5
72.5°	238.3	238.3	238.3	242.7	238.3	238.3	242.7	238.3
75°	185.4	185.4	185.4	185.4	185.4	185.4	185.4	185.4
77.5°	145.7	145.7	150.1	150.1	150.1	150.1	150.1	150.1
80°	119.1	119.1	119.1	119.1	123.5	119.1	119.1	119.1
82.5°	88.2	83.8	88.2	83.8	88.2	88.2	88.2	88.2
85°	52.9	52.9	52.9	52.9	52.9	52.9	52.9	52.9
87.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)