

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585148

Luminaire Tested: **HCC8S60D010SL-HM86080930-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010SL-HM86080930-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4990.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585148
CATALOG NUMBER: HCC8S60D010SL-HM86080930-81WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585148

CATALOG NUMBER: HCC8S60D010SL-HM86080930-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52																			
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48																			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																			
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99762
5°	99638
10°	98655
15°	97474
20°	96569
25°	95489
30°	90096
35°	73365
40°	40532
45°	27055
50°	23996
55°	22526
60°	22239
65°	22043
70°	19916
75°	17800
80°	15574
85°	13798



TEST NUMBER: P585148
 CATALOG NUMBER: HCC8S60D010SL-HM86080930-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.1	6.1
10°-20°	862.1	17.3
20°-30°	1281.0	25.7
30°-40°	1153.6	23.1
40°-50°	511.4	10.2
50°-60°	378.8	7.6
60°-70°	294.6	5.9
70°-80°	159.7	3.2
80°-90°	43.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2448.2	49.1
0°-40°	3601.8	72.2
0°-60°	4492.0	90.0
0°-90°	4990.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4990.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3235	
5°	3219	305
15°	3053	862
25°	2806	1281
35°	1949	1154
45°	620	511
55°	419	379
65°	302	295
75°	149	160
85°	39	44
90°	0	



TEST NUMBER: P585148
CATALOG NUMBER: HCC8S60D010SL-HM86080930-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3235.2
2.5°	3228.7
5°	3218.9
7.5°	3193.0
10°	3150.7
12.5°	3102.0
15°	3053.3
17.5°	3004.6
20°	2942.8
22.5°	2881.1
25°	2806.5
27.5°	2692.7
30°	2530.3
32.5°	2296.4
35°	1948.9
37.5°	1455.1
40°	1006.9
42.5°	743.8
45°	620.4
47.5°	548.9
50°	500.2
52.5°	454.8
55°	419.0
57.5°	389.7
60°	360.6
62.5°	334.6
65°	302.1
67.5°	263.1
70°	220.9
72.5°	185.1
75°	149.4
77.5°	117.0
80°	87.7
82.5°	61.7
85°	39.0
87.5°	16.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)