

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585169

Luminaire Tested: **HCC8S60D010MB-HM86080935-81WWWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010MB-HM86080935-81WWWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5230.6 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.18
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585169
CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585169

CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			87	
2	102	94	88	83	99	93	87	82	89	85	81	86	82	79	83	80	77	75			75	
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65			65	
4	87	76	68	62	84	75	67	61	72	66	61	70	64	60	68	63	59	57			57	
5	80	69	60	54	78	67	60	54	65	59	54	64	58	53	62	57	52	50			50	
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45			45	
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40			40	
8	65	52	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37	
9	61	48	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33			33	
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	30			30	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80196	80196	80196
5°	83130	79930	77184
10°	85482	79232	74028
15°	87389	77837	70760
20°	87522	74793	67885
25°	85846	70637	65486
30°	81418	65506	62611
35°	73982	59659	59798
40°	64684	53534	56360
45°	56064	47682	52518
50°	49091	42355	47853
55°	43692	37536	43294
60°	39415	33716	38052
65°	35585	29646	33148
70°	31980	24974	24650
75°	28165	19801	18479
80°	23618	16408	17722
85°	18292	14365	15674



TEST NUMBER: P585169
 CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.3	4.7
10°-20°	691.0	13.2
20°-30°	987.6	18.9
30°-40°	1049.3	20.1
40°-50°	903.5	17.3
50°-60°	675.5	12.9
60°-70°	430.8	8.2
70°-80°	196.1	3.7
80°-90°	51.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1923.9	36.8
0°-40°	2973.3	56.8
0°-60°	4552.2	87.0
0°-90°	5230.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5230.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2601	2601	2601	2601	2601	
5°	2686	2649	2582	2516	2494	257
15°	2737	2645	2438	2272	2216	771
25°	2523	2364	2076	1950	1925	1155
35°	1965	1829	1585	1544	1588	1224
45°	1286	1215	1093	1123	1204	999
55°	813	746	698	757	805	731
65°	488	432	406	425	454	486
75°	236	203	166	151	155	251
85°	52	44	41	44	44	62
90°	0	0	0	0	0	



TEST NUMBER: P585169

CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7
2.5°	2648.7	2641.3	2645.0	2641.3	2645.0	2645.0	2637.6	2637.6	2637.6	2637.6	2626.5
5°	2685.6	2681.9	2681.9	2678.2	2674.5	2678.2	2674.5	2670.8	2663.4	2659.7	2648.7
7.5°	2707.8	2707.8	2707.8	2707.8	2704.1	2700.5	2696.6	2689.3	2681.9	2674.5	2667.1
10°	2730.0	2733.7	2730.0	2726.3	2722.6	2715.2	2711.5	2704.1	2693.0	2681.9	2674.5
12.5°	2741.1	2741.1	2737.4	2737.4	2730.0	2726.3	2715.2	2704.1	2693.0	2681.9	2663.4
15°	2737.4	2737.4	2733.7	2730.0	2718.9	2715.2	2707.8	2696.6	2678.2	2663.4	2645.0
17.5°	2715.2	2711.5	2704.1	2704.1	2689.3	2685.6	2678.2	2663.4	2645.0	2622.8	2600.7
20°	2667.1	2667.1	2663.4	2659.7	2645.0	2633.9	2626.5	2608.1	2593.3	2567.5	2545.2
22.5°	2600.7	2608.1	2600.7	2593.3	2574.9	2571.2	2560.0	2537.8	2515.7	2486.2	2460.3
25°	2523.1	2519.4	2515.7	2508.3	2493.5	2486.2	2471.4	2449.2	2427.0	2393.8	2364.2
27.5°	2423.3	2408.5	2408.5	2393.8	2382.7	2371.6	2364.2	2342.1	2312.6	2286.6	2249.7
30°	2286.6	2290.3	2271.9	2268.2	2249.7	2242.3	2227.6	2205.4	2179.6	2149.9	2120.4
32.5°	2138.9	2127.8	2127.8	2113.0	2098.3	2087.2	2083.5	2057.7	2035.4	2005.9	1976.4
35°	1965.3	1965.3	1954.2	1950.5	1935.8	1928.4	1917.3	1902.4	1876.6	1850.7	1828.6
37.5°	1795.4	1788.0	1784.3	1776.9	1765.7	1754.7	1754.7	1728.8	1725.1	1695.6	1666.1
40°	1606.9	1614.3	1606.9	1595.8	1592.2	1584.8	1581.1	1566.3	1555.2	1529.4	1510.8
42.5°	1448.1	1440.7	1440.7	1437.0	1422.3	1422.3	1414.9	1407.5	1389.0	1381.5	1359.4
45°	1285.6	1293.0	1281.9	1285.6	1270.8	1270.8	1270.8	1256.1	1241.2	1230.1	1215.3
47.5°	1145.2	1148.9	1148.9	1137.8	1134.1	1134.1	1126.8	1119.4	1108.2	1093.4	1082.4
50°	1023.3	1027.0	1019.6	1015.9	1008.5	1004.8	1004.8	990.1	982.6	967.8	960.4
52.5°	912.5	912.5	908.8	908.8	897.7	897.7	890.3	879.2	871.9	864.5	845.9
55°	812.7	812.7	809.0	805.3	805.3	794.2	790.5	779.5	772.1	757.3	746.2
57.5°	716.6	720.3	716.6	712.9	709.2	705.5	698.2	687.1	679.7	668.6	661.2
60°	639.1	639.1	635.4	631.7	624.3	620.6	617.0	609.6	598.5	591.0	579.9
62.5°	565.2	561.5	557.8	554.1	546.7	546.7	539.3	531.9	520.9	513.5	506.1
65°	487.7	487.7	484.0	484.0	480.3	472.9	469.2	465.5	450.6	446.9	432.2
67.5°	417.4	421.1	413.7	413.7	406.3	406.3	402.7	391.6	387.9	380.5	373.1
70°	354.7	354.7	354.7	351.0	343.6	339.9	336.2	328.7	325.0	317.6	310.3
72.5°	291.8	291.8	288.1	288.1	284.4	280.7	277.0	269.7	269.7	262.3	254.9
75°	236.4	236.4	232.8	229.1	225.4	225.4	221.7	218.0	210.6	206.9	203.2
77.5°	181.0	181.0	181.0	177.3	173.6	173.6	173.6	166.2	158.8	158.8	155.1
80°	133.0	133.0	129.3	129.3	125.6	125.6	125.6	121.9	118.2	114.5	110.8
82.5°	88.7	88.7	88.7	88.7	85.0	85.0	85.0	81.3	77.6	77.6	77.6
85°	51.7	51.7	51.7	51.7	48.0	48.0	48.0	48.0	48.0	44.3	44.3
87.5°	22.1	18.5	22.1	18.5	22.1	18.5	22.1	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585169

CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7
2.5°	2630.2	2626.5	2622.8	2619.1	2619.1	2615.4	2608.1	2604.4	2600.7	2597.0	2597.0
5°	2645.0	2641.3	2633.9	2626.5	2622.8	2615.4	2608.1	2600.7	2593.3	2582.2	2578.5
7.5°	2656.0	2645.0	2637.6	2622.8	2619.1	2611.8	2600.7	2589.6	2574.9	2560.0	2548.9
10°	2656.0	2641.3	2630.2	2611.8	2604.4	2597.0	2582.2	2563.7	2545.2	2530.4	2512.0
12.5°	2648.7	2630.2	2611.8	2593.3	2582.2	2571.2	2548.9	2530.4	2508.3	2486.2	2471.4
15°	2622.8	2600.7	2578.5	2556.3	2545.2	2530.4	2508.3	2482.5	2460.3	2438.2	2412.2
17.5°	2574.9	2552.6	2526.8	2500.9	2486.2	2475.1	2441.9	2423.3	2390.1	2367.9	2345.8
20°	2512.0	2486.2	2452.9	2427.0	2408.5	2397.5	2371.6	2338.4	2312.6	2279.2	2257.1
22.5°	2430.7	2397.5	2364.2	2338.4	2319.9	2305.2	2271.9	2238.6	2216.5	2187.0	2161.0
25°	2334.7	2301.4	2268.2	2231.3	2212.8	2198.0	2168.4	2138.9	2109.3	2076.1	2054.0
27.5°	2220.2	2183.3	2153.6	2120.4	2102.0	2079.8	2046.6	2017.0	1987.4	1965.3	1935.8
30°	2094.6	2054.0	2024.3	1991.1	1972.7	1954.2	1921.0	1891.3	1865.5	1839.7	1824.9
32.5°	1943.1	1913.6	1884.0	1850.7	1836.0	1824.9	1791.7	1762.0	1732.5	1710.4	1699.3
35°	1799.1	1765.7	1739.9	1710.4	1691.9	1680.8	1651.3	1625.4	1610.6	1584.8	1570.0
37.5°	1647.6	1621.7	1592.2	1562.6	1551.6	1540.5	1518.3	1492.4	1470.2	1451.8	1444.4
40°	1488.7	1466.5	1440.7	1422.3	1411.2	1400.1	1381.5	1363.1	1348.3	1329.9	1322.5
42.5°	1337.3	1322.5	1300.3	1278.2	1267.1	1263.4	1241.2	1226.4	1219.0	1211.6	1204.3
45°	1200.6	1178.4	1163.7	1148.9	1137.8	1130.4	1119.4	1108.2	1100.8	1093.4	1086.0
47.5°	1067.6	1049.1	1034.4	1023.3	1012.2	1008.5	1001.2	990.1	982.6	982.6	982.6
50°	945.7	930.9	916.1	908.8	905.1	897.7	890.3	886.6	882.9	882.9	882.9
52.5°	838.5	823.8	812.7	805.3	805.3	797.9	790.5	786.8	786.8	786.8	786.8
55°	738.9	727.8	720.3	712.9	705.5	701.8	701.8	701.8	698.2	698.2	701.8
57.5°	650.2	642.8	631.7	624.3	620.6	620.6	617.0	613.3	617.0	620.6	624.3
60°	568.9	561.5	557.8	546.7	546.7	546.7	543.0	543.0	543.0	546.7	550.4
62.5°	495.0	491.3	484.0	480.3	476.6	476.6	472.9	472.9	472.9	472.9	476.6
65°	428.5	421.1	413.7	413.7	413.7	410.0	410.0	402.7	406.3	406.3	402.7
67.5°	365.7	358.4	354.7	351.0	347.3	347.3	343.6	339.9	336.2	336.2	336.2
70°	306.6	299.2	299.2	291.8	291.8	288.1	284.4	284.4	280.7	277.0	273.4
72.5°	247.5	243.8	240.1	236.4	236.4	236.4	232.8	229.1	225.4	221.7	214.3
75°	195.7	195.7	188.4	184.7	184.7	181.0	177.3	173.6	169.9	166.2	162.5
77.5°	151.4	147.8	140.4	136.7	136.7	136.7	133.0	129.3	125.6	121.9	118.2
80°	110.8	107.2	103.5	99.8	99.8	99.8	96.1	96.1	92.4	92.4	92.4
82.5°	73.9	73.9	70.2	70.2	70.2	70.2	66.6	66.6	66.6	66.6	66.6
85°	44.3	44.3	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6	40.6
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585169

CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7
2.5°	2589.6	2589.6	2582.2	2578.5	2574.9	2578.5	2571.2	2567.5	2563.7	2563.7	2560.0
5°	2567.5	2563.7	2548.9	2545.2	2541.5	2537.8	2530.4	2523.1	2515.7	2512.0	2508.3
7.5°	2537.8	2526.8	2512.0	2508.3	2504.6	2493.5	2482.5	2475.1	2464.0	2460.3	2452.9
10°	2497.2	2482.5	2471.4	2460.3	2452.9	2441.9	2430.7	2419.6	2404.8	2401.1	2390.1
12.5°	2449.2	2430.7	2408.5	2404.8	2393.8	2379.0	2364.2	2353.2	2342.1	2334.7	2323.6
15°	2390.1	2371.6	2349.5	2338.4	2327.3	2316.3	2297.7	2282.9	2271.9	2260.8	2249.7
17.5°	2319.9	2297.7	2279.2	2268.2	2260.8	2242.3	2227.6	2209.1	2198.0	2187.0	2175.9
20°	2234.9	2216.5	2190.7	2179.6	2175.9	2161.0	2142.6	2135.2	2120.4	2109.3	2102.0
22.5°	2138.9	2120.4	2098.3	2090.9	2076.1	2068.7	2050.3	2042.9	2035.4	2024.3	2020.6
25°	2031.7	2013.3	1994.8	1991.1	1980.0	1972.7	1961.6	1950.5	1950.5	1939.4	1939.4
27.5°	1921.0	1902.4	1887.7	1880.3	1876.6	1869.2	1858.1	1854.4	1850.7	1847.1	1847.1
30°	1802.8	1780.6	1773.1	1769.4	1765.7	1758.4	1754.7	1747.3	1751.0	1754.7	1751.0
32.5°	1677.2	1669.8	1655.0	1647.6	1651.3	1647.6	1640.1	1647.6	1643.8	1651.3	1655.0
35°	1555.2	1547.9	1540.5	1540.5	1533.1	1533.1	1533.1	1536.8	1544.2	1547.9	1555.2
37.5°	1437.0	1425.9	1422.3	1418.6	1422.3	1422.3	1422.3	1429.6	1437.0	1444.4	1455.5
40°	1311.4	1304.0	1304.0	1304.0	1304.0	1315.1	1311.4	1318.8	1326.2	1337.3	1348.3
42.5°	1193.2	1193.2	1196.9	1196.9	1196.9	1196.9	1204.3	1215.3	1226.4	1237.5	1248.6
45°	1082.4	1082.4	1082.4	1089.7	1089.7	1093.4	1108.2	1115.6	1123.1	1134.1	1145.2
47.5°	978.9	978.9	982.6	986.3	990.1	997.5	1004.8	1015.9	1027.0	1034.4	1045.4
50°	882.9	886.6	894.0	901.4	901.4	905.1	916.1	923.5	930.9	942.0	945.7
52.5°	790.5	797.9	805.3	809.0	812.7	820.1	823.8	834.8	838.5	849.6	853.3
55°	705.5	709.2	720.3	724.1	724.1	731.5	738.9	746.2	757.3	757.3	764.7
57.5°	628.0	631.7	639.1	642.8	639.1	650.2	653.9	661.2	664.9	672.3	676.0
60°	550.4	557.8	561.5	561.5	565.2	568.9	576.2	576.2	583.6	591.0	591.0
62.5°	476.6	480.3	484.0	487.7	491.3	487.7	498.7	498.7	506.1	509.8	517.2
65°	406.3	410.0	410.0	413.7	413.7	417.4	417.4	421.1	424.8	432.2	435.9
67.5°	336.2	336.2	336.2	339.9	336.2	339.9	339.9	343.6	343.6	351.0	354.7
70°	273.4	269.7	266.0	266.0	266.0	266.0	262.3	266.0	266.0	269.7	269.7
72.5°	210.6	206.9	203.2	199.5	199.5	195.7	192.0	195.7	195.7	199.5	199.5
75°	158.8	151.4	151.4	151.4	147.8	147.8	147.8	151.4	151.4	151.4	155.1
77.5°	118.2	118.2	114.5	114.5	114.5	118.2	118.2	121.9	121.9	121.9	121.9
80°	88.7	92.4	92.4	92.4	92.4	96.1	96.1	96.1	96.1	99.8	99.8
82.5°	66.6	66.6	66.6	66.6	70.2	70.2	70.2	70.2	70.2	70.2	70.2
85°	40.6	44.3	44.3	40.6	44.3	44.3	44.3	44.3	44.3	44.3	44.3
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585169

CATALOG NUMBER: HCC8S60D010MB-HM86080935-81WWWB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7	2600.7
2.5°	2556.3	2556.3	2556.3	2556.3	2552.6	2552.6	2552.6	2548.9
5°	2500.9	2500.9	2500.9	2493.5	2497.2	2497.2	2489.8	2493.5
7.5°	2445.6	2441.9	2438.2	2438.2	2434.4	2430.7	2427.0	2430.7
10°	2382.7	2371.6	2371.6	2367.9	2367.9	2360.5	2360.5	2364.2
12.5°	2312.6	2305.2	2305.2	2301.4	2297.7	2294.0	2290.3	2290.3
15°	2242.3	2234.9	2231.3	2227.6	2223.9	2216.5	2220.2	2216.5
17.5°	2172.2	2161.0	2161.0	2157.3	2153.6	2146.2	2146.2	2142.6
20°	2090.9	2087.2	2079.8	2083.5	2079.8	2072.4	2068.7	2068.7
22.5°	2009.6	2009.6	2005.9	2005.9	2002.2	1998.5	1994.8	1994.8
25°	1932.1	1928.4	1932.1	1932.1	1921.0	1921.0	1921.0	1924.7
27.5°	1843.4	1847.1	1843.4	1843.4	1843.4	1843.4	1847.1	1843.4
30°	1754.7	1754.7	1754.7	1758.4	1765.7	1762.0	1762.0	1758.4
32.5°	1658.7	1662.4	1662.4	1666.1	1669.8	1677.2	1677.2	1680.8
35°	1562.6	1570.0	1573.7	1570.0	1581.1	1581.1	1588.5	1588.5
37.5°	1462.9	1466.5	1473.9	1477.6	1485.0	1488.7	1492.4	1492.4
40°	1355.7	1370.5	1374.2	1377.9	1389.0	1389.0	1392.7	1400.1
42.5°	1256.1	1270.8	1274.5	1278.2	1285.6	1296.7	1293.0	1300.3
45°	1160.0	1171.0	1174.7	1178.4	1189.5	1193.2	1193.2	1204.3
47.5°	1056.5	1063.9	1067.6	1075.0	1082.4	1089.7	1097.1	1093.4
50°	953.1	964.1	971.5	975.2	986.3	990.1	993.8	997.5
52.5°	860.8	868.2	871.9	875.5	886.6	890.3	894.0	901.4
55°	772.1	775.8	783.2	779.5	790.5	794.2	797.9	805.3
57.5°	683.4	687.1	690.8	690.8	698.2	705.5	709.2	712.9
60°	598.5	605.9	609.6	609.6	609.6	617.0	617.0	617.0
62.5°	520.9	520.9	524.6	524.6	531.9	531.9	531.9	531.9
65°	439.6	443.3	446.9	446.9	454.3	450.6	458.0	454.3
67.5°	354.7	354.7	362.1	362.1	358.4	362.1	362.1	362.1
70°	269.7	269.7	273.4	273.4	273.4	273.4	273.4	273.4
72.5°	199.5	199.5	199.5	203.2	199.5	199.5	203.2	199.5
75°	155.1	155.1	155.1	155.1	155.1	155.1	155.1	155.1
77.5°	121.9	121.9	125.6	125.6	125.6	125.6	125.6	125.6
80°	99.8	99.8	99.8	99.8	103.5	99.8	99.8	99.8
82.5°	73.9	70.2	73.9	70.2	73.9	73.9	73.9	73.9
85°	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)