

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585178

Luminaire Tested: **HCC8S60D010SL-HM86080940-81RWWH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S60D010SL-HM86080940-81RWWH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5273.3 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585178
CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P585178

CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77	77	77	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67	67	67	67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59	59	59	59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52	52	52	52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47	47	47	47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42	42	42	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38	38	38	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35	35	35	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32	32	32	32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	86739	86739	86739
5°	88371	86365	84359
10°	89750	84856	81273
15°	90652	82741	77751
20°	90304	79548	74169
25°	87925	74959	70028
30°	83736	69490	65958
35°	75612	63419	61270
40°	66435	56923	56770
45°	57346	50033	52191
50°	49920	43886	46812
55°	44262	38117	40778
60°	39495	32199	33852
65°	35600	26136	26698
70°	31610	19592	15805
75°	27248	11354	6815
80°	20972	4049	2024
85°	13480	1344	1344



TEST NUMBER: P585178
 CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.1	5.0
10°-20°	735.1	13.9
20°-30°	1039.7	19.7
30°-40°	1095.6	20.8
40°-50°	931.1	17.7
50°-60°	670.5	12.7
60°-70°	386.8	7.3
70°-80°	132.3	2.5
80°-90°	18.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2038.9	38.7
0°-40°	3134.4	59.4
0°-60°	4736.0	89.8
0°-90°	5273.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5273.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2813	2813	2813	2813	2813	
5°	2855	2836	2790	2740	2725	273
15°	2840	2752	2592	2478	2436	800
25°	2584	2451	2203	2089	2058	1185
35°	2009	1890	1685	1624	1628	1251
45°	1315	1254	1147	1155	1197	1022
55°	823	758	709	736	758	741
65°	488	419	358	351	366	485
75°	229	172	95	61	57	241
85°	38	23	4	4	4	51
90°	0	0	0	0	0	



TEST NUMBER: P585178

CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9
2.5°	2839.6	2843.4	2839.6	2839.6	2835.7	2831.9	2828.1	2824.3	2816.7	2809.1	2809.1
5°	2854.9	2862.5	2854.9	2854.9	2843.4	2835.7	2828.1	2816.7	2801.5	2790.1	2790.1
7.5°	2866.3	2866.3	2866.3	2854.9	2847.2	2835.7	2816.7	2797.7	2778.7	2759.5	2751.9
10°	2866.3	2866.3	2862.5	2847.2	2839.6	2816.7	2797.7	2771.0	2744.3	2717.6	2710.0
12.5°	2854.9	2858.7	2851.0	2835.7	2816.7	2790.1	2763.3	2729.1	2698.6	2668.0	2652.8
15°	2839.6	2835.7	2828.1	2809.1	2786.3	2751.9	2725.3	2687.1	2645.2	2607.1	2591.8
17.5°	2801.5	2801.5	2790.1	2771.0	2740.5	2702.4	2660.4	2618.6	2572.8	2530.9	2511.8
20°	2751.9	2751.9	2736.7	2713.8	2683.3	2633.8	2588.0	2538.5	2485.1	2443.2	2424.1
22.5°	2679.5	2683.3	2664.2	2637.6	2603.2	2546.1	2500.3	2439.4	2386.0	2336.4	2321.2
25°	2584.2	2591.8	2572.8	2546.1	2500.3	2450.9	2393.7	2336.4	2275.5	2225.9	2203.1
27.5°	2473.7	2477.5	2458.5	2431.7	2386.0	2332.6	2275.5	2214.5	2157.3	2103.9	2081.1
30°	2351.7	2336.4	2328.8	2294.6	2245.0	2199.3	2134.5	2084.9	2023.9	1978.2	1951.6
32.5°	2180.2	2187.8	2164.9	2138.3	2100.1	2046.8	1993.4	1936.2	1879.1	1844.7	1825.7
35°	2008.6	2016.3	2004.8	1978.2	1936.2	1890.5	1837.1	1795.3	1745.7	1703.8	1684.7
37.5°	1829.5	1829.5	1821.9	1806.7	1776.1	1734.3	1680.8	1639.0	1597.0	1562.7	1551.3
40°	1650.4	1642.8	1639.0	1627.6	1600.8	1562.7	1528.4	1494.1	1452.2	1429.3	1414.1
42.5°	1475.1	1475.1	1467.5	1456.1	1429.3	1410.3	1376.0	1337.8	1307.4	1284.5	1284.5
45°	1315.0	1318.8	1307.4	1299.8	1284.5	1254.0	1223.5	1196.8	1170.1	1154.9	1147.3
47.5°	1173.9	1173.9	1162.5	1154.9	1139.7	1112.9	1086.3	1063.4	1044.4	1032.9	1029.1
50°	1040.6	1040.6	1040.6	1021.5	1002.4	983.4	964.4	937.6	926.2	918.6	914.8
52.5°	926.2	922.4	922.4	907.1	888.1	865.2	846.1	823.3	811.9	804.3	808.1
55°	823.3	823.3	819.5	800.5	781.3	758.5	739.4	720.4	712.8	705.2	709.0
56°	781.3	781.3	777.5	762.3	739.4	720.4	697.5	678.4	667.0	670.8	670.8
57°	750.9	743.3	743.3	724.2	705.2	678.4	659.4	640.4	632.8	628.9	628.9
58°	712.8	709.0	705.2	686.0	667.0	644.2	625.1	606.0	594.6	594.6	590.8
59°	674.6	674.6	667.0	651.8	632.8	609.8	590.8	571.7	560.3	556.5	556.5
60°	640.4	644.2	632.8	617.4	602.2	575.5	552.7	537.4	526.0	522.1	522.1
61°	609.8	609.8	602.2	583.2	564.1	545.1	522.1	503.1	495.5	487.9	487.9
62°	583.2	575.5	571.7	552.7	533.6	510.7	491.7	472.7	461.2	453.5	457.4
63°	548.9	545.1	537.4	522.1	503.1	480.3	457.4	442.1	430.7	419.3	423.1
64°	522.1	518.3	506.9	491.7	472.7	449.7	426.9	411.6	404.0	392.6	388.8
65°	487.9	484.1	480.3	461.2	442.1	419.3	400.2	385.0	373.6	365.9	358.2
66°	457.4	461.2	453.5	438.3	415.5	396.4	369.7	354.4	346.8	335.4	327.8
67°	430.7	430.7	423.1	407.8	385.0	365.9	346.8	327.8	316.4	305.0	301.2
67.5°	415.5	415.5	407.8	388.8	373.6	350.6	331.6	316.4	301.2	293.5	285.8
68°	400.2	400.2	396.4	381.2	362.1	339.2	320.2	301.2	285.8	274.4	270.6
69°	373.6	377.4	369.7	354.4	335.4	312.6	293.5	278.2	263.0	251.6	243.9
70°	350.6	346.8	339.2	324.0	305.0	289.7	270.6	251.6	236.3	221.1	217.3
71°	320.2	320.2	312.6	301.2	282.0	263.0	243.9	228.7	213.5	194.3	190.5
72°	297.3	297.3	289.7	274.4	259.2	240.1	221.1	202.0	190.5	171.5	163.9
72.5°	282.0	285.8	278.2	263.0	247.8	224.9	209.7	194.3	175.3	160.1	152.5
73°	274.4	270.6	266.8	251.6	232.5	217.3	198.2	182.9	163.9	148.7	141.1



TEST NUMBER: P585178
 CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
77.5°	171.5	171.5	167.7	152.5	137.3	121.9	106.7	91.5	76.2	61.0	53.4
80°	118.1	121.9	114.3	106.7	95.3	80.0	64.8	53.4	38.1	30.4	22.8
82.5°	76.2	76.2	72.4	64.8	57.2	45.8	38.1	26.6	19.0	15.2	11.4
85°	38.1	42.0	38.1	34.3	26.6	22.8	19.0	11.4	7.6	3.8	3.8
87.5°	15.2	15.2	15.2	11.4	11.4	7.6	3.8	3.8	3.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585178

CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9	2812.9
2.5°	2801.5	2801.5	2793.9	2790.1	2786.3	2782.5	2778.7	2774.8	2774.8	2778.7
5°	2778.7	2771.0	2755.7	2751.9	2740.5	2736.7	2729.1	2725.3	2729.1	2725.3
7.5°	2744.3	2729.1	2710.0	2702.4	2687.1	2679.5	2668.0	2668.0	2660.4	2664.2
10°	2698.6	2675.7	2652.8	2637.6	2626.2	2614.8	2607.1	2599.4	2595.6	2595.6
12.5°	2641.4	2614.8	2591.8	2569.0	2549.9	2542.3	2527.1	2527.1	2519.4	2515.6
15°	2576.6	2542.3	2515.6	2492.7	2477.5	2462.3	2450.9	2443.2	2435.5	2435.5
17.5°	2492.7	2462.3	2435.5	2408.9	2386.0	2374.6	2363.2	2351.7	2351.7	2344.1
20°	2401.3	2367.0	2344.1	2317.4	2298.4	2279.3	2264.0	2264.0	2256.4	2260.2
22.5°	2298.4	2256.4	2233.6	2214.5	2195.5	2180.2	2164.9	2164.9	2161.1	2157.3
25°	2184.0	2149.7	2123.1	2100.1	2088.7	2073.5	2069.7	2062.0	2058.2	2058.2
27.5°	2062.0	2035.4	2001.0	1989.6	1974.4	1966.8	1966.8	1963.0	1955.4	1959.2
30°	1932.4	1902.0	1882.9	1875.3	1860.0	1860.0	1856.2	1848.6	1848.6	1852.4
32.5°	1806.7	1776.1	1760.9	1757.1	1741.9	1741.9	1738.1	1741.9	1741.9	1745.7
35°	1669.4	1642.8	1639.0	1627.6	1623.8	1623.8	1623.8	1631.4	1639.0	1627.6
37.5°	1539.9	1520.8	1509.3	1505.5	1509.3	1509.3	1513.1	1524.6	1520.8	1517.0
40°	1406.5	1391.2	1383.6	1383.6	1391.2	1398.8	1398.8	1410.3	1414.1	1410.3
42.5°	1273.0	1261.6	1261.6	1265.4	1273.0	1276.8	1288.3	1299.8	1303.6	1307.4
45°	1147.3	1147.3	1147.3	1151.1	1154.9	1162.5	1177.7	1189.2	1193.0	1196.8
47.5°	1025.3	1021.5	1032.9	1036.8	1048.2	1052.0	1063.4	1078.7	1082.5	1086.3
50°	911.0	918.6	922.4	933.8	941.4	941.4	956.7	964.4	975.8	975.8
52.5°	804.3	815.7	819.5	830.9	834.7	838.5	846.1	857.6	865.2	865.2
55°	709.0	712.8	720.4	724.2	735.6	739.4	747.1	750.9	762.3	758.5
56°	667.0	674.6	678.4	686.0	693.7	697.5	705.2	709.0	716.6	720.4
57°	628.9	632.8	644.2	648.0	655.6	655.6	659.4	670.8	670.8	674.6
58°	590.8	598.4	602.2	606.0	613.6	617.4	625.1	628.9	632.8	628.9
59°	556.5	560.3	564.1	564.1	571.7	571.7	583.2	590.8	594.6	594.6
60°	522.1	522.1	526.0	529.8	537.4	541.3	541.3	548.9	548.9	548.9
61°	487.9	487.9	491.7	495.5	499.3	499.3	506.9	506.9	510.7	514.5
62°	457.4	453.5	453.5	457.4	457.4	465.1	468.9	472.7	476.5	472.7
63°	423.1	419.3	419.3	419.3	419.3	426.9	426.9	430.7	438.3	434.5
64°	385.0	385.0	385.0	385.0	388.8	388.8	396.4	400.2	404.0	407.8
65°	358.2	350.6	346.8	346.8	350.6	354.4	358.2	362.1	365.9	365.9
66°	327.8	320.2	316.4	316.4	316.4	316.4	324.0	324.0	331.6	331.6
67°	293.5	285.8	282.0	278.2	278.2	278.2	289.7	285.8	285.8	285.8
67.5°	282.0	270.6	266.8	263.0	259.2	266.8	263.0	266.8	266.8	263.0
68°	266.8	259.2	251.6	243.9	243.9	243.9	247.8	251.6	247.8	243.9
69°	236.3	232.5	221.1	213.5	209.7	213.5	209.7	213.5	209.7	213.5
70°	209.7	198.2	186.7	182.9	179.1	179.1	179.1	175.3	179.1	175.3
71°	182.9	171.5	160.1	152.5	148.7	148.7	144.9	148.7	144.9	148.7
72°	156.3	144.9	129.6	121.9	121.9	121.9	121.9	118.1	121.9	118.1
72.5°	144.9	129.6	118.1	110.5	106.7	106.7	106.7	106.7	102.9	106.7
73°	133.4	118.1	102.9	99.1	99.1	99.1	95.3	91.5	95.3	95.3



TEST NUMBER: P585178
 CATALOG NUMBER: HCC8S60D010SL-HM86080940-81RWWH

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
77.5°	45.8	34.3	30.4	30.4	30.4	30.4	30.4	30.4	26.6	26.6
80°	19.0	15.2	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
82.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	247.8	247.8	240.1	228.7	209.7	190.5	175.3	160.1	141.1	121.9	114.3
75°	228.7	224.9	217.3	205.8	190.5	171.5	156.3	137.3	121.9	102.9	95.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



74°	110.5	91.5	83.9	76.2	76.2	76.2	72.4	72.4	72.4	76.2
75°	87.7	72.4	64.8	57.2	61.0	57.2	61.0	57.2	57.2	57.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)