

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593878

Luminaire Tested: **HCC8S60D010MW-HM86080950-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593878  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S60D010MW-HM86080950-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6157.2 lumens  
Efficiency: N/A  
Efficacy: 110.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 56  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593878  
CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P593878  
 CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95					95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89					89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84					84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79					79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75					75			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71					71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67					67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64					64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61					61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58					58			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	367886
5°	351013
10°	303050
15°	231731
20°	177304
25°	140275
30°	105962
35°	56372
40°	21471
45°	10300
50°	4390
55°	1844
60°	703
65°	555
70°	343
75°	0
80°	0
85°	0



TEST NUMBER: P593878  
 CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1029.4	16.7
10°-20°	2026.4	32.9
20°-30°	1887.3	30.7
30°-40°	973.8	15.8
40°-50°	198.3	3.2
50°-60°	33.9	0.6
60°-70°	6.6	0.1
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4943.1	80.3
0°-40°	5916.9	96.1
0°-60°	6149.2	99.9
0°-90°	6157.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6157.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11930	
5°	11340	###
15°	7259	2026
25°	4123	1887
35°	1498	974
45°	236	198
55°	34	34
65°	8	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P593878  
CATALOG NUMBER: HCC8S60D010MW-HM86080950-81MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11930.3
2.5°	11770.3
5°	11339.8
7.5°	10631.0
10°	9678.4
12.5°	8428.6
15°	7258.8
17.5°	6245.2
20°	5403.1
22.5°	4717.3
25°	4122.8
27.5°	3558.9
30°	2975.9
32.5°	2282.5
35°	1497.5
37.5°	868.7
40°	533.4
42.5°	350.5
45°	236.2
47.5°	148.6
50°	91.5
52.5°	53.4
55°	34.3
57.5°	15.2
60°	11.4
62.5°	7.6
65°	7.6
67.5°	3.8
70°	3.8
72.5°	3.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)