

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593887

Luminaire Tested: **HCC8W60D010SL-HM86080950-81WWBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W60D010SL-HM86080950-81WWBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4747.5 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.07 / 1.16
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593887
CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	63	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	58	53	49	47								
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43								
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39								
9	62	50	43	37	61	50	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	47	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78596	78596	78596
5°	81840	78419	75123
10°	84577	77419	71454
15°	86719	75651	67743
20°	86885	72512	64384
25°	85421	67922	61049
30°	80849	62671	58196
35°	73715	56361	54644
40°	64104	49689	50454
45°	54991	43029	46191
50°	46970	37102	41487
55°	41165	31950	36047
60°	36652	27259	30312
65°	32528	22232	24188
70°	28860	16481	13740
75°	24067	8626	4087
80°	18948	2699	675
85°	13480	1344	0



TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.2	5.1
10°-20°	673.1	14.2
20°-30°	952.7	20.1
30°-40°	996.8	21.0
40°-50°	831.4	17.5
50°-60°	589.5	12.4
60°-70°	339.6	7.2
70°-80°	109.3	2.3
80°-90°	15.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1866.0	39.3
0°-40°	2862.8	60.3
0°-60°	4283.7	90.2
0°-90°	4747.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4747.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2549	2549	2549	2549	2549	
5°	2644	2610	2533	2457	2427	254
15°	2716	2606	2370	2183	2122	764
25°	2511	2324	1996	1836	1794	1146
35°	1958	1787	1497	1417	1452	1214
45°	1261	1158	987	998	1059	977
55°	766	686	594	625	670	692
65°	446	373	305	305	332	445
75°	202	149	72	34	34	219
85°	38	19	4	0	0	48
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8
2.5°	2602.1	2598.3	2594.5	2598.3	2594.5	2598.3	2594.5	2594.5	2590.7	2586.8	2586.8
5°	2643.9	2640.1	2640.1	2640.1	2636.3	2632.5	2632.5	2628.7	2621.1	2617.3	2609.7
7.5°	2670.7	2674.5	2674.5	2674.5	2666.8	2666.8	2659.2	2651.6	2643.9	2636.3	2624.9
10°	2701.1	2701.1	2697.3	2693.5	2685.9	2682.1	2678.3	2670.7	2659.2	2643.9	2632.5
12.5°	2712.6	2712.6	2708.8	2701.1	2697.3	2693.5	2689.7	2678.3	2663.0	2643.9	2628.7
15°	2716.4	2708.8	2705.0	2701.1	2693.5	2682.1	2682.1	2666.8	2647.7	2624.9	2605.9
17.5°	2685.9	2689.7	2682.1	2674.5	2663.0	2655.4	2643.9	2632.5	2609.7	2583.0	2564.0
20°	2647.7	2643.9	2640.1	2628.7	2613.5	2609.7	2598.3	2579.2	2560.2	2529.6	2503.0
22.5°	2586.8	2583.0	2575.4	2567.8	2552.6	2545.0	2533.4	2510.6	2484.0	2453.5	2423.1
25°	2510.6	2503.0	2491.6	2476.3	2464.9	2457.3	2442.1	2419.1	2388.7	2354.4	2324.0
27.5°	2388.7	2400.1	2392.5	2369.7	2358.2	2343.0	2339.2	2308.8	2282.0	2247.7	2213.5
30°	2270.6	2270.6	2259.2	2247.7	2228.7	2217.3	2202.1	2179.2	2152.5	2110.6	2084.0
32.5°	2122.0	2118.2	2103.0	2099.2	2084.0	2061.1	2057.3	2026.8	2000.1	1969.7	1935.4
35°	1958.2	1950.6	1935.4	1924.0	1916.3	1904.8	1893.4	1866.8	1840.1	1809.7	1786.7
37.5°	1771.5	1771.5	1767.7	1748.7	1741.1	1733.4	1722.0	1695.4	1680.2	1649.6	1626.8
40°	1592.5	1588.7	1577.3	1573.5	1565.9	1554.4	1546.7	1531.5	1508.6	1485.8	1463.0
42.5°	1417.2	1421.0	1405.8	1409.6	1394.3	1386.7	1382.9	1360.1	1348.7	1325.8	1306.8
45°	1261.0	1257.2	1249.6	1245.8	1238.2	1230.6	1223.0	1211.5	1192.5	1169.5	1158.1
47.5°	1116.3	1104.8	1104.8	1101.0	1097.2	1082.0	1078.2	1066.8	1055.4	1032.4	1017.2
50°	979.1	979.1	979.1	975.3	963.9	960.1	952.5	941.1	929.5	914.3	891.5
52.5°	868.6	868.6	868.6	864.8	849.6	845.8	842.0	826.8	811.5	800.0	784.8
55°	765.7	769.5	765.7	758.1	746.7	746.7	735.3	727.7	712.5	701.0	685.8
57.5°	678.1	678.1	670.5	666.7	659.1	655.2	647.6	640.0	621.0	609.6	590.5
60°	594.3	590.5	590.5	582.9	575.3	567.7	563.9	552.4	544.8	525.7	510.5
62.5°	518.1	518.1	510.5	510.5	495.3	495.3	491.5	480.0	468.6	449.6	442.0
65°	445.8	445.8	442.0	438.2	426.6	422.8	419.0	407.6	396.2	384.8	373.4
67.5°	381.0	381.0	373.4	369.5	361.9	358.1	350.5	342.9	331.5	320.1	308.5
70°	320.1	316.3	312.5	308.5	300.9	297.1	289.5	281.9	270.5	262.9	251.4
72.5°	259.1	259.1	255.2	247.6	243.8	240.0	236.2	228.6	217.2	205.8	198.2
75°	202.0	202.0	202.0	194.3	186.7	182.8	182.8	175.2	167.6	156.2	148.6
77.5°	156.2	152.4	148.6	148.6	140.9	137.1	133.3	129.5	118.1	114.3	106.7
80°	106.7	110.5	106.7	102.9	99.1	95.3	95.3	87.7	83.9	76.2	68.6
82.5°	72.4	68.6	68.6	64.8	64.8	60.9	60.9	53.3	49.5	45.7	41.9
85°	38.1	38.1	34.3	34.3	34.3	30.4	30.4	26.6	26.6	22.8	19.0
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8
2.5°	2583.0	2575.4	2571.6	2571.6	2567.8	2564.0	2560.2	2556.4	2548.8	2548.8	2541.1
5°	2602.1	2594.5	2590.7	2579.2	2571.6	2571.6	2556.4	2552.6	2541.1	2533.4	2525.8
7.5°	2617.3	2602.1	2590.7	2579.2	2571.6	2564.0	2548.8	2533.4	2518.2	2503.0	2495.4
10°	2617.3	2602.1	2583.0	2564.0	2556.4	2548.8	2529.6	2506.8	2487.8	2472.5	2453.5
12.5°	2609.7	2586.8	2564.0	2548.8	2533.4	2522.0	2499.2	2476.3	2453.5	2423.1	2407.7
15°	2586.8	2556.4	2533.4	2506.8	2495.4	2476.3	2457.3	2423.1	2396.3	2369.7	2350.6
17.5°	2541.1	2503.0	2476.3	2449.7	2430.7	2419.1	2388.7	2358.2	2327.8	2297.3	2274.4
20°	2472.5	2438.3	2407.7	2373.5	2358.2	2343.0	2305.0	2274.4	2243.9	2209.7	2186.8
22.5°	2388.7	2354.4	2312.6	2285.8	2263.0	2243.9	2209.7	2175.4	2144.9	2114.4	2084.0
25°	2285.8	2251.6	2213.5	2171.6	2156.3	2137.3	2099.2	2064.9	2030.6	1996.3	1969.7
27.5°	2175.4	2129.6	2099.2	2053.5	2038.2	2019.1	1977.3	1939.2	1908.6	1882.0	1851.6
30°	2042.0	2007.7	1965.9	1924.0	1908.6	1889.6	1855.4	1821.1	1790.5	1760.1	1729.6
32.5°	1897.2	1863.0	1821.1	1790.5	1767.7	1752.5	1718.2	1687.8	1657.2	1626.8	1600.1
35°	1744.9	1706.8	1676.4	1645.8	1626.8	1607.7	1573.5	1546.7	1523.9	1497.2	1470.6
37.5°	1588.7	1562.0	1531.5	1497.2	1478.2	1463.0	1436.3	1405.8	1386.7	1363.9	1344.9
40°	1436.3	1405.8	1379.1	1348.7	1333.4	1322.0	1295.3	1272.4	1253.4	1234.4	1223.0
42.5°	1280.0	1253.4	1226.8	1207.7	1196.3	1184.9	1165.7	1139.1	1127.7	1108.6	1097.2
45°	1135.3	1112.5	1093.4	1066.8	1059.2	1051.4	1028.6	1009.6	998.2	986.7	979.1
47.5°	998.2	982.9	960.1	944.9	933.4	925.7	910.5	895.3	883.9	876.2	868.6
50°	880.0	861.0	845.8	830.6	823.0	811.5	796.2	788.6	781.0	773.4	773.4
52.5°	769.5	750.5	735.3	723.9	716.3	708.6	697.2	693.4	685.8	685.8	681.9
55°	666.7	655.2	640.0	624.8	621.0	617.2	609.6	602.0	598.2	594.3	598.2
57.5°	579.1	567.7	552.4	540.9	537.1	533.3	529.5	521.9	518.1	518.1	518.1
60°	499.1	487.7	476.2	464.8	464.8	457.2	453.4	449.6	445.8	442.0	442.0
62.5°	426.6	415.2	403.8	396.2	392.4	388.6	381.0	377.2	373.4	373.4	369.5
65°	361.9	346.7	342.9	331.5	327.7	323.9	320.1	312.5	308.5	304.7	300.9
67.5°	297.1	289.5	278.1	270.5	266.7	262.9	259.1	251.4	247.6	243.8	236.2
70°	240.0	232.4	224.8	217.2	213.4	209.6	202.0	194.3	190.5	182.8	171.4
72.5°	186.7	179.0	171.4	163.8	160.0	156.2	148.6	140.9	133.3	125.7	118.1
75°	140.9	133.3	121.9	114.3	110.5	110.5	99.1	91.5	83.9	72.4	64.8
77.5°	99.1	87.7	83.9	76.2	72.4	64.8	57.1	49.5	41.9	38.1	30.4
80°	64.8	57.1	49.5	45.7	41.9	38.1	34.3	26.6	19.0	15.2	11.4
82.5°	38.1	34.3	30.4	26.6	22.8	19.0	15.2	15.2	11.4	7.6	3.8
85°	19.0	15.2	11.4	11.4	7.6	7.6	7.6	3.8	3.8	3.8	3.8
87.5°	7.6	3.8	3.8	3.8	3.8	3.8	3.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8
2.5°	2537.2	2533.4	2529.6	2525.8	2525.8	2518.2	2518.2	2514.4	2506.8	2503.0	2503.0
5°	2514.4	2503.0	2495.4	2491.6	2487.8	2476.3	2472.5	2464.9	2457.3	2449.7	2445.9
7.5°	2480.2	2461.1	2453.5	2449.7	2438.3	2426.9	2419.1	2407.7	2396.3	2384.9	2381.1
10°	2438.3	2419.1	2400.1	2392.5	2381.1	2373.5	2358.2	2343.0	2331.6	2320.2	2308.8
12.5°	2384.9	2362.0	2343.0	2335.4	2324.0	2308.8	2285.8	2278.2	2259.2	2251.6	2236.3
15°	2324.0	2297.3	2278.2	2266.8	2255.4	2232.5	2217.3	2202.1	2183.0	2175.4	2160.1
17.5°	2247.7	2217.3	2198.3	2186.8	2179.2	2160.1	2137.3	2118.2	2099.2	2091.6	2080.2
20°	2156.3	2137.3	2110.6	2099.2	2091.6	2068.7	2045.8	2038.2	2022.9	2007.7	1996.3
22.5°	2053.5	2034.4	2007.7	1996.3	1992.5	1973.5	1954.4	1943.0	1931.6	1920.1	1908.6
25°	1946.8	1924.0	1901.0	1893.4	1885.8	1870.6	1855.4	1847.7	1836.3	1828.7	1821.1
27.5°	1832.5	1809.7	1790.5	1779.1	1771.5	1760.1	1752.5	1744.9	1737.3	1729.6	1725.8
30°	1710.6	1687.8	1672.4	1664.8	1657.2	1653.4	1642.0	1638.2	1634.4	1626.8	1630.6
32.5°	1588.7	1569.7	1554.4	1542.9	1542.9	1535.3	1531.5	1531.5	1527.7	1527.7	1527.7
35°	1455.4	1443.9	1432.5	1428.7	1424.8	1421.0	1417.2	1421.0	1417.2	1421.0	1424.8
37.5°	1333.4	1322.0	1314.4	1310.6	1306.8	1310.6	1306.8	1306.8	1310.6	1318.2	1322.0
40°	1207.7	1200.1	1192.5	1196.3	1192.5	1192.5	1192.5	1203.9	1207.7	1211.5	1215.3
42.5°	1089.6	1082.0	1078.2	1078.2	1082.0	1078.2	1085.8	1089.6	1097.2	1108.6	1116.3
45°	975.3	971.5	971.5	975.3	971.5	979.1	979.1	986.7	998.2	1005.8	1013.4
47.5°	868.6	868.6	868.6	872.4	872.4	876.2	883.9	887.7	895.3	902.9	910.5
50°	769.5	773.4	777.2	777.2	777.2	784.8	792.4	796.2	800.0	803.8	815.3
52.5°	681.9	685.8	685.8	689.6	693.4	697.2	701.0	708.6	712.5	720.1	723.9
55°	598.2	598.2	605.8	609.6	609.6	609.6	617.2	617.2	624.8	628.6	636.2
57.5°	518.1	521.9	521.9	525.7	525.7	529.5	533.3	537.1	540.9	544.8	548.6
60°	442.0	442.0	442.0	445.8	449.6	453.4	449.6	457.2	457.2	464.8	468.6
62.5°	369.5	373.4	373.4	373.4	373.4	373.4	373.4	377.2	381.0	384.8	388.6
65°	300.9	300.9	300.9	297.1	300.9	297.1	300.9	304.7	304.7	308.5	312.5
67.5°	232.4	232.4	224.8	224.8	228.6	228.6	228.6	228.6	224.8	232.4	232.4
70°	167.6	163.8	160.0	156.2	156.2	152.4	152.4	148.6	148.6	148.6	148.6
72.5°	110.5	102.9	95.3	91.5	87.7	87.7	80.0	76.2	80.0	80.0	80.0
75°	57.1	49.5	45.7	41.9	38.1	38.1	34.3	34.3	34.3	34.3	34.3
77.5°	22.8	19.0	15.2	15.2	11.4	11.4	11.4	11.4	11.4	11.4	11.4
80°	7.6	7.6	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	3.8	0.0	0.0	3.8	0.0	3.8	3.8	3.8	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593887

CATALOG NUMBER: HCC8W60D010SL-HM86080950-81WWBB

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8	2548.8
2.5°	2499.2	2499.2	2495.4	2499.2	2491.6	2495.4	2491.6	2491.6
5°	2442.1	2434.5	2434.5	2434.5	2430.7	2430.7	2426.9	2426.9
7.5°	2373.5	2369.7	2365.9	2362.0	2358.2	2354.4	2354.4	2354.4
10°	2305.0	2297.3	2297.3	2293.4	2285.8	2282.0	2282.0	2282.0
12.5°	2224.9	2221.1	2217.3	2217.3	2202.1	2205.9	2202.1	2202.1
15°	2148.7	2144.9	2144.9	2133.4	2125.8	2125.8	2125.8	2122.0
17.5°	2068.7	2064.9	2061.1	2053.5	2045.8	2045.8	2042.0	2045.8
20°	1984.9	1981.1	1973.5	1973.5	1969.7	1965.9	1958.2	1962.0
22.5°	1901.0	1893.4	1889.6	1889.6	1885.8	1885.8	1878.2	1878.2
25°	1813.5	1809.7	1805.9	1809.7	1802.1	1802.1	1794.3	1794.3
27.5°	1722.0	1718.2	1718.2	1718.2	1714.4	1718.2	1714.4	1714.4
30°	1630.6	1630.6	1626.8	1626.8	1630.6	1626.8	1630.6	1634.4
32.5°	1531.5	1531.5	1535.3	1535.3	1539.1	1539.1	1539.1	1539.1
35°	1428.7	1436.3	1436.3	1440.1	1443.9	1447.7	1447.7	1451.6
37.5°	1333.4	1337.3	1341.1	1344.9	1352.5	1352.5	1352.5	1352.5
40°	1230.6	1234.4	1242.0	1238.2	1253.4	1257.2	1253.4	1253.4
42.5°	1123.9	1131.5	1135.3	1142.9	1146.7	1154.3	1158.1	1158.1
45°	1024.8	1028.6	1036.2	1043.8	1047.6	1059.2	1059.2	1059.2
47.5°	921.9	929.5	933.4	941.1	944.9	956.3	960.1	956.3
50°	823.0	830.6	838.2	838.2	849.6	853.4	861.0	864.8
52.5°	727.7	731.5	739.1	742.9	750.5	758.1	761.9	765.7
55°	636.2	640.0	647.6	647.6	659.1	662.9	670.5	670.5
57.5°	552.4	556.2	563.9	560.1	567.7	575.3	575.3	571.5
60°	472.4	472.4	472.4	480.0	483.9	487.7	491.5	491.5
62.5°	388.6	396.2	400.0	400.0	403.8	407.6	407.6	403.8
65°	312.5	320.1	323.9	323.9	327.7	327.7	327.7	331.5
67.5°	236.2	236.2	236.2	240.0	236.2	236.2	236.2	236.2
70°	148.6	148.6	148.6	148.6	144.8	148.6	148.6	152.4
72.5°	80.0	80.0	80.0	80.0	80.0	80.0	80.0	80.0
75°	34.3	34.3	34.3	38.1	34.3	34.3	34.3	34.3
77.5°	15.2	11.4	15.2	15.2	11.4	11.4	11.4	11.4
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	0.0	3.8	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)