

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585259

Luminaire Tested: **HCC8W80D010MW-HM86080927-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585259  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010MW-HM86080927-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4911.5 lumens  
Efficiency: N/A  
Efficacy: 70.2 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585259  
CATALOG NUMBER: HCC8W80D010MW-HM86080927-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585259

CATALOG NUMBER: HCC8W80D010MW-HM86080927-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100																			
	1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95	95	95	95	95	95																			
	2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89	89	89	89	89	89																			
	3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84	84	84	84	84	84																			
	4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80	80	80	80	80	80																			
	5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75	75	75	75	75	75																			
	6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72	72	72	72	72	72																			
	7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68	68	68	68	68	68																			
	8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65	65	65	65	65	65																			
	9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62	62	62	62	62	62																			
	10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59	59	59	59	59	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	390798
5°	331088
10°	240223
15°	180397
20°	142340
25°	114814
30°	85082
35°	34467
40°	14536
45°	7793
50°	3502
55°	1763
60°	1122
65°	795
70°	658
75°	441
80°	657
85°	1309



TEST NUMBER: P585259  
 CATALOG NUMBER: HCC8W80D010MW-HM86080927-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	918.4	18.7
10°-20°	1587.1	32.3
20°-30°	1534.5	31.2
30°-40°	673.9	13.7
40°-50°	145.7	3.0
50°-60°	32.7	0.7
60°-70°	11.2	0.2
70°-80°	4.4	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4040.0	82.3
0°-40°	4713.9	96.0
0°-60°	4892.3	99.6
0°-90°	4911.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4911.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12673	
5°	10696	918
15°	5651	1587
25°	3374	1535
35°	916	674
45°	179	146
55°	33	33
65°	11	11
75°	4	4
85°	4	4
90°	0	



TEST NUMBER: P585259  
CATALOG NUMBER: HCC8W80D010MW-HM86080927-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12673.3
1°	12578.5
2°	12319.5
3°	11852.5
4°	11294.4
5°	10696.1
6°	10043.1
7°	9386.4
8°	8769.9
9°	8197.2
10°	7671.9
11°	7175.7
12°	6730.7
13°	6325.7
14°	5968.2
15°	5650.8
17.5°	4939.5
20°	4337.6
22.5°	3808.6
25°	3374.5
27.5°	2933.0
30°	2389.5
32.5°	1623.3
35°	915.6
37.5°	539.9
40°	361.1
42.5°	255.4
45°	178.7
47.5°	116.8
50°	73.0
52.5°	43.8
55°	32.8
57.5°	25.6
60°	18.2
62.5°	14.6
65°	10.9
67.5°	7.3
70°	7.3
72.5°	3.7
75°	3.7
77.5°	3.7
80°	3.7
82.5°	3.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585259  
CATALOG NUMBER: HCC8W80D010MW-HM86080927-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	3.7
87.5°	3.7

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)