

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585258

Luminaire Tested: **HCC8S80D010BZ-HM86080927-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585258  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010BZ-HM86080927-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5386.8 lumens  
Efficiency: N/A  
Efficacy: 77.0 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585258  
CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P585258  
 CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96																			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																			
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87																			
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83																			
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80																			
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76																			
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73																			
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71																			
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68																			
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1013861
5°	650312
10°	293769
15°	177252
20°	135074
25°	109078
30°	79930
35°	28941
40°	10804
45°	4906
50°	1569
55°	392
60°	228
65°	270
70°	0
75°	0
80°	657
85°	1309



TEST NUMBER: P585258  
 CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1602.3	29.7
10°-20°	1627.5	30.2
20°-30°	1456.9	27.0
30°-40°	586.9	10.9
40°-50°	96.3	1.8
50°-60°	8.8	0.2
60°-70°	3.2	0.1
70°-80°	2.5	0.0
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4686.7	87.0
0°-40°	5273.5	97.9
0°-60°	5378.6	99.8
0°-90°	5387.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5386.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	32879	
5°	21009	###
15°	5552	1627
25°	3206	1457
35°	769	587
45°	112	96
55°	7	9
65°	4	3
75°	0	2
85°	4	4
90°	0	



TEST NUMBER: P585258  
CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81NDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	32878.8
0.5°	32777.3
1°	32352.9
1.5°	31671.2
2°	30637.6
2.5°	29415.4
3°	27884.9
3.5°	26205.8
4°	24544.9
4.5°	22684.5
5°	21008.9
5.5°	19184.8
6°	17705.0
6.5°	16163.7
7°	14952.5
7.5°	13672.3
8°	12642.4
8.5°	11608.8
9°	10832.6
9.5°	9976.8
10°	9382.0
12.5°	6919.5
15°	5552.3
17.5°	4743.6
20°	4116.2
22.5°	3615.7
25°	3205.9
27.5°	2796.1
30°	2244.8
32.5°	1443.4
35°	768.8
37.5°	424.4
40°	268.4
42.5°	177.8
45°	112.5
47.5°	69.0
50°	32.7
52.5°	10.9
55°	7.3
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7



TEST NUMBER: P585258  
CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	3.7
80°	3.7
82.5°	3.7
85°	3.7
87.5°	3.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.7
70°		0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)