

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585270

Luminaire Tested: **HCC8W80D010BZ-HM86080927-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W80D010BZ-HM86080927-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4933.2 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585270
CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

Luminous Intensity Polar Plot





TEST NUMBER: P585270

CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41					41			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	82425	82425	82425
5°	85325	81957	78698
10°	87220	80519	74269
15°	88462	77805	69355
20°	88191	74028	64387
25°	86010	69229	59107
30°	81490	63665	54240
35°	74140	57618	49288
40°	65115	51247	44529
45°	56783	45079	39697
50°	49412	39496	34972
55°	44068	34708	30418
60°	40038	30423	25946
65°	35994	26457	23553
70°	32043	22567	21260
75°	28094	19015	18145
80°	23831	15449	16106
85°	17973	11569	12843



TEST NUMBER: P585270
 CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.4	5.1
10°-20°	689.9	14.0
20°-30°	957.6	19.4
30°-40°	990.0	20.1
40°-50°	829.0	16.8
50°-60°	601.8	12.2
60°-70°	379.8	7.7
70°-80°	188.1	3.8
80°-90°	46.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1897.8	38.5
0°-40°	2887.8	58.5
0°-60°	4318.5	87.5
0°-90°	4933.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4933.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2673	2673	2673	2673	2673	
5°	2756	2724	2648	2575	2542	264
15°	2771	2666	2437	2241	2172	780
25°	2528	2365	2035	1814	1737	1158
35°	1970	1824	1531	1356	1309	1226
45°	1302	1208	1034	932	910	1007
55°	820	747	646	591	566	740
65°	493	432	363	319	323	492
75°	236	196	160	152	152	253
85°	51	40	33	36	36	62
90°	0	0	0	0	0	



TEST NUMBER: P585270

CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0
2.5°	2716.5	2716.5	2720.2	2716.5	2716.5	2716.5	2712.9	2712.9	2709.3	2709.3	2702.0
5°	2756.5	2749.2	2756.5	2749.2	2749.2	2749.2	2745.5	2738.3	2734.7	2727.4	2723.8
7.5°	2774.5	2771.0	2771.0	2767.3	2767.3	2763.7	2760.0	2756.5	2742.0	2738.3	2727.4
10°	2785.5	2781.8	2781.8	2778.2	2771.0	2771.0	2763.7	2760.0	2742.0	2734.7	2720.2
12.5°	2781.8	2781.8	2781.8	2778.2	2767.3	2763.7	2756.5	2745.5	2731.0	2716.5	2702.0
15°	2771.0	2771.0	2763.7	2760.0	2749.2	2742.0	2738.3	2720.2	2705.7	2687.5	2665.7
17.5°	2734.7	2734.7	2731.0	2723.8	2712.9	2705.7	2698.4	2680.2	2665.7	2636.7	2615.0
20°	2687.5	2683.9	2680.2	2669.4	2658.5	2654.9	2644.0	2618.7	2600.5	2578.7	2549.7
22.5°	2618.7	2615.0	2611.4	2604.1	2586.0	2578.7	2571.5	2553.4	2520.7	2498.9	2462.7
25°	2527.9	2527.9	2520.7	2509.9	2491.7	2484.4	2473.6	2455.4	2426.4	2393.7	2364.7
27.5°	2422.7	2419.1	2408.2	2400.9	2386.4	2375.6	2357.4	2335.7	2306.7	2281.3	2245.1
30°	2288.6	2288.6	2281.3	2270.4	2252.3	2245.1	2230.6	2205.1	2176.1	2143.5	2118.1
32.5°	2136.3	2136.3	2125.3	2118.1	2107.3	2089.1	2085.5	2056.5	2031.0	2005.7	1976.7
35°	1969.5	1973.0	1965.8	1951.3	1933.1	1933.1	1925.8	1900.5	1871.5	1846.0	1824.3
37.5°	1802.5	1791.7	1788.0	1780.8	1769.9	1755.4	1748.2	1737.2	1711.9	1693.7	1661.2
40°	1617.6	1621.2	1613.9	1606.7	1603.1	1592.2	1588.6	1570.4	1552.4	1530.6	1516.1
42.5°	1450.7	1450.7	1450.7	1443.4	1436.2	1425.4	1421.7	1410.9	1389.1	1374.6	1352.8
45°	1302.1	1291.1	1291.1	1287.6	1283.9	1276.6	1265.8	1258.6	1244.1	1233.1	1207.8
47.5°	1157.0	1160.6	1157.0	1153.3	1142.5	1138.8	1135.3	1120.8	1106.2	1095.3	1077.2
50°	1030.0	1037.3	1030.0	1030.0	1022.8	1019.2	1012.0	1001.0	990.2	972.0	953.8
52.5°	924.8	924.8	921.2	917.6	906.7	899.5	895.8	892.2	874.0	859.5	845.0
55°	819.7	823.3	823.3	812.4	808.8	801.5	797.9	787.0	779.7	758.0	747.2
57.5°	729.0	725.4	729.0	721.7	714.5	707.2	703.7	696.4	685.5	671.0	656.4
60°	649.2	641.9	641.9	638.4	631.1	627.4	620.2	609.4	598.4	583.9	573.1
62.5°	569.4	565.8	562.2	558.6	551.3	547.7	544.1	533.1	522.3	511.4	500.6
65°	493.3	493.3	489.6	482.4	478.7	475.1	471.4	464.2	449.7	442.4	431.6
67.5°	424.4	420.7	420.7	413.4	406.2	402.6	402.6	395.3	384.4	373.6	366.3
70°	355.4	359.1	355.4	351.8	344.6	344.6	337.3	333.6	319.1	315.6	304.6
72.5°	293.8	293.8	290.1	290.1	282.9	279.3	279.3	272.0	264.8	257.5	250.3
75°	235.8	235.8	235.8	232.1	228.5	221.3	221.3	217.6	210.3	203.1	195.8
77.5°	185.0	181.3	181.3	177.8	174.1	170.5	170.5	166.8	159.6	156.0	148.7
80°	134.2	130.6	130.6	130.6	123.3	127.0	123.3	119.7	116.0	112.5	108.8
82.5°	87.0	90.7	90.7	87.0	83.5	83.5	83.5	79.8	79.8	76.2	72.5
85°	50.8	50.8	50.8	50.8	47.2	47.2	47.2	43.5	43.5	43.5	40.0
87.5°	21.8	21.8	21.8	21.8	21.8	21.8	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585270

CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0
2.5°	2702.0	2694.7	2691.2	2687.5	2687.5	2683.9	2680.2	2673.0	2673.0	2665.7	2662.2
5°	2716.5	2705.7	2698.4	2691.2	2687.5	2680.2	2673.0	2662.2	2658.5	2647.7	2636.7
7.5°	2720.2	2702.0	2694.7	2680.2	2673.0	2665.7	2651.2	2640.4	2625.9	2615.0	2600.5
10°	2705.7	2691.2	2673.0	2654.9	2651.2	2640.4	2618.7	2604.1	2586.0	2571.5	2549.7
12.5°	2683.9	2662.2	2644.0	2622.2	2611.4	2600.5	2578.7	2556.9	2531.6	2506.2	2484.4
15°	2647.7	2622.2	2596.9	2571.5	2556.9	2546.1	2520.7	2495.4	2469.9	2437.2	2415.5
17.5°	2593.2	2564.2	2538.9	2506.2	2491.7	2480.8	2448.2	2419.1	2386.4	2353.9	2332.1
20°	2524.4	2488.1	2459.0	2422.7	2411.9	2393.7	2361.1	2328.4	2292.2	2255.9	2230.6
22.5°	2433.6	2397.4	2364.7	2328.4	2310.3	2292.2	2259.6	2219.6	2183.4	2154.3	2129.0
25°	2328.4	2295.8	2255.9	2223.3	2201.6	2179.8	2143.5	2110.8	2078.3	2034.7	2009.3
27.5°	2212.4	2172.5	2143.5	2100.0	2078.3	2063.7	2023.8	1980.3	1951.3	1911.3	1882.3
30°	2081.8	2045.6	2013.0	1969.5	1947.6	1933.1	1896.8	1857.0	1828.0	1788.0	1759.0
32.5°	1944.0	1904.1	1864.2	1835.2	1809.8	1795.3	1755.4	1730.0	1693.7	1661.2	1628.5
35°	1795.3	1755.4	1726.4	1686.5	1672.0	1657.5	1624.9	1592.2	1559.6	1530.6	1505.2
37.5°	1635.7	1606.7	1574.1	1545.1	1534.2	1519.7	1479.8	1450.7	1425.4	1396.4	1374.6
40°	1479.8	1454.4	1432.6	1403.6	1385.4	1374.6	1345.6	1320.1	1291.1	1273.1	1251.3
42.5°	1338.3	1309.3	1287.6	1265.8	1247.6	1236.8	1211.4	1193.3	1171.5	1153.3	1128.0
45°	1189.6	1175.1	1149.8	1131.6	1120.8	1106.2	1088.1	1066.3	1048.2	1033.7	1015.5
47.5°	1059.0	1044.5	1026.5	1004.7	997.5	986.5	968.3	953.8	939.3	924.8	906.7
50°	939.3	921.2	906.7	892.2	885.0	874.0	856.0	848.7	837.8	823.3	812.4
52.5°	830.5	816.0	801.5	783.4	779.7	772.5	761.7	747.2	736.2	729.0	721.7
55°	732.7	718.2	707.2	692.7	689.1	681.9	667.4	660.1	652.9	645.6	638.4
57.5°	645.6	631.1	616.6	609.4	602.1	594.9	591.2	580.4	573.1	569.4	562.2
60°	565.8	551.3	540.4	529.6	525.9	522.3	515.1	507.8	500.6	493.3	489.6
62.5°	489.6	475.1	467.9	460.6	453.4	453.4	446.1	438.9	431.6	427.9	420.7
65°	420.7	413.4	402.6	391.7	388.1	388.1	377.2	373.6	369.9	362.6	355.4
67.5°	355.4	348.1	337.3	333.6	330.1	326.4	322.8	315.6	308.3	304.6	297.4
70°	297.4	290.1	282.9	279.3	275.6	272.0	264.8	261.1	253.9	250.3	246.6
72.5°	239.3	235.8	228.5	224.8	221.3	217.6	214.0	210.3	203.1	199.5	195.8
75°	192.3	188.6	181.3	177.8	174.1	174.1	170.5	163.2	159.6	159.6	156.0
77.5°	145.1	141.5	137.8	134.2	130.6	130.6	127.0	123.3	119.7	119.7	116.0
80°	105.2	101.5	98.0	98.0	98.0	94.3	90.7	90.7	87.0	87.0	83.5
82.5°	69.0	69.0	65.3	65.3	65.3	61.7	61.7	58.0	58.0	58.0	58.0
85°	40.0	40.0	40.0	36.3	36.3	36.3	36.3	36.3	36.3	32.7	36.3
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P585270

CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0
2.5°	2658.5	2654.9	2647.7	2647.7	2640.4	2640.4	2636.7	2633.2	2629.5	2625.9	2622.2
5°	2633.2	2618.7	2611.4	2607.7	2600.5	2596.9	2586.0	2578.7	2575.1	2567.9	2560.6
7.5°	2586.0	2571.5	2556.9	2553.4	2549.7	2535.2	2524.4	2513.4	2506.2	2498.9	2491.7
10°	2531.6	2517.1	2498.9	2491.7	2484.4	2466.3	2451.7	2440.9	2426.4	2411.9	2408.2
12.5°	2466.3	2444.5	2422.7	2415.5	2404.6	2386.4	2371.9	2353.9	2342.9	2324.9	2321.2
15°	2390.1	2364.7	2346.6	2328.4	2321.2	2303.1	2277.6	2263.1	2241.4	2234.1	2216.1
17.5°	2299.4	2274.1	2248.6	2241.4	2230.6	2205.1	2179.8	2161.6	2139.8	2129.0	2118.1
20°	2205.1	2172.5	2147.1	2139.8	2125.3	2103.6	2078.3	2060.1	2042.0	2020.2	2009.3
22.5°	2096.3	2060.1	2038.3	2020.2	2016.5	1991.2	1962.1	1947.6	1933.1	1915.0	1900.5
25°	1976.7	1944.0	1918.6	1904.1	1896.8	1875.1	1853.3	1835.2	1813.5	1802.5	1784.5
27.5°	1853.3	1831.5	1799.0	1784.5	1773.5	1755.4	1730.0	1719.2	1697.4	1682.9	1672.0
30°	1733.7	1701.0	1682.9	1664.7	1653.9	1635.7	1613.9	1603.1	1584.9	1570.4	1559.6
32.5°	1603.1	1581.4	1555.9	1548.7	1534.2	1516.1	1501.6	1483.4	1468.9	1454.4	1450.7
35°	1483.4	1454.4	1428.9	1421.7	1410.9	1392.7	1385.4	1374.6	1356.4	1352.8	1338.3
37.5°	1352.8	1338.3	1309.3	1298.4	1294.8	1280.3	1265.8	1258.6	1247.6	1236.8	1233.1
40°	1229.5	1211.4	1196.8	1186.0	1178.8	1167.8	1153.3	1149.8	1142.5	1128.0	1124.3
42.5°	1113.5	1095.3	1080.8	1077.2	1066.3	1055.5	1048.2	1037.3	1033.7	1030.0	1022.8
45°	1001.0	990.2	975.6	972.0	968.3	953.8	946.6	939.3	932.1	928.5	921.2
47.5°	899.5	888.5	877.7	874.0	866.8	863.2	852.3	848.7	837.8	834.2	830.5
50°	801.5	794.3	787.0	783.4	776.2	772.5	765.2	758.0	750.7	747.2	743.5
52.5°	714.5	707.2	700.0	696.4	692.7	685.5	678.2	671.0	667.4	663.7	660.1
55°	631.1	623.9	620.2	616.6	612.9	609.4	598.4	594.9	591.2	587.6	580.4
57.5°	554.9	547.7	540.4	540.4	536.8	533.1	525.9	518.6	518.6	511.4	504.1
60°	485.9	478.7	471.4	467.9	464.2	456.9	453.4	449.7	446.1	442.4	435.2
62.5°	413.4	409.8	402.6	402.6	395.3	391.7	388.1	384.4	380.8	373.6	369.9
65°	351.8	348.1	340.9	337.3	337.3	333.6	326.4	322.8	319.1	319.1	315.6
67.5°	293.8	290.1	282.9	279.3	279.3	275.6	272.0	272.0	268.4	264.8	268.4
70°	243.0	235.8	235.8	232.1	232.1	228.5	224.8	224.8	224.8	228.5	228.5
72.5°	192.3	188.6	185.0	185.0	185.0	185.0	181.3	181.3	185.0	188.6	188.6
75°	152.3	148.7	148.7	148.7	145.1	145.1	148.7	148.7	152.3	152.3	152.3
77.5°	112.5	112.5	112.5	112.5	112.5	112.5	116.0	116.0	119.7	119.7	119.7
80°	83.5	83.5	83.5	83.5	83.5	87.0	87.0	87.0	87.0	87.0	90.7
82.5°	58.0	58.0	58.0	58.0	58.0	58.0	58.0	61.7	61.7	61.7	61.7
85°	32.7	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
87.5°	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P585270

CATALOG NUMBER: HCC8W80D010BZ-HM86080927-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0	2673.0
2.5°	2618.7	2618.7	2618.7	2622.2	2615.0	2615.0	2615.0	2615.0
5°	2556.9	2553.4	2549.7	2553.4	2546.1	2546.1	2542.4	2542.4
7.5°	2480.8	2477.2	2473.6	2473.6	2466.3	2466.3	2462.7	2459.0
10°	2397.4	2390.1	2393.7	2386.4	2382.9	2379.2	2375.6	2371.9
12.5°	2306.7	2299.4	2295.8	2288.6	2281.3	2277.6	2281.3	2274.1
15°	2208.8	2197.9	2194.3	2187.0	2179.8	2176.1	2176.1	2172.5
17.5°	2100.0	2092.8	2089.1	2081.8	2078.3	2071.0	2067.3	2063.7
20°	1998.5	1980.3	1984.0	1976.7	1973.0	1958.5	1958.5	1962.1
22.5°	1886.0	1875.1	1867.8	1860.5	1857.0	1849.7	1849.7	1846.0
25°	1773.5	1762.7	1759.0	1751.8	1748.2	1740.9	1737.2	1737.2
27.5°	1664.7	1650.2	1650.2	1643.0	1635.7	1632.1	1628.5	1624.9
30°	1548.7	1537.9	1534.2	1534.2	1530.6	1530.6	1519.7	1523.3
32.5°	1439.9	1432.6	1428.9	1421.7	1421.7	1418.1	1418.1	1407.2
35°	1331.1	1320.1	1323.8	1316.6	1312.9	1309.3	1312.9	1309.3
37.5°	1225.9	1218.6	1218.6	1211.4	1211.4	1207.8	1204.1	1211.4
40°	1120.8	1117.1	1113.5	1109.8	1113.5	1109.8	1102.6	1106.2
42.5°	1015.5	1015.5	1012.0	1012.0	1008.3	1008.3	1008.3	1008.3
45°	921.2	917.6	917.6	914.0	914.0	914.0	914.0	910.3
47.5°	826.9	823.3	823.3	823.3	819.7	819.7	816.0	819.7
50°	736.2	736.2	732.7	732.7	736.2	732.7	729.0	729.0
52.5°	652.9	652.9	649.2	649.2	645.6	641.9	645.6	645.6
55°	576.7	573.1	569.4	569.4	565.8	562.2	562.2	565.8
57.5°	504.1	500.6	496.9	496.9	489.6	485.9	485.9	485.9
60°	435.2	427.9	427.9	424.4	424.4	420.7	420.7	420.7
62.5°	369.9	366.3	366.3	366.3	366.3	362.6	362.6	362.6
65°	315.6	315.6	315.6	319.1	319.1	322.8	322.8	322.8
67.5°	272.0	275.6	275.6	275.6	279.3	279.3	279.3	275.6
70°	232.1	232.1	232.1	235.8	235.8	235.8	235.8	235.8
72.5°	192.3	192.3	192.3	192.3	192.3	192.3	192.3	192.3
75°	152.3	156.0	156.0	156.0	152.3	156.0	156.0	152.3
77.5°	119.7	119.7	119.7	119.7	119.7	119.7	119.7	119.7
80°	90.7	90.7	90.7	90.7	90.7	90.7	90.7	90.7
82.5°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7
85°	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3
87.5°	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)