

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585261

Luminaire Tested: **HCC8S80D010BZ-HM86080927-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585261  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010BZ-HM86080927-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5393.9 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585261  
CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585261  
 CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64																			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49																			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42																			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126611
5°	124962
10°	120388
15°	115677
20°	112478
25°	109095
30°	97894
35°	64176
40°	35480
45°	29580
50°	26970
55°	25741
60°	23935
65°	21700
70°	19619
75°	17716
80°	16106
85°	15391



TEST NUMBER: P585261  
 CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	379.3	7.0
10°-20°	1022.3	19.0
20°-30°	1454.9	27.0
30°-40°	1076.8	20.0
40°-50°	533.3	9.9
50°-60°	425.7	7.9
60°-70°	295.5	5.5
70°-80°	159.2	3.0
80°-90°	46.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2856.5	53.0
0°-40°	3933.3	72.9
0°-60°	4892.3	90.7
0°-90°	5393.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5393.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4106	
5°	4037	379
15°	3624	1022
25°	3206	1455
35°	1705	1077
45°	678	533
55°	479	426
65°	297	295
75°	149	159
85°	44	47
90°	0	



TEST NUMBER: P585261

CATALOG NUMBER: HCC8S80D010BZ-HM86080927-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4105.9
2.5°	4087.8
5°	4037.0
7.5°	3957.1
10°	3844.8
12.5°	3728.7
15°	3623.5
17.5°	3521.9
20°	3427.6
22.5°	3333.4
25°	3206.4
27.5°	3021.4
30°	2749.3
32.5°	2332.2
35°	1704.8
37.5°	1164.3
40°	881.4
42.5°	754.4
45°	678.3
47.5°	616.6
50°	562.2
52.5°	515.1
55°	478.8
57.5°	435.3
60°	388.1
62.5°	341.0
65°	297.4
67.5°	253.9
70°	217.6
72.5°	181.3
75°	148.7
77.5°	119.7
80°	90.7
82.5°	65.3
85°	43.5
87.5°	18.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)